




RECOMMENDED PC BOARD LAYOUT

- 1
- 3.81um [.000150] MIN TIN-LEAD OVER 0.76um [.000030] MIN NICKEL.
- 2
- 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 5.23 [.206] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.
- 3
- 3.81um [.000150] MIN TIN OVER 0.76um [.000030] MIN NICKEL.
- 4
- 0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] MIN FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 5.23 [.206] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

4	207614-7
3	207614-6
2	207614-3
1	207614-1
CONTACT FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.SIPE	08/07/92	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK J.McCLINTON	8-11-92			NAME	
		APVD -	-	PRODUCT SPEC		SIZE	
		APPLICATION SPEC		108-10033		CAGE CODE	
MATERIAL HOUSING: NYLON, RED CONTACTS: PH BRZ.		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DRAWING NO		RESTRICTED TO	
		0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH CONTACTS: SEE TABLE		WEIGHT -		A2 00779	
		CUSTOMER DRAWING		SCALE 2:1		SHEET 1 OF 1	