

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .04$	W $\pm .010$	C $\pm .015$	M $\pm .04$	H $\pm .010$
PN10-8FF	#8	1.05 (26.67)	.37 (9.40)	.28 (7.11)	.80 (20.32)	.17 (4.32)
PN10-10FF	#10	1.05 (26.67)	.37 (9.40)	.28 (7.11)	.80 (20.32)	.20 (5.08)

NOTES:

1. U.L. LISTED AND CSA CERTIFIED FOR:

- 600V MAX BUILDING WIRE
(1000V MAX IN SIGNS, FIXTURES, AND LUMINAIRES)
- #14-10 AWG SOLID OR STRANDED COPPER WIRE WITH
THE CT-550 INSTALLATION TOOL
- #12-10 AWG STRANDED AND #12 AWG SOLID COPPER WIRE
WITH THE CT-1550 AND CT-1551 INSTALLATION TOOLS
- #12-10 AWG SOLID OR STRANDED COPPER WIRE
WITH THE CT-100 INSTALLATION TOOL
- 221°F (105°C) MAX TEMP RATING

2. MATERIAL:


- STAMPING: .04" (1.02) THK COPPER, TIN PLATED
- HOUSING: NYLON, YELLOW
- SLEEVE: BRASS, TIN PLATED

3. STRIP LENGTH: 9/32 $\frac{+1/32}{-0}$

4. PACKAGE QUANTITY:

-L=50
-D=500

5. DIMENSIONS IN BRACKETS ARE IN INCHES



LISTED
587H
E52164



CERTIFIED
LR31212

A41241_07

07	1/01	KMD		CAD FILE SPEC. WAS N41241AA_PCD_06				PANDUIT CORP. TINLEY PARK, ILLINOIS
06	5/99	ED		UPDATED "A" & "M" DIM.S. AND MODIFIED DIMENSIONAL TOLERANCES	07661			
		-	-	FILESPEC WAS: A41241_05	-			#12-10 BARREL NYLON INSUL. FLANGED FORK, .225 (5.72) MAX. WIRE INSUL. DIA.
05	5/97	TM		UPDATED ALL NOTES AND "A" DIMS FILESPEC WAS A41241A	05826	LA	DBH	
REV	DATE	BY	CHK	DESCRIPTION	ECN#	CUST	PM	DRAWN BY DAW Ck'd SCALE NONE DRAWING NO. A41241

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PN10-10FF-L](#)