

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AA

27

P

LTR

DESCRIPTION

DATE

DWN

APVD


B

REDWN & REV; 0G1Z-0042-99


12MAY00

LMH

LHS



1. LOCKING LANCE FOR P/N -2 AND -7 ONLY.



.250	.750	.469	.609	.438	Ø.266	.141	.86	.938	2.125	606716-7
.250	.750	.469	.609	.438	Ø.266	.141	.86	.938	2.125	606716-6
.375	.750	.469	.609	.438	Ø.391	.141	.86	.938	2.125	606716-5
.500	.750	.469	.609	.500	Ø.516	.141	.86	.938	2.125	606716-4
.438	.750	.469	.609	.438	Ø.453	.141	.86	.938	2.125	606716-3
.375	.750	.469	.609	.438	Ø.391	.141	.86	.938	2.125	606716-2
.312	.750	.469	.609	.438	Ø.328	.141	.86	.938	2.125	606716-1
BOLT HOLE SIZE	L	H	G	F	E	D	C	B	A	PART NUMBER
DIMENSIONS, INCHES										

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

L.HALL

18APR00

CHK

L.H. SMITH

12MAY00

APVD

B. ANTHONY

12MAY00

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

AMP

AMP Incorporated

Harrisburg PA 17105-3608

NAME

AMP TUBULAR TERMINAL 1/0
(ROUND TONGUE)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=606716

SCALE NTS

SHEET

1 OF 1

REV

B

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ±
1 PLC ±
2 PLC ± .02
3 PLC ± .005
4 PLC ± .0005
ANGLES ± 3°MATERIAL
HIGH CONDUCTIVITY
WROUGHT COPPER

FINISH

ELECTRO TIN PLATE