



Application Range

Earthing gland, for applications where electrical interference fields can occur. Medical engineering, frequency convertors, measurement and control technologies.

Technical Data

Material:	Body:	Nickel Plated Brass
	Earthing Sleeve:	Plain Brass
	Seal:	CR/NBR
	O Ring:	NBR

Protection Rating: IP68

Temperature Range: -20°C to +80°C

Article List

Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
1829177	Cable gland, metal, EMC	PG16	8.5 – 10.8	24	37.5	6
1829155	Cable gland, metal, EMC	PG16	10.8 – 12.8	24	37.5	6
1829183	Cable gland, metal, EMC	PG16	12 – 14.8	24	37.5	6
1829199	Cable gland, metal, EMC	PG21	14 – 15.8	30	43.5	7
1829206	Cable gland, metal, EMC	PG21	15.8 – 17.8	30	43.5	7
1829212	Cable gland, metal, EMC	PG29	19.5 – 21.8	40	47.5	8

Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
2127725	Cable gland, metal, EMC	20mm	8.5 – 10.8	22	37.5	13
2127731	Cable gland, metal, EMC	20mm	10.8 – 12.8	24	37.5	13
2127747	Cable gland, metal, EMC	20mm	10.8 – 12.8	24	37.5	13
2127753	Cable gland, metal, EMC	25mm	14 – 15.8	30	43.5	13
2127769	Cable gland, metal, EMC	32mm	19.5 – 21.8	40	43.5	13