


- Low  $r_{DS(on)}$  . . . . . 0.4  $\Omega$  Typ
- High-Voltage Outputs . . . . . 60 V
- Pulsed Current . . . . . 5 A Per Channel
- Fast Commutation Speed


### description



The TPIC3302 is a monolithic power DMOS array that consists of three electrically isolated N-channel enhancement-mode DMOS transistors configured with a common drain and open sources. The TPIC3302 is offered in a standard eight-pin small-outline surface-mount (D) package.

The TPIC3302 is characterized for operation over the case temperature range of  $-40^{\circ}\text{C}$  to  $125^{\circ}\text{C}$ .

### schematic



### absolute maximum ratings over operating case temperature range (unless otherwise noted)<sup>†</sup>

Drain-to-source voltage, $V_{DS}$ . . . . .	60 V
Source-to-GND voltage . . . . .	100 V
Drain-to-GND voltage . . . . .	100 V
Gate-to-source voltage, $V_{GS}$ . . . . .	$\pm 20$ V
Continuous drain current, each output, all outputs on, $T_C = 25^{\circ}\text{C}$ . . . . .	1 A
Continuous source-to-drain diode current . . . . .	1 A
Pulsed drain current, each output, $T_C = 25^{\circ}\text{C}$ (see Note 1 and Figure 6) . . . . .	5 A
Single-pulse avalanche energy, $T_C = 25^{\circ}\text{C}$ , $E_{AS}$ (see Figure 4) . . . . .	9 mJ
Continuous total power dissipation at (or below) $T_C = 25^{\circ}\text{C}$ . . . . .	0.95 W
Operating virtual junction temperature range, $T_J$ . . . . .	$-40^{\circ}\text{C}$ to $150^{\circ}\text{C}$
Operating case temperature range, $T_C$ . . . . .	$-40^{\circ}\text{C}$ to $125^{\circ}\text{C}$
Storage temperature range, $T_{STG}$ . . . . .	$-65^{\circ}\text{C}$ to $150^{\circ}\text{C}$
Lead temperature 1.6 mm (1/16 inch) from case for 10 seconds . . . . .	260°C

<sup>†</sup> Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

NOTE 1: Pulse duration = 10 ms, duty cycle = 2%

# TPIC3302

## 3-CHANNEL COMMON-DRAIN POWER DMOS ARRAY

SLIS021B – APRIL 1994 – REVISED JULY 1995

### electrical characteristics, $T_C = 25^\circ\text{C}$ (unless otherwise noted)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$V_{(\text{BR})\text{DSX}}$	Drain-to-source breakdown voltage $I_D = 250 \mu\text{A}, V_{GS} = 0$	60			V
$V_{GS(\text{th})}$	Gate-to-source threshold voltage $I_D = 1 \text{ mA}, V_{DS} = V_{GS}$	1.5	1.85	2.2	V
$V_{(\text{BR})}$	Reverse drain-to-GND breakdown voltage (across D1) Drain-to-GND current = 250 $\mu\text{A}$	100			V
$V_{DS(\text{on})}$	Drain-to-source on-state voltage $I_D = 1 \text{ A}, V_{GS} = 10 \text{ V},$ See Notes 2 and 3		0.4	0.475	V
$V_F$	Forward on-state voltage, GND-to-drain $I_D = 1 \text{ A},$ See Notes 2 and 3		2		V
$V_F(\text{SD})$	Forward on-state voltage, source-to-drain $I_S = 1 \text{ A}, V_{GS} = 0,$ See Notes 2 and 3	0.9	1.1		V
$I_{DSS}$	$V_{DS} = 48 \text{ V},$ $V_{GS} = 0$	$T_C = 25^\circ\text{C}$	0.05	1	$\mu\text{A}$
		$T_C = 125^\circ\text{C}$	0.5	10	
$I_{GSSF}$	Forward gate current, drain short circuited to source $V_{GS} = 16 \text{ V}, V_{DS} = 0$	10	100		nA
$I_{GSSR}$	Reverse gate current, drain short circuited to source $V_{SG} = 16 \text{ V}, V_{DS} = 0$	10	100		nA
$I_{lk\text{g}}$	Leakage current, drain-to-GND $V_R = 48 \text{ V}$	$T_C = 25^\circ\text{C}$	0.05	1	$\mu\text{A}$
		$T_C = 125^\circ\text{C}$	0.5	10	
$r_{DS(\text{on})}$	Static drain-to-source on-state resistance $I_D = 1 \text{ A},$ See Notes 2 and 3 and Figures 6 and 7	$V_{GS} = 10 \text{ V},$ $T_C = 25^\circ\text{C}$	0.4	0.475	$\Omega$
		$T_C = 125^\circ\text{C}$	0.63	0.7	
$g_{fs}$	Forward transconductance $V_{DS} = 10 \text{ V}, I_D = 0.5 \text{ A},$ See Notes 2 and 3	0.85	1.02		S
$C_{iss}$	Short-circuit input capacitance, common source		115	145	$\text{pF}$
$C_{oss}$	Short-circuit output capacitance, common source		60	75	
$C_{rss}$	Short-circuit reverse-transfer capacitance, common source		30	40	

NOTES: 2. Technique should limit  $T_J - T_C$  to 10°C maximum, pulse duration  $\leq 5 \text{ ms}$ .  
3. These parameters are measured with voltage-sensing contacts separate from the current-carrying contacts.

### source-to-drain diode characteristics, $T_C = 25^\circ\text{C}$

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_{rr(\text{SD})}$	$I_S = 0.5 \text{ A}, V_{GS} = 0, V_{DS} = 48 \text{ V},$ $di/dt = 100 \text{ A}/\mu\text{s},$ See Figure 1	35			ns
$Q_{RR}$	Total diode charge	0.03			$\mu\text{C}$

### GND-to-drain diode characteristics, $T_C = 25^\circ\text{C}$ (see schematic, D1)

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_{rr}$	Reverse-recovery time $I_F = 0.5 \text{ A}, V_{DS} = 48 \text{ V},$ $di/dt = 100 \text{ A}/\mu\text{s},$ See Figure 1	90			ns
$Q_{RR}$	Total diode charge	0.2			$\mu\text{C}$

**resistive-load switching characteristics,  $T_C = 25^\circ\text{C}$**


PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$t_{d(on)}$	Turn-on delay time  $V_{DD} = 25 \text{ V}, R_L = 50 \Omega, t_{en} = 10 \text{ ns},$ $t_{dis} = 10 \text{ ns}, \text{ See Figure 2}$	21	42		ns
$t_{d(off)}$		20	40		
$t_r$		5	10		
$t_f$		13	26		
$Q_g$	$V_{DS} = 48 \text{ V}, I_D = 0.5 \text{ A}, V_{GS} = 10 \text{ V},$  $\text{See Figure 3}$	3.1	3.8		nC
$Q_{gs(\text{th})}$		0.4	0.5		
$Q_{gd}$		1.3	1.6		
$L_D$	Internal drain inductance	5			nH
$L_S$	Internal source inductance	5			
$R_g$	Internal gate resistance	0.25			$\Omega$

**thermal resistance**

PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	UNIT
$R_{\theta JA}$	Junction-to-ambient thermal resistance  All outputs with equal power, See Note 4	130			$^\circ\text{C}/\text{W}$
$R_{\theta JP}$		44			

NOTE 4: Package mounted on an FR4 printed-circuit board with no heat sink

**PARAMETER MEASUREMENT INFORMATION**



<sup>†</sup>  $I_{RM}$  = maximum recovery current

**Figure 1. Reverse-Recovery-Current Waveform of Source-to-Drain Diode**

# TPIC3302

## 3-CHANNEL COMMON-DRAIN POWER DMOS ARRAY

SLIS021B – APRIL 1994 – REVISED JULY 1995

### PARAMETER MEASUREMENT INFORMATION




Figure 2. Resistive-Switching Test Circuit and Voltage Waveforms





Figure 3. Gate-Charge Test Circuit and Voltage Waveform

### PARAMETER MEASUREMENT INFORMATION



TEST CIRCUIT

NOTES: A. The pulse generator has the following characteristics:  $t_r \leq 10$  ns,  $t_f \leq 10$  ns,  $Z_O = 50$  Ω.  
 B. Input pulse duration ( $t_W$ ) is increased until peak current  $I_{AS} = 5$  A.

$$\text{Energy test level is defined as } E_{AS} = \frac{I_{AS} \times V_{(BR)DSX} \times t_{av}}{2} = 9 \text{ mJ.}$$

Figure 4. Single-Pulse Avalanche-Energy Test Circuit and Waveforms

### TYPICAL CHARACTERISTICS

GATE-TO-SOURCE THRESHOLD VOLTAGE  
vs  
JUNCTION TEMPERATURE




Figure 5

STATIC DRAIN-TO-SOURCE ON-STATE RESISTANCE  
vs  
JUNCTION TEMPERATURE




Figure 6

# TPIC3302

## 3-CHANNEL COMMON-DRAIN POWER DMOS ARRAY

SLIS021B – APRIL 1994 – REVISED JULY 1995

### TYPICAL CHARACTERISTICS




Figure 7




Figure 8




Figure 9




Figure 10

**TYPICAL CHARACTERISTICS**




Figure 11




Figure 12




Figure 13





Figure 14

# TPIC3302

## 3-CHANNEL COMMON-DRAIN POWER DMOS ARRAY

SLIS021B – APRIL 1994 – REVISED JULY 1995

### THERMAL INFORMATION



† Less than 0.1 duty cycle

Figure 15





Figure 16

**THERMAL INFORMATION**

D PACKAGE<sup>†</sup>  
NORMALIZED JUNCTION-TO-AMBIENT THERMAL RESISTANCE  
VS  
PULSE DURATION



<sup>†</sup> Device mounted on FR4 printed-circuit board with no heat sink

NOTES:  $Z_{\theta JA}(t) = r(t) R_{\theta JA}$

$t_W$  = pulse duration

$t_C$  = cycle time

$d$  = duty cycle =  $t_W/t_C$

**Figure 17**

**PACKAGING INFORMATION**

Orderable Device	Status <sup>(1)</sup>	Package Type	Package Drawing	Pins	Package Qty	Eco Plan <sup>(2)</sup>	Lead/Ball Finish	MSL Peak Temp <sup>(3)</sup>
TPIC3302D	OBsolete	SOIC	D	8		TBD	Call TI	Call TI

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBsolete:** TI has discontinued the production of the device.

<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS) or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)


<sup>(3)</sup> MSL, Peak Temp. -- The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.

In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

D (R-PDSO-G8)

PLASTIC SMALL OUTLINE



NOTES: A. All linear dimensions are in inches (millimeters).

B. This drawing is subject to change without notice.

△C Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0.006 (0.15) each side.

△D Body width does not include interlead flash. Interlead flash shall not exceed 0.017 (0.43) each side.

E. Reference JEDEC MS-012 variation AA.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, modifications, enhancements, improvements, and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All products are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with TI's standard warranty. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

TI assumes no liability for applications assistance or customer product design. Customers are responsible for their products and applications using TI components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any TI patent right, copyright, mask work right, or other TI intellectual property right relating to any combination, machine, or process in which TI products or services are used. Information published by TI regarding third-party products or services does not constitute a license from TI to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI products or services with statements different from or beyond the parameters stated by TI for that product or service voids all express and any implied warranties for the associated TI product or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

TI products are not authorized for use in safety-critical applications (such as life support) where a failure of the TI product would reasonably be expected to cause severe personal injury or death, unless officers of the parties have executed an agreement specifically governing such use. Buyers represent that they have all necessary expertise in the safety and regulatory ramifications of their applications, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of TI products in such safety-critical applications, notwithstanding any applications-related information or support that may be provided by TI. Further, Buyers must fully indemnify TI and its representatives against any damages arising out of the use of TI products in such safety-critical applications.

TI products are neither designed nor intended for use in military/aerospace applications or environments unless the TI products are specifically designated by TI as military-grade or "enhanced plastic." Only products designated by TI as military-grade meet military specifications. Buyers acknowledge and agree that any such use of TI products which TI has not designated as military-grade is solely at the Buyer's risk, and that they are solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI products are neither designed nor intended for use in automotive applications or environments unless the specific TI products are designated by TI as compliant with ISO/TS 16949 requirements. Buyers acknowledge and agree that, if they use any non-designated products in automotive applications, TI will not be responsible for any failure to meet such requirements.

Following are URLs where you can obtain information on other Texas Instruments products and application solutions:

### Products

Audio	<a href="http://www.ti.com/audio">www.ti.com/audio</a>
Amplifiers	<a href="http://amplifier.ti.com">amplifier.ti.com</a>
Data Converters	<a href="http://dataconverter.ti.com">dataconverter.ti.com</a>
DLP® Products	<a href="http://www.dlp.com">www.dlp.com</a>
DSP	<a href="http://dsp.ti.com">dsp.ti.com</a>
Clocks and Timers	<a href="http://www.ti.com/clocks">www.ti.com/clocks</a>
Interface	<a href="http://interface.ti.com">interface.ti.com</a>
Logic	<a href="http://logic.ti.com">logic.ti.com</a>
Power Mgmt	<a href="http://power.ti.com">power.ti.com</a>
Microcontrollers	<a href="http://microcontroller.ti.com">microcontroller.ti.com</a>
RFID	<a href="http://www.ti-rfid.com">www.ti-rfid.com</a>
RF/IF and ZigBee® Solutions	<a href="http://www.ti.com/lprf">www.ti.com/lprf</a>

### Applications

Communications and Telecom	<a href="http://www.ti.com/communications">www.ti.com/communications</a>
Computers and Peripherals	<a href="http://www.ti.com/computers">www.ti.com/computers</a>
Consumer Electronics	<a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>
Energy and Lighting	<a href="http://www.ti.com/energy">www.ti.com/energy</a>
Industrial	<a href="http://www.ti.com/industrial">www.ti.com/industrial</a>
Medical	<a href="http://www.ti.com/medical">www.ti.com/medical</a>
Security	<a href="http://www.ti.com/security">www.ti.com/security</a>
Space, Avionics and Defense	<a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a>
Transportation and Automotive	<a href="http://www.ti.com/automotive">www.ti.com/automotive</a>
Video and Imaging	<a href="http://www.ti.com/video">www.ti.com/video</a>
Wireless	<a href="http://www.ti.com/wireless-apps">www.ti.com/wireless-apps</a>

[TI E2E Community Home Page](#)

[e2e.ti.com](#)

Mailing Address: Texas Instruments, Post Office Box 655303, Dallas, Texas 75265  
Copyright © 2011, Texas Instruments Incorporated