





	1	2	3	4	5	6	7																																																																														
A	  P.C.B LAYOUT  N=Number of contacts  Material Terminal body (metal housing): Brass(CuZn) Terminal screw: Steel Zinc plating "-" slot type Contacts: Brass Surface of solder tail: Tin plated Insulator (housing): Thermoplastic (UL94V-0),Green Electrical Voltage rating: 300VAC Current rating: 20A Solid wire(AWG): 12-30 Stranded wire(AWG): 12-30 Torque(Lb-In): 3.5 Screw: M3 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  US							A																																																																													
B								B																																																																													
C								C																																																																													
D								D																																																																													
E								E																																																																													
F								F																																																																													
G	RoHS compliant <table><tr><td>Scale</td><td>1:1</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td></td><td>Drawn</td><td>29.07.2009</td><td>Dean</td></tr><tr><td>X.</td><td>±0.50</td><td></td><td></td><td></td><td></td><td>Approved</td><td>29.07.2009</td><td>Helwig</td></tr><tr><td>X.X</td><td>±0.30</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td></td><td></td><td></td><td></td><td colspan="2" rowspan="4"></td><td>Drawing-No.</td></tr><tr><td>X.°</td><td>±1°</td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>X.X°</td><td>±X°</td><td>①</td><td>Drawn</td><td>29.07.2009</td><td>Dean</td><td>ASS 3595 CO</td><td>rev01</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td>Replace</td><td>Sheet</td></tr></table>							Scale	1:1					Date	Name	Customer-No.	TOLERANCE						Drawn	29.07.2009	Dean	X.	±0.50					Approved	29.07.2009	Helwig	X.X	±0.30								X.XX	±0.10								DIM	TOL							Drawing-No.	X.°	±1°						X.X°	±X°	①	Drawn	29.07.2009	Dean	ASS 3595 CO	rev01	Angle	TOL	Id.	Modification	Date	Name	Replace	Sheet	G
Scale	1:1					Date	Name	Customer-No.																																																																													
TOLERANCE						Drawn	29.07.2009	Dean																																																																													
X.	±0.50					Approved	29.07.2009	Helwig																																																																													
X.X	±0.30																																																																																				
X.XX	±0.10																																																																																				
DIM	TOL							Drawing-No.																																																																													
X.°	±1°																																																																																				
X.X°	±X°	①	Drawn	29.07.2009	Dean			ASS 3595 CO	rev01																																																																												
Angle	TOL	Id.	Modification	Date	Name			Replace	Sheet																																																																												
H								H																																																																													
	1	2	3	4	5	6	7	svxxxx																																																																													