








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	U	REVISED PER ECO-16-009792	2JUL2016	NK	MZ
	V	REVISED PER ECO-17-004657	06APR2017	BDA	MZ



- 1-66460-0 WILL BE SELECTIVELY LOADED INTO POSITIONS 2, 4, 6, 7, 9 AND 66464-3 WILL BE LOADED INTO POSITIONS 1, 3, 5, 8 OF THE HOUSING.
- LOAD ALL POSITIONS EXCEPT POSITION NUMBER 4.
- TIN PLATED CONTACTS.
- 194264-1 LOADED INTO POSITIONS 1 & 7.
- OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



4	OBSOLETE	—	.130	YES	YES	1-208223-3
	OBSOLETE	—	.245	NO	YES	1-208223-2
	3	—	.220	YES	YES	1-208223-1
	3	—	.220	NO	YES	1-208223-0
	3	—	.220	NO	NO	208223-9
	OBSOLETE	—	.220	YES	NO	208223-8
2	OBSOLETE	—	.220	NO	NO	208223-7
	OBSOLETE	—	.618	NO	YES	208223-6
5	OBSOLETE	—	.220	YES	YES	208223-5
1	OBSOLETE	—	.220	NO	NO	208223-4
		—	.220	NO	YES	208223-3
	OBSOLETE	—	.429	NO	NO	208223-2
		—	.220	NO	NO	208223-1
		B	A	PERIPHERAL SEAL	THREADED INSERTS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 6-22-91	TE Connectivity			
DIMENSIONS: INCHES		CHK W.G.LENKER 4-14-92				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	NAME			
0 PLC ± —		PRODUCT SPEC	RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 13-9, CPC			
1 PLC ± —		108-10024				
2 PLC ± —		APPLICATION SPEC				
3 PLC ± .005		—				
4 PLC ± —		—				
ANGLES ± —		—				
FINISH		—				
MATERIAL SEE CALLOUT		WEIGHT —				
		CUSTOMER DRAWING				
		SCALE 2:1				
		SHEET 1 of 1				
		REV V				

RECOMMENDED P.C. BOARD LAYOUT

RECOMMENDED P.C. BOARD LAYOUT
(1-208223-2 ONLY)