

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF
BUD INDUSTRIES INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT
THE WRITTEN PERMISSION OF BUD INDUSTRIES INC. IS PROHIBITED.

| | | | |
|----------|---------------------------------------|--|--|
| DWG. NO. | HH-3570 | | |
| ISSUE | REVISIONS | | |
| (A) | CHG'D MAT'L CALL- OUT 10-29-08 DAB | | |
| (B) | PER ECN #10509 7-9-09 DAB | | |
| (C) | ADD TORQUE SPEC. 8-11-11 DAB | | |

SCREW, M2.3 x 10mm THREAD FORMING,
ROUND HEAD, PHILLIPS RECESS, STEEL,
BLACK ANODIZED (4 PL'S, NOT SHOWN)
TIGHTEN SCREWS TO 1 IN./LBS. TORQUE MAX.


Ø .180 O.D. TYP.

.400 1.811

.293

Ø .095 I.D. TYP.

BATTERY DOOR
HOLDS (4) 'AA' BATTERIES
(CONTACT KIT IS INCLUDED)



6.574

.945

2.600

1.087

.918

.177 TALL PCB
MOUNTING BOSSSES

.536

.539

SECTION A-A

7.146

6.142

3.130

2.165

2.047

2.559

MATERIAL: ABS - UL94-HB (A)

FINISH: LIGHT TEXTURE
COLOR: BLACK (HH-3570-B) OR
LIGHT GRAY (HH-3570-G)

PACKAGING: SHRINK WRAP WITH A
SELF-ADHESIVE LABEL
AFFIXED ON THE OUTSIDE.

MAXIMUM PC BOARD SIZE: 3.50 x 2.312
(WITH MAX. 0.62 COMPONENT HEIGHT)

(B) .039 DEEP
SMOOTH RECESS

(B) .197 DIA BOSS WITH
.079 DIA HOLE (4)

| | | | |
|--|--|--|-----------------|
| TOLERANCES: +/- .005 BETWEEN HOLE CENTERS +/- .015 FROM SHEARED EDGE +/- .032 FROM A BENT SURFACE +/- .062 BETWEEN ASSEMBLED SURFACES UNLESS OTHERWISE SPECIFIED MATERIAL FINISH | | CAD GENERATED DRAWING, DO NOT MANUALLY UPDATE | |
| AS NOTED | | APPROVALS DRAWN DP | DATE 6/10/05 |
| AS NOTED | | CHECKED | |
| DO NOT SCALE DRAWING | | APPROVED | |

| QTY. | USED ON |
|------|---------|
| | |

| | | |
|---------------------|---------------------|--------------|
| BUD INDUSTRIES INC. | | |
| GRABBER STYLE J | | |
| SIZE B | DWG. NO. HH-3570 | REV. |
| SCALE | CAD FILE: | SHEET 1 OF 1 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bud Industries:

[HH-3570-B](#) [HH-3570-G](#) [HH-3444-C](#)