



DESCRIPTION: HIGH DENSITY - MALE - RIGHT ANGLE

44 PIN SHOWN



DIMENSIONS (IN.)							
No. OF PINS	A	B	C	D	E	F	G
15	1.213	0.984	0.666	0.090	0.329	0.496	0.639
	30.80	24.99	16.92	2.29	8.36	12.60	16.23
26	1.543	1.312	0.994	0.090	0.329	0.496	0.639
	39.19	33.32	25.25	2.29	8.36	12.60	16.23
44	2.087	1.852	1.534	0.090	0.329	0.496	0.639
	53.00	47.04	38.96	2.29	8.36	12.60	16.23
62	2.732	2.500	2.156	0.095	0.329	0.496	0.639
	69.30	63.50	54.76	2.41	8.36	12.60	16.23

181-YYY-1 1 3 R YY 1

SERIES _____
POSITIONS _____
015 _____
026 _____
044 _____
062 _____
GENDER _____
1 = MALE _____
TERMINATION _____
1 = DIP SOLDER _____
SHELL PLATING _____
3 = NICKEL PLATED _____
RoHS COMPLIANT _____
(HIGH TEMP. PROCESS) _____
HARDWARE OPTIONS _____
16 = Ø 0.120 HOLE / INSIDE GND STRAPS _____
17 = 4-40 INSERTS / INSIDE GND STRAPS _____
18 = 4-40 SCREWLOCKS / INSIDE GND STRAPS _____
43 = Ø 0.120 HOLE / METAL SHELL _____
45 = 4-40 INSERTS / METAL SHELL _____
48 = 4-40 SCREWLOCKS / METAL SHELL _____
53 = 4-40 INSERTS / BOARDLOCKS _____
55 = Ø 0.120 HOLE / BOARDLOCKS _____
56 = 4-40 SCREWLOCKS / BOARDLOCKS _____
PLATING OPTIONS _____
1 = GOLD FLASH _____

ELECTRICAL:

- CURRENT RATING: 2 AMPS
- CONTACT RESISTANCE: 15 MilliOhms Max.
- INSULATION RESISTANCE: 1,000 MEGOhms Min. at 500 VDC
- DIELECTRIC WITHSTANDING VOLTAGE: 1,000 VAC FOR 1 MINUTE
- WORKING VOLTAGE: 250 VAC
- TEMPERATURE: -55°C TO +105°C


MATERIALS:

- SHELL: SPCC, NICKEL PLATED
- INSULATOR: PA9T-BLACK (UL94-0)
- 260°C PROCESS TEMPERATURE
- CONTACT: BRASS, GOLD ENTIRE CONTACT
- RIVET: COPPER ALLOY, NICKEL PLATED
- BOARDLOCK: SPCC, TIN PLATED
- SCREWLOCK: ZINC ALLOY, NICKEL PLATED


DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: PAM JENKINS		DATE: 03-17-05					
			CHECKED:		DATE:					
			SCALE:	SHEET 1 OF 3	REV 13					
			DWG NO. 181-YYY-113RYY1							


RoHS COMPLIANT




15 POSITION



26 POSITION



44 POSITION



62 POSITION







181 SERIES
HIGH DENSITY
RIGHT ANGLE

HOLE PATTERN SHOWN
ARE FOR MALE

* TYP. ON ALL SIZES

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: C. SMITH		DATE: 03-09-06		
			CHECKED:		DATE:		
NorComp			SCALE: FULL		SHEET 2 OF 3		REV 13
			DWG NO. 181-YYY-113RYY1				

	 0.141 ±0.020 METAL SHELL WITH INSIDE GROUND STRAPS	 METAL SHELL	 METAL SHELL FORK BOARD LOCKS
 .120" DIA. HOLE	16	43	55
 4-40 FLUSH INSERT	17	45	53 BOARD LOCKS
 4-40 HEX STANDOFF FEMALE SCREWLOCK	18	48	56 BOARD LOCKS

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: WAYNE ROBBINS		DATE: 03-17-05		
		CHECKED:		DATE:		
NorComp			SCALE:	SHEET 3	OF 3	REV 13
			DWG NO. 181-YYY-113RYY1			