







RECOMMENDED P.C.B. LAYOUT

SCALE 4:1



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATINGS: 12VDC, 50mA
5. OPERATING FORCE: 100±50gf
6. TRAVEL: 0.25±0.1mm
7. CONTACT RESISTANCE: 100 Milli Ω Max.
8. DIELECTRIC STRENGTH: 250V RMS min.
9. INSULATION RESISTANCE: 100 Mega Ω min.
10. ELECTRICAL LIFE: 100,000 CYCLES min.
11. DESIGNATE MAJOR FEATURE:
12. HOUSING COLOR: BLACK
13. 2002/95/EC (ROHS) COMPLIANT



B	18742	LEG TOLERANCE WAS +/- 0.1	1/11/10	BLR
A	12357	ADD NOTCH	9/23/02	CB
REV.	ECN NO.	DESCRIPTION	DATE	CHKD

TITLE		E-SWITCH®		LAMBS INDUSTRIES	
TL1105JA F100 Q (STD BRACKET)		DATE		DR	
SCALE		1/11/10		BLR	
3:1		DATE		DWG	
1/11/10		BLR		P010209	
REV		B			

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED