

## 300MHz Low Noise Amplifiers

The EL5130 and EL5131 are ultra-low voltage noise, high speed voltage feedback amplifiers that are ideal for applications requiring low voltage noise, including communications and imaging. These devices offer extremely low power consumption for exceptional noise performance. Stable at gains as low as 5, these devices offer 100mA of drive performance. Not only do these devices find perfect application in high gain applications, they maintain their performance down to lower gain settings.

These amplifiers are available in small package options (SOT-23) as well as the industry-standard SOIC packages. All parts are specified for operation over the -40°C to +85°C temperature range.

## Ordering Information

| PART NUMBER          | PART MARKING | TAPE & REEL  | PACKAGE                       | PKG. DWG. # |
|----------------------|--------------|--------------|-------------------------------|-------------|
| EL5130IS             | 5130IS       | -            | 8 Ld SOIC (150 mil)           | MDP0027     |
| EL5130ISZ (Note)     | 5130ISZ      | -            | 8 Ld SOIC (150 mil) (Pb-free) | MDP0027     |
| EL5130IS-T7          | 5130IS       | 7"           | 8 Ld SOIC (150 mil)           | MDP0027     |
| EL5130ISZ-T7 (Note)  | 5130ISZ      | 7"           | 8 Ld SOIC (150 mil) (Pb-free) | MDP0027     |
| EL5130IS-T13         | 5130IS       | 13"          | 8 Ld SOIC (150 mil)           | MDP0027     |
| EL5130ISZ-T13 (Note) | 5130ISZ      | 13"          | 8 Ld SOIC (150 mil) (Pb-free) | MDP0027     |
| EL5131IW-T7          | BBAA         | 7" (3k pcs)  | 5 Ld SOT-23                   | P5.064A     |
| EL5131IWZ-T7 (Note)  | BRAA         | 7" (3k pcs)  | 5 Ld SOT-23 (Pb-free)         | P5.064A     |
| EL5131IW-T7A         | BBAA         | 7" (250 pcs) | 5 Ld SOT-23                   | P5.064A     |
| EL5131IWZ-T7A (Note) | BRAA         | 7" (250 pcs) | 5 Ld SOT-23 (Pb-free)         | P5.064A     |

NOTE: Intersil Pb-free plus anneal products employ special Pb-free material sets; molding compounds/die attach materials and 100% matte tin plate termination finish, which are RoHS compliant and compatible with both SnPb and Pb-free soldering operations. Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.



## Features

- 300MHz -3dB bandwidth
- Ultra low noise = 1.8nV/√Hz
- 350V/μs slew rate
- Low supply current = 4mA
- Single supplies from 5V to 12V
- Dual supplies from ±2.5V to ±6V
- Fast disable on the EL5130
- Low cost
- Pb-free plus anneal available (RoHS compliant)

## Applications

- Imaging
- Instrumentation
- Communications devices

## Pinouts



**Absolute Maximum Ratings** ( $T_A = +25^\circ\text{C}$ )

Slewrates between  $V_{S+}$  and  $V_{S-}$  ..... 1V/ $\mu\text{s}$   
 Supply Voltage from  $V_{S+}$  to  $V_{S-}$  ..... 13.2V  
 $I_{IN-}$ ,  $I_{IN+}$ , CE .....  $\pm 5\text{mA}$   
 Continuous Output Current ..... 100mA

**Thermal Information**

Storage Temperature .....  $-65^\circ\text{C}$  to  $+125^\circ\text{C}$   
 Ambient Operating Temperature .....  $-40^\circ\text{C}$  to  $+85^\circ\text{C}$   
 Operating Junction Temperature .....  $+125^\circ\text{C}$   
 Power Dissipation ..... See Curves  
 Pb-free reflow profile ..... see link below  
<http://www.intersil.com/pbfree/Pb-FreeReflow.asp>

**CAUTION:** Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

**IMPORTANT NOTE:** All parameters having Min/Max specifications are guaranteed. Typical values are for information purposes only. Unless otherwise noted, all tests are at the specified temperature and are pulsed tests, therefore:  $T_J = T_C = T_A$

**Electrical Specifications**  $V_{S+} = +5\text{V}$ ,  $V_{S-} = -5\text{V}$ ,  $R_L = 500\Omega$ ,  $R_G = 50\Omega$ ,  $C_L = 5\text{pF}$ ,  $T_A = +25^\circ\text{C}$ , Unless Otherwise Specified.

| PARAMETER     | DESCRIPTION                                | CONDITIONS                                                              | MIN       | TYP       | MAX | UNIT                         |
|---------------|--------------------------------------------|-------------------------------------------------------------------------|-----------|-----------|-----|------------------------------|
| $V_{OS}$      | Offset Voltage                             |                                                                         | -0.9      | 0.2       | 0.9 | mV                           |
| $T_C V_{OS}$  | Offset Voltage Temperature Coefficient     | Measured from $T_{MIN}$ to $T_{MAX}$                                    |           | 0.8       |     | $\mu\text{V}/^\circ\text{C}$ |
| $I_B$         | Input Bias Current                         | $V_{IN} = 0\text{V}$                                                    | 1.5       | 2.27      | 3.3 | $\mu\text{A}$                |
| $I_{OS}$      | Input Offset Current                       | $V_{IN} = 0\text{V}$                                                    | -500      | 100       | 500 | nA                           |
| $T_C I_{OS}$  | Input Bias Current Temperature Coefficient | Measured from $T_{MIN}$ to $T_{MAX}$                                    |           | -3        |     | nA/ $^\circ\text{C}$         |
| PSRR          | Power Supply Rejection Ratio               | $V_S = \pm 4.75\text{V}$ to $\pm 5.25\text{V}$                          | 75        | 90        |     | dB                           |
| CMRR          | Common Mode Rejection Ratio                | $V_{IN} = \pm 3.0\text{V}$                                              | 95        | 110       |     | dB                           |
| CMIR          | Common Mode Input Range                    | Guaranteed by CMRR test                                                 | $\pm 3$   | $\pm 3.3$ |     | V                            |
| $R_{IN}$      | Input Resistance                           | Common mode                                                             | 5         | 20        |     | M $\Omega$                   |
| $C_{IN}$      | Input Capacitance                          |                                                                         |           | 1         |     | pF                           |
| $I_S$         | Supply Current                             |                                                                         | 3.0       | 3.54      | 4.1 | mA                           |
| AVOL          | Open Loop Gain                             | $V_{OUT} = \pm 2.5\text{V}$ , $R_L = 1\text{k}\Omega$ to GND            | 10        | 16        |     | kV/V                         |
| $V_O$         | Output Voltage Swing                       | $R_L = 1\text{k}\Omega$ , $R_F = 900\Omega$ , $R_G = 100\Omega$         | $\pm 3.5$ | $\pm 3.8$ |     | V                            |
|               |                                            | $R_L = 150\Omega$                                                       | $\pm 3.5$ | $\pm 3.3$ |     | V                            |
| $I_{SC}$      | Short Circuit Current                      | $R_L = 10\Omega$                                                        | 50        | 100       |     | mA                           |
| BW            | -3dB Bandwidth                             | $A_V = +5$ , $R_L = 500\Omega$                                          |           | 300       |     | MHz                          |
| BW            | $\pm 0.1\text{dB}$ Bandwidth               | $A_V = +5$ , $R_L = 500\Omega$                                          |           | 60        |     | MHz                          |
| GBWP          | Gain Bandwidth Product                     |                                                                         |           | 1500      |     | MHz                          |
| PM            | Phase Margin                               | $R_L = 1\text{k}\Omega$ , $C_L = 6\text{pF}$                            |           | 55        |     | $^\circ$                     |
| SR            | Slew Rate                                  | $V_S = \pm 5\text{V}$ , $R_L = 150\Omega$ , $V_{OUT} = \pm 2.5\text{V}$ | 225       | 350       |     | V/ $\mu\text{s}$             |
| $t_R$ , $t_F$ | Rise Time, Fall Time                       | $\pm 0.1V_{STEP}$                                                       |           | TBD       |     | ns                           |
| $t_{PD}$      | Propagation Delay                          | $\pm 0.1V_{STEP}$                                                       |           | TBD       |     | ns                           |
| $t_S$         | 0.01% Settling Time                        |                                                                         |           | 14        |     | ns                           |
| dG            | Differential Gain                          | $A_V = +2$ , $R_F = 1\text{k}\Omega$                                    |           | 0.01      |     | %                            |
| dP            | Differential Phase                         | $A_V = +2$ , $R_F = 1\text{k}\Omega$                                    |           | 0.01      |     | $^\circ$                     |
| $e_N$         | Input Noise Voltage                        | $f = 10\text{kHz}$                                                      |           | 1.8       |     | nV/ $\sqrt{\text{Hz}}$       |
| $i_N$         | Input Noise Current                        | $f = 10\text{kHz}$                                                      |           | 1.1       |     | pA/ $\sqrt{\text{Hz}}$       |

## Typical Performance Curves




FIGURE 1. OPEN LOOP GAIN AND PHASE vs FREQUENCY




FIGURE 2. GAIN AND PHASE vs FREQUENCY (INVERTING)













FIGURE 3. GAIN AND PHASE vs FREQUENCY (NON-INVERTING)

FIGURE 4. GAIN vs FREQUENCY FOR VARIOUS  $A_V+$ FIGURE 5. PHASE vs FREQUENCY FOR VARIOUS  $A_V+$ FIGURE 6. GAIN vs FREQUENCY FOR VARIOUS  $R_L$  ( $A_V = +5$ )

## Typical Performance Curves

FIGURE 7. GAIN vs FREQUENCY FOR VARIOUS  $R_L$  ( $A_V=+10$ )FIGURE 8. GAIN vs FREQUENCY FOR VARIOUS  $R_F$  ( $A_V=+5$ )FIGURE 9. GAIN vs FREQUENCY FOR VARIOUS  $R_F$  ( $A_V=+10$ )FIGURE 10. GAIN vs FREQUENCY FOR VARIOUS  $C_L$  ( $A_V=+5$ )FIGURE 11. GAIN vs FREQUENCY FOR VARIOUS  $C_L$  ( $A_V=+10$ )FIGURE 12. GAIN vs FREQUENCY FOR VARIOUS  $C_{IN-}$  ( $A_V=+5$ )

## Typical Performance Curves




FIGURE 13. GAIN vs FREQUENCY FOR VARIOUS  $C_{IN}$  ( $A_V=+10$ )




FIGURE 14. GAIN vs FREQUENCY FOR VARIOUS  $\pm V_S$  ( $A_V=+5$ )




FIGURE 15. GAIN vs FREQUENCY FOR VARIOUS  $V_S\pm$  ( $A_V=+10$ )




FIGURE 16. FREQUENCY RESPONSE (-3dB ROLL-OFF)




FIGURE 17. FREQUENCY RESPONSE (0.1dB GAIN FLATNESS)




FIGURE 18. INPUT AND OUTPUT ISOLATION FOR DISABLE AMPLIFIER

## Typical Performance Curves




FIGURE 19. PSRR vs FREQUENCY




FIGURE 20. CMRR vs FREQUENCY




FIGURE 21. GROUP DELAY vs FREQUENCY




FIGURE 22. INPUT VOLTAGE NOISE




FIGURE 23. INPUT CURRENT NOISE




FIGURE 24. HARMONIC DISTORTION vs FREQUENCY ( $A_V=+5$ )

## Typical Performance Curves




FIGURE 25. HARMONIC DISTORTION vs FREQUENCY ( $A_V=+10$ )




FIGURE 26. THD vs OUTPUT VOLTAGE (WORST HARMONIC)




FIGURE 27. OUTPUT IMPEDANCE vs FREQUENCY




FIGURE 28. OUTPUT SWING vs FREQUENCY




FIGURE 29. SMALL SIGNAL PULSE RESPONSE/RISE TIME




FIGURE 30. SMALL SIGNAL PULSE RESPONSE/FALL TIME

## Typical Performance Curves




FIGURE 31. LARGE SIGNAL PULSE RESPONSE/RISE TIME




FIGURE 32. LARGE SIGNAL PULSE RESPONSE/RISE TIME




FIGURE 33. SLEW RATE (POSITIVE)




FIGURE 34. SLEW RATE (NEGATIVE)




FIGURE 35. ENABLE RESPONSE/TURN-ON TIME




FIGURE 36. DISABLE RESPONSE/TURN-OFF TIME

## Typical Performance Curves




FIGURE 37. THIRD-ORDER INTERCEPT POINT




FIGURE 38. SUPPLY CURRENT vs SUPPLY VOLTAGE




FIGURE 39. DIFFERENTIAL GAIN ERRORS




FIGURE 40. DIFFERENTIAL PHASE ERRORS




FIGURE 41. IP3

## Typical Performance Curves




FIGURE 42. PACKAGE POWER DISSIPATION vs AMBIENT TEMPERATURE




FIGURE 43. PACKAGE POWER DISSIPATION vs AMBIENT TEMPERATURE


All Intersil U.S. products are manufactured, assembled and tested utilizing ISO9000 quality systems.

Intersil Corporation's quality certifications can be viewed at [www.intersil.com/design/quality](http://www.intersil.com/design/quality)

Intersil products are sold by description only. Intersil Corporation reserves the right to make changes in circuit design, software and/or specifications at any time without notice. Accordingly, the reader is cautioned to verify that data sheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see [www.intersil.com](http://www.intersil.com)

# Small Outline Package Family (SO)



## MDP0027

### SMALL OUTLINE PACKAGE FAMILY (SO)

| SYMBOL | INCHES |       |               |                        |               |               |               | TOLERANCE | NOTES |
|--------|--------|-------|---------------|------------------------|---------------|---------------|---------------|-----------|-------|
|        | SO-8   | SO-14 | SO16 (0.150") | SO16 (0.300") (SOL-16) | SO20 (SOL-20) | SO24 (SOL-24) | SO28 (SOL-28) |           |       |
| A      | 0.068  | 0.068 | 0.068         | 0.104                  | 0.104         | 0.104         | 0.104         | MAX       | -     |
| A1     | 0.006  | 0.006 | 0.006         | 0.007                  | 0.007         | 0.007         | 0.007         | ±0.003    | -     |
| A2     | 0.057  | 0.057 | 0.057         | 0.092                  | 0.092         | 0.092         | 0.092         | ±0.002    | -     |
| b      | 0.017  | 0.017 | 0.017         | 0.017                  | 0.017         | 0.017         | 0.017         | ±0.003    | -     |
| c      | 0.009  | 0.009 | 0.009         | 0.011                  | 0.011         | 0.011         | 0.011         | ±0.001    | -     |
| D      | 0.193  | 0.341 | 0.390         | 0.406                  | 0.504         | 0.606         | 0.704         | ±0.004    | 1, 3  |
| E      | 0.236  | 0.236 | 0.236         | 0.406                  | 0.406         | 0.406         | 0.406         | ±0.008    | -     |
| E1     | 0.154  | 0.154 | 0.154         | 0.295                  | 0.295         | 0.295         | 0.295         | ±0.004    | 2, 3  |
| e      | 0.050  | 0.050 | 0.050         | 0.050                  | 0.050         | 0.050         | 0.050         | Basic     | -     |
| L      | 0.025  | 0.025 | 0.025         | 0.030                  | 0.030         | 0.030         | 0.030         | ±0.009    | -     |
| L1     | 0.041  | 0.041 | 0.041         | 0.056                  | 0.056         | 0.056         | 0.056         | Basic     | -     |
| h      | 0.013  | 0.013 | 0.013         | 0.020                  | 0.020         | 0.020         | 0.020         | Reference | -     |
| N      | 8      | 14    | 16            | 16                     | 20            | 24            | 28            | Reference | -     |

Rev. M 2/07

#### NOTES:






1. Plastic or metal protrusions of 0.006" maximum per side are not included.
2. Plastic interlead protrusions of 0.010" maximum per side are not included.
3. Dimensions "D" and "E1" are measured at Datum Plane "H".
4. Dimensioning and tolerancing per ASME Y14.5M-1994

# Package Outline Drawing

## P5.064A

### 5 LEAD SMALL OUTLINE TRANSISTOR PLASTIC PACKAGE

Rev 0, 2/10



#### NOTES:

1. Dimensions are in millimeters.  
Dimensions in ( ) for Reference Only.
2. Dimensioning and tolerancing conform to ASME Y14.5M-1994.
3. Dimension is exclusive of mold flash, protrusions or gate burrs.
4. Foot length is measured at reference to gauge plane.
5. This dimension is measured at Datum "H".
6. Package conforms to JEDEC MO-178AA.