


**Part Number: 71840-0138**

2.54mm Pitch C-Grid® Receptacle, Dual Row, Vertical, Low Profile, High-Temperature, 60 Circuits



Series image - Reference only

Status: **OBsolete**
Replacement: [15446860](#) (similar)
Series: 71840
Category: PCB Receptacles

Product Environmental ComplianceEU RoHS: ELV and RoHS CompliantChina RoHS: REACH SVHC: Contains SVHC: NoLow-Halogen Status: Not Low-Halogen**Part Detail****General**

Status	Obsolete
Category	PCB Receptacles
Series	71840
Application	Board-to-Board, Signal
Product Name	C-Grid®

Physical

Circuits (Loaded)	60
Circuits (maximum)	60
Color - Resin	Black
Durability (mating cycles max)	25
Glow-Wire Compliant	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Lead
Material - Plating Termination	Tin-Lead
Material - Resin	High Temperature Thermoplastic
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.49mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to PCB	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	2.5A
-------------------------------	------

Material Info

UPC	800754712514
-----	--------------

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be](#)

[available for this part](#)