

eH 150

Headphones | evolution Headphones

Cat. No. 500093

General Description

The eH 150 closed, dynamic hi-fi stereo headphones are the ideal partner for powerful, modern music, providing a high sound pressure level and a vivid, crisp bass response. Due to their effective attenuation of ambient noise, these headphones are particularly suitable for listening on the move.










Technical Data

Frequency response	18–18,000 Hz (–3 dB/1 kHz)
Transducer principle.....	dynamic, closed
Nominal impedance	32 Ω
Sound pressure level	115 dB (1 kHz, 1 V _{rms})
THD	< 0.5 %
Ear coupling	supra-aural
Weight (without cable)	approx. 130 g
Connector	3.5 mm jack plug with adaptor to 1/4" (6.3 mm) jack plug
Cable.....	3 m, OFC copper cable

Features

- Closed, supra-aural design ensures good attenuation of ambient noise, ideal for portable use
- "Turbine" embossed diaphragms for strong bass performance and precise treble
- Ultra-lightweight, rugged design for comfortable, extended listening pleasure
- Well defined mid-band and spatial sound reproduction due to foam damping element
- Precise trebles and high levels due to powerful neodymium magnets and lightweight diaphragms
- Powerful bass and increased signal levels for modern rhythm-driven music
- 3 m highly conductive OFC copper cable
- Easily replaceable leatherette ear pads

 18-18,000 Hz	 32 Ω	 < 0.5 %	 approx. 130 g
 3.5/6.3 mm	 OFC	 3 m	