

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

D2

REVISED PER ECO-11-004917

11MAR11

RK

HMR

MATERIAL:

HOUSING: THERMOPLASTIC, UL94V-0 BLACK.

TERMINALS: BRIGHT TIN PLATED, COPPER ALLOY.

SCREWS: #6-32, STEEL, ZINC PLATED WITH CLEAR CHROMATE.

ELECTRICAL:

CURRENT RATING UL/CSA:

CLASS C: 25A, 300V.

CLASS D: 5A, 600V.

WIRE RANGE: 12-22 AWG

MECHANICAL:

RECOMMENDED TORQUE: 7 IN-LB.





OPERATING TEMP.: 105°C MAX.

1 SCREWS ARE NICKEL PLATED BRASS.

2 SEE FIGURE.


3 MARK WITH WHITE PERMANENT INK.

4 ALL SCREWS BOTTOMED.

5 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

RECOMMENDED PCB LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHESTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± .02
3 PLC ± .010
4 PLC ± -
ANGLES ± 1°

MATERIAL

FINISH

DWN 8/19/03

S SCHLEGEL

CHK 8/19/03

S YODER

APVD 8/19/03

S YODER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

6PCV-XX-009 ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-796988-5

SCALE NTS

SHEET 1 OF 2

REV D2

4		3		2		1		
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION				
© COPYRIGHT - By -				ALL RIGHTS RESERVED.				
LOC FT		DIST 0		REVISIONS				
P		LTR		DESCRIPTION		DATE	DWN	APVD
		-		SEE SHEET 1		-	-	-

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

7-1546158-8

20

19

18

17

16

15

14

13

12

11

10

9

8

7

6

5

4

3

2

1

7-1546158-9

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL8/19/03		TE TE Connectivity				
DIMENSIONS: INCHES		CHK S YODER8/19/03						
		APVD S YODER8/19/03		NAME 6PCV-XX-009 ASSEMBLY				
		PRODUCT SPEC		SIZE A3				
		APPLICATION SPEC		CAGE CODE 00779		DRAWING NO C-796988-5		
MATERIAL -		FINISH -		WEIGHT -		RESTRICTED TO -		
CUSTOMER DRAWING				SCALE NTS		SHEET 2 OF 2		REV D2