







AMPOWER is a registered trademark of AMP Incorporated.

|     |      |           |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
| LOC | DIST | REVISIONS |     |                           |         |     |      |
| GP  | 00   | P         | LTR | DESCRIPTION               | DATE    | DWN | APYD |
|     |      |           | S   | REVISED PER ECO-12-005621 | 05SEP12 | KH  | DO   |



- 1 HOUSING MAT'L: POLYESTER
- 2 HOUSING MAT'L: POLYESTER HIGH TEMP
- 3 HOLE DIAMETER AFTER PLATING.
- 4 SOLDER TAIL: TIN-LEAD OVER NICKEL
- 5 SOLDER TAIL: SILVER OVER NICKEL
- 6 PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.



RECOMMENDED PC BOARD LAYOUT  
2.54 [ .100 ] CENTERLINES

|                                                                                       |              |                                                                                       |             |                            |            |
|---------------------------------------------------------------------------------------|--------------|---------------------------------------------------------------------------------------|-------------|----------------------------|------------|
| OBSOLETE                                                                              | WITH EYELETS |  | 5.72 [.225] | 1.57 [.062] TO 4.75 [.187] | 2=765206=2 |
| OBSOLETE                                                                              | WITH EYELETS |  | 4.19 [.165] | 1.57 [.062] TO 3.17 [.125] | 2=765206=1 |
|  | WITH EYELETS |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 2=765206=0 |
|  | W/O EYELETS  |  | 5.72 [.225] | 1.57 [.062] TO 4.75 [.187] | 1=765206=9 |
|  | W/O EYELETS  |  | 4.19 [.165] | 1.57 [.062] TO 3.17 [.125] | 1=765206=8 |
|  | W/O EYELETS  |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 1=765206=7 |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 1=765206=6 |
| OBSOLETE                                                                              |              |  | 7.49 [.295] | 6.35 [.250]                | 1=765206=5 |
| OBSOLETE                                                                              |              |  | 4.19 [.165] | 3.17 [.125]                | 1=765206=4 |
|                                                                                       | WITH EYELETS |  | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 1=765206=3 |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 1=765206=2 |
| OBSOLETE                                                                              |              |  | 7.49 [.295] | 6.35 [.250]                | 1=765206=1 |
| OBSOLETE                                                                              |              |  | 4.19 [.165] | 3.17 [.125]                | 1=765206=0 |
| OBSOLETE                                                                              |              |                                                                                       | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206=9   |
| OBSOLETE                                                                              |              |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 765206=8   |
| OBSOLETE                                                                              |              |                                                                                       | 7.49 [.295] | 6.35 [.250]                | 765206=7   |
|                                                                                       |              |  | 4.19 [.165] | 3.17 [.125]                | 765206=6   |
| OBSOLETE                                                                              |              |                                                                                       | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206=5   |
| OBSOLETE                                                                              | W/O EYELETS  |                                                                                       | 5.72 [.225] | 4.75 [.187]                | 765206=4   |
| OBSOLETE                                                                              |              |  | 7.49 [.295] | 6.35 [.250]                | 765206=3   |
|                                                                                       |              |  | 4.19 [.165] | 3.17 [.125]                | 765206=2   |
|                                                                                       |              |                                                                                       | 3.15 [.124] | 1.57 [.062] TO 2.36 [.093] | 765206=1   |
|                                                                                       |              | MATERIAL                                                                              | U           | BOARD THICKNESS            |            |

|                                                                                       |  |                                                                                                |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN: 12-08-09<br>U.K. DAILY<br>CWS: 12-14-09<br>CMS<br>APVD: --                                |  |  TE Connectivity |  |
| DIMENSIONS:<br>INCHES                                                                 |  | TOLERANCES UNLESS<br>OTHERWISE SPECIFIED:                                                      |  | NAME                                                                                                  |  |
|  |  | 0 PLC ± -<br>1 PLC ± -<br>2 PLC ± 0.25 [0.1]<br>3 PLC ± 0.13 [0.05]<br>4 PLC ± -<br>ANGLES ± - |  | PRODUCT SPEC<br>108-1308<br>APPLICATION SPEC<br>114-49005                                             |  |
| MATERIAL:<br>CONTACT, COPPER ALLOY                                                    |  | FINISH<br>SILVER ON MATING END,<br>ALL OVER NICKEL.                                            |  | SIZE CAGE CODE DRAWING NO RESTRICTED TO<br>A1 C-765206                                                |  |
| CUSTOMER DRAWING                                                                      |  | SCALE 4:1                                                                                      |  | SHEET 1 OF 1 REV S                                                                                    |  |