




FCIconnect.com

Copyright FCI

PRODUCT NO
SEE TABLE



mat'l. code				surface		tolerance	projection	product family	
-				ISO 1302		ISO 406 ISO 1101		CARD CONN	
ltr	ecr	no	dr	date	tolerances unless otherwise specified		INCH/MM	title	
F	REDRAWN	JRL	6/3/85		angles	linear		BERGCON HORIZ. CARD CONN.	
G	V40328	MSC	3/30/94					DOUBLE ROW .150/3.81	
H	V61666	LSS	12/20/96		0°±2°				
J	V70997	EPK	9/24/97	dr	JIM LINN	11/18/85	scale 4:1	dwg no	
K	V02518	MDF	10/31/00	enr	R. HOFFMAN	11/18/85		sheet 1 of 6 size	
L	M05-0181	MHT	8/17/05	chr	H. SUNDY	3/30/94		67210 A3	
M	M06-0117	AEA	06/26/06	appd	R. HOFFMAN	11/25/85		type Product Customer Drawing	
sheet	revision	M	M	M	M	M			
index	sheet	1	2	3	4	5	6		

form: A3



FCIconnect.com

Copyright FCI




FIGURE 1

NOTES:

- ① HOUSING MATERIAL: FILLED HIGH TEMPERATURE NYLON
COLOR: BLACK
- ② TERMINAL MATERIAL:
BODY: 1/4 HARD BRASS. .010/0.25 THICK — ALLOY 260
SPRING: BE — CU. HEAT TREATED. ALLOY 172
BODY PLATING: 30u"/0.76u GOLD OVER
50u"/1.27u NICKEL IN CONTACT AREA
SPRING PLATING: GOLD FLASH
3. APPLICATION INFORMATION:
A. RECOMMENDED MOUNTING HOLE PATTERN IS SHOWN AT LEFT.
B. ALL MATING PINS TO BE .025/0.84 SQUARE ON TRUE
CENTER OF GIVEN TERMINAL SPACING WITHIN .015/0.38 DIA.
C. SUGGESTED MATING PIN LENGTH .350±.020/8.89±0.51.
- ④ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD
FREE OPTION.
- ⑤ THESE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
6. THIS PART WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 20 SECONDS IN A WAVE SOLDER, INFRA-RED OR VAPOR PHASE
SOLDER PROCESS.

mat'l. code				surface	tolerance	projection	product family			
—				ISO 1302 ✓	ISO 406 ISO 1101		CARD CONN			
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title			
M					linear		BERGCON HORIZ. CARD CONN.			
					0°±2'		DOUBLE ROW .150/3.81			
						scale 4:1	dwg no			
				dr	JIM LINN	11/18/85	sheet 2 of 6 size			
				enr	R. HOFFMAN	11/18/85	67210			
				chr	H. SUNDY	3/30/94	A3			
				app	R. HOFFMAN	11/25/85	type Product Customer Drawing			
sheet	revision									
index	sheet									

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM A	DIM B	INSULATION PLUG	SPECIAL MARKINGS	LEAD FREE OPTION
67210-001	2X1	.00/.0	.150/3.81	NO		NOTE 5,6
-002	2X2	.150/3.81	.300/7.62	NO		
-003	2X3	.300/7.62	.450/11.43			
-004	2X4	.450/11.43	.600/15.24			
-005	2X5	.600/15.24	.750/19.05			
-006	2X6	.750/19.05	.900/22.86			
-007	2X7	.900/22.86	1.050/26.67			
-008	2X8	1.050/26.67	1.200/30.48			
-009	2X9	1.200/30.48	1.350/34.29			
-010	2X10	1.350/34.29	1.500/38.10			
-011	2X11	1.500/38.10	1.650/41.91			
-012	2X12	1.650/41.91	1.800/45.72			
-013	2X13	1.800/45.72	1.950/49.53			
-014	2X14	1.950/49.53	2.100/53.34			
-015	2X15	2.100/53.34	2.250/57.15			
-016	2X16	2.250/57.15	2.400/60.96			
-017	2X17	2.400/60.96	2.550/64.77			
-018	2X18	2.550/64.77	2.700/68.58			
-019	2X19	2.700/68.58	2.850/72.39			
-020	2X20	2.850/72.39	3.000/76.20			
-021	2X21	3.000/76.20	3.150/80.01			
-022	2X22	3.150/80.01	3.300/83.82			
-023	2X23	3.300/83.82	3.450/87.63			
-024	2X24	3.450/87.63	3.600/91.44			
67210-025	2X25	3.600/91.44	3.750/95.25	NO		NOTE 5,6

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406		CARD CONN
				tolerances unless otherwise specified			title
ltr	ecn	no	dr	date	linear	INCH/MM	BERGCON HORIZ. CARD CONN.
M					.XX±.01/.3		DOUBLE ROW .150/3.81
					.XXX ±.005/.13		
					.XXXX ±.0020/.051	scale 4:1	
				dr	JIM LINN	11/18/85	dwg no
				enr	R. HOFFMAN	11/18/85	sheet 3 of 6 size
				chr	H. SUNDY	3/30/94	67210 A3
				app	R. HOFFMAN	11/25/85	type Product Customer Drawing
sheet index	revision sheet						

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM A	DIM B	INSULATION PLUG	SPECIAL MARKINGS	LEAD FREE OPTION
67210-026	2X26	3.750/95.25	3.900/99.06	NO		NOTE 5,6
↑ -027	2X27	3.900/99.06	4.050/102.87	↑		
-028	2X28	4.050/102.87	4.200/106.68			
-029	2X29	4.200/106.68	4.350/110.49			
-030	2X30	4.350/110.49	4.500/114.30			
-031	2X31	4.500/114.30	4.650/118.11			
-032	2X32	4.650/118.11	4.800/121.92			
-033	2X33	4.800/121.92	4.950/125.73			
-034	2X34	4.950/125.73	5.100/129.54			
-035	2X35	5.100/129.54	5.250/133.35			
-036	2X36	5.250/133.35	5.400/137.16			
-037	2X37	5.400/137.16	5.550/140.97			
-038	2X38	5.550/140.97	5.700/144.78			
-039	2X39	5.700/144.78	5.850/148.59			
-040	2X40	5.850/148.59	6.000/152.40			
-041	2X41	6.000/152.40	6.150/156.21			
-042	2X42	6.150/156.21	6.300/160.02			
↓ 67210-043	2X43	6.300/160.02	6.450/163.83	NO		NOTE 5,6

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302 ✓	ISO 406 ISO 1101		CARD CONN
ltr	ecn	no	dr	date	tolerances unless otherwise specified	 INCH/MM scale 4:1	title
M					angles linear .XX±.01/.3		BERGCON HORIZ. CARD CONN.
					0'±2' .XXX ±.005/.13		DOUBLE ROW .150/3.81
					.XXX ±.0020/.051		
				dr	JIM LINN 11/18/85		dwg no
				enr	R. HOFFMAN 11/18/85		sheet 4 of 6 size
				chr	H. SUNDY 3/30/94		67210 A3
				app	R. HOFFMAN 11/25/85		type Product Customer Drawing
sheet index	revision sheet						

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM A	DIM B	INSULATION PLUG	SPECIAL MARKINGS	LEAD FREE OPTION
67210-501	2X1	.00/.0	.150/3.81	YES		NOTE 5,6
-502	2X2	.150/3.81	.300/7.62	YES		
-503	2X3	.300/7.62	.450/11.43			
-504	2X4	.450/11.43	.600/15.24			
-505	2X5	.600/15.24	.750/19.05			
-506	2X6	.750/19.05	.900/22.86			
-507	2X7	.900/22.86	1.050/26.67			
-508	2X8	1.050/26.67	1.200/30.48			
-509	2X9	1.200/30.48	1.350/34.29			
-510	2X10	1.350/34.29	1.500/38.10			
-511	2X11	1.500/38.10	1.650/41.91			
-512	2X12	1.650/41.91	1.800/45.72			
-513	2X13	1.800/45.72	1.950/49.53			
-514	2X14	1.950/49.53	2.100/53.34			
-515	2X15	2.100/53.34	2.250/57.15			
-516	2X16	2.250/57.15	2.400/60.96			
-517	2X17	2.400/60.96	2.550/64.77			
-518	2X18	2.550/64.77	2.700/68.58			
-519	2X19	2.700/68.58	2.850/72.39			
-520	2X20	2.850/72.39	3.000/76.20			
-521	2X21	3.000/76.20	3.150/80.01			
-522	2X22	3.150/80.01	3.300/83.82			
-523	2X23	3.300/83.82	3.450/87.63			
-524	2X24	3.450/87.63	3.600/91.44			
67210-525	2X25	3.600/91.44	3.750/95.25	YES		NOTE 5,6

mat'l. code				surface	tolerance	projection	product family
-				ISO 1302	ISO 406		CARD CONN
					ISO 1101		
ltr	ecr	no	dr	date	tolerances unless otherwise specified		title
M					linear	INCH/MM	BERGCON HORIZ. CARD CONN.
					0'±2'	scale 4:1	DOUBLE ROW .150/3.81
				dr	JIM LINN 11/18/85	FCI	dwg no
				enr	R. HOFFMAN 11/18/85		sheet 5 of 6 size
				chr	H. SUNDY 3/30/94		67210 A3
				app	R. HOFFMAN 11/25/85		type Product Customer Drawing
sheet index	revision sheet						

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO	NO. OF POS.	DIM A	DIM B	INSULATION PLUG	SPECIAL MARKINGS	LEAD FREE OPTION
67210-526	2X26	3.750/95.25	3.900/99.06	YES		NOTE 5,6
-527	2X27	3.900/99.06	4.050/102.87			
-528	2X28	4.050/102.87	4.200/106.68			
-529	2X29	4.200/106.68	4.350/110.49			
-530	2X30	4.350/110.49	4.500/114.30			
-531	2X31	4.500/114.30	4.650/118.11			
-532	2X32	4.650/118.11	4.800/121.92			
-533	2X33	4.800/121.92	4.950/125.73			
-534	2X34	4.950/125.73	5.100/129.54			
-535	2X35	5.100/129.54	5.250/133.35			
-536	2X36	5.250/133.35	5.400/137.16			
-537	2X37	5.400/137.16	5.550/140.97			
-538	2X38	5.550/140.97	5.700/144.78			
-539	2X39	5.700/144.78	5.850/148.59			
-540	2X40	5.850/148.59	6.000/152.40			
-541	2X41	6.000/152.40	6.150/156.21			
-542	2X42	6.150/156.21	6.300/160.02			
-543	2X43	6.300/160.02	6.450/163.83	YES		
-800	2X23	3.300/83.82	3.450/87.63	NO	503009-8 "LITTON"	NOTE 5,6
-801	2X30	4.350/110.49	4.500/114.30		503009-9 "LITTON"	
-802	2X41	6.000/152.40	6.150/156.21		503009-10 "LITTON"	
67210-803	2X42	6.150/156.21	6.300/160.02	NO	503009-12 "LITTON"	

mat'l. code				surface		tolerance		projection		product family			
-				ISO 1302		ISO 406				CARD CONN			
ltr				ecn		no		dr		date		title	
M												BERGCON HORIZ. CARD CONN.	
				tolerances unless otherwise specified		linear		INCH/MM				DOUBLE ROW .150/3.81	
				angles		.XX±.01/.3		scale 4:1					
				0°±2'		.XXX ±.005/.13							
						.XXXX ±.0020/.051							
				dr		JIM LINN		11/18/85		dwg no		sheet 6 of 6 size	
				enrg		R. HOFFMAN		11/18/85		67210		A3	
				chr		H. SUNDY		3/30/94		type		Product Customer Drawing	
				appd		R. HOFFMAN		11/25/85					
sheet index		revision sheet											

form: A3