



| PART NUMBER | LCD-S101D14TF                       | REV. | D    |
|-------------|-------------------------------------|------|------|
| DATE        | E.C.N. NUMBER AND REVISION COMMENTS |      | REV. |
| 09.09.02    | E.C.N. #10BRDR. & REDRAWN.          |      | A    |
| 02.07.07    | E.C.N. #11148.                      |      | B    |
| 12.28.12    | E.C.N. #10BRDR. & REDRAWN.          |      | C    |
| 10.22.14    | E.C.N. #11931.                      |      | D    |



| CHARACTERISTICS    |               |
|--------------------|---------------|
| FLUID TYPE:        | TN            |
| BACKGROUND COLOR:  | GRAY          |
| VIEWING DIRECTION: | 6:00          |
| DISPLAY MODE:      | TRANSFLECTIVE |
| OPERATING VOLTAGE: | 5.0 V A.C.    |
| OPERATING TEMP.    | 0°C TO 50°C   |
| STORAGE TEMP.      | -20°C TO 70°C |
| DRIVING METHODE:   | STATIC        |
| CONNECTION TYPE:   | 20 PINS       |



| PIN#  | SEG. |
|-------|------|
| 1-2   | COM. |
| 3-4   | E    |
| 5-6   | D    |
| 7-8   | C    |
| 9-10  | DP   |
| 11-12 | G    |
| 13-14 | B    |
| 15-16 | A    |
| 17-18 | F    |
| 19-20 | COM. |

B



\*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN= +DECIMAL PRECISION MAX.= +0.00 -DECIMAL PRECISION

UNCONTROLLED DOCUMENT