

Printed-circuit board connector - PC 4/ 4-G-7,62 BK - 1838239

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Header, Nominal current: 20 A, Number of positions: 4, Pitch: 7.62 mm, Color: Black, Contact surface: Tin

Key commercial data

Packing unit	1 PCE
GTIN	 4 017918 226930
Custom tariff number	85366990
Country of origin	GERMANY

Technical data

Dimensions

Pitch	7.62 mm
Dimension a	22.86 mm

Technical data

Range of articles	PC 4/..-G
Connection in acc. with standard	EN-VDE
Nominal current I_N	20 A
Nominal voltage U_N	400 V
Color	Black
Nominal voltage, UL/CUL Use Group B	300 V
Nominal current, UL/CUL Use Group B	20 A
Nominal voltage, UL/CUL Use Group C	300 V
Nominal current, UL/CUL Use Group C	20 A
Number of positions	4

Classifications

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002637
ETIM 5.0	EC002637

Printed-circuit board connector - PC 4/ 4-G-7,62 BK - 1838239

Classifications

UNSPSC

UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409
UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402

Approvals

Approvals

Approvals

CSA / UL Recognized / cUL Recognized / DNV / GOST / GOST / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

CSA 	B	C	
	Nominal current I _N	20 A	20 A
	Nominal voltage U _N	300 V	300 V

Printed-circuit board connector - PC 4/ 4-G-7,62 BK - 1838239

Approvals

UL Recognized 		
	B	C
Nominal current I _N	20 A	20 A
Nominal voltage U _N	300 V	300 V

cUL Recognized 		
	B	C
Nominal current I _N	20 A	20 A
Nominal voltage U _N	300 V	300 V

DNV

GOST 

GOST 

cULus Recognized 