



DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1501	A	RELEASED	JWM	4/28/03	HO	4/28/03	DJC	4/28/03




SCHEMATIC

	SWITCHING POSITION		
	Momentary	OFF	Momentary
Connected Terminals	2-3	OPEN	2-1
	SPDT 2 Comm.		

SOLDER LUG TERMINALS



PANEL MOUNTING



SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY: Jeff McVicker	DATE: 4/28/03	DRAWING TITLE: Paddle Switch, SPDT, 5 Amps			
	CHECKED BY: Hisham Odish	DATE: 4/28/03	SIZE A	DWG. NO. SPC12409	ELECTRONIC FILE 53H6668.dwg	REV A
	APPROVED BY: Daniel Carey	DATE: 4/28/03	SCALE: NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 2	

SPECIFICATIONS

ELECTRICAL

CONTACT RATING:

SILVER: 5A @ 120 VAC OR 28 VDC, 2A @ 250 VAC

CONTACT RESISTANCE: 10 MILLIOHMS MAX.

INSULATION RESISTANCE: 1,000 MEGOHMS MIN. AT 500 VDC

DIELECTRIC STRENGTH: 1,000 VRMS

MECHANICAL

LIFE: 50,000 CYCLES

ENVIRONMENTAL

OPERATING TEMPERATURE: -30°C TO +85°C

MATERIAL

CASE: DAP, UL 94V-0

HOUSING: STAINLESS STEEL

ACTUATOR: NYLON

BUSHING: BRASS, NICKEL PLATED

SUPPORT: BRASS, TIN PLATED

CONTACT/TERMINALS: COPPER ALLOY, SILVER PLATED

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F004.DWG

SIZE DWG. NO.

A

SPC12409

ELECTRONIC FILE

53H6668.dwg

REV

A

DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 2 OF 2