

## WV-508254-5-9 Product Details

[Share](#) [Print](#) [Email](#)


### WV-508254-5-9

TE Internal Number:  
E91539-000

[Active](#)

#### Label ID Products

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- Labels
- Region = Not Specified
- Printer Type = Thermal Transfer
- Label Height = 25.40 mm
- Label Width = 50.80 mm

[View all Features](#)

#### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- [Label ID Products](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Labels
- Self-Laminating = No
- UL Listed = No
- Color = White

#### Electrical Characteristics:

- [Printer Type](#) = Thermal Transfer
- Web Width (mm [in]) = 57.20 [2.250]

#### Dimensions:

- Recommended Wire/Cable OD Use Range (mm [in]) = 5.1 [0.2]

#### Body Features:

- [Material](#) = Vinyl

#### Configuration Features:

- [Number of Labels Across](#) = 1

#### Industry Standards:

#### Identification Marking:

- Energy Label Type = Pressure Sensitive

#### Environmental:

- [Operating Temperature](#) (°C [°F]) = -60 – +95 [-76 – +203]

#### Conditions for Usage:

- Energy Product = Yes

#### Packaging Features:

- [Packaging Quantity](#) = 5,000

#### Product Availability:

- Region = Not Specified

#### Other:

- [Series](#) = WV
- Configurator Part = Yes
- Brand = TE Connectivity

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- RoHS/ELV Compliance History = Always was RoHS compliant

**Printer/Label Features:**

- [Label Height \(mm \[in\]\)](#) = 25.40 [1.000]
- [Label Width \(mm \[in\]\)](#) = 50.80 [2.000]
- Self-Extinguishing = No
- Tamper Evident = No
- [Label Type](#) = Die-Cut
- Adhesive Type = Permanent Acrylic
- Vertical Repeat (mm [in]) = 28.60 [1.125]
- Recommended Printer = T308S
- Recommended Ribbon = 1330-3300-10

### Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)

### Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

### Keep Me Informed



## CROSS REFERENCE

Label format - Product Order Code . . . 87



## THERMAL TRANSFER LABELS

|                                        |     |                                       |     |
|----------------------------------------|-----|---------------------------------------|-----|
| WP White Polyester . . . . .           | 88  | NC Nylon Cloth Terminal Markers . . . | 110 |
| CP Clear Polyester . . . . .           | 90  | Kapton Labels . . . . .               | 112 |
| HW HighTack White Polyester . . . . .  | 92  | T1K Standard Polyimide . . . . .      | 113 |
| HM High Tack Metalized Polyester . . . | 94  | T2K High-performance Polyimide . . .  | 114 |
| MP Metalized Polyester . . . . .       | 96  | TSK Static-safe Polyimide . . . . .   | 115 |
| HMM High Tack Matte Metalized . . .    | 98  | KT T Tan Aerospace Polyimide . . . .  | 116 |
| MV Metalized Void Polyester . . . . .  | 100 | PVF Polyvinyl Fluoride . . . . .      | 118 |
| TN Tamper Proof Polyethylene . . . .   | 102 | EP Paper . . . . .                    | 120 |
| WV White Vinyl . . . . .               | 104 | VF Clear Tedlar® Overlamine . . . .   | 122 |
| NC Nylon Cloth . . . . .               | 106 |                                       |     |
| NC Nylon Cloth Wire Markers . . . . .  | 108 |                                       |     |



## DOT MATRIX LABELS

|                                        |     |
|----------------------------------------|-----|
| C Vinyl Cloth Labels . . . . .         | 124 |
| M Metalized Polyester Labels . . . . . | 126 |
| K Kapton Labels . . . . .              | 128 |
| E White Polyester Labels . . . . .     | 130 |



## LASER LABELS

|                                  |      |
|----------------------------------|------|
| LE Polyester . . . . .           | 132  |
| LM Metalized Polyester . . . . . | 132  |
| LEB2 Polyester . . . . .         | 1322 |

## Label format - Old format order code cross reference

### Thermal transfer

| Old label format | New product order code | Old label format | New product order code |
|------------------|------------------------|------------------|------------------------|
| 100              | TTP400XX-10            | 138              | XX-080080-10-#         |
| 101              | XX-381064-10-#         | 139              | XX-178095-10-#         |
| 102              | XX-381191-5-#          | 201              | XX-381064-10-#         |
| 103              | XX-699254-5-#          | 205              | XX-191064-10-#         |
| 104              | XX-762508-2.5-#        | 214              | XX-508127-10-#         |
| 105              | XX-191064-10-#         | 230              | XX-203127-10-#         |
| 106              | XX-101165-0.85-#       | 901              | XX-127032-10-#         |
| 107              | XX-254127-10-#         | 902              | XX-040033-10-#         |
| 108              | XX-064064-25-#         | 903              | XX-254045-10-#         |
| 109              | XX-165051-25-#         | 904              | XX-089047-10-#         |
| 110              | XX-254097-10-#         | 905              | XX-305047-10-#         |
| 111              | XX-318064-10-#         | 906              | XX-445064-10-#         |
| 112              | XX-508064-10-#         | 907              | XX-254064-10-#         |
| 114              | XX508127-10-#          | 908              | XX-095080-25-#         |
| 115              | XX-254254-10-#         | 909              | XX-208086-5-#          |
| 116              | XX-095095-10-#         | 911              | XX-508095-5-#          |
| 117              | XX-508318-2.5-#        | 912              | XX-318097-10-#         |
| 118              | XX-762381-2.5-#        | 913              | XX-165102-10-#         |
| 119              | XX-101635-2.5-#        | 914              | XX-445102-5-#          |
| 121              | XX-523841-1.5-#        | 916              | XX-127127-10-#         |
| 122              | XX-127111-10-#         | 917              | XX-381127-5-#          |
| 123              | XX-508254-5-#          | 918              | XX-222159-15-#         |
| 124              | XX-508508-3-#          | 919              | XX-171171-10-#         |
| 125              | XX-101508-2.5-#        | 920              | XX-478175-5-#          |
| 126              | XX-101762-1.8-#        | 921              | XX-699191-5-#          |
| 127              | XX-101101-1.3-#        | 922              | XX-406254-1.5-#        |
| 128              | XX-762127-1-#          | 923              | XX-250381-10-#         |
| 129              | XX-229064-10-#         | 924              | XX-381381-2.5-#        |
| 130              | XX-203127-10-#         | 925              | XX-610419-2.5-#        |
| 132              | XX-381020-10-#         | 926              | XX-445445-2-#          |
| 134              | XX-165051-25-#         | 927              | XX-381635-5-#          |
| 136              | XX-040040-25-#         | 928              | XX-191762-5-#          |
| 137              | XX-114040-25-#         |                  |                        |

XX = Insert material code from table below. # = Insert color code from table below right.

#### Examples

|                  | Old part number | New part number |
|------------------|-----------------|-----------------|
| Thermal transfer | 101-T1K-10      | T1K-381064-10-9 |
| Dot matrix       | 3-EW10F         | E-191064-10-9   |

### Dot matrix

| Old label format | New product order code |
|------------------|------------------------|
| 1                | X-165051-10-#          |
| 3                | X-191064-10-#          |
| 4                | X-203127-10-#          |
| 5                | X-254095-10-#          |
| 6A               | X-508095-5-#           |
| 7                | X-254127-10-#          |
| 8                | X-381191-10-#          |
| 11               | X-699254-2.5-#         |
| 12               | X-920381-2.5-#         |
| 13               | X-920254-2.5-#         |
| 16               | X-203365-10-#          |
| 17               | X-076191-10-#          |
| B2               | X-533064-5-#           |
| B4               | X-229064-10-#          |
| B6               | X-394064-10-#          |
| E                | X-203064-10-#          |
| L1               | X-080080-10-#          |
| M                | X-381064-10-S1-9       |
| L2               | X-064064-10-#          |
| L3               | X-095095-10-#          |
| R1               | X-508254-4-#           |
| R2               | X-673254-3-#           |
| R3               | X-508318-3-#           |
| R4               | X-673349-3-#           |
| R5               | X-762508-1-#           |
| R7               | X-165101-1-#           |
| V1               | X-127111-10-#          |
| Y3               | X-215055-10-#          |
| Y5               | X-115064-10-#          |
| Y6               | X-154064-10-#          |
| Y7               | X-293064-10-#          |
| Y8               | X-711064-5-#           |
| Y9               | X-121064-10-#          |
| Y10              | X-102070-10-#          |
| Y12              | X-159079-10-#          |
| Y13              | X-533114-5-#           |
| Y14              | X-572286-2.5-#         |
| Y15              | X-699318-2.5-#         |

X = Insert material code from table below left.  
# = Insert color code from table below.

#### Material codes – thermal transfer labels

|                                         |                                                  |
|-----------------------------------------|--------------------------------------------------|
| CP = Clear polyester                    | PVF = Polyvinylfluoride (Tedlar®)                |
| EP = Paper                              | T1K = Standard polyimide (Kapton®) 1 mil         |
| HM = High tack metalized polyester      | T1K = Standard polyimide (Kapton®) 1 mil         |
| HMM = High tack matte metalized         | T2K = High-performance polyimide (Kapton®) 2 mil |
| HW = High tack white polyester          | T2Y = Modified polyimide                         |
| KTT = Tan polyimide (Kapton®)           | TN = Tamper-proof polyethylene                   |
| MP = Metalized polyester                | TSK = Static-safe polyimide (Kapton®)            |
| MV = Tamper-evident metalized polyester | WP = White polyester                             |
| NC = Nylon cloth                        | WV = White vinyl                                 |

#### Material codes – dot matrix labels

|                     |                             |
|---------------------|-----------------------------|
| C = Vinyl cloth     | K = Tan polyimide (Kapton®) |
| E = White polyester | M = Metalized polyester     |

#### Color codes


|            |             |
|------------|-------------|
| 0 = Black  | 8 = Gray    |
| 1 = Brown  | 9 = White   |
| 2 = Red    | X = Clear   |
| 3 = Orange | 1A = Tan    |
| 4 = Yellow | 2L = Pink   |
| 5 = Green  | 8A = Silver |
| 6 = Blue   |             |
| 7 = Violet |             |

## WP White polyester labels

Tyco Electronics WP is a thermal transfer printable white polyester film with a permanent acrylic adhesive. It is ideal for bar coding, PCB and component labeling, as well as general purpose labeling applications that require a high durability white label. WP is resistant to a variety of solvents while maintaining print quality. It is UL Listed and print performance and durability are reliable when used with Tyco Electronics 1330-0607 ribbon.

### Features and benefits

- Thermal transfer printable
- Excellent for use in PCB component labeling
- Ink receptive topcoat
- Excellent for bar code applications
- UL Listed



### Specifications/approvals

|                  |                        |
|------------------|------------------------|
| Tyco Electronics | TTDS-073               |
| Industry         | UL MH17292 Group PGJ12 |

### Adhesive

Permanent acrylic

### Service temperature

-40°C to +150°C    -40°F to +302°F

### Recommended printer

T300 Series printers

### Recommended ribbon

1330-0607-10\*


\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.

### Part numbering system

WP-040040-10-9



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm    inches | Label height (B)<br>mm    inches | Horizontal repeat (C)<br>mm    inches | Vertical repeat (D)<br>mm    inches | Web width (E)<br>mm    inches |
|--------------------|------------------|---------------|---------------------------------|----------------------------------|---------------------------------------|-------------------------------------|-------------------------------|
| WP-040040-25-9     | 25,000           | 20            | 4.0    0.157                    | 4.0    0.157                     | 4.0    0.157                          | 7.2    0.281                        | 86.0    3.380                 |
| WP-064064-25-9     | 25,000           | 12            | 6.4    0.250                    | 6.4    0.250                     | 6.4    0.250                          | 9.5    0.375                        | 82.2    3.240                 |
| WP-080080-10-9     | 10,000           | 8             | 8.0    0.315                    | 8.0    0.315                     | 9.9    0.390                          | 13.3    0.525                       | 83.3    3.280                 |
| WP-089047-10-9     | 10,000           | 5             | 8.9    0.350                    | 4.7    0.185                     | 11.4    0.450                         | 7.9    0.313                        | 60.6    2.386                 |
| WP-095080-25-9     | 25,000           | 5             | 9.5    0.375                    | 8.0    0.315                     | 12.2    0.480                         | 12.7    0.500                       | 64.3    2.531                 |
| WP-095095-10-9     | 10,000           | 7             | 9.5    0.375                    | 9.5    0.375                     | 11.1    0.437                         | 12.7    0.500                       | 82.1    3.230                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## WP White polyester labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| WP-127111-10-9     | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8 <i>0.662</i>                         | 14.3 <i>0.563</i>                       | 86.0 <i>3.380</i>                 |
| WP-127127-10-9     | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| * WP-165051-25-9   | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| WP-165102-10-9     | 10,000           | 5             | 16.5 <i>0.650</i>                   | 10.2 <i>0.400</i>                    | 19.1 <i>0.750</i>                         | 13.8 <i>0.545</i>                       | 99.1 <i>3.900</i>                 |
| WP-171171-10-9     | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| * WP-178095-10-9   | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| * WP-191064-10-9   | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| WP-191114-15-9     | 15,000           | 3             | 19.1 <i>0.750</i>                   | 11.4 <i>0.450</i>                    | 22.2 <i>0.875</i>                         | 14.7 <i>0.579</i>                       | 69.5 <i>2.736</i>                 |
| * WP-203127-10-9   | 10,000           | 4             | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 22.9 <i>0.900</i>                         | 15.9 <i>0.625</i>                       | 94.6 <i>3.730</i>                 |
| WP-229064-10-9     | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| WP-254045-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| WP-254064-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| WP-254097-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| WP-254127-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| WP-254254-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| * WP-305047-10-9   | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| WP-318064-10-9     | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| WP-318097-10-9     | 10,000           | 1             | 31.8 <i>1.250</i>                   | 9.7 <i>0.380</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 37.8 <i>1.488</i>                 |
| WP-381064-10-9     | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| * WP-381127-5-9    | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.740</i>                         | 15.9 <i>0.630</i>                       | 88.2 <i>3.470</i>                 |
| WP-381191-5-9      | 5,000            | 2             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 22.2 <i>0.875</i>                       | 87.6 <i>3.450</i>                 |
| * WP-381381-2.5-9  | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.610</i>                       | 88.9 <i>3.500</i>                 |
| * WP-381635-5-9    | 5,000            | 2             | 38.1 <i>1.500</i>                   | 63.5 <i>2.500</i>                    | 40.6 <i>1.600</i>                         | 66.7 <i>2.630</i>                       | 84.7 <i>3.340</i>                 |
| * WP-406254-1.5-9  | 1,500            | 2             | 40.6 <i>1.600</i>                   | 25.4 <i>1.000</i>                    | 55.9 <i>2.200</i>                         | 38.1 <i>1.500</i>                       | 102.9 <i>4.050</i>                |
| WP-445064-10-9     | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| WP-445102-5-9      | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.986</i>                 |
| WP-445445-2-9      | 2,000            | 1             | 44.5 <i>1.750</i>                   | 44.5 <i>1.750</i>                    | N/A    N/A                                | 47.6 <i>1.875</i>                       | 50.4 <i>1.986</i>                 |
| WP-478175-5-9      | 5,000            | 1             | 47.8 <i>1.880</i>                   | 17.5 <i>0.690</i>                    | N/A    N/A                                | 24.4 <i>0.962</i>                       | 66.0 <i>2.600</i>                 |
| WP-508064-10-9     | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| WP-508095-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| WP-508127-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |
| WP-508254-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 57.2 <i>2.250</i>                 |
| WP-508318-2.5-9    | 2,500            | 1             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | N/A    N/A                                | 34.9 <i>1.375</i>                       | 56.9 <i>2.240</i>                 |
| WP-508508-3-9      | 3,000            | 1             | 50.8 <i>2.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 54.0 <i>2.130</i>                 |
| WP-523841-1.5-9    | 1,500            | 1             | 52.3 <i>2.060</i>                   | 84.1 <i>3.310</i>                    | N/A    N/A                                | 88.9 <i>3.500</i>                       | 58.2 <i>2.290</i>                 |
| WP-610419-2.5-9    | 2,500            | 1             | 61.0 <i>2.400</i>                   | 41.9 <i>1.650</i>                    | N/A    N/A                                | 45.5 <i>1.792</i>                       | 67.3 <i>2.650</i>                 |
| WP-699191-5-9      | 5,000            | 1             | 69.9 <i>2.750</i>                   | 19.1 <i>0.750</i>                    | N/A    N/A                                | 23.3 <i>0.917</i>                       | 76.2 <i>3.000</i>                 |
| WP-699254-5-9      | 5,000            | 1             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 76.2 <i>3.000</i>                 |
| WP-762254-5-9      | 5,000            | 1             | 76.2 <i>3.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 82.3 <i>3.240</i>                 |
| WP-762381-2.5-9    | 2,500            | 1             | 76.2 <i>3.000</i>                   | 38.1 <i>1.500</i>                    | N/A    N/A                                | 41.3 <i>1.625</i>                       | 82.3 <i>3.240</i>                 |
| WP-762508-2.5-9    | 2,500            | 1             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.0 <i>2.125</i>                       | 82.6 <i>3.240</i>                 |
| WP-762127-1-9      | 1,000            | 1             | 76.2 <i>3.000</i>                   | 127.0 <i>5.000</i>                   | N/A    N/A                                | 129.5 <i>5.100</i>                      | 79.4 <i>3.130</i>                 |
| WP-101508-2.5-9    | 2,500            | 1             | 101.6 <i>4.000</i>                  | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 104.1 <i>4.100</i>                |
| WP-101635-2.5-9    | 2,500            | 1             | 101.6 <i>4.000</i>                  | 63.5 <i>2.500</i>                    | N/A    N/A                                | 66.7 <i>2.625</i>                       | 107.7 <i>4.240</i>                |
| WP-101762-1.8-9    | 1,800            | 1             | 101.6 <i>4.000</i>                  | 76.2 <i>3.000</i>                    | N/A    N/A                                | 79.4 <i>3.125</i>                       | 104.1 <i>4.100</i>                |
| WP-101101-1.3-9    | 1,300            | 1             | 101.6 <i>4.000</i>                  | 101.6 <i>4.000</i>                   | N/A    N/A                                | 104.8 <i>4.125</i>                      | 104.1 <i>4.100</i>                |
| WP-101165-0.85-9   | 850              | 1             | 101.6 <i>4.000</i>                  | 165.1 <i>6.500</i>                   | N/A    N/A                                | 168.3 <i>6.680</i>                      | 104.9 <i>4.130</i>                |

\* NOTE: Standard Format Not Compatible with T200 Printers

## CP Clear polyester labels

CP is a thermal transfer printable clear polyester film with a permanent acrylic adhesive and can be used as an over laminate. Designed for rating plates, nameplates, equipment labels, serial number plates and general labeling applications that require a high durability transparent label. For reliable print performance and durability, use with Tyco Electronics 1330-0607 ribbon.

### Features and benefits

- Thermal transfer printable
- Ideal for general labeling applications



### Specifications/approvals

Tyco Electronics TTDS-083

**Adhesive** Permanent acrylic

**Service temperature** -40°C to +150°C -40°F to +302°F

**Recommended Printer** T300 Series printers


**Recommended Ribbon** 1330-0607-10\*

\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.




### Part numbering system

CP-762508-25-X



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| CP-165051-25-X     | 25,000           | 4             | 16.5 0.650                   | 5.1 0.200                     | 17.8 0.700                         | 8.3 0.325                        | 75.8 2.990                 |
| CP-191064-10-X     | 10,000           | 4             | 19.1 0.750                   | 6.4 0.250                     | 21.6 0.850                         | 9.5 0.375                        | 89.9 3.540                 |
| CP-229064-10-X     | 10,000           | 3             | 22.9 0.900                   | 6.4 0.250                     | 28.6 1.125                         | 9.5 0.375                        | 86.0 3.390                 |

**\* NOTE: Standard Format Not Compatible with T200 Printers**

## CP Clear polyester labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| CP-254097-10-X     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| CP-254127-10-X     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| CP-381064-10-X     | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| CP-381127-5-X      | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| CP-381191-5-X      | 5,000            | 2             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 22.2 <i>0.875</i>                       | 87.6 <i>3.450</i>                 |
| CP-406254-1.5-X    | 1,500            | 2             | 40.6 <i>1.600</i>                   | 25.4 <i>1.000</i>                    | 55.9 <i>2.200</i>                         | 38.1 <i>1.500</i>                       | 102.9 <i>4.050</i>                |
| CP-508127-5-X      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |
| CP-508254-5-X      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 57.2 <i>2.250</i>                 |
| CP-508318-2.5-X    | 2,500            | 1             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | N/A    N/A                                | 34.9 <i>1.375</i>                       | 56.9 <i>2.240</i>                 |
| CP-699254-5-X      | 5,000            | 1             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 76.2 <i>3.000</i>                 |
| CP-762254-5-X      | 5,000            | 1             | 76.2 <i>3.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 82.3 <i>3.240</i>                 |
| CP-762508-2.5-X    | 2,500            | 1             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.0 <i>2.125</i>                       | 82.3 <i>3.240</i>                 |
| CP-101635-2.5-X    | 2,500            | 1             | 101.6 <i>4.000</i>                  | 63.5 <i>2.500</i>                    | N/A    N/A                                | 66.7 <i>2.625</i>                       | 107.7 <i>4.240</i>                |

\* NOTE: Standard Format Not Compatible with T200 Printers



## HW High tack white polyester labels

Tyco Electronics HW is a thermal transfer printable white polyester film with a high tack permanent acrylic adhesive. Designed for application to rough surfaces or where increased adhesion is required, HW is also excellent for bar-coding, electronic PCB, component and general labeling applications. The high tack adhesion of HW will bond to the most demanding surfaces, including textured and contoured surfaces. For reliable print performance and durability, use with Tyco Electronics 1330-0607 ribbon.



### Features and benefits

- Thermal transfer printable
- Aggressive adhesive for textured and powdered surfaces
- UL Listed



### Specifications/Approvals

Tyco Electronics TTDS-076  
Industry UL MH17292 Group PGJ12

**Adhesive** Permanent acrylic

**Service temperature** -40°C to +150°C -40°F to +302°F


**Recommended printer** T300 Series printers

**Recommended ribbon** 1330-0607-10\*


\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.

### Part numbering system

HW-064064-25-9



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| HW-040040-25-9     | 25,000           | 20            | 4.0 0.157                    | 4.0 0.157                     | 4.0 0.157                          | 7.2 0.281                        | 86.0 3.380                 |
| HW-064064-25-9     | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| * HW-080080-10-9   | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| HW-089047-10-9     | 10,000           | 5             | 8.9 0.350                    | 4.7 0.186                     | 11.4 0.450                         | 7.9 0.313                        | 60.6 2.386                 |
| HW-095080-25-9     | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.480                         | 12.7 0.500                       | 64.3 2.531                 |
| HW-095095-10-9     | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## HW High tack white polyester labels

### Product dimensions

| Product           | Package  | Labels | Label width (A) |        | Label height (B) |        | Horizontal repeat (C) |        | Vertical repeat (D) |        | Web width (E) |        |
|-------------------|----------|--------|-----------------|--------|------------------|--------|-----------------------|--------|---------------------|--------|---------------|--------|
| order code        | quantity | across | mm              | inches | mm               | inches | mm                    | inches | mm                  | inches | mm            | inches |
| HW-127111-10-9    | 10,000   | 5      | 12.7            | 0.500  | 11.1             | 0.437  | 16.8                  | 0.662  | 14.3                | 0.563  | 86.0          | 3.380  |
| HW-127127-10-9    | 10,000   | 5      | 12.7            | 0.500  | 12.7             | 0.500  | 15.9                  | 0.625  | 15.9                | 0.625  | 82.6          | 3.250  |
| * HW-165051-25-9  | 25,000   | 4      | 16.5            | 0.650  | 5.1              | 0.200  | 17.8                  | 0.700  | 8.3                 | 0.325  | 75.8          | 2.990  |
| HW-165102-10-9    | 10,000   | 5      | 16.5            | 0.650  | 10.2             | 0.400  | 19.1                  | 0.750  | 13.8                | 0.545  | 99.1          | 3.900  |
| HW-171171-10-9    | 10,000   | 5      | 17.1            | 0.674  | 17.1             | 0.674  | 19.7                  | 0.774  | 20.3                | 0.800  | 101.8         | 4.006  |
| * HW-178095-10-9  | 10,000   | 4      | 17.8            | 0.700  | 9.5              | 0.375  | 19.1                  | 0.750  | 12.7                | 0.500  | 80.9          | 3.190  |
| * HW-191064-10-9  | 10,000   | 4      | 19.1            | 0.750  | 6.4              | 0.250  | 21.6                  | 0.850  | 9.5                 | 0.375  | 89.9          | 3.540  |
| HW-191114-15-9    | 15,000   | 3      | 19.1            | 0.750  | 11.4             | 0.450  | 22.2                  | 0.875  | 14.7                | 0.579  | 69.5          | 2.736  |
| * HW-203127-10-9  | 10,000   | 4      | 20.3            | 0.800  | 12.7             | 0.500  | 22.9                  | 0.900  | 15.9                | 0.625  | 94.6          | 3.730  |
| HW-229064-10-9    | 10,000   | 3      | 22.9            | 0.900  | 6.4              | 0.250  | 28.6                  | 1.125  | 9.5                 | 0.375  | 86.0          | 3.390  |
| HW-254045-10-9    | 10,000   | 3      | 25.4            | 1.000  | 4.6              | 0.180  | 31.8                  | 1.250  | 8.5                 | 0.333  | 95.3          | 3.750  |
| HW-254064-10-9    | 10,000   | 3      | 25.4            | 1.000  | 6.4              | 0.250  | 27.9                  | 1.100  | 9.5                 | 0.375  | 87.3          | 3.436  |
| HW-254097-10-9    | 10,000   | 3      | 25.4            | 1.000  | 9.7              | 0.380  | 27.9                  | 1.100  | 12.7                | 0.500  | 87.4          | 3.440  |
| HW-254127-10-9    | 10,000   | 3      | 25.4            | 1.000  | 12.7             | 0.500  | 27.9                  | 1.100  | 16.9                | 0.666  | 87.4          | 3.440  |
| HW-254254-10-9    | 10,000   | 3      | 25.4            | 1.000  | 25.4             | 1.000  | 27.9                  | 1.100  | 28.6                | 1.125  | 87.4          | 3.440  |
| * HW-305047-10-9  | 10,000   | 2      | 30.5            | 1.200  | 4.7              | 0.185  | 33.0                  | 1.300  | 7.8                 | 0.306  | 69.5          | 2.736  |
| HW-318064-10-9    | 10,000   | 1      | 31.8            | 1.250  | 6.4              | 0.250  | N/A                   | N/A    | 9.5                 | 0.375  | 37.9          | 1.490  |
| HW-318097-10-9    | 10,000   | 1      | 31.8            | 1.250  | 9.7              | 0.380  | N/A                   | N/A    | 12.7                | 0.500  | 37.8          | 1.488  |
| HW-381064-10-9    | 10,000   | 1      | 38.1            | 1.500  | 6.4              | 0.250  | N/A                   | N/A    | 9.5                 | 0.375  | 44.5          | 1.750  |
| * HW-381127-5-9   | 5,000    | 2      | 38.1            | 1.500  | 12.7             | 0.500  | 44.2                  | 1.738  | 15.9                | 0.625  | 88.2          | 3.472  |
| HW-381191-5-9     | 5,000    | 2      | 38.1            | 1.500  | 19.1             | 0.750  | 43.2                  | 1.700  | 22.2                | 0.875  | 87.6          | 3.450  |
| * HW-381381-2.5-9 | 2,500    | 2      | 38.1            | 1.500  | 38.1             | 1.500  | 44.5                  | 1.750  | 40.8                | 1.607  | 88.9          | 3.500  |
| * HW-381635-5-9   | 5,000    | 2      | 38.1            | 1.500  | 63.5             | 2.500  | 40.6                  | 1.600  | 66.7                | 2.625  | 84.7          | 3.338  |
| * HW-406254-1.5-9 | 1,500    | 2      | 40.6            | 1.600  | 25.4             | 1.000  | 55.9                  | 2.200  | 38.1                | 1.500  | 102.9         | 4.050  |
| HW-445064-10-9    | 10,000   | 1      | 44.5            | 1.750  | 6.4              | 0.250  | N/A                   | N/A    | 9.5                 | 0.375  | 50.4          | 1.986  |
| HW-445102-5-9     | 5,000    | 1      | 44.5            | 1.750  | 10.2             | 0.400  | N/A                   | N/A    | 12.7                | 0.500  | 50.4          | 1.986  |
| HW-445445-2-9     | 2,000    | 1      | 44.5            | 1.750  | 44.5             | 1.750  | N/A                   | N/A    | 47.6                | 1.875  | 50.4          | 1.986  |
| HW-478175-5-9     | 5,000    | 1      | 47.8            | 1.880  | 17.5             | 0.690  | N/A                   | N/A    | 24.4                | 0.962  | 66.0          | 2.600  |
| HW-508064-10-9    | 10,000   | 1      | 50.8            | 2.000  | 6.4              | 0.250  | N/A                   | N/A    | 9.5                 | 0.375  | 56.9          | 2.240  |
| HW-508095-5-9     | 5,000    | 1      | 50.8            | 2.000  | 9.5              | 0.375  | N/A                   | N/A    | 12.7                | 0.500  | 57.2          | 2.250  |
| HW-508127-5-9     | 5,000    | 1      | 50.8            | 2.000  | 12.7             | 0.500  | N/A                   | N/A    | 15.9                | 0.625  | 56.9          | 2.240  |
| HW-508254-5-9     | 5,000    | 1      | 50.8            | 2.000  | 25.4             | 1.000  | N/A                   | N/A    | 28.6                | 1.125  | 57.2          | 2.250  |
| HW-508318-2.5-9   | 2,500    | 1      | 50.8            | 2.000  | 31.8             | 1.250  | N/A                   | N/A    | 34.9                | 1.375  | 56.9          | 2.240  |
| HW-508508-3-9     | 3,000    | 1      | 50.8            | 2.000  | 50.8             | 2.000  | N/A                   | N/A    | 54.6                | 2.150  | 54.0          | 2.130  |
| HW-523841-1.5-9   | 1,500    | 1      | 52.3            | 2.060  | 84.1             | 3.310  | N/A                   | N/A    | 88.9                | 3.500  | 58.2          | 2.290  |
| HW-610419-2.5-9   | 2,500    | 1      | 61.0            | 2.400  | 41.9             | 1.650  | N/A                   | N/A    | 45.5                | 1.792  | 67.3          | 2.650  |
| HW-699191-5-9     | 5,000    | 1      | 69.9            | 2.750  | 19.1             | 0.750  | N/A                   | N/A    | 23.3                | 0.917  | 76.2          | 3.000  |
| HW-699254-5-9     | 5,000    | 1      | 69.9            | 2.750  | 25.4             | 1.000  | N/A                   | N/A    | 28.6                | 1.125  | 76.2          | 3.000  |
| HW-762381-2.5-9   | 2,500    | 1      | 76.2            | 3.000  | 38.1             | 1.500  | N/A                   | N/A    | 41.3                | 1.625  | 82.3          | 3.240  |
| HW-762508-2.5-9   | 2,500    | 1      | 76.2            | 3.000  | 50.8             | 2.000  | N/A                   | N/A    | 54.0                | 2.125  | 82.6          | 3.240  |
| HW-762127-1-9     | 1,000    | 1      | 76.2            | 3.000  | 127.0            | 5.000  | N/A                   | N/A    | 129.5               | 5.100  | 79.4          | 3.130  |
| HW-101508-2.5-9   | 2,500    | 1      | 101.6           | 4.000  | 50.8             | 2.000  | N/A                   | N/A    | 54.6                | 2.150  | 104.1         | 4.100  |
| HW-101635-2.5-9   | 2,500    | 1      | 101.6           | 4.000  | 63.5             | 2.500  | N/A                   | N/A    | 66.7                | 2.625  | 107.7         | 4.240  |
| HW-101762-1.8-9   | 1,800    | 1      | 101.6           | 4.000  | 76.2             | 3.000  | N/A                   | N/A    | 79.4                | 3.125  | 104.1         | 4.100  |
| HW-101101-1.3-9   | 1,300    | 1      | 101.6           | 4.000  | 101.6            | 4.000  | N/A                   | N/A    | 104.8               | 4.125  | 104.1         | 4.100  |
| HW-101165-0.85-9  | 850      | 1      | 101.6           | 4.000  | 165.1            | 6.500  | N/A                   | N/A    | 168.3               | 6.680  | 104.9         | 4.130  |

\* NOTE: Standard Format Not Compatible with T200 Printers

## HM High tack metalized polyester labels

Tyco Electronics HM is a thermal transfer printable metalized polyester film with a high tack permanent acrylic adhesive, designed for application to rough surfaces or where increased adhesion is required, and applications that require a metal look such as rating plates. The high tack adhesion of HM will bond to the most demanding surfaces, including textured and contoured surfaces. For reliable print performance and durability, use with Tyco Electronics 1330-0607 series ribbon.

### Features and benefits

- Thermal transfer printable
- Aggressive adhesive which permanently bonds to both high and low surface energy plastics
- UL Listed



#### Specifications/Approvals

Tyco Electronics TTDS-075  
Industry UL MH17292 Group PGJ12

**Adhesive** Permanent acrylic

**Service temperature** -40°C to +150°C -40°F to +302°F

**Recommended printer** T300 Series printers


**Recommended ribbon** 1330-0607-10\*

\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.




### Part numbering system

HM-080080-10-8A



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| HM-040040-25-8A    | 25,000           | 20            | 4.0 0.157                    | 4.0 0.157                     | 4.0 0.157                          | 7.2 0.281                        | 86.0 3.380                 |
| HM-064064-25-8A    | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| HM-080080-10-8A    | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| HM-089047-10-8A    | 10,000           | 5             | 8.9 0.350                    | 4.7 0.185                     | 11.4 0.450                         | 7.9 0.313                        | 60.6 2.386                 |
| HM-095080-25-8A    | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.480                         | 12.7 0.500                       | 64.3 2.531                 |
| HM-095095-10-8A    | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## HM High tack metalized polyester labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| HM-127111-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8 <i>0.662</i>                         | 14.3 <i>0.563</i>                       | 86.0 <i>3.380</i>                 |
| HM-127127-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| * HM-165051-25-8A  | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| HM-165102-10-8A    | 10,000           | 5             | 16.5 <i>0.650</i>                   | 10.2 <i>0.400</i>                    | 19.1 <i>0.750</i>                         | 13.8 <i>0.545</i>                       | 99.1 <i>3.900</i>                 |
| HM-171171-10-8A    | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| * HM-178095-10-8A  | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| * HM-191064-10-8A  | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| HM-191114-15-8A    | 15,000           | 3             | 19.1 <i>0.750</i>                   | 11.4 <i>0.450</i>                    | 22.2 <i>0.875</i>                         | 14.7 <i>0.579</i>                       | 69.5 <i>2.736</i>                 |
| * HM-203127-10-8A  | 10,000           | 4             | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 22.9 <i>0.900</i>                         | 15.9 <i>0.625</i>                       | 94.6 <i>3.730</i>                 |
| HM-229064-10-8A    | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| HM-254045-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| HM-254064-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| HM-254097-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| HM-254127-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| HM-254254-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| * HM-305047-10-8A  | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| HM-318064-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| HM-318097-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 9.7 <i>0.380</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 37.8 <i>1.488</i>                 |
| HM-381020-10-8A    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 2.0 <i>0.080</i>                     | N/A    N/A                                | 10.7 <i>0.423</i>                       | 44.1 <i>1.740</i>                 |
| HM-381064-10-8A    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| * HM-381127-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| HM-381191-5-8A     | 5,000            | 2             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 22.2 <i>0.875</i>                       | 87.6 <i>3.450</i>                 |
| * HM-381381-2.5-8A | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.607</i>                       | 88.9 <i>3.500</i>                 |
| * HM-381635-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                   | 63.5 <i>2.500</i>                    | 40.6 <i>1.600</i>                         | 66.7 <i>2.625</i>                       | 84.7 <i>3.336</i>                 |
| * HM-406254-1.5-8A | 1,500            | 2             | 40.6 <i>1.600</i>                   | 25.4 <i>1.000</i>                    | 55.9 <i>2.200</i>                         | 38.1 <i>1.500</i>                       | 102.9 <i>4.050</i>                |
| HM-445064-10-8A    | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| HM-445102-5-8A     | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.986</i>                 |
| HM-445445-2-8A     | 2,000            | 1             | 44.5 <i>1.750</i>                   | 44.5 <i>1.750</i>                    | N/A    N/A                                | 47.6 <i>1.875</i>                       | 50.4 <i>1.986</i>                 |
| HM-478175-5-8A     | 5,000            | 1             | 47.8 <i>1.880</i>                   | 17.5 <i>0.690</i>                    | N/A    N/A                                | 24.4 <i>0.962</i>                       | 66.0 <i>2.600</i>                 |
| HM-508064-10-8A    | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| HM-508095-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| HM-508127-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |
| HM-508254-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 57.2 <i>2.250</i>                 |
| HM-508318-2.5-8A   | 2,500            | 1             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | N/A    N/A                                | 34.9 <i>1.375</i>                       | 56.9 <i>2.240</i>                 |
| HM-508508-3-8A     | 3,000            | 1             | 50.8 <i>2.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 54.0 <i>2.130</i>                 |
| HM-523841-1.5-8A   | 1,500            | 1             | 52.3 <i>2.060</i>                   | 84.1 <i>3.310</i>                    | N/A    N/A                                | 88.9 <i>3.500</i>                       | 58.2 <i>2.290</i>                 |
| HM-610419-2.5-8A   | 2,500            | 1             | 61.0 <i>2.400</i>                   | 41.9 <i>1.650</i>                    | N/A    N/A                                | 45.5 <i>1.792</i>                       | 67.3 <i>2.650</i>                 |
| HM-699191-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                   | 19.1 <i>0.750</i>                    | N/A    N/A                                | 23.3 <i>0.917</i>                       | 76.2 <i>3.000</i>                 |
| HM-699254-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 76.2 <i>3.000</i>                 |
| HM-762381-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                   | 38.1 <i>1.500</i>                    | N/A    N/A                                | 41.3 <i>1.625</i>                       | 82.3 <i>3.240</i>                 |
| HM-762508-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.0 <i>2.125</i>                       | 82.6 <i>3.240</i>                 |
| HM-762127-1-8A     | 1,000            | 1             | 76.2 <i>3.000</i>                   | 127.0 <i>5.000</i>                   | N/A    N/A                                | 129.5 <i>5.100</i>                      | 79.4 <i>3.130</i>                 |
| HM-101508-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                  | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 104.1 <i>4.100</i>                |
| HM-101635-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                  | 63.5 <i>2.500</i>                    | N/A    N/A                                | 66.7 <i>2.625</i>                       | 107.7 <i>4.240</i>                |
| HM-101762-1.8-8A   | 1,800            | 1             | 101.6 <i>4.000</i>                  | 76.2 <i>3.000</i>                    | N/A    N/A                                | 79.4 <i>3.125</i>                       | 104.1 <i>4.100</i>                |
| HM-101101-1.3-8A   | 1,300            | 1             | 101.6 <i>4.000</i>                  | 101.6 <i>4.000</i>                   | N/A    N/A                                | 104.8 <i>4.125</i>                      | 104.1 <i>4.100</i>                |
| HM-101165-0.85-8A  | 850              | 1             | 101.6 <i>4.000</i>                  | 165.1 <i>6.500</i>                   | N/A    N/A                                | 168.3 <i>6.680</i>                      | 104.9 <i>4.130</i>                |

\* NOTE: Standard Format Not Compatible with T200 Printers

## MP Metalized polyester labels

Tyco Electronics MP is a thermal transfer printable metalized polyester film with a permanent acrylic adhesive, designed for rating plates and other applications that require a metal look, such as nameplates, equipment labels, detailed product information labels and serial number plates. MP is UL Listed. Print performance and durability are reliable when used with Tyco Electronics 1330-0607 series ribbon.

### Features and benefits

- Thermal transfer printable
- Metalized appearance
- Ideal for rating plate applications
- Several die-cut sizes available
- UL Listed



### Specifications/Approvals

Tyco Electronics TTDS-074  
Industry UL MH17292 Group PGJ12

**Adhesive** Permanent acrylic

**Service temperature** -40°C to +150°F -40°F to +302°F

**Recommended printer** T300 Series printers


**Recommended ribbon** 1330-0607-10\*

\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.




### Part numbering system

MP-080080-10-8A



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| MP-040040-25-8A    | 25,000           | 20            | 4.0 0.157                    | 4.0 0.160                     | 4.0 0.157                          | 7.2 0.281                        | 86.0 3.380                 |
| MP-064064-25-8A    | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| MP-080080-10-8A    | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| MP-089047-10-8A    | 10,000           | 5             | 8.9 0.350                    | 4.7 0.185                     | 11.4 0.450                         | 7.9 0.313                        | 60.6 2.386                 |
| MP-095080-25-8A    | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.475                         | 12.7 0.500                       | 64.3 2.531                 |
| MP-095095-10-8A    | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## MP Metalized polyester labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm<br><i>inches</i> | Label height (B)<br>mm<br><i>inches</i> | Horizontal repeat (C)<br>mm<br><i>inches</i> | Vertical repeat (D)<br>mm<br><i>inches</i> | Web width (E)<br>mm<br><i>inches</i> |
|--------------------|------------------|---------------|----------------------------------------|-----------------------------------------|----------------------------------------------|--------------------------------------------|--------------------------------------|
| MP-127111-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                      | 11.1 <i>0.437</i>                       | 16.8 <i>0.662</i>                            | 14.3 <i>0.563</i>                          | 86.0 <i>3.380</i>                    |
| MP-127127-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                      | 12.7 <i>0.500</i>                       | 15.9 <i>0.625</i>                            | 15.9 <i>0.625</i>                          | 82.6 <i>3.250</i>                    |
| * MP-165051-25-8A  | 25,000           | 4             | 16.5 <i>0.650</i>                      | 5.1 <i>0.200</i>                        | 17.8 <i>0.700</i>                            | 8.3 <i>0.325</i>                           | 75.8 <i>2.990</i>                    |
| MP-165102-10-8A    | 10,000           | 5             | 16.5 <i>0.650</i>                      | 10.2 <i>0.400</i>                       | 19.1 <i>0.750</i>                            | 13.8 <i>0.545</i>                          | 99.1 <i>3.900</i>                    |
| MP-171171-10-8A    | 10,000           | 5             | 17.1 <i>0.674</i>                      | 17.1 <i>0.674</i>                       | 19.7 <i>0.774</i>                            | 20.3 <i>0.800</i>                          | 101.8 <i>4.006</i>                   |
| * MP-178095-10-8A  | 10,000           | 4             | 17.8 <i>0.700</i>                      | 9.5 <i>0.375</i>                        | 19.1 <i>0.750</i>                            | 12.7 <i>0.500</i>                          | 80.9 <i>3.190</i>                    |
| * MP-191064-10-8A  | 10,000           | 4             | 19.1 <i>0.750</i>                      | 6.4 <i>0.250</i>                        | 21.6 <i>0.850</i>                            | 9.5 <i>0.375</i>                           | 89.9 <i>3.540</i>                    |
| MP-191114-15-8A    | 15,000           | 3             | 19.1 <i>0.750</i>                      | 11.4 <i>0.450</i>                       | 22.2 <i>0.875</i>                            | 14.7 <i>0.579</i>                          | 69.5 <i>2.736</i>                    |
| * MP-203127-10-8A  | 10,000           | 4             | 20.3 <i>0.800</i>                      | 12.7 <i>0.500</i>                       | 22.9 <i>0.900</i>                            | 15.9 <i>0.625</i>                          | 94.6 <i>3.730</i>                    |
| MP-229064-10-8A    | 10,000           | 3             | 22.9 <i>0.900</i>                      | 6.4 <i>0.250</i>                        | 28.6 <i>1.125</i>                            | 9.5 <i>0.375</i>                           | 86.0 <i>3.390</i>                    |
| MP-254045-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 4.6 <i>0.180</i>                        | 31.8 <i>1.250</i>                            | 8.5 <i>0.333</i>                           | 95.3 <i>3.750</i>                    |
| MP-254064-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 6.4 <i>0.250</i>                        | 27.9 <i>1.100</i>                            | 9.5 <i>0.375</i>                           | 87.3 <i>3.436</i>                    |
| MP-254097-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 9.7 <i>0.380</i>                        | 27.9 <i>1.100</i>                            | 12.7 <i>0.500</i>                          | 87.4 <i>3.440</i>                    |
| MP-254127-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 12.7 <i>0.500</i>                       | 27.9 <i>1.100</i>                            | 16.9 <i>0.666</i>                          | 87.4 <i>3.440</i>                    |
| MP-254254-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 25.4 <i>1.000</i>                       | 27.9 <i>1.100</i>                            | 28.6 <i>1.125</i>                          | 87.4 <i>3.440</i>                    |
| * MP-305047-10-8A  | 10,000           | 2             | 30.5 <i>1.200</i>                      | 4.7 <i>0.185</i>                        | 33.0 <i>1.300</i>                            | 7.8 <i>0.306</i>                           | 69.5 <i>2.736</i>                    |
| MP-318064-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 37.9 <i>1.490</i>                    |
| MP-318097-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                      | 9.7 <i>0.380</i>                        | N/A N/A                                      | 12.7 <i>0.500</i>                          | 37.8 <i>1.488</i>                    |
| MP-381064-10-8A    | 10,000           | 1             | 38.1 <i>1.500</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 44.5 <i>1.750</i>                    |
| * MP-381127-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                      | 12.7 <i>0.500</i>                       | 44.2 <i>1.738</i>                            | 15.9 <i>0.625</i>                          | 88.2 <i>3.472</i>                    |
| MP-381191-5-8A     | 5,000            | 2             | 38.1 <i>1.500</i>                      | 19.1 <i>0.750</i>                       | 43.2 <i>1.700</i>                            | 22.2 <i>0.875</i>                          | 87.6 <i>3.450</i>                    |
| * MP-381381-2.5-8A | 2,500            | 2             | 38.1 <i>1.500</i>                      | 38.1 <i>1.500</i>                       | 44.5 <i>1.750</i>                            | 40.8 <i>1.607</i>                          | 88.9 <i>3.500</i>                    |
| * MP-381635-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                      | 63.5 <i>2.500</i>                       | 40.6 <i>1.600</i>                            | 66.7 <i>2.625</i>                          | 84.7 <i>3.336</i>                    |
| * MP-406254-1.5-8A | 1,500            | 2             | 40.6 <i>1.600</i>                      | 25.4 <i>1.000</i>                       | 55.9 <i>2.200</i>                            | 38.1 <i>1.500</i>                          | 102.9 <i>4.050</i>                   |
| MP-445064-10-8A    | 10,000           | 1             | 44.5 <i>1.750</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 50.4 <i>1.986</i>                    |
| MP-445102-5-8A     | 5,000            | 1             | 44.5 <i>1.750</i>                      | 10.2 <i>0.400</i>                       | N/A N/A                                      | 12.7 <i>0.500</i>                          | 50.4 <i>1.986</i>                    |
| MP-445445-2-8A     | 2,000            | 1             | 44.5 <i>1.750</i>                      | 44.5 <i>1.750</i>                       | N/A N/A                                      | 47.6 <i>1.875</i>                          | 50.4 <i>1.986</i>                    |
| MP-478175-5-8A     | 5,000            | 1             | 47.8 <i>1.875</i>                      | 17.5 <i>0.690</i>                       | N/A N/A                                      | 24.4 <i>0.962</i>                          | 66.0 <i>2.600</i>                    |
| MP-508064-10-8A    | 10,000           | 1             | 50.8 <i>2.000</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 56.9 <i>2.240</i>                    |
| MP-508095-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 9.5 <i>0.375</i>                        | N/A N/A                                      | 12.7 <i>0.500</i>                          | 57.2 <i>2.250</i>                    |
| MP-508127-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 12.7 <i>0.500</i>                       | N/A N/A                                      | 15.9 <i>0.625</i>                          | 56.9 <i>2.240</i>                    |
| MP-508254-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 25.4 <i>1.000</i>                       | N/A N/A                                      | 28.6 <i>1.125</i>                          | 57.2 <i>2.250</i>                    |
| MP-508318-2.5-8A   | 2,500            | 1             | 50.8 <i>2.000</i>                      | 31.8 <i>1.250</i>                       | N/A N/A                                      | 34.9 <i>1.375</i>                          | 56.9 <i>2.240</i>                    |
| MP-508508-3-8A     | 3,000            | 1             | 50.8 <i>2.000</i>                      | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.6 <i>2.150</i>                          | 54.0 <i>2.130</i>                    |
| MP-523841-1.5-8A   | 1,500            | 1             | 52.3 <i>2.060</i>                      | 84.1 <i>3.310</i>                       | N/A N/A                                      | 88.9 <i>3.500</i>                          | 58.2 <i>2.290</i>                    |
| MP-610419-2.5-8A   | 2,500            | 1             | 61.0 <i>2.400</i>                      | 41.9 <i>1.650</i>                       | N/A N/A                                      | 45.5 <i>1.792</i>                          | 67.3 <i>2.650</i>                    |
| MP-699191-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                      | 19.1 <i>0.750</i>                       | N/A N/A                                      | 23.3 <i>0.917</i>                          | 76.2 <i>3.000</i>                    |
| MP-699254-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                      | 25.4 <i>1.000</i>                       | N/A N/A                                      | 28.6 <i>1.125</i>                          | 76.2 <i>3.000</i>                    |
| MP-762381-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                      | 38.1 <i>1.500</i>                       | N/A N/A                                      | 41.3 <i>1.625</i>                          | 82.3 <i>3.240</i>                    |
| MP-762508-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                      | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.0 <i>2.125</i>                          | 82.6 <i>3.240</i>                    |
| MP-762127-1-8A     | 1,000            | 1             | 76.2 <i>3.000</i>                      | 127.0 <i>5.000</i>                      | N/A N/A                                      | 129.5 <i>5.100</i>                         | 79.4 <i>3.130</i>                    |
| MP-101508-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                     | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.6 <i>2.150</i>                          | 104.1 <i>4.100</i>                   |
| MP-101635-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                     | 63.5 <i>2.500</i>                       | N/A N/A                                      | 66.7 <i>2.625</i>                          | 107.7 <i>4.240</i>                   |
| MP-101762-1.8-8A   | 1,800            | 1             | 101.6 <i>4.000</i>                     | 76.2 <i>3.000</i>                       | N/A N/A                                      | 79.4 <i>3.125</i>                          | 104.1 <i>4.100</i>                   |
| MP-101101-1.3-8A   | 1,300            | 1             | 101.6 <i>4.000</i>                     | 101.6 <i>4.000</i>                      | N/A N/A                                      | 104.8 <i>4.125</i>                         | 104.1 <i>4.100</i>                   |
| MP-101165-0.85-8A  | 850              | 1             | 101.6 <i>4.000</i>                     | 165.1 <i>6.500</i>                      | N/A N/A                                      | 168.3 <i>6.680</i>                         | 104.9 <i>4.130</i>                   |

\* NOTE: Standard Format Not Compatible with T200 Printers



## HMM High Tack Matte Metalized Polyester Labels

HMM is a high performance thermal transfer printable matte metalized polyester with an aggressive high tack permanent acrylic adhesive. Designed for applications such as rating plates and serial plates that require high adhesion to textured surfaces, metals low surface energy plastics and powder coated surfaces. The matte surface provides excellent mark permanence and the high tack adhesion of HMM will bond to the most demanding surfaces. For reliable print performance and durability, use with Tyco Electronics 1330-0607 series ribbon.

### Features and benefits

- Thermal transfer printable
- Ideal for rating plate applications
- Ultra aggressive adhesive for application to textured and powder coated surfaces
- UL Listed



### Specifications/Approvals

Tyco Electronics TTDS-118  
Industry UL MH17292 Group PGJ12

**Adhesive** Permanent acrylic-High Tack

**Service temperature** -40°C to +150°F -40°F to +302°F

**Recommended printer** T300 Series printers


**Recommended ribbon** 1330-0607-10\*

*\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.*




### Part numbering system

HMM-508254-5 - 8A



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| HMM-095095-10-8A   | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |
| HMM-127127-10-8A   | 10,000           | 5             | 12.7 0.500                   | 12.7 0.500                    | 15.9 0.625                         | 15.9 0.625                       | 82.6 3.250                 |
| HMM-165051-25-8A   | 25,000           | 4             | 16.5 0.650                   | 5.1 0.200                     | 17.8 0.700                         | 8.3 0.325                        | 75.8 2.990                 |
| HMM-191064-10-8A   | 10,000           | 4             | 19.1 0.750                   | 6.4 0.250                     | 21.6 0.850                         | 9.5 0.375                        | 89.9 3.540                 |
| HMM-229064-10-8A   | 10,000           | 3             | 22.9 0.900                   | 6.4 0.250                     | 28.6 1.125                         | 9.5 0.375                        | 86.0 3.390                 |
| HMM-254097-10-8A   | 10,000           | 3             | 25.4 1.000                   | 9.7 0.380                     | 27.9 1.100                         | 12.7 0.500                       | 87.4 3.440                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## HMM High Tack Matte Metalized Polyester Labels

### Product dimensions

| Product<br>order code | Package<br>quantity | Labels<br>across | Label width (A) |               | Label height (B) |               | Horizontal repeat (C) |               | Vertical repeat (D) |               | Web width (E) |               |
|-----------------------|---------------------|------------------|-----------------|---------------|------------------|---------------|-----------------------|---------------|---------------------|---------------|---------------|---------------|
|                       |                     |                  | mm              | <i>inches</i> | mm               | <i>inches</i> | mm                    | <i>inches</i> | mm                  | <i>inches</i> | mm            | <i>inches</i> |
| HMM-254127-10-8A      | 10,000              | 3                | 25.4            | <i>1.000</i>  | 12.7             | <i>0.500</i>  | 27.9                  | <i>1.100</i>  | 16.9                | <i>0.666</i>  | 87.4          | <i>3.440</i>  |
| HMM-254254-10-8A      | 10,000              | 3                | 25.4            | <i>1.000</i>  | 25.4             | <i>1.000</i>  | 27.9                  | <i>1.100</i>  | 28.6                | <i>1.125</i>  | 87.4          | <i>3.440</i>  |
| HMM-318064-10-8A      | 10,000              | 1                | 31.8            | <i>1.250</i>  | 6.4              | <i>0.250</i>  | N/A                   | N/A           | 9.5                 | <i>0.375</i>  | 37.9          | <i>1.490</i>  |
| HMM-381064-10-8A      | 10,000              | 1                | 38.1            | <i>1.500</i>  | 6.4              | <i>0.250</i>  | N/A                   | N/A           | 9.5                 | <i>0.375</i>  | 44.5          | <i>1.750</i>  |
| * HMM-381127-5-8A     | 5,000               | 2                | 38.1            | <i>1.500</i>  | 12.7             | <i>0.500</i>  | 44.2                  | <i>1.738</i>  | 15.9                | <i>0.625</i>  | 88.2          | <i>3.472</i>  |
| HMM-381191-5-8A       | 5,000               | 2                | 38.1            | <i>1.500</i>  | 19.1             | <i>0.750</i>  | 43.2                  | <i>1.700</i>  | 22.2                | <i>0.875</i>  | 87.6          | <i>3.450</i>  |
| * HMM-406254-1.5-8A   | 1,500               | 2                | 40.6            | <i>1.600</i>  | 25.4             | <i>1.000</i>  | 55.9                  | <i>2.200</i>  | 38.1                | <i>0.500</i>  | 102.9         | <i>4.050</i>  |
| HMM-508064-10-8A      | 10,000              | 1                | 50.8            | <i>2.000</i>  | 6.4              | <i>0.250</i>  | N/A                   | N/A           | 9.5                 | <i>0.375</i>  | 56.9          | <i>2.240</i>  |
| HMM-508095-5-8A       | 5,000               | 1                | 50.8            | <i>2.000</i>  | 9.5              | <i>0.375</i>  | N/A                   | N/A           | 12.7                | <i>0.500</i>  | 57.2          | <i>2.250</i>  |
| HMM-508127-5-8A       | 5,000               | 1                | 50.8            | <i>2.000</i>  | 12.7             | <i>0.500</i>  | N/A                   | N/A           | 15.9                | <i>0.625</i>  | 56.9          | <i>2.240</i>  |
| HMM-508254-5-8A       | 5,000               | 1                | 50.8            | <i>2.000</i>  | 25.4             | <i>1.000</i>  | N/A                   | N/A           | 28.6                | <i>1.125</i>  | 57.2          | <i>2.250</i>  |
| HMM-508318-2.5-8A     | 2,500               | 1                | 50.8            | <i>2.000</i>  | 31.8             | <i>1.250</i>  | N/A                   | N/A           | 34.9                | <i>1.375</i>  | 56.9          | <i>2.240</i>  |
| HMM-508508-3-8A       | 3,000               | 1                | 50.8            | <i>2.000</i>  | 50.8             | <i>2.000</i>  | N/A                   | N/A           | 54.6                | <i>2.150</i>  | 54.0          | <i>2.130</i>  |
| HMM-699254-5-8A       | 5,000               | 1                | 69.9            | <i>2.750</i>  | 25.4             | <i>1.000</i>  | N/A                   | N/A           | 28.6                | <i>1.125"</i> | 76.2          | <i>3.000</i>  |
| HMM-762254-5-8A       | 5,000               | 1                | 76.2            | <i>3.000</i>  | 25.4             | <i>1.000</i>  | N/A                   | N/A           | 28.6                | <i>1.125"</i> | 82.3          | <i>3.240</i>  |
| HMM-762381-2.5-8A     | 2,500               | 1                | 76.2            | <i>3.000</i>  | 38.1             | <i>1.500</i>  | N/A                   | N/A           | 41.3                | <i>1.625</i>  | 82.3          | <i>3.240</i>  |
| HMM-762508-2.5-8A     | 2,500               | 1                | 76.2            | <i>3.000</i>  | 50.8             | <i>2.000</i>  | N/A                   | N/A           | 54.0                | <i>2.125</i>  | 82.3          | <i>3.240</i>  |
| HMM-101635-2.5-8A     | 2,500               | 1                | 101.6           | <i>4.000</i>  | 63.5             | <i>2.500</i>  | N/A                   | N/A           | 66.7                | <i>2.625</i>  | 107.7         | <i>4.240</i>  |
| HMM-101101-1.3-8A     | 1,300               | 1                | 101.6           | <i>4.000</i>  | 101.6            | <i>4.000</i>  | N/A                   | N/A           | 104.8               | <i>4.125</i>  | 104.1         | <i>4.100</i>  |

\* NOTE: Standard Format Not Compatible with T200 Printers



## MV Tamper-evident metalized polyester labels

Tyco Electronics MV is a thermal transfer printable metalized polyester film with a permanent acrylic adhesive, designed with a tamper-evident feature which leaves a void footprint when removed. It is ideal for applications such as rating plate and serial number labels that require protection against removal. For reliable print performance and durability, use with Tyco Electronics 1330-0607 ribbon.

### Features and benefits

- Thermal transfer printable
- Metalized appearance
- Ideal for security applications
- UL Recognized



### Specifications/Approvals

Tyco Electronics TTDS-084  
Industry UL MH17292 Group PGJ12

**Adhesive** Permanent acrylic

**Service temperature** -40°C to +150°C -40°F to +302°F


**Recommended printer** T300 Series printers

**Recommended ribbon** 1330-0607-10\*


\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.

### Part numbering system

MV-080080-10-8A



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| MV-040040-25-8A    | 25,000           | 20            | 4.0 0.157                    | 4.0 0.157                     | 4.0 0.157                          | 7.2 0.281                        | 86.0 3.380                 |
| MV-064064-25-8A    | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| * MV-080080-10-8A  | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| MV-089047-10-8A    | 10,000           | 5             | 8.9 0.350                    | 4.7 0.185                     | 11.4 0.450                         | 7.9 0.313                        | 60.6 2.386                 |
| MV-095080-25-8A    | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.480                         | 12.7 0.500                       | 64.3 2.531                 |
| MV-095095-10-8A    | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |

**\* NOTE: Standard Format Not Compatible with T200 Printers**

## MV Tamper-evident metalized polyester labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm<br><i>inches</i> | Label height (B)<br>mm<br><i>inches</i> | Horizontal repeat (C)<br>mm<br><i>inches</i> | Vertical repeat (D)<br>mm<br><i>inches</i> | Web width (E)<br>mm<br><i>inches</i> |
|--------------------|------------------|---------------|----------------------------------------|-----------------------------------------|----------------------------------------------|--------------------------------------------|--------------------------------------|
| MV-127111-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                      | 11.1 <i>0.437</i>                       | 16.8 <i>0.662</i>                            | 14.3 <i>0.563</i>                          | 86.0 <i>3.380</i>                    |
| MV-127127-10-8A    | 10,000           | 5             | 12.7 <i>0.500</i>                      | 12.7 <i>0.500</i>                       | 15.9 <i>0.625</i>                            | 15.9 <i>0.625</i>                          | 82.6 <i>3.250</i>                    |
| * MV-165051-25-8A  | 25,000           | 4             | 16.5 <i>0.650</i>                      | 5.1 <i>0.200</i>                        | 17.8 <i>0.700</i>                            | 8.3 <i>0.325</i>                           | 75.8 <i>2.990</i>                    |
| MV-165102-10-8A    | 10,000           | 5             | 16.5 <i>0.650</i>                      | 10.2 <i>0.400</i>                       | 19.1 <i>0.750</i>                            | 13.8 <i>0.545</i>                          | 99.1 <i>3.900</i>                    |
| MV-171171-10-8A    | 10,000           | 5             | 17.1 <i>0.674</i>                      | 17.1 <i>0.674</i>                       | 19.7 <i>0.774</i>                            | 20.3 <i>0.800</i>                          | 101.8 <i>4.006</i>                   |
| * MV-178095-10-8A  | 10,000           | 4             | 17.8 <i>0.700</i>                      | 9.5 <i>0.375</i>                        | 19.1 <i>0.750</i>                            | 12.7 <i>0.500</i>                          | 80.9 <i>3.190</i>                    |
| * MV-191064-10-8A  | 10,000           | 4             | 19.1 <i>0.750</i>                      | 6.4 <i>0.250</i>                        | 21.6 <i>0.850</i>                            | 9.5 <i>0.375</i>                           | 89.9 <i>3.540</i>                    |
| MV-191114-15-8A    | 15,000           | 3             | 19.1 <i>0.750</i>                      | 11.4 <i>0.450</i>                       | 22.2 <i>0.875</i>                            | 14.7 <i>0.579</i>                          | 69.5 <i>2.736</i>                    |
| * MV-203127-10-8A  | 10,000           | 4             | 20.3 <i>0.800</i>                      | 12.7 <i>0.500</i>                       | 22.9 <i>0.900</i>                            | 15.9 <i>0.625</i>                          | 94.6 <i>3.730</i>                    |
| MV-229064-10-8A    | 10,000           | 3             | 22.9 <i>0.900</i>                      | 6.4 <i>0.250</i>                        | 28.6 <i>1.125</i>                            | 9.5 <i>0.375</i>                           | 86.0 <i>3.390</i>                    |
| MV-254045-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 4.6 <i>0.180</i>                        | 31.8 <i>1.250</i>                            | 8.5 <i>0.333</i>                           | 95.3 <i>3.750</i>                    |
| MV-254064-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 6.4 <i>0.250</i>                        | 27.9 <i>1.100</i>                            | 9.5 <i>0.375</i>                           | 87.3 <i>3.436</i>                    |
| MV-254097-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 9.7 <i>0.380</i>                        | 27.9 <i>1.100</i>                            | 12.7 <i>0.500</i>                          | 87.4 <i>3.440</i>                    |
| MV-254127-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 12.7 <i>0.500</i>                       | 27.9 <i>1.100</i>                            | 16.9 <i>0.666</i>                          | 87.4 <i>3.440</i>                    |
| MV-254254-10-8A    | 10,000           | 3             | 25.4 <i>1.000</i>                      | 25.4 <i>1.000</i>                       | 27.9 <i>1.100</i>                            | 28.6 <i>1.125</i>                          | 87.4 <i>3.440</i>                    |
| * MV-305047-10-8A  | 10,000           | 2             | 30.5 <i>1.200</i>                      | 4.7 <i>0.185</i>                        | 33.0 <i>1.300</i>                            | 7.8 <i>0.306</i>                           | 69.5 <i>2.736</i>                    |
| MV-318064-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 37.9 <i>1.490</i>                    |
| MV-318097-10-8A    | 10,000           | 1             | 31.8 <i>1.250</i>                      | 9.7 <i>0.380</i>                        | N/A N/A                                      | 12.7 <i>0.500</i>                          | 37.8 <i>1.486</i>                    |
| MV-381064-10-8A    | 10,000           | 1             | 38.1 <i>1.500</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 44.5 <i>1.750</i>                    |
| * MV-381127-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                      | 12.7 <i>0.500</i>                       | 44.2 <i>1.738</i>                            | 15.9 <i>0.625</i>                          | 88.2 <i>3.472</i>                    |
| MV-381191-5-8A     | 5,000            | 2             | 38.1 <i>1.500</i>                      | 19.1 <i>0.750</i>                       | 43.2 <i>1.700</i>                            | 22.2 <i>0.875</i>                          | 87.6 <i>3.450</i>                    |
| * MV-381381-2.5-8A | 2,500            | 2             | 38.1 <i>1.500</i>                      | 38.1 <i>1.500</i>                       | 44.5 <i>1.750</i>                            | 40.8 <i>1.607</i>                          | 88.9 <i>3.500</i>                    |
| * MV-381635-5-8A   | 5,000            | 2             | 38.1 <i>1.500</i>                      | 63.5 <i>2.500</i>                       | 40.6 <i>1.600</i>                            | 66.7 <i>2.625</i>                          | 84.7 <i>3.336</i>                    |
| * MV-406254-1.5-8A | 1,500            | 2             | 40.6 <i>1.600</i>                      | 25.4 <i>1.000</i>                       | 55.9 <i>2.200</i>                            | 38.1 <i>1.500</i>                          | 102.9 <i>4.050</i>                   |
| MV-445064-10-8A    | 10,000           | 1             | 44.5 <i>1.750</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 50.4 <i>1.986</i>                    |
| MV-445102-5-8A     | 5,000            | 1             | 44.5 <i>1.750</i>                      | 10.2 <i>0.400</i>                       | N/A N/A                                      | 12.7 <i>0.500</i>                          | 50.4 <i>1.986</i>                    |
| MV-445445-2-8A     | 2,000            | 1             | 44.5 <i>1.750</i>                      | 44.5 <i>1.750</i>                       | N/A N/A                                      | 47.6 <i>1.875</i>                          | 50.4 <i>1.986</i>                    |
| MV-478175-5-8A     | 5,000            | 1             | 47.8 <i>1.880</i>                      | 17.5 <i>0.690</i>                       | N/A N/A                                      | 24.4 <i>0.962</i>                          | 66.0 <i>2.600</i>                    |
| MV-508064-10-8A    | 10,000           | 1             | 50.8 <i>2.000</i>                      | 6.4 <i>0.250</i>                        | N/A N/A                                      | 9.5 <i>0.375</i>                           | 56.9 <i>2.240</i>                    |
| MV-508095-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 9.5 <i>0.375</i>                        | N/A N/A                                      | 12.7 <i>0.500</i>                          | 57.2 <i>2.250</i>                    |
| MV-508127-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 12.7 <i>0.500</i>                       | N/A N/A                                      | 15.9 <i>0.625</i>                          | 56.9 <i>2.240</i>                    |
| MV-508254-5-8A     | 5,000            | 1             | 50.8 <i>2.000</i>                      | 25.4 <i>1.000</i>                       | N/A N/A                                      | 28.6 <i>1.125</i>                          | 57.2 <i>2.250</i>                    |
| MV-508318-2.5-8A   | 2,500            | 1             | 50.8 <i>2.000</i>                      | 31.8 <i>1.250</i>                       | N/A N/A                                      | 34.9 <i>1.375</i>                          | 56.9 <i>2.240</i>                    |
| MV-508508-3-8A     | 3,000            | 1             | 50.8 <i>2.000</i>                      | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.6 <i>2.150</i>                          | 54.0 <i>2.130</i>                    |
| MV-523841-1.5-8A   | 1,500            | 1             | 52.3 <i>2.060</i>                      | 84.1 <i>3.310</i>                       | N/A N/A                                      | 88.9 <i>3.500</i>                          | 58.2 <i>2.290</i>                    |
| MV-610419-2.5-8A   | 2,500            | 1             | 61.0 <i>2.400</i>                      | 41.9 <i>1.650</i>                       | N/A N/A                                      | 45.5 <i>1.792</i>                          | 67.3 <i>2.650</i>                    |
| MV-699191-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                      | 19.1 <i>0.750</i>                       | N/A N/A                                      | 23.3 <i>0.917</i>                          | 76.2 <i>3.000</i>                    |
| MV-699254-5-8A     | 5,000            | 1             | 69.9 <i>2.750</i>                      | 25.4 <i>1.000</i>                       | N/A N/A                                      | 28.6 <i>1.125</i>                          | 76.2 <i>3.000</i>                    |
| MV-762381-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                      | 38.1 <i>1.500</i>                       | N/A N/A                                      | 41.3 <i>1.625</i>                          | 82.3 <i>3.240</i>                    |
| MV-762508-2.5-8A   | 2,500            | 1             | 76.2 <i>3.000</i>                      | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.0 <i>2.125</i>                          | 82.6 <i>3.240</i>                    |
| MV-762127-1-8A     | 1,000            | 1             | 76.2 <i>3.000</i>                      | 127.0 <i>5.000</i>                      | N/A N/A                                      | 129.5 <i>5.100</i>                         | 79.4 <i>3.130</i>                    |
| MV-101508-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                     | 50.8 <i>2.000</i>                       | N/A N/A                                      | 54.6 <i>2.150</i>                          | 104.1 <i>4.100</i>                   |
| MV-101635-2.5-8A   | 2,500            | 1             | 101.6 <i>4.000</i>                     | 63.5 <i>2.500</i>                       | N/A N/A                                      | 66.7 <i>2.625</i>                          | 107.7 <i>4.240</i>                   |
| MV-101762-1.8-8A   | 1,800            | 1             | 101.6 <i>4.000</i>                     | 76.2 <i>3.000</i>                       | N/A N/A                                      | 79.4 <i>3.125</i>                          | 104.1 <i>4.100</i>                   |
| MV-101101-1.3-8A   | 1,300            | 1             | 101.6 <i>4.000</i>                     | 101.6 <i>4.000</i>                      | N/A N/A                                      | 104.8 <i>4.125</i>                         | 104.1 <i>4.100</i>                   |
| MV-101165-0.85-8A  | 850              | 1             | 101.6 <i>4.000</i>                     | 165.1 <i>6.500</i>                      | N/A N/A                                      | 168.3 <i>6.680</i>                         | 104.9 <i>4.130</i>                   |

\* NOTE: Standard Format Not Compatible with T200 Printers

## TN Tamper proof destructible polyethylene labels

Tyco Electronics TN is a thermal transfer printable, tamper proof destructible polyethylene label with a permanent acrylic adhesive, designed to fracture upon removal after 72 hours. It is ideal for serial number labels and calibration information labeling, or other applications that require a tamper proof label. For reliable print performance and durability, use with Tyco Electronics 1330-0607 ribbon.



### Features and benefits

- Thermal transfer printable
- Ideal for security applications
- Several die-cut sizes available



#### Specifications/Approvals

Industry UL MH17292 Group PGJ12

**Adhesive** Permanent rubber-based

**Service temperature** -40°C to +80°C -40°F to +176°F


**Recommended printer** T300 Series printers

**Recommended ribbon** 1330-0607-10\*


*\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.*

### Part numbering system

TN - 191064-10-9



### Ordering information



#### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| TN-040040-25-9     | 25,000           | 20            | 4.0 0.157                    | 4.0 0.157                     | 4.0 0.157                          | 7.2 0.281                        | 86.0 3.380                 |
| TN-064064-25-9     | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| * TN-080080-10-9   | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| TN-089047-10-9     | 10,000           | 5             | 8.9 0.350                    | 4.7 0.185                     | 11.4 0.450                         | 7.9 0.313                        | 60.6 2.386                 |
| TN-095080-25-9     | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.480                         | 12.7 0.500                       | 64.3 2.531                 |
| TN-095095-10-9     | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |

**\* NOTE: Standard Format Not Compatible with T200 Printers**

## TN Tamper proof destructible polyethylene labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| TN-127111-10-9     | 10,000           | 5             | 12.7 0.500                   | 11.1 0.437                    | 16.8 0.662                         | 14.3 0.563                       | 86.0 3.380                 |
| TN-127127-10-9     | 10,000           | 5             | 12.7 0.500                   | 12.7 0.500                    | 15.9 0.625                         | 15.9 0.625                       | 82.6 3.250                 |
| * TN-165051-25-9   | 25,000           | 4             | 16.5 0.650                   | 5.1 0.200                     | 17.8 0.700                         | 8.3 0.325                        | 75.8 2.990                 |
| TN-165102-10-9     | 10,000           | 5             | 16.5 0.650                   | 10.2 0.400                    | 19.1 0.750                         | 13.8 0.545                       | 99.1 3.900                 |
| TN-171171-10-9     | 10,000           | 5             | 17.1 0.674                   | 17.1 0.674                    | 19.7 0.774                         | 20.3 0.800                       | 101.8 4.006                |
| * TN-178095-10-9   | 10,000           | 4             | 17.8 0.700                   | 9.5 0.375                     | 19.1 0.750                         | 12.7 0.500                       | 80.9 3.190                 |
| * TN-191064-10-9   | 10,000           | 4             | 19.1 0.750                   | 6.4 0.250                     | 21.6 0.850                         | 9.5 0.375                        | 89.9 3.540                 |
| TN-191114-15-9     | 15,000           | 3             | 19.1 0.750                   | 11.4 0.450                    | 22.2 0.875                         | 14.7 0.579                       | 69.5 2.736                 |
| * TN-203127-10-9   | 10,000           | 4             | 20.3 0.800                   | 12.7 0.500                    | 22.9 0.900                         | 15.9 0.625                       | 94.6 3.730                 |
| TN-229064-10-9     | 10,000           | 3             | 22.9 0.900                   | 6.4 0.250                     | 28.6 1.125                         | 9.5 0.375                        | 86.0 3.390                 |
| TN-254045-10-9     | 10,000           | 3             | 25.4 1.000                   | 4.6 0.180                     | 31.8 1.250                         | 8.5 0.333                        | 95.3 3.750                 |
| TN-254064-10-9     | 10,000           | 3             | 25.4 1.000                   | 6.4 0.250                     | 27.9 1.100                         | 9.5 0.375                        | 87.3 3.436                 |
| TN-254097-10-9     | 10,000           | 3             | 25.4 1.000                   | 9.7 0.380                     | 27.9 1.100                         | 12.7 0.500                       | 87.4 3.440                 |
| TN-254127-10-9     | 10,000           | 3             | 25.4 1.000                   | 12.7 0.500                    | 27.9 1.100                         | 16.9 0.666                       | 87.4 3.440                 |
| TN-254254-10-9     | 10,000           | 3             | 25.4 1.000                   | 25.4 1.000                    | 27.9 1.100                         | 28.6 1.125                       | 87.4 3.440                 |
| * TN-305047-10-9   | 10,000           | 2             | 30.5 1.200                   | 4.7 0.185                     | 33.0 1.300                         | 7.8 0.306                        | 69.5 2.736                 |
| TN-318064-10-9     | 10,000           | 1             | 31.8 1.250                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 37.9 1.490                 |
| TN-318097-10-9     | 10,000           | 1             | 31.8 1.250                   | 9.7 0.380                     | N/A N/A                            | 12.7 0.500                       | 37.8 1.488                 |
| TN-381064-10-9     | 10,000           | 1             | 38.1 1.500                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 44.5 1.750                 |
| * TN-381127-5-9    | 5,000            | 2             | 38.1 1.500                   | 12.7 0.500                    | 44.2 1.738                         | 15.9 0.625                       | 88.2 3.472                 |
| TN-381191-5-9      | 5,000            | 2             | 38.1 1.500                   | 19.1 0.750                    | 43.2 1.700                         | 22.2 0.875                       | 87.6 3.450                 |
| * TN-381381-2.5-9  | 2,500            | 2             | 38.1 1.500                   | 38.1 1.500                    | 44.5 1.750                         | 40.8 1.607                       | 88.9 3.500                 |
| * TN-381635-5-9    | 5,000            | 2             | 38.1 1.500                   | 63.5 2.500                    | 40.6 1.600                         | 66.7 2.625                       | 84.7 3.336                 |
| * TN-406254-1.5-9  | 1,500            | 2             | 40.6 1.600                   | 25.4 1.000                    | 55.9 2.200                         | 38.1 1.500                       | 102.9 4.050                |
| TN-445064-10-9     | 10,000           | 1             | 44.5 1.750                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 50.4 1.986                 |
| TN-445102-5-9      | 5,000            | 1             | 44.5 1.750                   | 10.2 0.400                    | N/A N/A                            | 12.7 0.500                       | 50.4 1.986                 |
| TN-445445-2-9      | 2,000            | 1             | 44.5 1.750                   | 44.5 1.750                    | N/A N/A                            | 47.6 1.875                       | 50.4 1.986                 |
| TN-478175-5-9      | 5,000            | 1             | 47.8 1.880                   | 17.5 0.690                    | N/A N/A                            | 24.4 0.962                       | 66.0 2.600                 |
| TN-508064-10-9     | 10,000           | 1             | 50.8 2.000                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 56.9 2.240                 |
| TN-508095-5-9      | 5,000            | 1             | 50.8 2.000                   | 9.5 0.375                     | N/A N/A                            | 12.7 0.500                       | 57.2 2.250                 |
| TN-508127-5-9      | 5,000            | 1             | 50.8 2.000                   | 12.7 0.500                    | N/A N/A                            | 15.9 0.625                       | 56.9 2.240                 |
| TN-508254-5-9      | 5,000            | 1             | 50.8 2.000                   | 25.4 1.000                    | N/A N/A                            | 28.6 1.125                       | 57.2 2.250                 |
| TN-508318-2.5-9    | 2,500            | 1             | 50.8 2.000                   | 31.8 1.250                    | N/A N/A                            | 34.9 1.375                       | 56.9 2.240                 |
| TN-508508-3-9      | 3,000            | 1             | 50.8 2.000                   | 50.8 2.000                    | N/A N/A                            | 54.6 2.150                       | 54.0 2.130                 |
| TN-523841-1.5-9    | 1,500            | 1             | 52.3 2.060                   | 84.1 3.310                    | N/A N/A                            | 88.9 3.500                       | 58.2 2.290                 |
| TN-610419-2.5-9    | 2,500            | 1             | 61.0 2.400                   | 41.9 1.650                    | N/A N/A                            | 45.5 1.792                       | 67.3 2.650                 |
| TN-699191-5-9      | 5,000            | 1             | 69.9 2.750                   | 19.1 0.750                    | N/A N/A                            | 23.3 0.917                       | 76.2 3.000                 |
| TN-699254-5-9      | 5,000            | 1             | 69.9 2.750                   | 25.4 1.000                    | N/A N/A                            | 28.6 1.125                       | 76.2 3.000                 |
| TN-762381-2.5-9    | 2,500            | 1             | 76.2 3.000                   | 38.1 1.500                    | N/A N/A                            | 41.3 1.625                       | 82.3 3.240                 |
| TN-762508-2.5-9    | 2,500            | 1             | 76.2 3.000                   | 50.8 2.000                    | N/A N/A                            | 54.0 2.125                       | 82.6 3.240                 |
| TN-762127-1-9      | 1,000            | 1             | 76.2 3.000                   | 127.0 5.000                   | N/A N/A                            | 129.5 5.100                      | 79.4 3.130                 |
| TN-101508-2.5-9    | 2,500            | 1             | 101.6 4.000                  | 50.8 2.000                    | N/A N/A                            | 54.6 2.150                       | 104.1 4.100                |
| TN-101635-2.5-9    | 2,500            | 1             | 101.6 4.000                  | 63.5 2.500                    | N/A N/A                            | 66.7 2.625                       | 107.7 4.240                |
| TN-101762-1.8-9    | 1,800            | 1             | 101.6 4.000                  | 76.2 3.000                    | N/A N/A                            | 79.4 3.125                       | 104.1 4.100                |
| TN-101101-1.3-9    | 1,300            | 1             | 101.6 4.000                  | 101.6 4.000                   | N/A N/A                            | 104.8 4.125                      | 104.1 4.100                |
| TN-101165-0.85-9   | 850              | 1             | 101.6 4.000                  | 165.1 6.500                   | N/A N/A                            | 168.3 6.680                      | 104.9 4.130                |

\* NOTE: Standard Format Not Compatible with T200 Printers

## WV White vinyl labels

Tyco Electronics WV is a thermal transfer printable, flexible white vinyl film with a permanent acrylic adhesive. It offers excellent conformability to round, irregular or flexible surfaces, and is ideal for wire and cable identification, including flat ribbon cables that are subject to repeated bending. WV is resistant to oil, mild solvents, water and outdoor exposure. For reliable print performance and durability use with Tyco Electronics 1330-0607 ribbon.


### Features and benefits

- Thermal transfer printable
- High tack adhesive bonds to most substrates including painted metal and low surface energy plastics such as polyethylene




|                                                                                                                                         |                                     |
|-----------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------|
| <b>Specifications</b>                                                                                                                   | TTDS-090                            |
| <b>Adhesive</b>                                                                                                                         | Permanent acrylic high initial tack |
| <b>Service temperature</b>                                                                                                              | -40°C to +80°C    -40°F to +176°F   |
| <b>Recommended printer</b>                                                                                                              | T300 Series printers                |
| <b>Recommended ribbon</b>                                                                                                               | 1330-0607-10*                       |
| *Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information. |                                     |

### Part numbering system



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm    inches | Label height (B)<br>mm    inches | Horizontal repeat (C)<br>mm    inches | Vertical repeat (D)<br>mm    inches | Web width (E)<br>mm    inches |
|--------------------|------------------|---------------|---------------------------------|----------------------------------|---------------------------------------|-------------------------------------|-------------------------------|
| WV-040040-25-9     | 25,000           | 20            | 4.0    0.157                    | 4.0    0.157                     | 4.0    0.157                          | 7.2    0.281                        | 86.0    3.380                 |
| * WV-080080-10-9   | 10,000           | 8             | 8.0    0.315                    | 8.0    0.315                     | 9.9    0.390                          | 13.3    0.525                       | 83.3    3.280                 |
| WV-089047-10-9     | 10,000           | 5             | 8.9    0.350                    | 4.7    0.185                     | 11.4    0.450                         | 7.9    0.313                        | 60.6    2.386                 |
| WV-095080-25-9     | 25,000           | 5             | 9.5    0.375                    | 8.0    0.315                     | 12.2    0.480                         | 12.7    0.500                       | 64.3    2.531                 |
| WV-095095-10-9     | 10,000           | 7             | 9.5    0.375                    | 9.5    0.375                     | 11.1    0.437                         | 12.7    0.500                       | 82.1    3.230                 |
| WV-127111-10-9     | 10,000           | 5             | 12.7    0.500                   | 11.1    0.437                    | 16.8    0.662                         | 14.3    0.563                       | 86.0    3.380                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

## WV White vinyl labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| WW-127127-10-9     | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| * WW-165051-25-9   | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| WW-165102-10-9     | 10,000           | 5             | 16.5 <i>0.650</i>                   | 10.2 <i>0.400</i>                    | 19.1 <i>0.750</i>                         | 13.8 <i>0.545</i>                       | 99.1 <i>3.900</i>                 |
| WW-171171-10-9     | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| * WW-178095-10-9   | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| * WW-191064-10-9   | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| WW-191114-15-9     | 15,000           | 3             | 19.1 <i>0.750</i>                   | 11.4 <i>0.450</i>                    | 22.2 <i>0.875</i>                         | 14.7 <i>0.579</i>                       | 69.5 <i>2.736</i>                 |
| WW-191762-5-9      | 5,000            | 3             | 19.1 <i>0.750</i>                   | 76.2 <i>3.000</i>                    | 21.6 <i>0.850</i>                         | 88.9 <i>3.500</i>                       | 68.2 <i>2.686</i>                 |
| * WW-203127-10-9   | 10,000           | 4             | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 22.9 <i>0.900</i>                         | 15.9 <i>0.625</i>                       | 94.6 <i>3.730</i>                 |
| WW-229064-10-9     | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| * WW-250381-10-9   | 10,000           | 4             | 24.9 <i>0.980</i>                   | 38.1 <i>1.500</i>                    | 27.4 <i>1.080</i>                         | 47.6 <i>1.875</i>                       | 113.5 <i>4.470</i>                |
| WW-254045-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| WW-254064-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| WW-254097-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| WW-254127-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| WW-254254-10-9     | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| * WW-305047-10-9   | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| WW-318064-10-9     | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| WW-318097-10-9     | 10,000           | 1             | 31.8 <i>1.250</i>                   | 9.7 <i>0.380</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 37.8 <i>1.488</i>                 |
| WW-381064-10-9     | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| * WW-381127-5-9    | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| WW-381191-5-9      | 5,000            | 2             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 22.2 <i>0.875</i>                       | 87.6 <i>3.450</i>                 |
| * WW-381381-2.5-9  | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.607</i>                       | 88.9 <i>3.500</i>                 |
| WW-445064-10-9     | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| WW-445102-5-9      | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.986</i>                 |
| WW-445445-2-9      | 2,000            | 1             | 44.5 <i>1.750</i>                   | 44.5 <i>1.750</i>                    | N/A    N/A                                | 47.6 <i>1.875</i>                       | 50.4 <i>1.986</i>                 |
| WW-478175-5-9      | 5,000            | 1             | 47.8 <i>1.880</i>                   | 17.5 <i>0.690</i>                    | N/A    N/A                                | 24.4 <i>0.962</i>                       | 66.0 <i>2.600</i>                 |
| WW-508064-10-9     | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| WW-508095-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| WW-508127-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |
| WW-508254-5-9      | 5,000            | 1             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 57.2 <i>2.250</i>                 |
| WW-508318-2.5-9    | 2,500            | 1             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | N/A    N/A                                | 34.9 <i>1.375</i>                       | 56.9 <i>2.240</i>                 |
| WW-508508-3-9      | 3,000            | 1             | 50.8 <i>2.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 54.0 <i>2.130</i>                 |
| WW-523841-1.5-9    | 1,500            | 1             | 52.3 <i>2.060</i>                   | 84.1 <i>3.310</i>                    | N/A    N/A                                | 88.9 <i>3.500</i>                       | 58.2 <i>2.290</i>                 |
| WW-610419-2.5-9    | 2,500            | 1             | 61.0 <i>2.400</i>                   | 41.9 <i>1.650</i>                    | N/A    N/A                                | 45.5 <i>1.792</i>                       | 67.3 <i>2.650</i>                 |
| WW-699191-5-9      | 5,000            | 1             | 69.9 <i>2.750</i>                   | 19.1 <i>0.750</i>                    | N/A    N/A                                | 23.3 <i>0.917</i>                       | 76.2 <i>3.000</i>                 |
| WW-699254-5-9      | 5,000            | 1             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 76.2 <i>3.000</i>                 |
| WW-762381-2.5-9    | 2,500            | 1             | 76.2 <i>3.000</i>                   | 38.1 <i>1.500</i>                    | N/A    N/A                                | 41.3 <i>1.625</i>                       | 82.3 <i>3.240</i>                 |
| WW-762508-2.5-9    | 2,500            | 1             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.0 <i>2.125</i>                       | 82.6 <i>3.240</i>                 |
| WW-762127-1-9      | 1,000            | 1             | 76.2 <i>3.000</i>                   | 127.0 <i>5.000</i>                   | N/A    N/A                                | 129.5 <i>5.100</i>                      | 79.4 <i>3.130</i>                 |
| WW-101508-2.5-9    | 2,500            | 1             | 101.6 <i>4.000</i>                  | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 104.1 <i>4.100</i>                |
| WW-101635-2.5-9    | 2,500            | 1             | 101.6 <i>4.000</i>                  | 63.5 <i>2.500</i>                    | N/A    N/A                                | 66.7 <i>2.625</i>                       | 107.7 <i>4.240</i>                |
| WW-101762-1.8-9    | 1,800            | 1             | 101.6 <i>4.000</i>                  | 76.2 <i>3.000</i>                    | N/A    N/A                                | 79.4 <i>3.125</i>                       | 104.1 <i>4.100</i>                |
| WW-101101-1.3-9    | 1,300            | 1             | 101.6 <i>4.000</i>                  | 101.6 <i>4.000</i>                   | N/A    N/A                                | 104.8 <i>4.125</i>                      | 104.1 <i>4.100</i>                |
| WW-101165-0.85-9   | 850              | 1             | 101.6 <i>4.000</i>                  | 165.1 <i>6.500</i>                   | N/A    N/A                                | 168.3 <i>6.680</i>                      | 104.9 <i>4.130</i>                |

\* NOTE: Standard Format Not Compatible with T200 Printers



## NC Nylon cloth labels

Tyco Electronics NC is a thermal transfer printable, flexible nylon cloth with a permanent acrylic adhesive, designed for application to irregular surfaces where conformability is required. It is ideal for wire marking and other round or flexible surfaces such as cables and tubing. NC is not recommended for outdoor use or immersion in liquid. For reliable print performance and durability, use with Tyco Electronics 1330-0607 ribbon.


### Features and benefits

- Thermal transfer printable
- Surface coating applied to enhance ink receptivity
- Flexible material conforms to curved surfaces
- Several die-cut sizes available




|                            |                                    |
|----------------------------|------------------------------------|
| <b>Specifications</b>      | TTDS-051                           |
| <b>Adhesive</b>            | Permanent acrylic                  |
| <b>Service temperature</b> | -40°C to +140°C    -40°F to +284°F |
| <b>Recommended printer</b> | T300 Series printers               |
| <b>Recommended ribbon</b>  | 1330-0606-10*                      |

*\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.*




### Part numbering system





## NC Nylon cloth labels

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| NC-064064-25-9     | 25,000           | 12            | 6.4 0.250                    | 6.4 0.250                     | 6.4 0.250                          | 9.5 0.375                        | 82.2 3.240                 |
| * NC-080080-10-9   | 10,000           | 8             | 8.0 0.315                    | 8.0 0.315                     | 9.9 0.390                          | 13.3 0.525                       | 83.3 3.280                 |
| NC-095080-25-9     | 25,000           | 5             | 9.5 0.375                    | 8.0 0.315                     | 12.2 0.480                         | 12.7 0.500                       | 64.3 2.531                 |
| NC-095095-10-9     | 10,000           | 7             | 9.5 0.375                    | 9.5 0.375                     | 11.1 0.437                         | 12.7 0.500                       | 82.1 3.230                 |
| NC-127111-10-9     | 10,000           | 5             | 12.7 0.500                   | 11.1 0.437                    | 16.8 0.662                         | 14.3 0.563                       | 86.0 3.380                 |
| NC-127127-10-9     | 10,000           | 5             | 12.7 0.500                   | 12.7 0.500                    | 15.9 0.625                         | 15.9 0.625                       | 82.6 3.250                 |
| * NC-165051-25-9   | 25,000           | 4             | 16.5 0.650                   | 5.1 0.200                     | 17.8 0.700                         | 8.3 0.325                        | 75.8 2.990                 |
| * NC-178095-10-9   | 10,000           | 4             | 17.8 0.700                   | 9.5 0.375                     | 19.1 0.750                         | 12.7 0.500                       | 80.9 3.190                 |
| * NC-191064-10-9   | 10,000           | 4             | 19.1 0.750                   | 6.4 0.250                     | 21.6 0.850                         | 9.5 0.375                        | 89.9 3.540                 |
| NC-229064-10-9     | 10,000           | 3             | 22.9 0.900                   | 6.4 0.250                     | 28.6 1.125                         | 9.5 0.375                        | 86.0 3.390                 |
| NC-254064-10-9     | 10,000           | 3             | 25.4 1.000                   | 6.4 0.250                     | 27.9 1.100                         | 9.5 0.375                        | 87.3 3.436                 |
| NC-254097-10-9     | 10,000           | 3             | 25.4 1.000                   | 9.7 0.380                     | 27.9 1.100                         | 12.7 0.500                       | 87.4 3.440                 |
| NC-254127-10-9     | 10,000           | 3             | 25.4 1.000                   | 12.7 0.500                    | 27.9 1.100                         | 16.9 0.666                       | 87.4 3.440                 |
| NC-318064-10-9     | 10,000           | 1             | 31.8 1.250                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 37.9 1.490                 |
| NC-381064-10-S1-9  | 10,000           | 1**           | 38.1 1.500                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 44.5 1.750                 |
| NC-381064-10-9     | 10,000           | 1             | 38.1 1.500                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 44.5 1.750                 |
| * NC-381127-5-9    | 5,000            | 2             | 38.1 1.500                   | 12.7 0.500                    | 44.2 1.738                         | 15.9 0.625                       | 88.2 3.472                 |
| NC-445064-10-9     | 10,000           | 1             | 44.5 1.750                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 50.4 1.986                 |
| NC-445102-5-9      | 5,000            | 1             | 44.5 1.750                   | 10.2 0.400                    | N/A N/A                            | 12.7 0.500                       | 50.4 1.986                 |
| NC-445445-2-9      | 2,000            | 1             | 44.5 1.750                   | 44.5 1.750                    | N/A N/A                            | 47.6 1.875                       | 50.4 1.986                 |
| NC-508064-10-9     | 10,000           | 1             | 50.8 2.000                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 56.9 2.240                 |
| NC-508095-5-9      | 5,000            | 1             | 50.8 2.000                   | 9.5 0.375                     | N/A N/A                            | 12.7 0.500                       | 57.2 2.250                 |
| NC-508127-5-9      | 5,000            | 1             | 50.8 2.000                   | 12.7 0.500                    | N/A N/A                            | 15.9 0.625                       | 56.9 2.240                 |
| NC-523841-1.5-9    | 1,500            | 1             | 52.3 2.060                   | 84.1 3.310                    | N/A N/A                            | 88.9 3.500                       | 58.2 2.290                 |

\* NOTE: Standard Format Not Compatible with T200 Printers


\*\* Perforated

## NC Nylon cloth wire markers

NC is a thermal transfer printable, flexible nylon cloth with a permanent acrylic adhesive. These formats are designed specifically for wrap around wire and cable marking applications. For reliable print performance and durability, use with Tyco Electronics 1330-0606 ribbon.

### Features and benefits

- Thermal transfer printable
- Flexible cloth material conforms well for wrap around wire marking



|                            |                                 |
|----------------------------|---------------------------------|
| <b>Specifications</b>      | TTDS-051                        |
| <b>Adhesive</b>            | Permanent acrylic               |
| <b>Service temperature</b> | -40°C to +140°C -40°F to +284°F |
| <b>Recommended printer</b> | T300 Series printers            |
| <b>Recommended ribbon</b>  | 1330-0606-10*                   |

*\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.*


### Part numbering system

NC-07619110-9



## NC Nylon cloth wire markers

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| NC-076191-10-9     | 10,000           | 8             | 7.6 0.300                    | 19.1 0.750                    | 7.6 0.300                          | 22.2 0.875                       | 67.3 2.650                 |
| * NC-127191-10-9   | 10,000           | 4             | 12.7 0.500                   | 19.1 0.750                    | 15.2 0.600                         | 22.2 0.875                       | 63.5 2.500                 |
| NC-127365-10-9     | 10,000           | 6             | 12.7 0.500                   | 36.5 1.437                    | 16.8 0.662                         | 42.2 1.661                       | 102.8 4.046                |
| * NC-191254-10-9   | 10,000           | 4             | 19.1 0.750                   | 25.4 1.000                    | 22.2 0.875                         | 31.8 1.250                       | 91.7 3.611                 |
| NC-191762-5-9      | 5,000            | 3             | 19.1 0.750                   | 76.2 3.000                    | 21.6 0.850                         | 88.9 3.500                       | 68.2 2.686                 |
| * NC-250381-10-9   | 10,000           | 4             | 24.9 0.980                   | 38.1 1.500                    | 27.4 1.080                         | 47.6 1.875                       | 113.5 4.470                |
| NC-254254-10-9     | 10,000           | 3             | 25.4 1.000                   | 25.4 1.000                    | 27.9 1.100                         | 28.6 1.125                       | 87.4 3.440                 |
| * NC-381381-2.5-9  | 2,500            | 2             | 38.1 1.500                   | 38.1 1.500                    | 44.5 1.750                         | 40.8 1.607                       | 88.9 3.500                 |
| * NC-381635-5-9    | 5,000            | 2             | 38.1 1.500                   | 63.5 2.500                    | 40.6 1.600                         | 66.7 2.625                       | 84.7 3.336                 |
| NC-508508-3-9      | 3,000            | 1             | 50.8 2.000                   | 50.8 2.000                    | N/A N/A                            | 54.6 2.150                       | 54.0 2.130                 |

\* NOTE: Standard Format Not Compatible with T200 Printers \*

## NC Nylon cloth terminal markers

NC is a thermal transfer printable, flexible nylon cloth with a permanent acrylic adhesive. These continuous strip formats are designed specifically for terminal block marking applications. For reliable print performance and durability, use with Tyco Electronics 1330-0606 ribbon.

### Features and benefits


- Thermal transfer printable
- Continuous format is universal for any length terminal strip marker



|                                                                                                                                         |                                   |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|
| <b>Specifications</b>                                                                                                                   | TTDS-051                          |
| <b>Adhesive</b>                                                                                                                         | Permanent acrylic                 |
| <b>Service temperature</b>                                                                                                              | -40°C to +140°C   -40°F to +284°F |
| <b>Recommended printer</b>                                                                                                              | T300 Series printers              |
| <b>Recommended ribbon</b>                                                                                                               | 1330-0606-10*                     |
| *Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information. |                                   |

## NC Nylon cloth terminal markers

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A) |        | Label height (B) |      | Horizontal repeat (C) |        | Vertical repeat (D) |        | Web width (E) |        |
|--------------------|------------------|---------------|-----------------|--------|------------------|------|-----------------------|--------|---------------------|--------|---------------|--------|
|                    |                  |               | mm              | inches | mm               | feet | mm                    | inches | mm                  | inches | mm            | inches |
| NC155WE-100S4      | 500 FEET         | 5             | 7.9             | 0.312  | 30.5             | 100  | 7.9                   | 0.312  | N/A                 | N/A    | 45.7          | 1.800  |
| NC150WE-100S3      | 400 FEET         | 4             | 9.5             | 0.375  | 30.5             | 100  | 9.5                   | 0.375  | N/A                 | N/A    | 44.5          | 1.750  |

## Kapton® labels

Tyco Electronics polyimide (Kapton®) labels are all ideal for high temperature labeling requirements such as printed circuit boards. They are suitable for direct wave (bottom side) and IR reflow (top side) PCB applications. Tyco Electronics Kapton® labels are designed to withstand the fluxes, cleaning solvents and molten solder encountered in the manufacture of printed circuit boards. They offer excellent contrast for bar code applications. Tyco Electronics Kapton® labels are suitable for the harshest high temperature applications. For reliable print performance and durability, use with Tyco Electronics's 1330-0619 ribbon.

### Features and benefits

- UL Listed: T1K and T2K
- Thermal transfer printable
- High temperature permanent acrylic adhesive

### T1K

- Gloss white topcoat
- Withstands surface mount board processes on either the top or bottom side of the board
- Low profile 1 mil film offers polyimide thermal performance at competitive cost
- Ideal for manual apply applications

### T2K


- Gloss white topcoat
- Withstands surface mount board processes on either the top or bottom side of the board
- Ideal for auto apply applications

### KTT

- Matte tan topcoat
- Withstands surface mount board processes on either the top or bottom side of the board
- Product approved for aerospace/defense applications.
- Low outgassing

### TSK

- High opacity gloss white topcoat
- Withstands surface mount board processes on either the top or bottom side of the board
- Deemed to be a static safe product in accordance with EIA 625, EIA 541. Test methods employed were in accordance with EOS/ESD S11.11
- Ideal for auto apply applications



### Specifications/Approvals

|                  |    |     |                     |
|------------------|----|-----|---------------------|
| Tyco Electronics |    | T1K | TTDS-034            |
|                  |    | T2K | TTDS-035            |
|                  |    | TSK | TTDS-085            |
| Industry         | UL | T1K | MH17292 Group PGJ12 |
|                  |    | T2K | MH17292 Group PGJ12 |

### Adhesive

Permanent acrylic

### Service temperature

|                                       |                 |                 |
|---------------------------------------|-----------------|-----------------|
| T1K <sup>1</sup> , T2K <sup>2</sup> , | -40°C to +260°C | -40°F to +500°F |
| TSK <sup>2</sup> , KTT <sup>2</sup>   |                 |                 |

<sup>1</sup> Flash exposure to +472°C (+800°F)

<sup>2</sup> Flash exposure to +538°C (+1000°F)

### Recommended printer


|                    |        |
|--------------------|--------|
| T1K, T2K, TSK, T2Y | T312S* |
| KTT                |        |

### Recommended ribbon

1330-0619-10\*  
\* Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.


### Part numbering system

T1K-044033-10-9



## T1K White Kapton® labels

### Ordering information



### Product dimensions


| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| T1K-044033-10-9    | 10,000           | 20            | 4.4 <i>0.170</i>                    | 3.3 <i>0.130</i>                     | 4.4 <i>0.170</i>                          | 9.5 <i>0.375</i>                        | 92.4 <i>3.636</i>                 |
| T1K-064064-25-9    | 25,000           | 12            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4 <i>0.250</i>                          | 9.5 <i>0.375</i>                        | 82.2 <i>3.240</i>                 |
| *T1K-080080-10-9   | 10,000           | 8             | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 9.9 <i>0.390</i>                          | 13.3 <i>0.525</i>                       | 83.3 <i>3.280</i>                 |
| T1K-095080-25-9    | 25,000           | 5             | 9.5 <i>0.375</i>                    | 8.0 <i>0.315</i>                     | 12.2 <i>0.480</i>                         | 12.7 <i>0.500</i>                       | 64.3 <i>2.531</i>                 |
| T1K-095095-10-9    | 10,000           | 7             | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 11.1 <i>0.437</i>                         | 12.7 <i>0.500</i>                       | 82.1 <i>3.230</i>                 |
| T1K-127032-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 3.2 <i>0.125</i>                     | 19.1 <i>0.750</i>                         | 3.2 <i>0.250</i>                        | 94.9 <i>3.736</i>                 |
| T1K-127111-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8 <i>0.662</i>                         | 14.3 <i>0.563</i>                       | 86.0 <i>3.380</i>                 |
| T1K-127127-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| *T1K-165051-25-9   | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| T1K-171171-10-9    | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| *T1K-178095-10-9   | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| *T1K-191064-10-9   | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| T1K-229064-10-9    | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| T1K-254045-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| T1K-254064-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| T1K-254097-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| T1K-254127-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| T1K-254254-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| *T1K-305047-10-9   | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| T1K-318064-10-9    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| T1K-381020-10-9    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 2.0 <i>0.080</i>                     | N/A    N/A                                | 10.7 <i>0.423</i>                       | 44.1 <i>1.740</i>                 |
| *T1K-381127-5-9    | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| T1K-381381-2-5-9   | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.607</i>                       | 88.9 <i>3.500</i>                 |
| T1K-445064-10-9    | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| T1K-445102-5-9     | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.386</i>                 |
| T1K-508064-10-9    | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| T1K-508095-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| T1K-508127-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |

\* NOTE: Kapton®/polyimide labels not compatible with T200 Printers



## T2K White Kapton® labels

### Ordering information




### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| T2K-044033-10-9    | 10,000           | 20            | 4.4 <i>0.170</i>                    | 3.3 <i>0.130</i>                     | 4.4 <i>0.170</i>                          | 9.5 <i>0.375</i>                        | 92.4 <i>3.636</i>                 |
| T2K-064064-25-9    | 25,000           | 12            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4 <i>0.250</i>                          | 9.5 <i>0.375</i>                        | 82.2 <i>3.240</i>                 |
| *T2K-080080-10-9   | 10,000           | 8             | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 9.9 <i>0.390</i>                          | 13.3 <i>0.525</i>                       | 83.3 <i>3.280</i>                 |
| T2K-095080-25-9    | 25,000           | 5             | 9.5 <i>0.375</i>                    | 8.0 <i>0.315</i>                     | 12.2 <i>0.480</i>                         | 12.7 <i>0.500</i>                       | 64.3 <i>2.531</i>                 |
| T2K-095095-10-9    | 10,000           | 7             | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 11.1 <i>0.437</i>                         | 12.7 <i>0.500</i>                       | 82.1 <i>3.230</i>                 |
| T2K-127032-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 3.2 <i>0.125</i>                     | 19.1 <i>0.750</i>                         | 3.2 <i>0.250</i>                        | 94.9 <i>3.736</i>                 |
| T2K-127111-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8 <i>0.662</i>                         | 14.3 <i>0.563</i>                       | 86.0 <i>3.380</i>                 |
| T2K-127127-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| *T2K-165051-25-9   | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| T2K-171171-10-9    | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| *T2K-178095-10-9   | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| *T2K-191064-10-9   | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| T2K-229064-10-9    | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| T2K-254045-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| T2K-254064-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| T2K-254097-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| T2K-254127-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| T2K-254254-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| *T2K-305047-10-9   | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| T2K-318064-10-9    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| T2K-381020-10-9    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 2.0 <i>0.080</i>                     | N/A    N/A                                | 10.7 <i>0.423</i>                       | 44.1 <i>1.740</i>                 |
| T2K-381064-10-9    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| *T2K-381127-5-9    | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| T2K-381381-2-5-9   | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.607</i>                       | 88.9 <i>3.500</i>                 |
| T2K-445064-10-9    | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| T2K-445102-5-9     | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.386</i>                 |
| T2K-508064-10-9    | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| T2K-508091-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.1 <i>0.358</i>                     | N/A    N/A                                | 12.2 <i>0.480</i>                       | 57.2 <i>2.250</i>                 |
| T2K-508095-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| T2K-508127-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |

\* NOTE: Kapton®/polyimide labels not compatible with T200 Printers

## TSK White polyimide labels

### Ordering information




### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm    inches | Label height (B)<br>mm    inches | Horizontal repeat (C)<br>mm    inches | Vertical repeat (D)<br>mm    inches | Web width (E)<br>mm    inches |
|--------------------|------------------|---------------|---------------------------------|----------------------------------|---------------------------------------|-------------------------------------|-------------------------------|
| TSK-044033-10-9    | 10,000           | 20            | 4.4    0.170                    | 3.3    0.130                     | 4.4    0.170                          | 9.5    0.375                        | 92.4    3.636                 |
| TSK-064064-25-9    | 25,000           | 12            | 6.4    0.250                    | 6.4    0.250                     | 6.4    0.250                          | 9.5    0.375                        | 82.2    3.240                 |
| *TSK-080080-10-9   | 10,000           | 8             | 8.0    0.315                    | 8.0    0.315                     | 9.9    0.390                          | 13.3    0.525                       | 83.3    3.280                 |
| TSK-095080-25-9    | 25,000           | 5             | 9.5    0.375                    | 8.0    0.315                     | 12.2    0.480                         | 12.7    0.500                       | 64.3    2.531                 |
| TSK-095095-10-9    | 10,000           | 7             | 9.5    0.375                    | 9.5    0.375                     | 11.1    0.437                         | 12.7    0.500                       | 82.1    3.230                 |
| TSK-127032-10-9    | 10,000           | 5             | 12.7    0.500                   | 3.2    0.125                     | 19.1    0.750                         | 3.2    0.250                        | 94.9    3.736                 |
| TSK-127111-10-9    | 10,000           | 5             | 12.7    0.500                   | 11.1    0.437                    | 16.8    0.662                         | 14.3    0.563                       | 86.0    3.380                 |
| TSK-127127-10-9    | 10,000           | 5             | 12.7    0.500                   | 12.7    0.500                    | 15.9    0.625                         | 15.9    0.625                       | 82.6    3.250                 |
| TSK-165051-25-9    | 25,000           | 4             | 16.5    0.650                   | 5.1    0.200                     | 17.8    0.700                         | 8.3    0.325                        | 75.8    2.990                 |
| TSK-171171-10-9    | 10,000           | 5             | 17.1    0.674                   | 17.1    0.674                    | 19.7    0.774                         | 20.3    0.800                       | 101.8    4.006                |
| TSK-178095-10-9    | 10,000           | 4             | 17.8    0.700                   | 9.5    0.375                     | 19.1    0.750                         | 12.7    0.500                       | 80.9    3.190                 |
| *TSK-191064-10-9   | 10,000           | 4             | 19.1    0.750                   | 6.4    0.250                     | 21.6    0.850                         | 9.5    0.375                        | 89.9    3.540                 |
| TSK-229064-10-9    | 10,000           | 3             | 22.9    0.900                   | 6.4    0.250                     | 28.6    1.125                         | 9.5    0.375                        | 86.0    3.390                 |
| TSK-254045-10-9    | 10,000           | 3             | 25.4    1.000                   | 4.6    0.180                     | 31.8    1.250                         | 8.5    0.333                        | 95.3    3.750                 |
| TSK-254064-10-9    | 10,000           | 3             | 25.4    1.000                   | 6.4    0.250                     | 27.9    1.100                         | 9.5    0.375                        | 87.3    3.436                 |
| TSK-254097-10-9    | 10,000           | 3             | 25.4    1.000                   | 9.7    0.380                     | 27.9    1.100                         | 12.7    0.500                       | 87.4    3.440                 |
| TSK-254127-10-9    | 10,000           | 3             | 25.4    1.000                   | 12.7    0.500                    | 27.9    1.100                         | 16.9    0.666                       | 87.4    3.440                 |
| TSK-254254-10-9    | 10,000           | 3             | 25.4    1.000                   | 25.4    1.000                    | 27.9    1.100                         | 28.6    1.125                       | 87.4    3.440                 |
| *TSK-305047-10-9   | 10,000           | 2             | 30.5    1.200                   | 4.7    0.185                     | 33.0    1.300                         | 7.8    0.306                        | 69.5    2.736                 |
| TSK-318064-10-9    | 10,000           | 1             | 31.8    1.250                   | 6.4    0.250                     | N/A    N/A                            | 9.5    0.375                        | 37.9    1.490                 |
| TSK-381020-10-9    | 10,000           | 1             | 38.1    1.500                   | 2.0    0.080                     | N/A    N/A                            | 10.7    0.423                       | 44.1    1.740                 |
| TSK-381064-10-9    | 10,000           | 1             | 38.1    1.500                   | 6.4    0.250                     | N/A    N/A                            | 9.5    0.375                        | 44.5    1.750                 |
| *TSK-381127-5-9    | 5,000            | 2             | 38.1    1.500                   | 12.7    0.500                    | 44.2    1.738                         | 15.9    0.625                       | 88.2    3.472                 |
| TSK-381381-2-5-9   | 2,500            | 2             | 38.1    1.500                   | 38.1    1.500                    | 44.5    1.750                         | 40.8    1.607                       | 88.9    3.500                 |
| TSK-445064-10-9    | 10,000           | 1             | 44.5    1.750                   | 6.4    0.250                     | N/A    N/A                            | 9.5    0.375                        | 50.4    1.986                 |
| TSK-445102-5-9     | 5,000            | 1             | 44.5    1.750                   | 10.2    0.400                    | N/A    N/A                            | 12.7    0.500                       | 50.4    1.386                 |
| TSK-508064-10-9    | 10,000           | 1             | 50.8    2.000                   | 9.5    0.375                     | N/A    N/A                            | 12.7    0.500                       | 57.2    2.250                 |
| TSK-508095-10-9    | 5,000            | 1             | 50.8    2.000                   | 12.7    0.500                    | N/A    N/A                            | 15.9    0.625                       | 56.9    2.240                 |
| TSK-508127-5-9     | 5,000            | 1             | 50.8    2.000                   | 12.7    0.500                    | N/A    N/A                            | 15.9    0.625                       | 56.9    2.240                 |

\* NOTE: Kapton®/polyimide labels not compatible with T200 Printers

## KTT Tan Kapton® labels

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| KTT-044033-10-1A   | 10,000           | 20            | 4.4 <i>0.170</i>                    | 3.3 <i>0.130</i>                     | 4.4    0.170                              | 9.5    0.375                            | 92.4    3.636                     |
| KTT-064064-25-1A   | 25,000           | 12            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4    0.250                              | 9.5    0.375                            | 82.2    3.240                     |
| *KTT-080080-10-1A  | 10,000           | 8             | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 9.9    0.390                              | 13.3    0.525                           | 83.3    3.280                     |
| KTT-095080-25-1A   | 25,000           | 5             | 9.5 <i>0.375</i>                    | 8.0 <i>0.315</i>                     | 12.2    0.480                             | 12.7    0.500                           | 64.3    2.531                     |
| KTT-095095-10-1A   | 10,000           | 7             | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 11.1    0.437                             | 12.7    0.500                           | 82.1    3.230                     |
| KTT-127032-10-1A   | 10,000           | 5             | 12.7 <i>0.500</i>                   | 3.2 <i>0.125</i>                     | 19.1    0.750                             | 3.2    0.250                            | 94.9    3.736                     |
| KTT-127111-10-1A   | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8    0.662                             | 14.3    0.563                           | 86.0    3.380                     |
| KTT-127127-10-1A   | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9    0.625                             | 15.9    0.625                           | 82.6    3.250                     |
| *KTT-165051-25-1A  | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8    0.700                             | 8.3    0.325                            | 75.8    2.990                     |
| KTT-171171-10-1A   | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7    0.774                             | 20.3    0.800                           | 101.8    4.006                    |
| *KTT-178095-10-1A  | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1    0.750                             | 12.7    0.500                           | 80.9    3.190                     |
| *KTT-191064-10-1A  | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6    0.850                             | 9.5    0.375                            | 89.9    3.540                     |
| KTT-229064-10-1A   | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6    1.125                             | 9.5    0.375                            | 86.0    3.390                     |
| KTT-254045-10-1A   | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8    1.250                             | 8.5    0.333                            | 95.3    3.750                     |
| KTT-254064-10-1A   | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9    1.100                             | 9.5    0.375                            | 87.3    3.436                     |
| KTT-254097-10-1A   | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9    1.100                             | 12.7    0.500                           | 87.4    3.440                     |
| KTT-254127-10-1A   | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9    1.100                             | 16.9    0.666                           | 87.4    3.440                     |
| KTT-254254-10-1A   | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9    1.100                             | 28.6    1.125                           | 87.4    3.440                     |
| *KTT-305047-10-1A  | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0    1.300                             | 7.8    0.306                            | 69.5    2.736                     |
| KTT-318064-10-1A   | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5    0.375                            | 37.9    1.490                     |
| KTT-381020-10-1A   | 10,000           | 1             | 38.1 <i>1.500</i>                   | 2.0 <i>0.080</i>                     | N/A    N/A                                | 10.7    0.423                           | 44.1    1.740                     |
| KTT-381064-10-1A   | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5    0.375                            | 44.5    1.750                     |
| *KTT-381127-5-1A   | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2    1.738                             | 15.9    0.625                           | 88.2    3.472                     |
| KTT-381381-2.5-1A  | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5    1.750                             | 40.8    1.607                           | 88.9    3.500                     |
| KTT-445064-10-1A   | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5    0.375                            | 50.4    1.986                     |
| KTT-445102-5-1A    | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7    0.500                           | 50.4    1.986                     |
| KTT-508064-10-1A   | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5    0.375                            | 56.9    2.240                     |
| KTT-508095-5-1A    | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7    0.500                           | 57.2    2.250                     |
| KTT-508127-5-1A    | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9    0.625                           | 56.9    2.240                     |

\* NOTE: Kapton®/polyimide labels not compatible with T200 Printers

## Engineering Notes

## PVF Polyvinyl fluoride labels

Tyco Electronics PVF is a thermal transfer printable polyvinylfluoride (Tedlar®) film with a permanent acrylic adhesive, designed for wire and cable marking and other general labeling applications that require the "self-extinguishing" properties of Tedlar®. It is ideal in a variety of harsh physical and chemical environments; resists water, oil, cleaning agents and oil based solvents; and filters ultraviolet light. For reliable print performance and durability use with Tyco Electronics's 1330-3300 ribbon.

### Features and benefits


- Thermal transfer printable
- Ideal for wire and cable marking
- Self-extinguishing adhesive
- Resistant to a variety of solvents




|                                                                                                                                                |                   |                 |
|------------------------------------------------------------------------------------------------------------------------------------------------|-------------------|-----------------|
| <b>Adhesive</b>                                                                                                                                | Permanent acrylic |                 |
| <b>Service temperature</b>                                                                                                                     | -53°C to +135°C   | -65°F to +275°F |
| <b>Recommended printer</b>                                                                                                                     | T308S*            |                 |
| <b>Recommended ribbon</b>                                                                                                                      | 1330-3300-10*     |                 |
| <i>*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.</i> |                   |                 |



### Part numbering system



### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm<br><i>inches</i> | Label height (B)<br>mm<br><i>inches</i> | Horizontal repeat (C)<br>mm<br><i>inches</i> | Vertical repeat (D)<br>mm<br><i>inches</i> | Web width (E)<br>mm<br><i>inches</i> |
|--------------------|------------------|---------------|----------------------------------------|-----------------------------------------|----------------------------------------------|--------------------------------------------|--------------------------------------|
| PVF-064064-25-9    | 25,000           | 12            | 6.4<br><i>0.250</i>                    | 6.4<br><i>0.250</i>                     | 6.4<br><i>0.250</i>                          | 9.5<br><i>0.375</i>                        | 82.2<br><i>3.240</i>                 |
| * PVF-080080-10-9  | 10,000           | 8             | 8.0<br><i>0.315</i>                    | 8.0<br><i>0.315</i>                     | 9.9<br><i>0.390</i>                          | 13.3<br><i>0.525</i>                       | 83.3<br><i>3.280</i>                 |
| PVF-095080-25-9    | 25,000           | 5             | 9.5<br><i>0.375</i>                    | 8.0<br><i>0.315</i>                     | 12.2<br><i>0.480</i>                         | 12.7<br><i>0.500</i>                       | 64.3<br><i>2.531</i>                 |
| PVF-095095-10-9    | 10,000           | 7             | 9.5<br><i>0.375</i>                    | 9.5<br><i>0.375</i>                     | 11.1<br><i>0.437</i>                         | 12.7<br><i>0.500</i>                       | 82.1<br><i>3.230</i>                 |

\* NOTE: Standard Format Not Compatible with T200 Printers

Replace -9 suffix with -4 for yellow labels

## PVF Polyvinyl fluoride labels

### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| PVF-127111-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 16.8 <i>0.662</i>                         | 14.3 <i>0.563</i>                       | 86.0 <i>3.380</i>                 |
| PVF-127127-10-9    | 10,000           | 5             | 12.7 <i>0.500</i>                   | 12.7 <i>0.500</i>                    | 15.9 <i>0.625</i>                         | 15.9 <i>0.625</i>                       | 82.6 <i>3.250</i>                 |
| * PVF-165051-25-9  | 25,000           | 4             | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 17.8 <i>0.700</i>                         | 8.3 <i>0.325</i>                        | 75.8 <i>2.990</i>                 |
| PVF-165102-10-9    | 10,000           | 5             | 16.5 <i>0.650</i>                   | 10.2 <i>0.400</i>                    | 19.1 <i>0.750</i>                         | 13.8 <i>0.545</i>                       | 99.1 <i>3.900</i>                 |
| PVF-171171-10-9    | 10,000           | 5             | 17.1 <i>0.674</i>                   | 17.1 <i>0.674</i>                    | 19.7 <i>0.774</i>                         | 20.3 <i>0.800</i>                       | 101.8 <i>4.006</i>                |
| * PVF-178095-10-9  | 10,000           | 4             | 17.8 <i>0.700</i>                   | 9.5 <i>0.375</i>                     | 19.1 <i>0.750</i>                         | 12.7 <i>0.500</i>                       | 80.9 <i>3.190</i>                 |
| * PVF-191064-10-9  | 10,000           | 4             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 21.6 <i>0.850</i>                         | 9.5 <i>0.375</i>                        | 89.9 <i>3.540</i>                 |
| PVF-191114-15-9    | 15,000           | 3             | 19.1 <i>0.750</i>                   | 11.4 <i>0.450</i>                    | 22.2 <i>0.875</i>                         | 14.7 <i>0.579</i>                       | 69.5 <i>2.736</i>                 |
| PVF-191762-5-9     | 5,000            | 3             | 19.1 <i>0.750</i>                   | 76.2 <i>3.000</i>                    | 21.6 <i>0.850</i>                         | 88.9 <i>3.500</i>                       | 68.2 <i>2.686</i>                 |
| * PVF-203127-10-9  | 10,000           | 4             | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 22.9 <i>0.900</i>                         | 15.9 <i>0.625</i>                       | 94.6 <i>3.730</i>                 |
| PVF-229064-10-9    | 10,000           | 3             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 28.6 <i>1.125</i>                         | 9.5 <i>0.375</i>                        | 86.0 <i>3.390</i>                 |
| * PVF-250381-10-9  | 10,000           | 4             | 24.9 <i>0.980</i>                   | 38.1 <i>1.500</i>                    | 27.4 <i>1.080</i>                         | 47.6 <i>1.875</i>                       | 113.5 <i>4.470</i>                |
| PVF-254045-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 4.6 <i>0.180</i>                     | 31.8 <i>1.250</i>                         | 8.5 <i>0.333</i>                        | 95.3 <i>3.750</i>                 |
| PVF-254064-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        | 87.3 <i>3.436</i>                 |
| PVF-254097-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 9.7 <i>0.380</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 87.4 <i>3.440</i>                 |
| PVF-254127-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 87.4 <i>3.440</i>                 |
| PVF-254254-10-9    | 10,000           | 3             | 25.4 <i>1.000</i>                   | 25.4 <i>1.000</i>                    | 27.9 <i>1.100</i>                         | 28.6 <i>1.125</i>                       | 87.4 <i>3.440</i>                 |
| * PVF-305047-10-9  | 10,000           | 2             | 30.5 <i>1.200</i>                   | 4.7 <i>0.185</i>                     | 33.0 <i>1.300</i>                         | 7.8 <i>0.306</i>                        | 69.5 <i>2.736</i>                 |
| PVF-318064-10-9    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 37.9 <i>1.490</i>                 |
| PVF-318097-10-9    | 10,000           | 1             | 31.8 <i>1.250</i>                   | 9.7 <i>0.380</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 37.8 <i>1.488</i>                 |
| PVF-381064-10-9    | 10,000           | 1             | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 44.5 <i>1.750</i>                 |
| * PVF-381127-5-9   | 5,000            | 2             | 38.1 <i>1.500</i>                   | 12.7 <i>0.500</i>                    | 44.2 <i>1.738</i>                         | 15.9 <i>0.625</i>                       | 88.2 <i>3.472</i>                 |
| PVF-381191-5-9     | 5,000            | 2             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 22.2 <i>0.875</i>                       | 87.6 <i>3.450</i>                 |
| * PVF-381381-2.5-9 | 2,500            | 2             | 38.1 <i>1.500</i>                   | 38.1 <i>1.500</i>                    | 44.5 <i>1.750</i>                         | 40.8 <i>1.607</i>                       | 88.9 <i>3.500</i>                 |
| * PVF-381635-5-9   | 5,000            | 2             | 38.1 <i>1.500</i>                   | 63.5 <i>2.500</i>                    | 40.6 <i>1.600</i>                         | 66.7 <i>2.625</i>                       | 84.7 <i>3.336</i>                 |
| * PVF-406254-1.5-9 | 1,500            | 2             | 40.6 <i>1.600</i>                   | 25.4 <i>1.000</i>                    | 55.9 <i>2.200</i>                         | 38.1 <i>1.500</i>                       | 102.9 <i>4.050</i>                |
| PVF-445064-10-9    | 10,000           | 1             | 44.5 <i>1.750</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 50.4 <i>1.986</i>                 |
| PVF-445102-5-9     | 5,000            | 1             | 44.5 <i>1.750</i>                   | 10.2 <i>0.400</i>                    | N/A    N/A                                | 12.7 <i>0.500</i>                       | 50.4 <i>1.986</i>                 |
| PVF-445445-2-9     | 2,000            | 1             | 44.5 <i>1.750</i>                   | 44.5 <i>1.750</i>                    | N/A    N/A                                | 47.6 <i>1.875</i>                       | 50.4 <i>1.986</i>                 |
| PVF-478175-5-9     | 5,000            | 1             | 47.8 <i>1.880</i>                   | 17.5 <i>0.690</i>                    | N/A    N/A                                | 24.4 <i>0.962</i>                       | 66.0 <i>2.600</i>                 |
| PVF-508064-10-9    | 10,000           | 1             | 50.8 <i>2.000</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 9.5 <i>0.375</i>                        | 56.9 <i>2.240</i>                 |
| PVF-508095-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | N/A    N/A                                | 12.7 <i>0.500</i>                       | 57.2 <i>2.250</i>                 |
| PVF-508127-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 12.7 <i>0.500</i>                    | N/A    N/A                                | 15.9 <i>0.625</i>                       | 56.9 <i>2.240</i>                 |
| PVF-508254-5-9     | 5,000            | 1             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 57.2 <i>2.250</i>                 |
| PVF-508318-2.5-9   | 2,500            | 1             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | N/A    N/A                                | 34.9 <i>1.375</i>                       | 56.9 <i>2.240</i>                 |
| PVF-508508-3-9     | 3,000            | 1             | 50.8 <i>2.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 54.0 <i>2.130</i>                 |
| PVF-523841-1.5-9   | 1,500            | 1             | 52.3 <i>2.060</i>                   | 84.1 <i>3.310</i>                    | N/A    N/A                                | 88.9 <i>3.500</i>                       | 58.2 <i>2.290</i>                 |
| PVF-610419-2.5-9   | 2,500            | 1             | 61.0 <i>2.400</i>                   | 41.9 <i>1.650</i>                    | N/A    N/A                                | 45.5 <i>1.792</i>                       | 67.3 <i>2.650</i>                 |
| PVF-699191-5-9     | 5,000            | 1             | 69.9 <i>2.750</i>                   | 19.1 <i>0.750</i>                    | N/A    N/A                                | 23.3 <i>0.917</i>                       | 76.2 <i>3.000</i>                 |
| PVF-699254-5-9     | 5,000            | 1             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | N/A    N/A                                | 28.6 <i>1.125</i>                       | 76.2 <i>3.000</i>                 |
| PVF-762381-2.5-9   | 2,500            | 1             | 76.2 <i>3.000</i>                   | 38.1 <i>1.500</i>                    | N/A    N/A                                | 41.3 <i>1.625</i>                       | 82.3 <i>3.240</i>                 |
| PVF-762508-2.5-9   | 2,500            | 1             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.0 <i>2.125</i>                       | 82.6 <i>3.240</i>                 |
| PVF-762127-1-9     | 1,000            | 1             | 76.2 <i>3.000</i>                   | 127.0 <i>5.000</i>                   | N/A    N/A                                | 129.5 <i>5.100</i>                      | 79.4 <i>3.130</i>                 |
| PVF-101508-2.5-9   | 2,500            | 1             | 101.6 <i>4.000</i>                  | 50.8 <i>2.000</i>                    | N/A    N/A                                | 54.6 <i>2.150</i>                       | 104.1 <i>4.100</i>                |
| PVF-101635-2.5-9   | 2,500            | 1             | 101.6 <i>4.000</i>                  | 63.5 <i>2.500</i>                    | N/A    N/A                                | 66.7 <i>2.625</i>                       | 107.7 <i>4.240</i>                |
| PVF-101762-1.8-9   | 1,800            | 1             | 101.6 <i>4.000</i>                  | 76.2 <i>3.000</i>                    | N/A    N/A                                | 79.4 <i>3.125</i>                       | 104.1 <i>4.100</i>                |
| PVF-101101-1.3-9   | 1,300            | 1             | 101.6 <i>4.000</i>                  | 101.6 <i>4.000</i>                   | N/A    N/A                                | 104.8 <i>4.125</i>                      | 104.1 <i>4.100</i>                |
| PVF-101165-0.85-9  | 850              | 1             | 101.6 <i>4.000</i>                  | 165.1 <i>6.500</i>                   | N/A    N/A                                | 168.3 <i>6.680</i>                      | 104.9 <i>4.130</i>                |

\* NOTE: Standard Format Not Compatible with T200 Printers

Replace -9 suffix with -4 for yellow labels

## EP Economy paper labels

Tyco Electronics EP is a thermal transfer printable paper with a permanent adhesive, designed for use in general purpose labeling applications requiring a low cost label material. EP has an aggressive adhesive for bonding to corrugated, films and plastic materials, and it is ideal for labeling in mild environments. The ultra-smooth finish is excellent for bar coding applications. EP remains bonded permanently to most surfaces and typically results in label or substrate tear when removal is attempted. For reliable print performance use with Tyco Electronics 1330-0600 ribbon.

### Features and benefits

- Thermal transfer printable
- Ultra-smooth coated facestock
- Versatile adhesive with excellent initial tack
- Several die-cut sizes available



### Specifications/Approvals

Industry UL MH17001 Group PGDQ2

**Adhesive** Permanent rubber-based

**Service temperature** -53°C to +93°C -65°F to +200°F

**Recommended printer** T308S\*

**Recommended ribbon** 1330-0600-10\*

\*Alternative printers and ribbons are available for special applications. Contact Tyco Electronics Identification for more information.

### Part numbering system


EP 101 508 2.5 9





## EP Economy paper labels

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm inches | Label height (B)<br>mm inches | Horizontal repeat (C)<br>mm inches | Vertical repeat (D)<br>mm inches | Web width (E)<br>mm inches |
|--------------------|------------------|---------------|------------------------------|-------------------------------|------------------------------------|----------------------------------|----------------------------|
| * EP-191064-10-9   | 10,000           | 4             | 19.1 0.750                   | 6.4 0.250                     | 21.6 0.850                         | 9.5 0.375                        | 89.9 3.540                 |
| EP-254097-10-9     | 10,000           | 3             | 25.4 1.000                   | 9.7 0.380                     | 27.9 1.100                         | 12.7 0.500                       | 87.4 3.440                 |
| EP-254127-10-9     | 10,000           | 3             | 25.4 1.000                   | 12.7 0.500                    | 27.9 1.100                         | 16.9 0.666                       | 87.4 3.440                 |
| EP-254254-10-9     | 10,000           | 3             | 25.4 1.000                   | 25.4 1.000                    | 27.9 1.100                         | 28.6 1.125                       | 87.4 3.440                 |
| EP-318064-10-9     | 10,000           | 1             | 31.8 1.250                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 37.9 1.490                 |
| EP-318097-10-9     | 10,000           | 1             | 31.8 1.250                   | 9.7 0.380                     | N/A N/A                            | 12.7 0.500                       | 37.8 1.488                 |
| EP-381064-10-9     | 10,000           | 1             | 38.1 1.500                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 44.5 1.750                 |
| * EP-381127-5-9    | 5,000            | 2             | 38.1 1.500                   | 12.7 0.500                    | 44.2 1.738                         | 15.9 0.625                       | 88.2 3.472                 |
| EP-381191-5-9      | 5,000            | 2             | 38.1 1.500                   | 19.1 0.750                    | 43.2 1.700                         | 22.2 0.875                       | 87.6 3.450                 |
| * EP-381381-2.5-9  | 2,500            | 2             | 38.1 1.500                   | 38.1 1.500                    | 44.5 1.750                         | 40.8 1.607                       | 88.9 3.500                 |
| * EP-381635-5-9    | 5,000            | 2             | 38.1 1.500                   | 63.5 2.500                    | 40.6 1.600                         | 66.7 2.625                       | 84.7 3.336                 |
| * EP-406254-1.5-9  | 1,500            | 2             | 40.6 1.600                   | 25.4 1.000                    | 55.9 2.200                         | 38.1 1.500                       | 102.9 4.050                |
| EP-445102-5-9      | 5,000            | 1             | 44.5 1.750                   | 10.2 0.400                    | N/A N/A                            | 12.7 0.500                       | 50.4 1.986                 |
| EP-445445-2-9      | 2,000            | 1             | 44.5 1.750                   | 44.5 1.750                    | N/A N/A                            | 47.6 1.875                       | 50.4 1.986                 |
| EP-508064-10-9     | 10,000           | 1             | 50.8 2.000                   | 6.4 0.250                     | N/A N/A                            | 9.5 0.375                        | 56.9 2.240                 |
| EP-508095-5-9      | 5,000            | 1             | 50.8 2.000                   | 9.5 0.375                     | N/A N/A                            | 12.7 0.500                       | 57.2 2.250                 |
| EP-508127-5-9      | 5,000            | 1             | 50.8 2.000                   | 12.7 0.500                    | N/A N/A                            | 15.9 0.625                       | 56.9 2.240                 |
| EP-508254-5-9      | 5,000            | 1             | 50.8 2.000                   | 25.4 1.000                    | N/A N/A                            | 28.6 1.125                       | 57.2 2.250                 |
| EP-508318-2.5-9    | 2,500            | 1             | 50.8 2.000                   | 31.8 1.250                    | N/A N/A                            | 34.9 1.375                       | 56.9 2.240                 |
| EP-508508-3-9      | 3,000            | 1             | 50.8 2.000                   | 50.8 2.000                    | N/A N/A                            | 54.6 2.150                       | 54.0 2.130                 |
| EP-523841-1.5-9    | 1,500            | 1             | 52.3 2.060                   | 84.1 3.310                    | N/A N/A                            | 88.9 3.500                       | 58.2 2.290                 |
| EP-610419-2.5-9    | 2,500            | 1             | 61.0 2.400                   | 41.9 1.650                    | N/A N/A                            | 45.5 1.792                       | 67.3 2.650                 |
| EP-699191-5-9      | 5,000            | 1             | 69.9 2.750                   | 19.1 0.750                    | N/A N/A                            | 23.3 0.917                       | 76.2 3.000                 |
| EP-699254-5-9      | 5,000            | 1             | 69.9 2.750                   | 25.4 1.000                    | N/A N/A                            | 28.6 1.125                       | 76.2 3.000                 |
| EP-762381-2.5-9    | 2,500            | 1             | 76.2 3.000                   | 38.1 1.500                    | N/A N/A                            | 41.3 1.625                       | 82.3 3.240                 |
| EP-762508-2.5-9    | 2,500            | 1             | 76.2 3.000                   | 50.8 2.000                    | N/A N/A                            | 54.0 2.125                       | 82.6 3.240                 |
| EP-762127-1-9      | 1,000            | 1             | 76.2 3.000                   | 127.0 5.000                   | N/A N/A                            | 129.5 5.100                      | 79.4 3.130                 |
| EP-762254-5-9      | 5,000            | 1             | 76.2 3.000                   | 25.4 1.000                    | N/A N/A                            | 28.6 1.125                       | 82.3 3.240                 |
| EP-101508-2.5-9    | 2,500            | 1             | 101.6 4.000                  | 50.8 2.000                    | N/A N/A                            | 54.6 2.150                       | 104.1 4.100                |
| EP-101635-2.5-9    | 2,500            | 1             | 101.6 4.000                  | 63.5 2.500                    | N/A N/A                            | 66.7 2.625                       | 107.7 4.240                |
| EP-101762-1.8-9    | 1,800            | 1             | 101.6 4.000                  | 76.2 3.000                    | N/A N/A                            | 79.4 3.125                       | 104.1 4.100                |
| EP-101101-1.3-9    | 1,300            | 1             | 101.6 4.000                  | 101.6 4.000                   | N/A N/A                            | 104.8 4.125                      | 104.1 4.100                |
| EP-101165-0.85-9   | 850              | 1             | 101.6 4.000                  | 165.1 6.500                   | N/A N/A                            | 168.3 6.680                      | 104.9 4.130                |

\* NOTE: Standard Format Not Compatible with T200 Printers

## VF Clear Tedlar® overlaminate

VF-X is a non-printable clear Tedlar® designed for use as an over laminate for labels where resistance to UV light and weathering is necessary. Adds further protection from chemicals, solvents, abrasion, heat and moisture.

### Features and benefits

- UV and weather resistant
- Ideal to use as an overlaminate in combination with all printable Tyco Electronics labels
- Resistant to water, oil, cleaning agents and solvents



### Specifications/Approvals

Tyco Electronics

TTDS-006

### Adhesive

Permanent rubber-based

### Service temperature

-53°C to +135°C    -65°F to +275°F



### Part numbering system


VF 508318 2.5 X



Color  
Pack size  
Label height (mm)  
Label width (mm)  
Product family

## VF Clear Tedlar® overlamine

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A) |        | Label height (B) |        | Horizontal repeat (C) |        | Vertical repeat (D) |        | Web width (E) |        |
|--------------------|------------------|---------------|-----------------|--------|------------------|--------|-----------------------|--------|---------------------|--------|---------------|--------|
|                    |                  |               | mm              | inches | mm               | inches | mm                    | inches | mm                  | inches | mm            | inches |
| VF-191064-10-X     | 10,000           | 4             | 19.1            | 0.750  | 6.4              | 0.250  | 21.6                  | 0.850  | 9.5                 | 0.375  | 89.9          | 3.540  |
| VF-229064-10-X     | 10,000           | 3             | 22.9            | 0.900  | 6.4              | 0.250  | 28.6                  | 1.125  | 9.5                 | 0.375  | 86.0          | 3.390  |
| VF-254097-10-X     | 10,000           | 3             | 25.4            | 1.000  | 9.7              | 0.380  | 27.9                  | 1.100  | 12.7                | 0.500  | 87.4          | 3.440  |
| VF-254127-10-X     | 10,000           | 3             | 25.4            | 1.000  | 12.7             | 0.500  | 27.9                  | 1.100  | 16.9                | 0.666  | 87.4          | 3.440  |
| VF-381064-10-X     | 10,000           | 1             | 38.1            | 1.500  | 6.4              | 0.250  | N/A                   | N/A    | 9.5                 | 0.375  | 44.5          | 1.750  |
| VF-381127-5-X      | 5,000            | 2             | 38.1            | 1.500  | 12.7             | 0.500  | 44.2                  | 1.738  | 15.9                | 0.625  | 88.2          | 3.472  |
| VF-381191-5-X      | 5,000            | 2             | 38.1            | 1.500  | 19.1             | 0.750  | 43.2                  | 1.700  | 22.2                | 0.875  | 87.6          | 3.450  |
| VF-406254-1.5-X    | 1,500            | 2             | 40.6            | 1.600  | 25.4             | 1.000  | 55.9                  | 2.200  | 38.1                | 1.500  | 102.9         | 4.050  |
| VF-508127-5-X      | 5,000            | 1             | 50.8            | 2.000  | 12.7             | 0.500  | N/A                   | N/A    | 15.9                | 0.625  | 56.9          | 2.240  |
| VF-508254-5-X      | 5,000            | 1             | 50.8            | 2.000  | 25.4             | 1.000  | N/A                   | N/A    | 28.6                | 1.125  | 57.2          | 2.250  |
| VF-508318-2.5-X    | 2,500            | 1             | 50.8            | 2.000  | 31.8             | 1.250  | N/A                   | N/A    | 34.9                | 1.375  | 56.9          | 2.240  |
| VF-699254-5-X      | 5,000            | 1             | 69.9            | 2.750  | 25.4             | 1.000  | N/A                   | N/A    | 28.6                | 1.125" | 76.2          | 3.000  |
| VF-762254-5-X      | 5,000            | 1             | 76.2            | 3.000  | 25.4             | 1.000  | N/A                   | N/A    | 28.6                | 1.125" | 82.3          | 3.240  |
| VF-762508-2.5-X    | 2,500            | 1             | 76.2            | 3.000  | 50.8             | 2.000  | N/A                   | N/A    | 54.0                | 2.125  | 82.3          | 3.240  |
| VF-101635-2.5-X    | 2,500            | 1             | 101.6           | 4.000  | 63.5             | 2.500  | N/A                   | N/A    | 66.7                | 2.625  | 107.7         | 4.240  |

## C Vinyl cloth labels

Tyco Electronics C labels are dot matrix printable vinyl coated cloth material with a permanent acrylic adhesive that is designed for application to irregular surfaces where conformability is required. It is ideal for permanent wire marking, or it can be flagged onto wires for temporary marking. C labels are also ideal for electronic component identification and other general purpose labeling applications. For reliable print performance and durability, use with Tyco Electronics's 1892BK01 ribbon.

### Features and benefits

- Flexible, easily conforms to curved surfaces
- Dot matrix printable
- Several die-cut sizes available
- Excellent abrasion resistance
- Resistant to oil, water and several common fluids




### Specifications/Approvals

|                            |                                   |
|----------------------------|-----------------------------------|
| Tyco Electronics           | TTDS-053                          |
| <b>Adhesive</b>            | Permanent acrylic                 |
| <b>Service temperature</b> | -29°C to +80°C    -20°F to +176°F |
| <b>Recommended printer</b> | AM6310                            |
| <b>Recommended ribbon</b>  | 1892BK01                          |


### Part numbering system

C-064064-10-9



## C Vinyl cloth labels

### Ordering information



### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| C-064064-10-9      | 10,000           | 20            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4 <i>0.250</i>                          | 8.5 <i>0.333</i>                        | 152.4 <i>6.000</i>                |
| C-076191-10-9      | 10,000           | 16            | 7.6 <i>0.300</i>                    | 19.1 <i>0.750</i>                    | 7.6 <i>0.300</i>                          | 25.4 <i>1.000</i>                       | 147.3 <i>5.800</i>                |
| C-080080-10-9      | 10,000           | 10            | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 8.0 <i>0.315</i>                          | 12.7 <i>0.500</i>                       | 105.4 <i>4.150</i>                |
| C-095095-10-9      | 10,000           | 16            | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 12.7 <i>0.500</i>                         | 12.7 <i>0.500</i>                       | 226.1 <i>8.900</i>                |
| C-165051-10-9      | 10,000           | 10            | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 20.3 <i>0.800</i>                         | 6.4 <i>0.250</i>                        | 224.8 <i>8.850</i>                |
| C-191064-10-9      | 10,000           | 9             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 22.9 <i>0.900</i>                         | 8.5 <i>0.333</i>                        | 227.3 <i>8.950</i>                |
| C-203127-10-9      | 10,000           | 10            | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 20.3 <i>0.800</i>                         | 15.9 <i>0.625</i>                       | 228.6 <i>9.000</i>                |
| C-203365-10-9      | 10,000           | 6             | 20.3 <i>0.800</i>                   | 36.5 <i>1.437</i>                    | 22.9 <i>0.900</i>                         | 38.1 <i>1.500</i>                       | 160.0 <i>6.300</i>                |
| C-229064-10-9      | 10,000           | 8             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 25.4 <i>1.000</i>                         | 8.5 <i>0.333</i>                        | 226.1 <i>8.900</i>                |
| C-254095-10-9      | 10,000           | 7             | 25.4 <i>1.000</i>                   | 9.5 <i>0.375</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 218.4 <i>8.600</i>                |
| C-254127-10-9      | 10,000           | 7             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 218.4 <i>8.600</i>                |
| C-381064-10-S1-9   | 10,000           | 4**           | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | 45.7 <i>1.800</i>                         | 8.5 <i>0.333</i>                        | 200.7 <i>7.900</i>                |
| C-508095-5-9       | 5,000            | 3             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | 53.3 <i>2.100</i>                         | 12.7 <i>0.500</i>                       | 182.9 <i>7.200</i>                |
| C-533064-5-9       | 5,000            | 3             | 53.3 <i>2.100</i>                   | 6.4 <i>0.250</i>                     | 55.9 <i>2.200</i>                         | 8.5 <i>0.333</i>                        | 190.5 <i>7.500</i>                |
| C-533114-5-9       | 5,000            | 3             | 53.3 <i>2.100</i>                   | 11.4 <i>0.450</i>                    | 55.9 <i>2.200</i>                         | 14.7 <i>0.579</i>                       | 190.5 <i>7.500</i>                |


\*\*Perforated

## M Metalized polyester labels

Tyco Electronics M is a dot matrix printable metalized polyester film with a permanent acrylic adhesive that is designed for rating plate applications and other applications that require a “metal look” such as nameplates, rating plates and equipment labels to detail product information and serial numbers. M is UL Listed and its print performance and durability are reliable when used with Tyco Electronics 1892BK01 ribbon.


### Features and benefits

- Dot matrix printable
- Exceptional durability and strength
- Matte finish ink receptive coating for better contrast
- Resistant to oil, water and several common fluids
- UL Listed



### Part numbering system

M-064064-10-8A




### Specifications/Approvals

|                            |                                   |
|----------------------------|-----------------------------------|
| Tyco Electronics           | TTDS-072                          |
| Industry                   | UL MH17292 Group PGGU2MH14363     |
| <b>Adhesive</b>            | Permanent acrylic                 |
| <b>Service temperature</b> | -53°C to +93°C    -65°F to +200°F |
| <b>Recommended printer</b> | AM6310                            |
| <b>Recommended ribbon</b>  | 1892BK01                          |

## M Metalized polyester labels

### Ordering information




### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm<br><i>inches</i> | Label height (B)<br>mm<br><i>inches</i> | Horizontal repeat (C)<br>mm<br><i>inches</i> | Vertical repeat (D)<br>mm<br><i>inches</i> | Web width (E)<br>mm<br><i>inches</i> |
|--------------------|------------------|---------------|----------------------------------------|-----------------------------------------|----------------------------------------------|--------------------------------------------|--------------------------------------|
| M-064064-10-8A     | 10,000           | 20            | 6.4 <i>0.250</i>                       | 6.4 <i>0.250</i>                        | 6.4 <i>0.250</i>                             | 8.5 <i>0.333</i>                           | 152.4 <i>6.000</i>                   |
| M-080080-10-8A     | 10,000           | 10            | 8.0 <i>0.315</i>                       | 8.0 <i>0.315</i>                        | 8.0 <i>0.315</i>                             | 12.7 <i>0.500</i>                          | 105.4 <i>4.150</i>                   |
| M-095095-10-8A     | 10,000           | 16            | 9.5 <i>0.375</i>                       | 9.5 <i>0.375</i>                        | 12.7 <i>0.500</i>                            | 12.7 <i>0.500</i>                          | 226.1 <i>8.900</i>                   |
| M-127111-10-8A     | 10,000           | 13            | 12.7 <i>0.500</i>                      | 11.1 <i>0.437</i>                       | 15.2 <i>0.600</i>                            | 15.9 <i>0.625</i>                          | 221.0 <i>8.700</i>                   |
| M-154064-10-8A     | 10,000           | 7             | 15.4 <i>0.600</i>                      | 6.4 <i>0.250</i>                        | 17.8 <i>0.700</i>                            | 8.5 <i>0.333</i>                           | 147.3 <i>5.800</i>                   |
| M-165051-10-8A     | 10,000           | 10            | 16.5 <i>0.650</i>                      | 5.1 <i>0.200</i>                        | 20.3 <i>0.800</i>                            | 6.4 <i>0.250</i>                           | 224.8 <i>8.850</i>                   |
| M-191064-10-8A     | 10,000           | 9             | 19.1 <i>0.750</i>                      | 6.4 <i>0.250</i>                        | 22.9 <i>0.900</i>                            | 8.5 <i>0.333</i>                           | 227.3 <i>8.950</i>                   |
| M-203127-10-8A     | 10,000           | 10            | 20.3 <i>0.800</i>                      | 12.7 <i>0.500</i>                       | 20.3 <i>0.800</i>                            | 15.9 <i>0.625</i>                          | 228.6 <i>9.000</i>                   |
| M-229064-10-8A     | 10,000           | 8             | 22.9 <i>0.900</i>                      | 6.4 <i>0.250</i>                        | 25.4 <i>1.000</i>                            | 8.5 <i>0.333</i>                           | 226.1 <i>8.900</i>                   |
| M-254095-10-8A     | 10,000           | 7             | 25.4 <i>1.000</i>                      | 9.5 <i>0.375</i>                        | 27.9 <i>1.100</i>                            | 12.7 <i>0.500</i>                          | 218.4 <i>8.600</i>                   |
| M-254127-10-8A     | 10,000           | 7             | 25.4 <i>1.000</i>                      | 12.7 <i>0.500</i>                       | 27.9 <i>1.100</i>                            | 16.9 <i>0.666</i>                          | 218.4 <i>8.600</i>                   |
| M-293064-10-8A     | 10,000           | 4             | 29.3 <i>1.150</i>                      | 6.4 <i>0.250</i>                        | 9.4 <i>0.370</i>                             | 30.5 <i>1.200</i>                          | 146.1 <i>5.750</i>                   |
| M-381191-10-8A     | 10,000           | 4             | 38.1 <i>1.500</i>                      | 19.1 <i>0.750</i>                       | 43.2 <i>1.700</i>                            | 25.4 <i>1.000</i>                          | 193.0 <i>7.600</i>                   |
| M-394064-10-8A     | 10,000           | 4             | 39.4 <i>1.550</i>                      | 6.4 <i>0.250</i>                        | 41.9 <i>1.650</i>                            | 8.5 <i>0.333</i>                           | 190.5 <i>7.500</i>                   |
| M-508095-5-8A      | 5,000            | 3             | 50.8 <i>2.000</i>                      | 9.5 <i>0.375</i>                        | 53.3 <i>2.100</i>                            | 12.7 <i>0.500</i>                          | 182.9 <i>7.200</i>                   |
| M-508254-4-8A      | 4,000            | 4             | 50.8 <i>2.000</i>                      | 25.4 <i>1.075</i>                       | 50.8 <i>2.000</i>                            | 28.6 <i>1.125</i>                          | 228.6 <i>9.000</i>                   |
| M-508318-3-8A      | 3,000            | 4             | 50.8 <i>2.000</i>                      | 31.8 <i>1.250</i>                       | 50.8 <i>2.000</i>                            | 34.9 <i>1.375</i>                          | 228.6 <i>9.000</i>                   |
| M-533064-5-8A      | 5,000            | 3             | 53.3 <i>2.100</i>                      | 6.4 <i>0.250</i>                        | 55.9 <i>2.200</i>                            | 8.5 <i>0.333</i>                           | 190.5 <i>7.500</i>                   |
| M-673254-3-8A      | 3,000            | 3             | 67.3 <i>2.650</i>                      | 25.4 <i>1.000</i>                       | 67.3 <i>2.650</i>                            | 38.1 <i>1.500</i>                          | 227.3 <i>8.950</i>                   |
| M-673349-3-8A      | 3,000            | 3             | 67.3 <i>2.650</i>                      | 34.9 <i>1.375</i>                       | 67.3 <i>2.650</i>                            | 38.1 <i>1.500</i>                          | 227.3 <i>8.950</i>                   |
| M-699254-2.5-8A    | 2,500            | 3             | 69.9 <i>2.750</i>                      | 25.4 <i>1.000</i>                       | 73.0 <i>2.875</i>                            | 28.6 <i>1.125</i>                          | 241.3 <i>9.500</i>                   |
| M-699318-2.5-8A    | 2,500            | 3             | 69.9 <i>2.750</i>                      | 31.8 <i>1.250</i>                       | 73.0 <i>2.875</i>                            | 34.9 <i>1.375</i>                          | 241.3 <i>9.500</i>                   |
| M-711064-5-8A      | 5,000            | 1             | 71.1 <i>2.800</i>                      | 6.4 <i>0.250</i>                        | N/A <i>N/A</i>                               | 8.5 <i>0.333</i>                           | 96.5 <i>3.800</i>                    |
| M-762508-1-8A      | 1,000            | 2             | 76.2 <i>3.000</i>                      | 50.8 <i>2.000</i>                       | 79.4 <i>3.125</i>                            | 54.0 <i>2.125</i>                          | 181.0 <i>7.130</i>                   |
| M-920254-2.5-8A    | 2,500            | 2             | 92.0 <i>3.620</i>                      | 25.4 <i>1.000</i>                       | 94.6 <i>3.725</i>                            | 28.6 <i>1.125</i>                          | 212.1 <i>8.350</i>                   |
| M-920381-2.5-8A    | 2,500            | 2             | 92.0 <i>3.620</i>                      | 38.1 <i>1.500</i>                       | 95.3 <i>3.750</i>                            | 41.3 <i>1.625</i>                          | 212.8 <i>8.380</i>                   |
| M-165101-1-8A      | 1,000            | 1             | 165.1 <i>6.500</i>                     | 101.6 <i>4.000</i>                      | N/A <i>N/A</i>                               | 108.0 <i>4.250</i>                         | 190.5 <i>7.500</i>                   |



## K Kapton® labels

Tyco Electronics K is a dot matrix printable, 2 mil thick tan polyimide (Kapton®) with a permanent acrylic adhesive that is ideal for high temperature labeling requirements such as printed circuit boards. It is suitable for direct wave (bottom side) and IR reflow (top side) PCB applications, and is designed to withstand the fluxes, cleaning solvents and molten solder encountered in the manufacture of printed circuit boards. With a flash exposure service temperature of +538°C (+1000°F), K is suitable for the harshest high temperature applications. For reliable print performance and durability, use with Tyco Electronics 1892BK01 ribbon.



### Features and benefits


- Dot matrix printable
- Matte finish for better print contrast
- Product approved for aerospace/defense applications
- Exceptional durability and tear resistance
- High temperature permanent acrylic adhesive
- Superior solvent and UV resistance
- Low outgassing



|                             |                                                                           |
|-----------------------------|---------------------------------------------------------------------------|
| <b>Specifications</b>       | TTDS-007                                                                  |
| <b>Adhesive</b>             | Permanent acrylic                                                         |
| <b>Service temperature*</b> | -40°C to +260°C    -40°F to +500°F<br>*Flash exposure to +538°C (+1000°F) |
| <b>Recommended printer</b>  | AM6310                                                                    |
| <b>Recommended ribbon</b>   | 1892BK01                                                                  |


### Part numbering system

K-064064-10-1A



## K Kapton® labels

### Ordering information




### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| K-064064-10-1A     | 10,000           | 20            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4 <i>0.250</i>                          | 8.5 <i>0.333</i>                        | 152.4 <i>6.000</i>                |
| K-080080-10-1A     | 10,000           | 10            | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 8.0 <i>0.315</i>                          | 12.7 <i>0.500</i>                       | 105.4 <i>4.150</i>                |
| K-095095-10-1A     | 10,000           | 16            | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 12.7 <i>0.500</i>                         | 12.7 <i>0.500</i>                       | 226.1 <i>8.900</i>                |
| K-165051-10-1A     | 10,000           | 10            | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 20.3 <i>0.800</i>                         | 6.4 <i>0.250</i>                        | 224.8 <i>8.850</i>                |
| K-191064-10-1A     | 10,000           | 9             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 22.9 <i>0.900</i>                         | 8.5 <i>0.333</i>                        | 227.3 <i>8.950</i>                |
| K-229064-10-1A     | 10,000           | 8             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 25.4 <i>1.000</i>                         | 8.5 <i>0.333</i>                        | 226.1 <i>8.900</i>                |
| K-254095-10-1A     | 10,000           | 7             | 25.4 <i>1.000</i>                   | 9.5 <i>0.375</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 218.4 <i>8.600</i>                |
| K-254127-10-1A     | 10,000           | 7             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 218.4 <i>8.600</i>                |
| K-293064-10-1A     | 10,000           | 4             | 29.3 <i>1.150</i>                   | 6.4 <i>0.250</i>                     | 9.4 <i>0.370</i>                          | 30.5 <i>1.200</i>                       | 146.1 <i>5.750</i>                |

## E White polyester labels

Tyco Electronics E is a dot matrix printable white polyester film with a permanent acrylic adhesive that is ideal for PCB and component labeling, as well as general purpose labeling applications that require a high durability white label. It is resistant to a variety of solvents while maintaining print quality. E is UL Listed and its print performance and durability are reliable when used with Tyco Electronics 1892BK01 ribbon.



### Features and benefits

- Dot matrix printable
- Cost-efficient for general purpose, low volume applications
- Exceptional durability and strength
- Resistant to oil, water and several common fluids
- UL Listed



#### Specifications/Approvals

|                  |                        |
|------------------|------------------------|
| Tyco Electronics | TTDS-071               |
| Industry         | UL MH14363 Group PGGU2 |

#### Adhesive

Permanent acrylic

#### Service temperature

-53°C to +93°C    -65°F to +200°F

#### Recommended printer


AM6310

#### Recommended ribbon

1892BK01


### Part numbering system

**E-064064-10-9**



## E White polyester labels

### Ordering information




### Product dimensions

| Product order code | Package quantity | Labels across | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> | Web width (E)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|-----------------------------------|
| E-064064-10-9      | 10,000           | 20            | 6.4 <i>0.250</i>                    | 6.4 <i>0.250</i>                     | 6.4 <i>0.250</i>                          | 8.5 <i>0.333</i>                        | 152.4 <i>6.000</i>                |
| E-080080-10-9      | 10,000           | 10            | 8.0 <i>0.315</i>                    | 8.0 <i>0.315</i>                     | 8.0 <i>0.315</i>                          | 12.7 <i>0.500</i>                       | 105.4 <i>4.150</i>                |
| E-095095-10-9      | 10,000           | 16            | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 12.7 <i>0.500</i>                         | 12.7 <i>0.500</i>                       | 226.1 <i>8.900</i>                |
| E-127111-10-9      | 10,000           | 13            | 12.7 <i>0.500</i>                   | 11.1 <i>0.437</i>                    | 15.2 <i>0.600</i>                         | 15.9 <i>0.625</i>                       | 221 <i>8.700</i>                  |
| E-154064-10-9      | 10,000           | 7             | 15.4 <i>0.600</i>                   | 6.4 <i>0.250</i>                     | 17.8 <i>0.700</i>                         | 8.5 <i>0.333</i>                        | 147.3 <i>5.800</i>                |
| E-165051-10-9      | 10,000           | 10            | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 20.3 <i>0.800</i>                         | 6.4 <i>0.250</i>                        | 224.8 <i>8.850</i>                |
| E-191064-10-9      | 10,000           | 9             | 19.1 <i>0.750</i>                   | 6.4 <i>0.250</i>                     | 22.9 <i>0.900</i>                         | 8.5 <i>0.333</i>                        | 227.3 <i>8.950</i>                |
| E-203127-10-9      | 10,000           | 10            | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 20.3 <i>0.800</i>                         | 15.9 <i>0.625</i>                       | 228.6 <i>9.000</i>                |
| E-229064-10-9      | 10,000           | 8             | 22.9 <i>0.900</i>                   | 6.4 <i>0.250</i>                     | 25.4 <i>1.000</i>                         | 8.5 <i>0.333</i>                        | 226.1 <i>8.900</i>                |
| E-254095-10-9      | 10,000           | 7             | 25.4 <i>1.000</i>                   | 9.5 <i>0.375</i>                     | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       | 218.4 <i>8.600</i>                |
| E-254127-10-9      | 10,000           | 7             | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 16.9 <i>0.666</i>                       | 218.4 <i>8.600</i>                |
| E-293064-10-9      | 10,000           | 4             | 29.3 <i>1.150</i>                   | 6.4 <i>0.250</i>                     | 9.4 <i>0.370</i>                          | 30.5 <i>1.200</i>                       | 146.1 <i>5.750</i>                |
| E-381191-10-9      | 10,000           | 4             | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 43.2 <i>1.700</i>                         | 25.4 <i>1.000</i>                       | 193.0 <i>7.600</i>                |
| E-394064-10-9      | 10,000           | 4             | 39.4 <i>1.550</i>                   | 6.4 <i>0.250</i>                     | 41.9 <i>1.650</i>                         | 8.5 <i>0.333</i>                        | 190.5 <i>7.500</i>                |
| E-508095-5-9       | 5,000            | 3             | 50.8 <i>2.000</i>                   | 9.5 <i>0.375</i>                     | 53.3 <i>2.100</i>                         | 12.7 <i>0.500</i>                       | 182.9 <i>7.200</i>                |
| E-508254-4-9       | 4,000            | 4             | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | 50.8 <i>2.000</i>                         | 28.6 <i>1.125</i>                       | 228.6 <i>9.000</i>                |
| E-508318-3-9       | 3,000            | 4             | 50.8 <i>2.000</i>                   | 31.8 <i>1.250</i>                    | 50.8 <i>2.000</i>                         | 34.9 <i>1.375</i>                       | 228.6 <i>9.000</i>                |
| E-533064-5-9       | 5,000            | 3             | 53.3 <i>2.100</i>                   | 6.4 <i>0.250</i>                     | 55.9 <i>2.200</i>                         | 8.5 <i>0.333</i>                        | 190.5 <i>7.500</i>                |
| E-673254-3-9       | 3,000            | 3             | 67.3 <i>2.650</i>                   | 25.4 <i>1.000</i>                    | 67.3 <i>2.650</i>                         | 38.1 <i>1.500</i>                       | 227.3 <i>8.950</i>                |
| E-673349-3-9       | 3,000            | 3             | 67.3 <i>2.650</i>                   | 34.9 <i>1.375</i>                    | 67.3 <i>2.650</i>                         | 38.1 <i>1.500</i>                       | 227.3 <i>8.950</i>                |
| E-699254-2.5-9     | 2,500            | 3             | 69.9 <i>2.750</i>                   | 25.4 <i>1.000</i>                    | 73.0 <i>2.875</i>                         | 28.6 <i>1.125</i>                       | 241.3 <i>9.500</i>                |
| E-699318-2.5-9     | 2,500            | 3             | 69.9 <i>2.750</i>                   | 31.8 <i>1.250</i>                    | 73.0 <i>2.875</i>                         | 34.9 <i>1.375</i>                       | 241.3 <i>9.500</i>                |
| E-711064-5-9       | 5,000            | 1             | 71.1 <i>2.800</i>                   | 6.4 <i>0.250</i>                     | N/A    N/A                                | 8.5 <i>0.333</i>                        | 96.5 <i>3.800</i>                 |
| E-762508-1-9       | 1,000            | 2             | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | 79.4 <i>3.125</i>                         | 54.0 <i>2.125</i>                       | 181.0 <i>7.130</i>                |
| E-920254-2.5-9     | 2,500            | 2             | 92.0 <i>3.620</i>                   | 25.4 <i>1.000</i>                    | 94.6 <i>3.725</i>                         | 28.6 <i>1.125</i>                       | 212.1 <i>8.350</i>                |
| E-920381-2.5-9     | 2,500            | 2             | 92.0 <i>3.620</i>                   | 38.1 <i>1.500</i>                    | 95.3 <i>3.750</i>                         | 41.3 <i>1.625</i>                       | 212.8 <i>8.380</i>                |
| E-165101-1-9       | 1,000            | 1             | 165.1 <i>6.500</i>                  | 101.6 <i>4.000</i>                   | N/A    N/A                                | 108.0 <i>4.250</i>                      | 190.5 <i>7.500</i>                |

## LE/LM/LEB2 Polyester labels

### LE


Tyco Electronics LE is a white polyester film with a permanent acrylic adhesive and a special top-coat designed specifically for use with laser and ink jet printers. It is ideal for bar coding, PCB and component labeling, and general labeling applications requiring a white high durability label. LE offers high print resolution as well as good solvent and smudge resistance.



### LM

Tyco Electronics LM is a metalized polyester film with a permanent acrylic adhesive and a special top-coat designed specifically for use with laser and ink jet printers. It is ideal for rating plate applications and other applications that require a "metal look" such as nameplates and equipment labels to detail product information and serial numbers.

Note: On large label formats, some curl may occur on printing due to duration of time in the laser printer.



### LEB2

LEB2, our A4 size symmetrically-designed laser and ink jet labels, guarantee a proper feeding in the paper tray. The label sheet can be used in both directions and is also usable for the stack function of your printer. The sheets can be used several times if partial label amounts need to be printed. Special surface coatings guarantee an extremely high aging-resistance of the printing image.

### Features and benefits

- Laser printable
- Exceptional durability and tear strength
- Suitable for low volume applications
- Excellent for bar code applications
- Good resistance to common fluids and water
- LM metalized appearance is ideal for rating plate applications.
- LEB2 features symmetrical design – can be printed on from both top sides



#### Specifications/Approvals

|                  |    |    |                     |
|------------------|----|----|---------------------|
| Tyco Electronics |    | LE | TTDS-069            |
|                  |    | LM | TTDS-070            |
| Industry         | UL | LM | MH14363 Group PGGU2 |


#### Adhesive

Permanent acrylic

#### Service temperature

–40°C to +150°C    –40°F to +302°F

### Ordering information



## LE/LM/LEB2 Polyester labels

### Ordering information

#### LE

| Product order code | Package quantity | Labels across | Labels per sheet | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|------------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|
| 314-LE             | 4,000            | 16            | 400              | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 12.7 <i>0.500</i>                         | 9.5 <i>0.375</i>                        |
| 301-LE             | 4,800            | 10            | 480              | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 20.3 <i>0.800</i>                         | 5.1 <i>0.200</i>                        |
| 303-LE             | 3,040            | 8             | 304              | 20.3 <i>0.800</i>                   | 6.4 <i>0.250</i>                     | 25.4 <i>1.000</i>                         | 6.4 <i>0.250</i>                        |
| 304-LE             | 1,520            | 8             | 152              | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 25.4 <i>1.000</i>                         | 12.7 <i>0.500</i>                       |
| 309-LE             | 2,660            | 7             | 266              | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 6.4 <i>0.250</i>                        |
| 305-LE             | 1,750            | 7             | 175              | 25.4 <i>1.000</i>                   | 9.5 <i>0.375</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        |
| 307-LE             | 1,330            | 7             | 133              | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       |
| 310-LE             | 1,900            | 5             | 190              | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | 40.6 <i>1.600</i>                         | 6.4 <i>0.250</i>                        |
| 308-LE             | 600              | 5             | 60               | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 40.6 <i>1.600</i>                         | 19.1 <i>0.750</i>                       |
| 318-LE             | 400              | 4             | 40               | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | 50.8 <i>2.000</i>                         | 25.4 <i>1.000</i>                       |
| 319-LE             | 100              | 2             | 10               | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | 88.9 <i>3.500</i>                         | 50.8 <i>2.000</i>                       |
| 325-LE             | 10               | 1             | 1                | 215.9 <i>8.500</i>                  | 279.4 <i>11.000</i>                  | N/A N/A                                   | N/A N/A                                 |

#### LM

| Product order code | Package quantity | Labels across | Labels per sheet | Label width (A)<br>mm <i>inches</i> | Label height (B)<br>mm <i>inches</i> | Horizontal repeat (C)<br>mm <i>inches</i> | Vertical repeat (D)<br>mm <i>inches</i> |
|--------------------|------------------|---------------|------------------|-------------------------------------|--------------------------------------|-------------------------------------------|-----------------------------------------|
| 314-LM             | 4,000            | 16            | 400              | 9.5 <i>0.375</i>                    | 9.5 <i>0.375</i>                     | 12.7 <i>0.500</i>                         | 9.5 <i>0.375</i>                        |
| 301-LM             | 4,800            | 10            | 480              | 16.5 <i>0.650</i>                   | 5.1 <i>0.200</i>                     | 20.3 <i>0.800</i>                         | 5.1 <i>0.200</i>                        |
| 303-LM             | 3,040            | 8             | 304              | 20.3 <i>0.800</i>                   | 6.4 <i>0.250</i>                     | 25.4 <i>1.000</i>                         | 6.4 <i>0.250</i>                        |
| 304-LM             | 1,520            | 8             | 152              | 20.3 <i>0.800</i>                   | 12.7 <i>0.500</i>                    | 25.4 <i>1.000</i>                         | 12.7 <i>0.500</i>                       |
| 309-LM             | 2,660            | 7             | 266              | 25.4 <i>1.000</i>                   | 6.4 <i>0.250</i>                     | 27.9 <i>1.100</i>                         | 6.4 <i>0.250</i>                        |
| 305-LM             | 1,750            | 7             | 175              | 25.4 <i>1.000</i>                   | 9.5 <i>0.375</i>                     | 27.9 <i>1.100</i>                         | 9.5 <i>0.375</i>                        |
| 307-LM             | 1,330            | 7             | 133              | 25.4 <i>1.000</i>                   | 12.7 <i>0.500</i>                    | 27.9 <i>1.100</i>                         | 12.7 <i>0.500</i>                       |
| 310-LM             | 1,900            | 5             | 190              | 38.1 <i>1.500</i>                   | 6.4 <i>0.250</i>                     | 40.6 <i>1.600</i>                         | 6.4 <i>0.250</i>                        |
| 308-LM             | 600              | 5             | 60               | 38.1 <i>1.500</i>                   | 19.1 <i>0.750</i>                    | 40.6 <i>1.600</i>                         | 19.1 <i>0.750</i>                       |
| 318-LM             | 400              | 4             | 40               | 50.8 <i>2.000</i>                   | 25.4 <i>1.000</i>                    | 50.8 <i>2.000</i>                         | 25.4 <i>1.000</i>                       |
| 319-LM             | 100              | 2             | 10               | 76.2 <i>3.000</i>                   | 50.8 <i>2.000</i>                    | 88.9 <i>3.500</i>                         | 50.8 <i>2.000</i>                       |
| 325-LM             | 10               | 1             | 1                | 215.9 <i>8.500</i>                  | 279.4 <i>11.000</i>                  | N/A N/A                                   | N/A N/A                                 |

#### LEB2

| Product order code | Labels per sheet | Label height<br>mm <i>inches</i> | Label width<br>mm <i>inches</i> | Labels per column | Labels per row |
|--------------------|------------------|----------------------------------|---------------------------------|-------------------|----------------|
| LEB2-0615P <color> | 480              | 6.0 <i>0.236</i>                 | 15.0 <i>0.590</i>               | 48                | 10             |
| LEB2-0818P <color> | 324              | 8.0 <i>0.315</i>                 | 18.0 <i>0.709</i>               | 36                | 9              |
| LEB2-0820P <color> | 288              | 8.0 <i>0.315</i>                 | 20.0 <i>0.787</i>               | 36                | 8              |
| LEB2-0825P <color> | 252              | 8.0 <i>0.315</i>                 | 25.0 <i>0.984</i>               | 36                | 7              |
| LEB2-0916P <color> | 320              | 9.0 <i>0.354</i>                 | 16.0 <i>0.630</i>               | 32                | 10             |
| LEB2-1318P <color> | 198              | 13.0 <i>0.512</i>                | 18.0 <i>0.709</i>               | 22                | 9              |
| LEB2-1325P <color> | 154              | 13.0 <i>0.512</i>                | 25.0 <i>0.984</i>               | 22                | 7              |

### Sheet sizes

|        |            |
|--------|------------|
| LE, LM | 8.5" x 11" |
| LEB2   | A4         |

### Options (LEB2 only)

|        |        |       |        |
|--------|--------|-------|--------|
| Colors | Yellow | White | Silver |
| Code   | 4      | 9     | 8A     |