




PRODUCT NUMBER
SEE SHEET 1


PRESS-FIT HOLES

HOLE DIAMETER AFTER PLATING	$\varnothing 0.65\text{--}\varnothing 0.80$ *	$\varnothing 1.53$
DRILLED HOLE	$\varnothing 0.81\text{--}\varnothing 0.86$ ($\varnothing 0.85$ DRILL)	$\varnothing 1.61\text{--}\varnothing 1.66$ ($\varnothing 1.65$ DRILL)
COPPER PLATING	0.025-0.050	0.025-0.050
SnPb PLATING	0.005-0.015	0.005-0.015

*SEE DRAWING 58351 FOR OTHER OPTIONS



RECOMMENDED PCB HOLE
PATTERN-COMPONENT SIDE

mat'l code SEE NOTE 2				tolerances unless otherwise specified		CUSTOMER		FCi www.fciconnect.com			
ltr	ecr no.	dr	date	linear	0.X ± 0.3		COPY		title RIGHT ANGLE SIGNAL RECEPTACLE 8 ROW, 96 POSITION		
T					0.XX ± 0.10		projection				
				angles	0.XXX ± 0.050						
					0° ± 2°						
				dr	S. KLINE	2000-03-09	MM		product family	METRAL 1000	code
				enrg	M. HAHN	2000-03-09	←		size	dwg no	213
				chr	S. STONER	2000-08-24	scale				sheet
				appd	M. HAHN	2000-08-24	1:1		A	74981	2
sheet index	revision sheet										

Pro/E

3

cage code 22526

4

PDM: Rev:T

STATUS: Released

Printed: May 13, 2011

PRODUCT NUMBER

SEE SHEET 1


NOTES

1. UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994
2. HOUSING MATERIAL: LIQUID CRYSTAL POLYMER, GLASS FILLED FLAME RETARDANT PER UL94V-0
GROUND SHIELD MATERIAL: COPPER ALLOY
SIGNAL CONTACT MATERIAL: COPPER ALLOY
3. PLATING:
PRESS-FIT TAIL AREA: SnPb ON STANDARD
Sn ON LEAD FREE
MATING CONTACT POINTS: MEETS PERFORMANCE LEVEL SHOWN IN TABLE ON SHEET 1.
4. Ø2.05 HOLE IS UNPLATED.
5. Ø1.53 PLATED HOLES (2X) ARE FOR GROUNDS.
6. AVOID TRACES IN THIS AREA ON TOP OF PCB DUE TO EXPOSED GROUND SHIELD.
7. UNDERPLATING FOR SHIELD AND SIGNAL CONTACTS IS 1.3 µm Ni MIN.
8. COMPONENT KEEP OUT ZONE FOR PRESS BLOCK CLEARANCE.
9. PRODUCT MARKING: DATE AND LOT CODE.
10. SEE GS-20-018 FOR APPLICATION OF CONNECTOR TO PCB.
11. PCB THICKNESS RANGE: 1.3mm TO 3.4mm.
12. SEE PRODUCT SPECIFICATION GS-12-134 FOR PRODUCT PERFORMANCE CHARACTERISTICS.

13. THIS GROUND ROW OF VIA-HOLES ONLY REQUIRED FOR PREVIOUS REVISIONS OF THIS DESIGN WHERE THE TOP SHIELDS HAD EON PRESS-FIT. DUE TO INVENTORIES OF PREVIOUS VERSION, WE RECOMMEND THEY BE DESIGNED IN.

14. PRODUCTS WHERE THE PART NUMBER ENDS IN LF MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

ALL PRODUCTS WILL WITHSTAND EXPOSURE TO 260°C FOR 60 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

mat'l code SEE NOTE 2				tolerances unless otherwise specified			CUSTOMER		 www.fciconnect.com				
ltr	ecn no.	dr	date	linear	0.X ±0.3			COPY					
T					0.XX ±0.10			projection					
				angles	0.XXX ±0.050								
					0° ±2°								
				dr	S. KLINE	2000-03-09			product family METRAL 1000			code	
				enrg	M. HAHN	2000-03-09			size	dwg no	213		
				chr	S. STONER	2000-08-24			A			sheet	
				appd	M. HAHN	2000-08-24	scale 2:1					3	
sheet index	revision sheet												


cage code 22526



This document is the property of and embodies CONFIDENTIAL and PROPRIETARY information of FCI. No part of the information shown on this document may be used in any way or disclosed to others without the written consent of FCI. Copyright FCI.

PRODUCT NUMBER
SEE SHEET 1

DISTANCE FROM CONTACT POINT TO BOARD	
CONTACT	DISTANCE
A	12.5
B	15.9
C	18.9
D	21.9
E	25.0
F	28.0
G	31.1
H	34.1



CONTACT POINT AND SKEW

mat'l code SEE NOTE 2				tolerances unless otherwise specified				CUSTOMER		FCi www.fciconnect.com			
ltr	ecr no.	dr	date	linear	0.X ± 0.3		COPY		RIGHT ANGLE SIGNAL RECEPTACLE 8 ROW, 96 POSITION				
T					0.XX ± 0.10		projection						
				0.XXX ± 0.050									
				angles	0° $\pm 2^\circ$								
		dr	S. KLINE	2000-03-09	MM scale 3:1		product family		METRAL 1000		code		
		enr	M. HAHN	2000-03-09			size	dwg no		213			
		chr	S. STONER	2000-08-24			A		74981		sheet 4		
		appd	M. HAHN	2000-08-24									
sheet index		revision sheet											

This document is the property of and embodies
CONFIDENTIAL and PROPRIETARY information of FCI.
No part of the information shown on this
document may be used in any way or disclosed
to others without the written consent of FCI.
Copyright FCI.