


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO. 10014744	DIM A	VOLTAGE KEY	BOARD OFFSET DIM C	PACKING
-002 (-N02)	1.0	5.0V	0.3	SEE NOTE 5 FOR DETAIL DESCRIPTION
-003 (-N03)	1.0	5.0V	0	
-004 (-N04)	1.0	5.0V	-0.3	
-006 (-N06)	2.1	3.3V	0.3	
-007 (-N07)	2.1	3.3V	0	
-008 (-N08)	2.1	3.3V	-0.3	
-011 (N11)	1.0	5.0V	0.6	
-012 (-N12)	2.1	3.3V	0.6	
-013 (-N13)	1.0	5.0V	-0.6	
-014 (-N14)	2.1	3.3V	-0.6	
-015 (-N15)	1.0	5.0V	-0.8	
-021 (-N21)	1.0	5.0V	0	
SEE NOTE 6 FOR -NXX DETAIL				
SEE NOTE 7 FOR LEAD FREE DETAIL				
(NOTE: -021 & -N21 IS REVERSED TYPE)				



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	FCI			
ltr	ecn no	dr	date				www.fciconnect.com			
H	0G08-0116	NZ	05/27/08	linear	.X ±.3	projection	title			
					.XX ±.13		68PIN PCMCIA			
					.XXX ±.050		RECEPTACLE ASS'Y			
C	T03-0099	TAI	03/21/03	angles	0° ±2°					
D	T03-0186	TAI	05/21/03	dr	KENNY TAI 12/17/02	MM	product family PCMCIA			
E	T03-0332	TAI	07/22/04	enr	KENNY TAI 12/17/02		size dwg no			
F	T03-0358	TAI	08/23/04	chr	KENNY TAI 12/17/02	scale	A3 10014744			
G	0G06-0154	CS	04/06/06	appd	PAUL WANG 12/17/02	1:1				
sheet	revision	H	H	H	H					
index	sheet	1	2	3	4					

cage code
22526


ACAD

PDM: Rev:H

STATUS: Released

Printed: Jun 07, 2008

A
FCI



mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com			
ltr	ecn no	dr	date	linear	.X ±.3				projection 	title 68PIN PCMCIA RECEPTACLE ASS'Y			
H					.XX ±.13								
					.XXX ±.050								
				angles	0° ±2°				← MM → scale 1:1	product family PCMCIA		code	
				dr	KENNY TAI	12/17/02	size dwg no	A3		10014744	—		
				enrg	KENNY TAI	12/17/02							
				chr	KENNY TAI	12/17/02							
				appd	PAUL WANG	12/17/02					sheet 2 of		
sheet index		revision sheet											

cage code
22526

ACAD

PDM: Rev:H





STATUS: Released

Printed: Jun 07, 2008



Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.



mat'l. code				tolerances unless otherwise specified			CUSTOMER COPY		 www.fciconnect.com		
ltr	ecm no	dr	date	linear	.X ±.3		projection 	title 68PIN PCMCIA RECEPTACLE ASS'Y			
H					.XX ±.13						
					.XXX ±.050						
				angles	0° ±2°			product family PCMCIA size dwg no A3 10014744			
			dr	KENNY TAI	12/17/02	code					
			enrg	KENNY TAI	12/17/02	—					
				chr	KENNY TAI	12/17/02	scale 1:1	A3 10014744			sheet 3 of
			appd	PAUL WANG	12/17/02						
sheet index	revision sheet										


cage code 22526

ACAD

PDM: Rev:H

STATUS: Released

Printed: Jun 07, 2008



RECOMMENDED P.C.B. LAYOUT

NOTE:

1. MATERIAL:
CONTACT: PHBR 0.12t
HOUSING: LCP UL94V-0 (BLACK COLOR: -XXX; NATURAL COLOR: -NXX)
- FINISH:
CONTACT: ALL OVER--- Ni UNDER 0.5 MICRON THK.
CONTACT AREA--- Au or GXT 0.38 MICRON THK.
SOLDER TAIL---TIN LEAD 2.5 MICRON THK.
2. MAXIMUM PCB BOW ON THIS DIMENSION IS 0.1mm.
3. PACKING SPEC. REFER TO GS-14-723.
4. ELIMINATE THE CORNER TO PREVENT INTERFERENCE WITH SOLDER TAIL.
5. -XXX (-NXX) USE STD. PACKAGE, 1872 PCS / CARTON;
-XXXT (-NXXT) USE TAPE AND REEL, 750 PCS / REEL;
-XXXS (-NXXS) USE STD. PACKAGE, 200 PCS / CARTON;
-XXXX (-NXXX) USE TAPE AND REEL, 600 PCS / REEL.
6. -NXX USE NATURAL COLOR HOUSING. EX. -N02 IS THE SAME WITH -002 EXCEPT NATURAL COLOR.
7. -XXXXLF IS LEAD FREE PLATING. SOLDER TAIL IS PLATED TIN 2.5 MICRON.
8. PRODUCT SPEC. REFER TO GS-12-228.

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY	 www.fciconnect.com
ltr	ecn no	dr	date	linear	.X ±.3				
H					.XX ±.13				
					.XXX ±.050				
				angles	0° ±2°				title 68PIN PCMCIA RECEPTACLE ASS'Y
				dr	KENNY TAI	12/17/'02	MM		
				enrg	KENNY TAI	12/17/'02		scale	
				chr	KENNY TAI	12/17/'02	1:1		
				appd	PAUL WANG	12/17/'02		A3	
sheet index	revision sheet								10014744

cage code
22526