


RED INDICATES ORIGINAL

DATA CONTAINED IN THIS DOCUMENT IS
 PROPRIETARY TO TROMPETER ELECTRONICS, INC.
 AND SHALL NOT BE DISCLOSED, COPIED OR USED
 FOR REPRODUCTION OR MANUFACTURE WITHOUT
 EXPRESS WRITTEN PERMISSION.



REVISIONS			305-0152	SH 1
REV	EO	DESCRIPTION	DWN	APPROVED
J	12437	ADDED -3; SEE ECO	DBN	11/1/88

DASH NO	MODEL NO	IMPEDANCE VALUE	COLOR CODE
-1	LPTW2TP-78	78 OHMS	BLUE
-2	LPTW2TP-124	124 OHMS	BLUE
-3	LPTW2TP-110	110 OHMS	BLUE

INCH	MM
.010	0.25
.030	0.76
.540	13.72
.590	14.98
.625	15.88
1.200	30.48
2.250	57.15
2.994	76.05



SCHEMATIC



-1 SHOWN

3. STANDARD SIZE TWINAX / TRIAX SOCKET CONTACT TYPE LOOPING PLUG WITH 2 TEST POINTS
2. FINISH: BARRELS; TFS-1A (NICKEL) CASE; SEE CODE IN TABLE
1. ALL DIMENSIONS ARE IN INCHES.

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL. UNLESS SPECIFIED .001 ± .0005 ± .030 X.0000 ± ANGLES	TROMPETER ELECTRONICS, INC.	LPTW2TP	
DWN DBN 4/25/88	MATERIAL	CODE IDENT	DRAWING NO.
CHK WM 4-30-88		14949	305-0152
ENGR	DATE	5-6-74	REV J
APPR	SCALE: 2/1	DATE	SHEET 1 OF 2