


LOC	DIST	REVISIONS					
CM	54	P	LTR	DESCRIPTION	DATE	DWN	APVD
			T	ECR-13-008537	16SEP13	M.T	D.Z
			T1	ECO-14-012257	31OCT2014	KR	OC



 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.

7	SUPERCEDED BY 5-641219-4	95.10	[3.744]	24	2-641219-4
	SUPERCEDED BY 5-641219-3	91.14	[3.588]	23	2-641219-3
	SUPERCEDED BY 5-641219-2	87.17	[3.432]	22	2-641219-2
	SUPERCEDED BY 5-641219-1	83.21	[3.276]	21	2-641219-1
	SUPERCEDED BY 5-641219-0	79.25	[3.120]	20	2-641219-0
	SUPERCEDED BY 4-641219-9	75.29	[2.964]	19	1-641219-9
	SUPERCEDED BY 4-641219-8	71.32	[2.808]	18	1-641219-8
	SUPERCEDED BY 4-641219-7	67.36	[2.652]	17	1-641219-7
	SUPERCEDED BY 4-641219-6	63.40	[2.496]	16	1-641219-6
	SUPERCEDED BY 4-641219-5	59.44	[2.340]	15	1-641219-5
	SUPERCEDED BY 4-641219-4	55.47	[2.184]	14	1-641219-4
SUPERCEDED BY 4-641219-3		51.51	[2.028]	13	1-641219-3
		47.55	[1.872]	12	1-641219-2
7	SUPERCEDED BY 4-641219-1	43.59	[1.716]	11	1-641219-1
7	SUPERCEDED BY 4-641219-0	39.62	[1.560]	10	1-641219-0
		35.66	[1.404]	9	641219-9
		31.70	[1.248]	8	641219-8
		27.74	[1.092]	7	641219-7
7	SUPERCEDED BY 3-641219-6	23.77	[.936]	6	641219-6
		19.81	[.780]	5	641219-5
		15.85	[.624]	4	641219-4
		11.89	[.468]	3	641219-3
		7.92	[.312]	2	641219-2
DIM A				NO OF CIRCUITS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. LEWIS 12 FEB 91 CHK R. SWING 12 FEB 91 APVD D. CLARK 20 FEB 91		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-156 CONNECTOR ASSEMBLY, 22 AWG, STANDARD —	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -			
MATERIAL 		FINISH 			
		PRODUCT SPEC 108-1051 APPLICATION SPEC 114-1020		SIZE A2	
		WEIGHT —		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-641219	
				RESTRICTED TO —	
				SCALE 4:1 SHEET 1 OF 1 REV T1	

METRIC