



English
日本語

Product Catalog Engineering Info Company Links Contact Us

Fan Motors Engineering

Information

DC Fans

- 1.Common Spec.
- 2.Numbering (Axial Fans)
- 3.Numbering (FB)
- 4.Numbering (Blowers BM)
- 5.Numbering (Blowers BG)
- 6.Numbering (FAL)
- 7.Sensors
- 8.Speed Control

AC Fans

Technical Information

Handling Precautions

Quality & Environment

DC Axial Fans Part Numbering System

To show details, place the mouse cursor on each item of the part number. Click "Display All" button to show all details.

24	10	M	L	-	04	W	-	B	1	0	-	X	00	Display All					
(1)	(2)	(3)	(4)		(5)	(6)		(7)	(8)	(9)		(10)	(11)						
1. Size				2. Thickness				3. Series				5. Input Voltage		4. Function		7. Bearing			
10	25mm	28	70mm	04	10mm			P Series		S Series		01	5V	06	36V	Brushless Type		B	Ball Bearing
12	30mm	31	80mm	06	15mm			M Series		F Series		02	6V	07	48V	DCM		S	Sleeve Bearing
14	35mm	36	92mm	08	20mm			N Series				03	9V	09	Custom	6. Termination		8. Speed	
16	40mm	47	119mm	10	25mm			K Series				04	12V	voltage	w				
20	50mm	50	127mm	12	32mm			H Series				05	24V			T	Terminal Type	low	high
21	52mm	59	150mm	15	38mm														
24	60mm	68	172mm	20	50mm														
9. Special Control Function											11. Individual Specifications								
0 Standard type																			
9 Sensor type											Standard Type								
8 2-speed type											00 Standard								
7 Temperature detecting variable speed type/PWM control type											01-99 Custom								
6 Temperature detecting variable speed type/Sensor type																			
5 2-speed type / Sensor type											00 Sensor Type								
											00 Locked Rotor Alarm Signal(Standard)								
											01-49 Locked Rotor Alarm Signal(Custom)								
											50 Tachometer Signal (Standard)								
											51-99 Tachometer Signal (Custom)								