

DE5SC4M

40V 5A


FEATURES

- SMT
- $T_j 150^{\circ}\text{C}$
- P_{RRSM} avalanche guaranteed
- High current capacity with Small Package

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS

● Absolute Maximum Ratings (If not specified $T_c=25^{\circ}\text{C}$)


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T_{stg}		$-40 \sim 150$	$^{\circ}\text{C}$
Operating Junction Temperature	T_j		150	$^{\circ}\text{C}$
Maximum Reverse Voltage	V_{RM}		40	V
Repetitive Peak Surge Reverse Voltage	V_{RRSM}	Pulse width 0.5ms, duty 1/40	45	V
Average Rectified Forward Current	I_o	50Hz sine wave, R-load, Rating for each diode $I_o/2$, $T_a=25^{\circ}\text{C}$, On alumina substrate	3	A
		50Hz sine wave, R-load, Rating for each diode $I_o/2$, $T_c=101^{\circ}\text{C}$	5	
Peak Surge Forward Current	I_{FSM}	50Hz sine wave, Non-repetitive 1 cycle peak value, $T_j=125^{\circ}\text{C}$	80	A
Repetitive Peak Surge Reverse Power	P_{RRSM}	Pulse width 10 μ s, Rating of per diode, $T_j=25^{\circ}\text{C}$	330	W

● Electrical Characteristics (If not specified $T_c=25^{\circ}\text{C}$)


Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	V_F	$I_F=2.5\text{A}$, Pulse measurement, Rating of per diode	Max.0.55	V
Reverse Current	I_R	$V_R=V_{RM}$, Pulse measurement, Rating of per diode	Max.3.5	mA
Junction Capacitance	C_j	$f=1\text{MHz}$, $V_R=10\text{V}$, Rating of per diode	Typ.150	pF
Thermal Resistance	θ_{jc}	junction to case	Max.12	$^{\circ}\text{C/W}$
	θ_{ja}	junction to ambient, On alumina substrate	Max.55	

DE5SC4M

Forward Voltage




DE5SC4M Junction Capacitance




DE5SC4M


Reverse Current




DE5SC4M Reverse Power Dissipation



$T_j = 150^\circ\text{C}$



DE5SC4M Forward Power Dissipation




$T_j = 150^\circ\text{C}$



DE5SC4M

Derating Curve




$V_R = 20V$




DE5SC4M


Derating Curve



$V_R = 20V$



DE5SC4M Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

