



Design Kit for Switcher CAD III Inductors



SMT Power-Chokes for Switcher CAD III Inductors

744 510 1 L: 1.0 μ H RDC: 0.04 Ω I: 3.0 A	744 511 0 L: 10.0 μ H RDC: 0.075 Ω I: 1.0 A	744 540 4 L: 4.7 μ H RDC: 0.04 Ω I: 2.7 A	744 561 68 L: 68.0 μ H RDC: 0.24 Ω I: 1.6 A	744 570 27 L: 2.7 μ H RDC: 8.4 m Ω I: 10.0 A	744 773 056 L: 5.6 μ H RDC: 126.0 m Ω I: 1.58 A	744 776 10 L: 10.0 μ H RDC: 0.06 Ω I: 2.98 A
744 510 22 L: 2.2 μ H RDC: 0.05 Ω I: 1.8 A	744 511 15 L: 15.0 μ H RDC: 0.09 Ω I: 0.8 A	744 540 68 L: 6.8 μ H RDC: 0.055 Ω I: 2.2 A	744 562 0 L: 100.0 μ H RDC: 0.33 Ω I: 1.4 A	744 571 15 L: 15.0 μ H RDC: 35.0 m Ω I: 5.0 A	744 774 127 L: 27.0 μ H RDC: 0.2 Ω I: 1.19 A	744 776 122 L: 22.0 μ H RDC: 0.1 Ω I: 2.04 A
744 510 33 L: 3.3 μ H RDC: 0.055 Ω I: 1.6 A	744 511 22 L: 22.0 μ H RDC: 0.11 Ω I: 0.7 A	744 560 1 L: 1.0 μ H RDC: 0.007 Ω I: 8.6 A	744 562 22 L: 220.0 μ H RDC: 0.78 Ω I: 0.9 A	744 773 018 L: 1.8 μ H RDC: 64.0 m Ω I: 2.7 A	744 775 112 L: 12.0 μ H RDC: 0.08 Ω I: 2.18 A	744 776 127 L: 27.0 μ H RDC: 0.11 Ω I: 1.95 A
744 510 47 L: 4.7 μ H RDC: 0.06 Ω I: 1.4 A	744 511 33 L: 33.0 μ H RDC: 0.19 Ω I: 0.6 A	744 561 33 L: 33.0 μ H RDC: 0.12 Ω I: 2.3 A	744 562 47 L: 470.0 μ H RDC: 1.7 Ω I: 0.6 A	744 773 022 L: 2.2 μ H RDC: 71.0 m Ω I: 2.5 A	744 775 139 L: 39.0 μ H RDC: 0.16 Ω I: 1.25 A	744 777 10 L: 10.0 μ H RDC: 0.049 Ω I: 2.0 A
744 510 68 L: 6.8 μ H RDC: 0.065 Ω I: 1.2 A	744 511 47 L: 47.0 μ H RDC: 0.23 Ω I: 0.5 A	744 561 47 L: 47.0 μ H RDC: 0.19 Ω I: 1.8 A	744 570 12 L: 1.2 μ H RDC: 3.8 m Ω I: 15.0 A	744 773 033 L: 3.3 μ H RDC: 86.0 m Ω I: 2.0 A	744 775 168 L: 68.0 μ H RDC: 0.28 Ω I: 0.99 A	744 777 122 L: 22.0 μ H RDC: 0.11 Ω I: 1.41 A

Würth Elektronik eiSos GmbH & Co. KG

EMC & Inductive Solutions

Max-Eyth Str. 1

D-74638 Waldenburg

Tel. +49 (0) 79 42 945-0

Fax +49 (0) 79 42 945-400

eiSos@we-online.de



Please check datasheets for
specifications on www.we-online.com

© 2005

Würth Elektronik eiSos GmbH & Co. KG

EMC & Inductive Solutions