



# Fastite® 2000™ 05LP




| English                                                                            | Français                                                                           | Deutsch                                                                                             | Italiano                                                                               | Español                                                                           |
|------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
| Round large head Torx®                                                             | Tête ronde large Torx®                                                             | Rundkopf groß Torx®                                                                                 | Testa 1/2 Tonda con finta rondella Torx®                                               | Cabeza alomada con ala Torx®                                                      |
| Steel case hardened*<br>Hardness:<br>Surface: > 450 HV0,3<br>Core: 290 to 370 HV10 | Acier cémenté*<br>Dureté:<br>Superficielle: > 450 HV0,3<br>À coeur: 290 à 370 HV10 | Stahl einsatzgehärtet*<br>Härte:<br>Oberfläche: > 450 HV0,3<br>Kern: 290 bis 370 HV10               | Acciaio cementato*<br>Durezza:<br>Superficiale: > 450 HV0,3<br>A cuore: 290 a 370 HV10 | Acero cementado*<br>Dureza:<br>Superficial: > 450 HV0,3<br>Núcleo: 290 a 370 HV10 |
| Zinc alkaline clear <sup>1)</sup> or<br>Zinc -nickel alkaline clear <sup>2)</sup>  | Zinc alcalin claire <sup>1)</sup> ou<br>Zinc-nickel alcalin claire <sup>2)</sup>   | Zink alkalisch transparent <sup>1)</sup><br>oder Zink-Nickel alkalisch<br>transparent <sup>2)</sup> | Zinco alcalino chiaro <sup>1)</sup> o<br>Zinco-Nichel alcalino<br>chiaro <sup>2)</sup> | Zincado y pasivado claro <sup>1)</sup><br>o Niquelado <sup>2)</sup>               |



1) 96 h / 2) 720 h \*\*

\* : EN ISO 7085

\*\* : to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo (ASTM B117)



| Ø     | Ø C            | Ø D            | Pitch / Pas/<br>Steigung/<br>Passo /<br>Paso | Cp<br>max. | Ø Dk             | K              | s<br>ca. | Torx® | t              | L        | Part No/ref |
|-------|----------------|----------------|----------------------------------------------|------------|------------------|----------------|----------|-------|----------------|----------|-------------|
| MM3.0 | 2.93<br>- 3.02 | 2.88<br>- 2.97 | 2 x 0.5                                      | 1.70       | 6.00<br>- 6.60   | 2.40<br>- 2.77 | 0.8      | T10   | 1.01<br>- 1.27 | 8 ±0.50  | 05LP3000801 |
|       |                |                |                                              |            |                  |                |          |       |                | 10 ±0.50 | 05LP3001001 |
|       |                |                |                                              |            |                  |                |          |       |                | 12 ±0.75 | 05LP3001201 |
|       |                |                |                                              |            |                  |                |          |       |                | 16 ±0.75 | 05LP3001601 |
|       |                |                |                                              |            |                  |                |          |       |                | 20 ±0.75 | 05LP3002001 |
|       |                |                |                                              |            |                  |                |          |       |                | 25 ±0.75 | 05LP3002501 |
| MM4.0 | 3.92<br>- 4.02 | 3.85<br>- 3.95 | 2 x 0.7                                      | 2.20       | 9.00<br>- 9.50   | 3.20<br>- 3.60 | 1.0      | T20   | 1.42<br>- 1.80 | 30 ±0.75 | 05LP3003001 |
|       |                |                |                                              |            |                  |                |          |       |                | 8 ±0.50  | 05LP4000801 |
|       |                |                |                                              |            |                  |                |          |       |                | 10 ±0.50 | 05LP4001001 |
|       |                |                |                                              |            |                  |                |          |       |                | 12 ±0.75 | 05LP4001201 |
|       |                |                |                                              |            |                  |                |          |       |                | 16 ±0.75 | 05LP4001601 |
|       |                |                |                                              |            |                  |                |          |       |                | 20 ±0.75 | 05LP4002001 |
| MM5.0 | 4.91<br>- 5.02 | 4.83<br>- 4.94 | 2 x 0.8                                      | 2.90       | 10.50<br>- 11.00 | 3.65<br>- 4.08 | 1.2      | T25   | 1.90<br>- 2.30 | 25 ±0.75 | 05LP4002501 |
|       |                |                |                                              |            |                  |                |          |       |                | 30 ±0.75 | 05LP4003001 |
|       |                |                |                                              |            |                  |                |          |       |                | 35 ±0.75 | 05LP4003501 |
|       |                |                |                                              |            |                  |                |          |       |                | 10 ±0.50 | 05LP5001001 |
|       |                |                |                                              |            |                  |                |          |       |                | 12 ±0.75 | 05LP5001201 |
|       |                |                |                                              |            |                  |                |          |       |                | 16 ±0.75 | 05LP5001601 |
| MM5.0 | 4.91<br>- 5.02 | 4.83<br>- 4.94 | 2 x 0.8                                      | 2.90       | 10.50<br>- 11.00 | 3.65<br>- 4.08 | 1.2      | T25   | 1.90<br>- 2.30 | 20 ±0.75 | 05LP5002001 |
|       |                |                |                                              |            |                  |                |          |       |                | 25 ±0.75 | 05LP5002501 |
|       |                |                |                                              |            |                  |                |          |       |                | 30 ±0.75 | 05LP5003001 |
|       |                |                |                                              |            |                  |                |          |       |                | 35 ±0.75 | 05LP5003501 |
|       |                |                |                                              |            |                  |                |          |       |                | 40 ±0.75 | 05LP5004001 |
|       |                |                |                                              |            |                  |                |          |       |                |          |             |

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros



www.acument.com

© 2008 Acument Intellectual Properties, LLC

Torx® is a trademark of Acument Intellectual Properties, LLC. Fastite® 2000™ is Licensed by Research Engineering & Manufacturing, Inc. page 1/2  
Data shown is subject to change without prior notice as a result of continuous product development and improvement policy.  
Your local Acument Global Technologies representative is at your disposal should you need to confirm latest information.

# Fastite® 2000™ 05LP

| Ø     | Ø C            | Ø D            | Pitch / Pas/<br>Steigung/<br>Passo /<br>Paso | Cp<br>max. | Ø Dk             | K              | s<br>ca. | Torx® | t              | L        | Part No/ref |
|-------|----------------|----------------|----------------------------------------------|------------|------------------|----------------|----------|-------|----------------|----------|-------------|
| MM6.0 | 5.90<br>- 6.03 | 5.80<br>- 5.93 | 2 x 1.0                                      | 3.40       | 13.00<br>- 13.50 | 4.46<br>- 5.00 | 1.4      | T30   | 2.28<br>- 2.67 | 12 ±0.75 | 05LP6001201 |
|       |                |                |                                              |            |                  |                |          |       |                | 16 ±0.75 | 05LP6001601 |
|       |                |                |                                              |            |                  |                |          |       |                | 20 ±0.75 | 05LP6002001 |
|       |                |                |                                              |            |                  |                |          |       |                | 25 ±0.75 | 05LP6002501 |
|       |                |                |                                              |            |                  |                |          |       |                | 30 ±0.75 | 05LP6003001 |
|       |                |                |                                              |            |                  |                |          |       |                | 35 ±0.75 | 05LP6003501 |
|       |                |                |                                              |            |                  |                |          |       |                | 40 ±0.75 | 05LP6004001 |
|       |                |                |                                              |            |                  |                |          |       |                | 45 ±0.75 | 05LP6004501 |
|       |                |                |                                              |            |                  |                |          |       |                | 50 ±0.75 | 05LP6005001 |
| MM8.0 | 7.87<br>- 8.03 | 7.71<br>- 7.91 | 2 x 1.25                                     | 4.80       | 16.20<br>- 17.00 | 6.00<br>- 6.60 | 1.8      | T40   | 2.79<br>- 3.18 | 16 ±0.75 | 05LP8001601 |
|       |                |                |                                              |            |                  |                |          |       |                | 20 ±0.75 | 05LP8002001 |
|       |                |                |                                              |            |                  |                |          |       |                | 25 ±0.75 | 05LP8002501 |
|       |                |                |                                              |            |                  |                |          |       |                | 30 ±0.75 | 05LP8003001 |
|       |                |                |                                              |            |                  |                |          |       |                | 35 ±0.75 | 05LP8003501 |
|       |                |                |                                              |            |                  |                |          |       |                | 40 ±0.75 | 05LP8004001 |
|       |                |                |                                              |            |                  |                |          |       |                | 45 ±0.75 | 05LP8004501 |
|       |                |                |                                              |            |                  |                |          |       |                | 50 ±0.75 | 05LP8005001 |

all dimensions in mm / en millimètres / alle Maße in mm / in millimetri / en milímetros

Quality level / Niveau qualité / Qualitätsniveau / Livello qualità / Nivel de calidad: 150 ppm

Optional heat treatment : surface hardness 570 - 700 HV

Traitement thermique optionnel: dureté superficielle 570 - 700 HV


Optionale Wärmebehandlung: Oberflächenhärte 570 - 700 HV

Trattamento termico opzionale: durezza superficiale 570 - 700 HV

Tratamiento térmico opcional: Dureza superficial 570 - 700 HV

Highlighted part numbers are non standard, non in stock - Références surlignées non standard et non tenues en stock - Markierte Artikel-Nummern sind kein Standard, keine Lagerware - I codici evidenziati non sono standard, non sono a stock - Referencias no estándar, generalmente no en stock

## Finishes / finition / Oberflächen / superficie / superficie

| Type     | Description / description / Beschreibung / descrizione / descripción                                                                                                                                                                                                                                                                                                |  |  | Code <sup>4)</sup> |
|----------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--------------------|
| Standard | Zinc alkaline 8 µm mini clear, friction 0.12 - 0.18 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.12 - 0.18 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.12 - 0.18 | ✓                                                                                     | 96 h                                                                                  | <sup>3)</sup> AB   |
| Optional | Zinc alkaline 8 µm mini clear, friction 0.12 - 0.18 / Zinc alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink alkalisch 8µm min. transparent, Reibkoeffizient 0.12 - 0.18 / Zinco alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Zincado y pasivado claro min. 8 µm coeficiente de fricción 0.12 - 0.18 | ✓                                                                                     | 400 h                                                                                 | AC                 |
| Optional | Zinc-nickel alkaline clear, friction 0.12 - 0.18 / Zinc-nickel alcalin 8µm mini passivation claire, coefficient de frottement 0.12 - 0.18 / Zink-Nickel alkalisch transparent, Reibkoeffizient 0.12 - 0.18 / Zinco Nickel alcalino 8µm min. passivazione chiara, coefficiente d'attrito 0.12 - 0.18 / Niquelado claro min. 8 µm coeficiente de fricción 0.12 - 0.18 | ✓                                                                                     | 720 h                                                                                 | BA                 |
| Optional | Zinc-nickel alkaline black, friction 0.12 - 0.18 / Zinc-nickel alcalin 8µm mini passivation noir, coefficient de frottement 0.12 - 0.18 / Zink-Nickel alkalisch schwarz, Reibkoeffizient 0.12 - 0.18 / Zinco Nickel alcalino 8µm min. passivazione nera, coefficiente d'attrito 0.12 - 0.18 / Niquelado negro min. 8 µm coeficiente de fricción 0.12 - 0.18         | ✓                                                                                     | 720 h                                                                                 | BB                 |

3) to red rust / à la rouille rouge / bis Rotrost / alla ruggine rossa / al óxido rojo

4) add code to the part number / ajoutez le code à la référence / fügen Sie den Code zur Artikel-Nummer hinzu / aggiungere il codice alla referenza / añadir numeración a la referencia

