



STANDARD & RUGGED USB 2.0

FILE NO. E31150






3D cutaway diagram of a composite material structure. The structure consists of a red core and a grey shell. A yellow arrow points to the interface between the core and the shell, labeled "Increased".

*Through-hole
option*



Increased retention option

TYPE	B	S	PLATING	COLOR	TERMINATION	OTHER OPTION
USB = Standard Connector	–F = Gold Flash on Mating Area, Tin on Tails	–S = 30μ" (0,76 μm) Gold on Mating Area, Tin on Tails	–B = Black (USB only)	–W = White (USB only)	–TH = Through-hole	–TR = Tape and Reel Packaging (–SM only)
USB-R = Increased Retention Connector (Complies with Class 1, DIV II minimum withdrawal requirement of 15N.)			–O = Orange (USB-R only)		–SM = Surface Mount (USB only)	
					–VT = Vertical Top Entry	


MATING / UNMATING FORCE (100 CYCLES)		
SERIES	MATING	UNMATING
USB	5.3 (23,59N)	6.1 (27,15N)
USBR	11.8 (52,51N)	11.5 (51,18N)



-5M



-TH

 $-\nabla T$