





LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
A		REV PER ECOS11-0201-04		21JUN2005	GA	SF	
B		REV PER ECO-07-004583		02MAR2007	RG	JW	
B1		REVISED PER ECO-10-000445		11JAN10	KK	AEG	




- △ HOUSING: PCT POLYESTER, BLACK, UL 94V-0. IR REFLOW PROCESS COMPATIBLE
TERMINALS: 0.305 THICK PHOS BRONZE PLATED WITH 1.27µm MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 2.03µm MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27µm MINIMUM THICK NICKEL UNDERPLATE.
SHIELD: 0.196 THICK COPPER ALLOY PLATED WITH 1.27µm MINIMUM NICKEL AND 2.03µm MINIMUM HOT TIN DIP ON PCB GROUND TABS.
- △ JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F
- △ PCB HOLES ONLY REQUIRED FOR 6339170-1
- △ USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES
5. RECOMMENDED APPLICATIONS: FAST ETHERNET, AND 10/100 BASE-T ETHERNET (CAT 5 TWO PAIR 1/2, 3/6)
- △ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI




6	OBSOLETE	NONE	6339170-2
		7	6339170-1
		NUMBER OF REAR PCB TABS	PART NO.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN: G. ATTADIA 21JUN2005		tyco AMP Incorporated	
mm		0 PLC ±.25		CHK: J. WESTMAN 21JUN2005		Electronics Harrisburg, PA 17105-3608	
		1 PLC ±.25		APVD: S. FLICKINGER 21JUN2005		NAME	
		2 PLC ±.25		PRODUCT SPEC		ASSEMBLY, STACKED JACK, 2X8, 8 POSITION, SHIELDED, WAVE PANEL GROUND	
		3 PLC ±.25		APPLICATION SPEC		SIZE	
		4 PLC ±.25		114-2048		CAGE CODE	
		ANGLES		WEIGHT		DRAWING NO	
		FINISH		A100779		C=6339170	
				CUSTOMER DRAWING		RESTRICTED TO	
						SCALE	
						4:1	
						SHEET	
						1	
						OF	
						2	
						REV	
						B1	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AA	22	-	-	SEE SHEET 1	-	-	-



PC BOARD LAYOUT VIEWED FROM COMPONENT SIDE OF BOARD
SCALE 4:1



SUGGESTED PANEL CUTOUT DIMENSIONS
SCALE 3:1

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DWN		21 JUN 2005		tyco <i>Electronics</i>		AMP Incorporated Harrisburg, PA 17105-3608	
				CHK		21 JUN 2005					
mm		0 PLC ±.25 1 PLC ±.25 2 PLC ±.25 3 PLC ±.25 4 PLC ±.25		APVD		21 JUN 2005		NAME		ASSEMBLY, STACKED JACK, 2X8, 8 POSITION, SHIELDED, WAVE PANEL GROUND	
		ANGLES ±.5 FINISH		PRODUCT SPEC		108-1163-9		APPLICATION SPEC			
MATERIAL		WEIGHT		SIZE		CASE CODE		DRAWING NO		RESTRICTED TO	
		-		A		100779		C=6339170		-	
CUSTOMER DRAWING				SCALE		4:1		SHEET		2 OF 2	
										REV B1	