


## STAK 25 (952 589)


Allows series connection (connection of two conductors) of surge protective devices up to 25 mm<sup>2</sup>  
 Allows EMC-optimised feed-through wiring according to IEC 60364-5-53



Figure without obligation



Use of STAK 25 with DEHNgard S



Dimension drawing STAK 25

Pin-shaped terminal for EMC-optimised feed-through wiring of lightning current and surge arresters according to IEC 60364-5-53

Type	STAK 25
Part No.	952 589
Nominal a.c./d.c. voltage (U <sub>N</sub> )	600 V
Nominal load current a.c. (I <sub>L</sub> )	100 A
Lightning impulse current (10/350 µs)	25 kA
Rated insulation voltage (U <sub>i</sub> )	630 V
Rated impulse withstand voltage (U <sub>imp</sub> )	6 kV
Operating temperature range (T <sub>U</sub> )	-40°C...+80°C
Cross-sectional area (min.)	1.5 mm <sup>2</sup> solid/flexible
Cross-sectional area (max.)	25 mm <sup>2</sup> stranded/16mm <sup>2</sup> flexible
Type of connection	front
Suitable for	DEHNgard S, DEHNgard M, DEHNshield, DK 25 feed-through terminal
PU	4 pc(s)
Weight	2,000 g
Customs tarif number	74199990
GTIN	4013364132306

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.