

Customer Information Sheet

SPECIFICATION:

MATERIAL:
MOULDING = PA9T, UL94V-0, BLACK
CONTACT = BRASS
FINISH = 0.76-1.52µ NICKEL ALL OVER,
0.012µ MIN GOLD ON CONTACT AREA,
2.54-5.08µ 100% TIN ON TAILS



ELECTRICAL:
CURRENT RATING = 1A
CONTACT RESISTANCE = 20mΩ MAX
INSULATION RESISTANCE = 1000MΩ MAX
VOLTAGE PROOF = 500V AC FOR ONE MINUTE

MECHANICAL:
DURABILITY = 500 CYCLES

ENVIRONMENTAL:
OPERATING TEMPERATURE = -40°C TO +105°C

PACKING:
SEE ORDER CODE
FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C029XX (LATEST ISSUE)

NOTES:
1. FOR TAPE AND REEL DETAILS, SEE SHEET 4.






ORDER CODE:

M50-363XX42X

No. OF CONTACTS: 02 TO 06, 08, 10, 20

PACKING: BLANK = TUBE
R = TAPE AND REEL (SHEET 4)



SB	I	02.08.16	----
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		S.BENNETT	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

1.27mm PITCH, SIL VERTICAL
SMT HEADER

DRAWING NUMBER:

M50-363XX42X

SHT
3
OF
4

Customer Information Sheet

DRAWING No.: M50-363XX42X

SHEET 4 OF 4

IF IN DOUBT - ASK

©



NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



TAPE DETAILS FOR
02, 03, 04, 05, 06, 08 & 10 WAYS ONLY

TAPE DETAILS FOR 20 WAY ONLY



NOTES:
1. FOR CONNECTOR DETAILS AND SPECIFICATIONS, SEE SHEET 3.
2. PRODUCT IS TAPE AND REELED IN GENERAL ACCORDANCE
WITH EIA-481 (ELECTRAL INDUSTRIES ASSOCIATION).

ORDER CODE: **M50-363XX42X**
No. OF CONTACTS: _____
02 TO 06, 08, 10, 20
PACKING: _____
BLANK = TUBE
R = TAPE AND REEL (SHEET 1)



PART No.	DIMENSION			REEL QUANTITY
	DIM 'A'	DIM 'B'	DIM 'C'	
M50-3630242R	16.00±0.30	7.50	3.54	800
M50-3630342R			4.81	
M50-3630442R			6.08	
M50-3630542R			7.35	
M50-3630642R	24.00±0.30	11.50	8.62	
M50-3630842R			11.16	
M50-3631042R			13.70	
M50-3632042R			26.40	

SB	I	02.08.16	----
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		S.BENNETT	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:
SEE ABOVE
FINISH: SEE ABOVE
S/AREA: mm²

TITLE:
1.27mm PITCH, SIL VERTICAL
SMT HEADER
DRAWING NUMBER:
M50-363XX42X
SHT
4 OF 4