

DESCRIPTION: DIP SOLDER FEMALE/STAMPED

SPECIFICATIONS:



MATERIALS:

SHELL: STEEL, NICKEL PLATED
INSULATOR: UL 94V-0 RATED BLACK NYLON 9T
CONTACTS: BRASS, GOLD PLATED
RoHS COMPLIANT

ELECTRICALS:

CURRENT RATING: 5 AMPS
CONTACT RESISTANCE: 15 MOHMS MAX
INSULATOR RESISTANCE: 1000 MOHMS MIN
VOLTAGE: 500V AC FOR 1 MINUTE
TEMPERATURE: -50°C TO +100°C

POS.	A	B	C	D	E	F	G
09	1.213	0.984	0.642	0.756	0.311	0.109	0.496
	30.80	24.99	16.30	19.20	7.90	2.77	12.60
15	1.541	1.312	0.971	1.091	0.311	0.109	0.496
	39.14	33.32	24.65	27.70	7.90	2.77	12.60
25	2.087	1.852	1.512	1.618	0.311	0.109	0.496
	53.00	47.04	38.40	41.10	7.90	2.77	12.60
37	2.728	2.500	2.157	2.256	0.311	0.109	0.496
	69.29	63.50	54.80	57.30	7.90	2.77	12.60
50	2.638	2.406	2.055	2.169	0.429	0.109	0.602
	67.00	61.00	52.20	55.10	10.90	2.77	15.30



171-YYY-213RYY1

SERIES
POSITIONS
009
015
025
037
050
GENDER
1 = MALE
2 = FEMALE
TERMINATION
1 = DIP SOLDER
SHELL PLATING
3 = NICKEL
HARDWARE OPTIONS
00 = NO HARDWARE
01 = .098" 4-40 CLINCH NUT BOARD SIDE
02 = .236" 4-40 CLINCH NUT BOARD SIDE
03 = .236" 4-40 CLINCH NUT MATING SIDE
05 = .237" 4-40 BOARD LOCK
08 = .228" 4-40 BOARD LOCK
90 = .237" 4-40 BOARD LOCK
FOR 0.093" BOARD
91 = .237" 4-40 SPACER/BOARD LOCK
92 = .237" 4-40 SPACER/BOARD LOCK
FOR 0.093" BOARD
PLATING OPTIONS
1 = GOLD FLASH
2 = 30 MICRO-INCH GOLD

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

DATE:
8-12-98

CHECKED:

DATE:

SCALE:

SHEET

OF

1

3

REV






11

DWG NO.

171-YYY-213RYY1

RoHS COMPLIANT

NorComp



* TYP. ON ALL SIZES


DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-08-06		
		CHECKED:		DATE:		
NorComp		SCALE: FULL		SHEET 2 OF 3		REV 11
		DWG NO. 171-YYY-213RYY1				


ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS

TOLERANCE:
ALL DIMENSIONS ARE ±0.010


01X 0.098" (BOARD SIDE) - CN1




02X 0.236" (BOARD SIDE) - CN2




03X..... 0.236" (MATING SIDE) - CN8




05X 0.237" (BOARD SIDE) - CN10




08X 0.228" (BOARD SIDE) - CN3




91X 0.237" BOARD SIDE
0.197 MATING SIDE
CN10/SFSO4404



90X 0.237" (BOARD SIDE) - CN10-237-093



92X 0.237" BOARD SIDE
0.197 MATING SIDE
CN10-237-093/SFSO4404



NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

NOTE: 4-40 FEMALE SCREW LOCK IS REMOVABLE

NOTE: 90 & 92 OPTION FOR 0.093" MAX. BOARD THICKNESS

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.		DRAWN: WAYNE ROBBINS		DATE: 11-28-05	
			CHECKED:		DATE:	
	NorComp		SCALE:	SHEET 3	OF 3	REV 11
DWG NO. 171-YYY-213RYY1						