



Ring Terminal T&B Catalog Number:

UPC Number:

D10361

Status:

78621082955

Description:

Active

Non-Insulated - Tubular Ring Terminal For Wire Range 8 Stud Size #10, Metallic, Military Specified (MIL-SPEC MS20659-107)


WEB_USE

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

Features

These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).



General

Insulation Type	Non-Insulated - Tubular
Terminal Series	D
Material	Copper
Finish	Electro -Tin Plated
Color	Metallic
Wire Range	8
Stud Size	#10

Dimension Information

Stock Thickness	.04
A (inches)	1.15
B (inches)	.41
C (inches)	.28
M (inches)	.95

Specifications

Temperature Rating	150°C
Voltage Rating	600V
Flammability Rating	UL 94 V-0
MIL Specification	MS-20659-107

Tooling

Tool Charts	Available on Website
Application Tools	WT115A, TBM6, TBM6S, WT3185
Recommended Tool	ERG4005, ERG4008

Packaging

T&B Order Multiple	200
T&B Inner Pack	200
Package in Units	2000
Package Type	Standard
T&B Sold in UOM	Each
T&B Weight Per UOM	0.97 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000168
Overview	Available on Website

Wire Guide Tables

Available on Website

Notes

Not available on Mylar Tape.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com