

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0681631310

Status:

Obsolete

Overview:


sherlock

Description:

2.00mm (.079") Pitch Sherlock™ II Wire-to-Board Header, Right Angle, with Positive Lock, 13 Circuits

Replacement Part Number:

NONE



Series
image - Reference only

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	68163
Application	Signal, Wire-to-Board
Obsolete Date	2001/08/01
Overview	sherlock
Product Name	Sherlock™
Replacement Part Number	NONE

Physical

Breakaway	No
Circuits (Loaded)	13
Circuits (maximum)	13
Color - Resin	Natural
Durability (mating cycles max)	30
Flammability	94V-0
Glow-Wire Compliant	No
Lock to Mating Part	None
Material - Resin	Nylon
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.20mm (.126")
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Bag
Pitch - Mating Interface	2.00mm (.079")
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C

Electrical

Current - Maximum per Contact	2A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-68163-001
Product Specification	PS-35585-001
Sales Drawing	SD-68163-001

<u>EU RoHS</u>	<u>China RoHS</u>
Compliance Status	
Not Reviewed	
REACH SVHC	
Not Reviewed	
Low-Halogen Status	
Not Reviewed	

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
68163Series

Mates With
35585

This document was generated on 05/03/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION