









THIS DRAWING IS A CONTROLLED DOCUMENT. DWG NO 1583001

TOOL NUMBER 	WIRE SIZE mm ² [AWG] 	INSULATION DIAMETER mm [in.] 	INSUL. ADJ. 	FLIP LOCATOR 	STRIP LENGTH mm [in.] 	CRIMP HEIGHT mm [in.] 	CONTACT PART NUMBERS 		CONTACT DESCRIPTION	APPLIC. SPECIF.
							LOOSE PIECE 	STRIP FORM 		
91501-1 91501-3	0.2 - 0.38 [24-22]	1.52 MAX [.060 MAX]	YES	NO	3.18 ± 0.38 [.125 ± .015]	0.74 ± 0.05 [.029 ± .002]	794610-[]	794606-[]	Micro MATE-N-LOK Contacts	114-13000
	0.5-0.6 [20]					0.89 ± 0.05 [.035 ± .002]				
91502-1 91502-3	0.05-0.15 [26-30]	1.52 MAX [.060 MAX]	YES	NO	3.81 ± 0.38 [.150 ± .015]	0.58 ± .05 [.023 ± .002]	794611-[]	794607-[]	Micro MATE-N-LOK Contacts	114-13000
91504-1 91504-3	0.5 - 2.1 [20-14]	2.54 - 3.3 [.100-.130]	YES	NO	4.75 ± 0.38 [.187 ± .015]	1.35 ± 0.05 [.053 ± .002]	60619-[] 60620-[] 170121-[]	61117-[] 61118-[] 170120-[]	Commercial MATE-N-LOK contacts	114-1012
	(Two Wires Total) 0.8-0.9[18] plus (+) 0.8-1.4[18-16]	2.92 MAX [.115 MAX]				1.63 ± 0.08 [.064 ± .003]	350638-[] 350639-[]	350557-[] 350558-[] 917636-1		
91512-1 91512-3	0.20 - 0.56 [24-20]	1.52 - 2.54 [.060-.100]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002]	61473-[] 60618-[] 60617-[] 170148-[]	61115-[] 61116-[] 61314-[] 170147-[]	Commercial MATE-N-LOK contacts	114-1012
	0.75 - 0.96 [18]					1.24 ± 0.05 [.049 ± .002]				
91528-1 91528-3	0.2 - 0.6 [24-20]	1.09-1.91 [.043-.075]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002]	61473-[] 60618-[] 60617-[]	61115-[] 61116-[] 61314-[]	Commercial MATE-N-LOK contacts	114-1012
	0.8 - 0.9 [18]	1.52-2.54 [.060-.100\]				1.24 ± 0.05 [.049 ± .002]				
91597-1 91597-3	0.20 - 0.56 [24-20]	1.52 - 2.54 [.060-.100]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002]	640706-[] 640707-[] 770258-[] 770522-[]	640252-[] 350980-[] 770476-[]	SL-156 receptacles	114-1021
	0.75 - 0.89 [18]					1.24 ± 0.05 [.049 ± .002]			BIFURCATED LEAF CONTACT	114-1015
91598-1 91598-3	0.2 - 0.6 [24-20]	1.09-1.91 [.043-.075]	YES	NO	4.75 ± 0.38 [.187 ± .015]	0.99 ± 0.05 [.039 ± .002]	640706-[] 640707-[] 770258-[] 770522-[]	640252-[] 350980-[] 770476-[]	SL-156 receptacles	114-1021
	0.8 - 0.9 [18]	1.52-2.54 [.060-.100\]				1.24 ± 0.05 [.049 ± .002]			BIFURCATED LEAF CONTACT	114-1015

-  LIST OF APPLIED CONTACT PART NUMBERS IS SUBJECT TO CHANGE. FOR CURRENT INFORMATION, CONTACT THE TOOLING ASSISTANCE CENTER : 1-800-722-1111.
2. AMP, CERTI-CRIMP, and MATE-N-LOK are trademarks.
-  -1 IS A CERTICRIMP II HAND TOOL ASSEMBLY.
-3 IS A CERTICRIMP II HEAD SUB-ASSEMBLY.
4. THE HAND TOOL INSTRUCTION SHEET, ALSO KNOWN AS AN "IS", FOR MOST CERTI-CRIMP II TOOLS USE IS 408-8547. IF THE TOOL HAS A FLIP LOCATOR USE IS 408-10414.

CERTI-CRIMP II DATA SHEET

DWN	21FEB2012	MATERIAL	-	HEAT TREAT	-
CHK	22FEB2012				
B.A. WOLFE					
APVD	22FEB2012				
B.A. WOLFE					
NAME					
CERTI-CRIMP II TOOL DATA SHEET					
MATE-N-LOK CONTACT FAMILY					
SCALE	-	SIZE	A1	DRAWING NO	1583001
				SHEET	1 of 1
				REV	B5

0	PLC	± -
1	PLC	± -
2	PLC	± -
3	PLC	± -
4	PLC	± -

ANGLES±	-
SURFACE TEXTURE	✓

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TFCO. IT IS TO BE KEPT UNCLASSIFIED AND UNCONTROLLED UNLESS AND UNLESS OTHERWISE SPECIFIED BY THE TFCO. IT IS TO BE KEPT UNCLASSIFIED AND UNCONTROLLED UNLESS AND UNLESS OTHERWISE SPECIFIED BY THE TFCO. IT IS TO BE KEPT UNCLASSIFIED AND UNCONTROLLED UNLESS AND UNLESS OTHERWISE SPECIFIED BY THE TFCO.

LOC
A
DIST
00