



Artikel-Nr.: 741387



Bez.: TNC-Crimpkupplung, Teflon-Isolation, Aircom Plus / Ecoflex 10

NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)

1. BODY: BRASS PER JIS-C3604
2. CONTACT: BRASS PER JIS-C3604
3. CONNECTOR INTERFACE PER MIL-STD-348A
4. PART TO BE CLEAN AND FREE BURRS
5. NICKEL PL. 70 μ " THICK OVER COPPER STRIKE
6. GOLD PL. 1-3 μ " OVER NICKEL PL. 70 μ " THICK OVER COPPER STRIKE



Impedance	50 Ω
Frequency range	0 to 4GHz
Voltage rating	500 volts peak
Dielectric withstanding voltage	1500 volts rms
VSWR	M39012 straight connectors: 1.3 max. 0-4GHz M39012 right angle: 1.3 max. 0-4GHz
Temperature range	-55°C+165°C
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact 1.5 m Ω outer contact 0.2 m Ω Insertion loss: 0.2db max at 3.0GHz Insulation resistance: 5000 megohms(min)



- 1: CRIMPED CONTACT
HEX CRIMP SIZE: .137"
- 2: CRIMPED FERRULE
HEX CRIMP SIZE: .429"

4	Ferrule	Brass	Nickel
3	Insulator	Teflon	White
2	Contact	Brass	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

www.bkl-electronic.de

Technische Änderungen vorbehalten. Ausführungen können variieren. Sollten Sie ein Muster benötigen kontaktieren Sie uns bitte.

BKL-ELECTRONIC Kreimendahl GmbH • Märkenstück 14 • 58509 Lüdenscheid

Tel: +49 (0)2351-3621-0 • Fax: +49 (0)2351-3621-29 • info@bkl-electronic.de

