

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO. **	PANEL THICKNESS	A	B	C	D	E	F *	G *
						REF.	REF.	REF.
GE _ 36FR-C	TO 0.036 (0.91)	0.025 (0.64)	0.045 (1.14)	0.097 (2.21)	0.030 (0.78)	0.106 (2.69)	.105	0.150 (3.81)
GE _ 62FR-C	0.036 - 0.062 (0.91)-(1.57)	0.035 (0.89)	0.070 (1.78)	0.130 (3.30)	0.030 (0.78)	0.131 (3.33)	.105	0.150 (3.81)
GE _ 99FR-C	0.062 - 0.099 (1.57)-(2.51)	0.054 (1.37)	0.108 (2.74)	0.155 (3.94)	0.030 (0.78)	0.169 (4.29)	.125	0.150 (3.81)
GE _ 144FR-C	0.099 - 0.144 (2.51)-(3.66)	0.080 (2.29)	0.152 (3.86)	0.192 (4.88)	0.030 (0.78)	0.213 (5.41)	.160	0.150 (3.81)
GE _ 189FR-C	0.144 - 0.189 (3.66)-(4.80)	0.125 (3.18)	0.206 (5.23)	0.255 (6.48)	0.046 (1.17)	0.297 (7.55)	—	—



NOTES:

* 1) DIM'S F & G APPLY ONLY TO SLOTTED GROMMET EDGING.


** 2) PART NO. EXAMPLE:

GE S 36 FR - C
 100 FOOT ROLL
 FR=FLAME RETARDANT POLYETHYLENE
 MAX. PANEL THICKNESS
 S=SOLID
 E=SLOTTED
 GROMMET EDGING

- 3) SEE CURRENT PRICE SHEET FOR PART NO. SUFFIX DESIGNATION FOR PACKAGE SIZE.
 4) COLOR: NATURAL
 5) SLOTTED WALL STYLE IS RECOMMENDED FOR INSIDE EDGE OF PANEL CUT OUTS.
 SOLID WALL STYLE IS RECOMMENDED FOR STRAIGHT, OUTSIDE EDGES.



SOLID WALL



SLOTTED WALL

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

OLD FILENAME/LAYERS

GB0281BA_PB_FRGROMEDGE_03A

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

FLAME RETARDANT POLYETHYLENE
GROMMET EDGING

3	6/12/02	LGG		UPDATED DIM 'F' AS REFERENCE	GB0281BA	3				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.1(2.5) (.XXX) ±0.020(1.5) (.XX) ±0.05(1.3) ANGLES ±5°	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
2	8-5-98	JAD		ADDED NOTE #5, UPDATED FILE NAME	GB0281BA	2					
1	3-24-94	JAD		ADDED GE_189FR-C AND RELATED DIM'S	GB0281BA	1				DRAWN BY SJSU	SCALE NONE
R	4-15-93	SJSU		INITIAL RELEASE	GB0281BA	R				DATE 4-15-93	DRAWING NO. GB0281BA
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP			SEE NOTE #2	DWG SIZE A