





1 CAP MAY BE ROTATED OR REVERSED
TO PERMIT COMPLETE CABLE RANGE
TO BE TAKEN EITHER IN LINE OR
90° TO STUD.



A COPPER STUD	COMPLETE CONDUCTOR RANGE SEE NOTE #1				FIGURE 1																				
	AA COPPER CABLE COMPLETE RANGE SEE NOTE 1		COPPER IPS RANGE		"X" GROOVE		"XX" GROOVE		Z GROOVE		ZZ GROOVE		CATALOG NUMBER	FIG. NO.	B	BB	H	J	JJ	L	R	W	Y	E	REF. DWG.
	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.	MIN.	MAX.													
1/2-13	6 SOL.	4/0 STR.	—	—	6 SOL.	1 STR.	2/0 SOL.	4/0 STR.	—	—	—	—	NDR6328T13	2	1.53	1.82	1.74	3/8-16	3/8-16	3.60	1.22	1.82	.94	1.06	FC31959
3/4-16	6 SOL.	4/0 STR.	—	—	6 SOL.	1 STR.	2/0 SOL.	4/0 STR.	—	—	—	—	NDR6428T16	2	1.53	1.82	1.74	3/8-16	3/8-16	3.60	1.22	2.00	1.07	1.06	FC31957
3/4-16	6 SOL.	500 MCM	3/8	1/2	250 MCM	350 MCM	400 MCM	500 MCM	6 SOL.	2 STR.	1/0 SOL.	4/0 STR.	NDR6434T16	1	1.53	2.19	2.24	3/8-16	3/8-16	4.09	1.47	2.19	1.07	1.44	FC31956
1"-14	6 SOL.	4/0 STR.	—	—	6 SOL.	1 STR.	2/0 SOL.	4/0 STR.	—	—	—	—	NDR6528T14	2	1.53	1.82	1.74	3/8-16	3/8-16	4.09	1.38	2.19	1.19	1.06	FD31358
1"-14	6 SOL.	500 MCM	3/8	1/2	250 MCM	350 MCM	400 MCM	500 MCM	6 SOL.	2 STR.	1/0 SOL.	4/0 STR.	NDR6534T14	1	1.53	2.19	2.24	3/8-16	3/8-16	3.96	1.45	2.28	1.19	1.44	FD31955
1 1/8-12	6 SOL.	4/0 STR.	—	—	6 SOL.	1 STR.	2/0 SOL.	4/0 STR.	—	—	—	—	NDR65528T12	2	1.53	1.82	1.74	3/8-16	3/8-16	4.12	1.46	2.25	1.25	1.06	FD31954
1 1/8-12	6 SOL.	500 MCM	3/8	1/2	250 MCM	350 MCM	400 MCM	500 MCM	6 SOL.	2 STR.	1/0 SOL.	4/0 STR.	NDR65534T12	1	1.53	2.19	2.24	3/8-16	3/8-16	3.97	1.50	2.38	1.25	1.44	FD31953
1 1/8-12	2 SOL.	1000 MCM	3/8	3/4	550 MCM	700 MCM	750 MCM	1000 MCM	2 SOL.	250 MCM	300 MCM	500 MCM	NDR65544T12	1	1.53	2.88	2.82	3/8-16	1/2-13	4.66	1.94	2.88	1.25	1.88	FD31952
1 1/2-12	6 SOL.	4/0 STR.	—	—	6 SOL.	1 STR.	2/0 SOL.	4/0 STR.	—	—	—	—	NDR6728T12	2	2.09	1.82	2.24	1/2-13	3/8-16	4.75	1.88	2.62	1.62	1.06	FD31951
1 1/2-12	6 SOL.	500 MCM	3/8	1/2	250 MCM	350 MCM	400 MCM	500 MCM	6 SOL.	2 STR.	1/0 SOL.	4/0 STR.	NDR6734T12	1	2.09	2.19	2.32	1/2-13	3/8-16	4.94	1.96	2.75	1.62	1.44	FD31950
1 1/2-12	2 SOL.	1000 MCM	3/8	3/4	550 MCM	700 MCM	750 MCM	1000 MCM	2 SOL.	250 MCM	300 MCM	500 MCM	NDR6744T12	1	2.09	2.19	2.82	1/2-13	1/2-13	5.10	1.96	3.00	1.62	1.75	FD54215
1 1/2-12	4/0 STR.	2000 MCM	3/8	1 1/4	1250 MCM	1600 MCM	1700 MCM	2000 MCM	4/0 STR.	600 MCM	650 MCM	1200 MCM	NDR6748T12	1	2.03	3.38	3.25	1/2-13	1/2-13	5.73	2.28	3.38	1.66	2.38	FD31948
3/4-16	2 SOL.	1000 MCM	3/8	3/4	550 MCM	700 MCM	750 MCM	1000 MCM	2 SOL.	250 MCM	300 MCM	500 MCM	NDR6444T16	1	1.53	2.88	2.82	3/8-16	1/2-13	4.66	1.92	2.88	1.07	1.88	FD32906
1"-14	2 SOL.	1000 MCM	3/8	3/4	550 MCM	700 MCM	750 MCM	1000 MCM	2 SOL.	250 MCM	300 MCM	500 MCM	NDR6544T14	1	1.53	2.88	2.82	3/8-16</							

20	12-71	SHIT TWO ADDED	(2035171)	CAR	JPS
19	7-11-68	NDR6648T12 ADDED MK.	(Q701-274)	PTM	JFS
18	3-19-66	SEE REV. REF. PRINT	(DC3529)	CAR	JHB
17	8-5-65	NDR 675 48T12 ADDED MK.	(Q252-577)	JPS	PTM
16	7-1-65	REV. REF. PRINT MK.	(SUPP. EC31404)	JPS	MTM
15	4-19-65	REV. REF. PRINT APP. MK.	(EC31404)	JL	MTM
14	4-6-61	REPRODUCED WITHOUT CHANGE		JA	RED
REV.	DATE	REVISION DESCRIPTION		BY	CHK'D.

STUD CONNECTOR	
CAT. NO. NDR - (TABLE)	SCALE 1" = 1'
DRAWN 9-15-54 E.R.D.	CHECKED A.K.K. 9-15-54

BURN DY
Corporation
NORWALK, CONNECT.

DRAWING NO.	REV.
SD31476	2
SHIT 1 OF 2	