


## 374 Series, TR5®, Time-Lag Fuse



### Agency Approvals

| Agency | Agency File Number      | Ampere Range |
|--------|-------------------------|--------------|
|        | File number:<br>E 67006 | 50mA - 6.3A  |
|        | Certification:<br>51378 | 50mA - 6.3A  |
|        | File number:<br>E 67006 | 8A - 10A     |

### Description

The TR5® 374 Series are time-Lag 250V rated fuses, that are designed in accordance to UL 248-14.

### Features

- Lead-free
- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shock safe casing
- Vibration resistant
- Halogen free
- Available from 50mA to 10A

### Applications

- Battery Chargers
- Consumer Electronics
- Power supplies
- Industrial Controllers

### Electrical Characteristics

| % of Ampere Rating | Opening Time |
|--------------------|--------------|
| 200%               | 60 Seconds,  |

### Additional Information



**Datasheet**



**Resources**




**Samples**

## Electrical Characteristics


| Amp Code | Rated Current       | Voltage Rating | Breaking Capacity                               | Voltage Drop<br>$1.0 \times I_N$<br>max. (mV) | Power Dissipation<br>$1.0 \times I_N$<br>max. (mW) | Melting Integral<br>$10 \times I_N$<br>min. (A <sup>2</sup> s) | Agency Approvals |    |       |
|----------|---------------------|----------------|-------------------------------------------------|-----------------------------------------------|----------------------------------------------------|----------------------------------------------------------------|------------------|----|-------|
|          |                     |                |                                                 |                                               |                                                    |                                                                | UL               | SP | cULus |
| 0050     | 50mA                | 250V           | 50 A / 250 VAC<br>50-60 Hz<br>$\cos \phi = 1.0$ | 900                                           | 45                                                 | 0.0056                                                         | x                | x  |       |
| 0063     | 63mA                | 250V           |                                                 | 800                                           | 50                                                 | 0.009                                                          | x                | x  |       |
| 0080     | 80mA                | 250V           |                                                 | 700                                           | 55                                                 | 0.014                                                          | x                | x  |       |
| 0100     | 100mA               | 250V           |                                                 | 600                                           | 60                                                 | 0.025                                                          | x                | x  |       |
| 0125     | 125mA               | 250V           |                                                 | 550                                           | 70                                                 | 0.044                                                          | x                | x  |       |
| 0160     | 160mA               | 250V           |                                                 | 480                                           | 80                                                 | 0.058                                                          | x                | x  |       |
| 0200     | 200mA               | 250V           |                                                 | 390                                           | 80                                                 | 0.1                                                            | x                | x  |       |
| 0250     | 250mA               | 250V           |                                                 | 350                                           | 90                                                 | 0.17                                                           | x                | x  |       |
| 0315     | 315mA               | 250V           |                                                 | 300                                           | 95                                                 | 0.26                                                           | x                | x  |       |
| 0400     | 400mA               | 250V           |                                                 | 250                                           | 100                                                | 0.32                                                           | x                | x  |       |
| 0500     | 500mA               | 250V           |                                                 | 220                                           | 110                                                | 0.6                                                            | x                | x  |       |
| 0630     | 630mA               | 250V           |                                                 | 210                                           | 135                                                | 0.75                                                           | x                | x  |       |
| 0800     | 800mA               | 250V           |                                                 | 160                                           | 130                                                | 0.98                                                           | x                | x  |       |
| 1100     | 1.00A               | 250V           |                                                 | 155                                           | 155                                                | 2.1                                                            | x                | x  |       |
| 1125     | 1.25A               | 250V           |                                                 | 145                                           | 185                                                | 3.2                                                            | x                | x  |       |
| 1160     | 1.60A               | 250V           |                                                 | 130                                           | 210                                                | 4.5                                                            | x                | x  |       |
| 1200     | 2.00A               | 250V           |                                                 | 125                                           | 250                                                | 7.5                                                            | x                | x  |       |
| 1250     | 2.50A               | 250V           |                                                 | 120                                           | 300                                                | 14                                                             | x                | x  |       |
| 1315     | 3.15A               | 250V           |                                                 | 110                                           | 350                                                | 22                                                             | x                | x  |       |
| 1400     | 4.00A               | 250V           |                                                 | 100                                           | 400                                                | 36                                                             | x                | x  |       |
| 1500     | 5.00A               | 250V           |                                                 | 95                                            | 475                                                | 59                                                             | x                | x  |       |
| 1630     | 6.30A               | 250V           |                                                 | 90                                            | 570                                                | 110                                                            | x                | x  |       |
| 1800     | 8.00A <sup>1</sup>  | 250V           |                                                 | 80                                            | 1000                                               | 150                                                            |                  |    | x     |
| 2100     | 10.00A <sup>1</sup> | 250V           |                                                 | 90                                            | 1250                                               | 280                                                            |                  |    | x     |

Note: 1.00 means the number one with two decimal places. 1,000 means the number one thousand.


## Temperature Derating Curve



## Average Time Current Curves



## Soldering Parameters - Wave Soldering



## Recommended Process Parameters:

| Wave Parameter                                              | Lead-Free Recommendation          |
|-------------------------------------------------------------|-----------------------------------|
| <b>Preheat:</b><br>(Depends on Flux Activation Temperature) | (Typical Industry Recommendation) |
| Temperature Minimum:                                        | 100° C                            |
| Temperature Maximum:                                        | 150° C                            |
| Preheat Time:                                               | 60-180 seconds                    |
| <b>Solder Pot Temperature:</b>                              | 260° C Maximum                    |
| <b>Solder Dwell Time:</b>                                   | 2-5 seconds                       |

## Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350° C +/- 5° C  
Heating Time: 5 seconds max.


**Note:** These devices are not recommended for IR or Convection Reflow process.

## Product Characteristics

|                                  |                                                                                                |
|----------------------------------|------------------------------------------------------------------------------------------------|
| <b>Materials</b>                 | Base/Cap: Brown Thermoplastic<br>Polyamide PA 6.6, UL 94 V-0<br>Round Pins: Copper, Tin-plated |
| <b>Lead Pull Strength</b>        | 10 N (EN 60068-2-21)                                                                           |
| <b>Solderability</b>             | 260°C, ≤ 3s. (Wave)<br>350°C, ≤ 1s. (Soldering Iron)                                           |
| <b>Soldering Heat Resistance</b> | 260°C, 10s. (IEC 60068-2-20)<br>350°C, 3s. (Soldering Iron)                                    |

|                              |                                                                                                                      |
|------------------------------|----------------------------------------------------------------------------------------------------------------------|
| <b>Operating Temperature</b> | -40°C to +85°C (consider de-rating)                                                                                  |
| <b>Climatic Category</b>     | -40°C/+85°C/21 days<br>(EN 60068-1,-2-1,-2-2,-2-78)                                                                  |
| <b>Stock Conditions</b>      | +10°C to +60°C<br>RH ≤ 75% yearly average, without dew, maximum value for 30 days-95%                                |
| <b>Vibration Resistance</b>  | 24 cycles at 15 min. each<br>(EN 60068-2-6)<br>10 - 60 Hz at 0.75 mm amplitude<br>60 - 2000 Hz at 10G's acceleration |

## Dimensions



## Part Numbering System

|                       |                                                                                                               |             |
|-----------------------|---------------------------------------------------------------------------------------------------------------|-------------|
| <b>374</b>            | <b>xxxx</b>                                                                                                   | <b>0000</b> |
| <b>Series</b>         |                                                                                                               |             |
| <b>Amp Code</b>       |                                                                                                               |             |
|                       | Refer to Amp Code column of Electrical Characteristics Table                                                  |             |
| <b>Packaging Code</b> |                                                                                                               |             |
|                       | 0000 Tape/Ammopack (1,000 pcs.)<br>0410 Short Leads - Bulk (1,000 pcs.)<br>0430 Short Leads - Bulk (200 pcs.) |             |

## Packaging

| Packaging Option  | Packaging Specification | Quantity | Quantity & Packaging Code | Taping Width |
|-------------------|-------------------------|----------|---------------------------|--------------|
| <b>374 Series</b> |                         |          |                           |              |
| Tape & Ammopack   | N/A                     | 1,000    | 0000                      | N/A          |
| Short Leads       | N/A                     | 1,000    | 0410                      | N/A          |
| Short Leads       | N/A                     | 200      | 0430                      | N/A          |