




N-Channel 30-V (D-S), 175°C, MOSFET PWM Optimized

PRODUCT SUMMARY


$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A) ^a
30	0.010 @ $V_{GS} = 10$ V	20
	0.014 @ $V_{GS} = 4.5$ V	18

FEATURES

- TrenchFET® Power MOSFET
- 175°C Maximum Junction Temperature
- 100% R_g Tested



Ordering Information: SUD50N03-10BP



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	30	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$) ^a	$T_A = 25^\circ\text{C}$	I_D	20	A
	$T_A = 100^\circ\text{C}$		14	
Pulsed Drain Current		I_{DM}	100	
Continuous Source Current (Diode Conduction) ^a		I_S	20	W
Maximum Power Dissipation	$T_C = 25^\circ\text{C}$	P_D	71 ^b	
	$T_A = 25^\circ\text{C}$		8.3 ^a	
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Typical	Maximum	Unit
Maximum Junction-to-Ambient ^a	$t \leq 10$ sec	R_{thJA}	15	18	$^\circ\text{C}/\text{W}$
	Steady State		40	50	
Maximum Junction-to-Case	Steady State	R_{thJC}	1.75	2.1	







Notes:

- a. Surface mounted on 1" x 1" FR4 Board, $t \leq 10$ sec.
b. See SOA curve for voltage derating.



MOSFET SPECIFICATIONS ($T_J = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$	30			V
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_{DS} = 250\text{ }\mu\text{A}$	0.8	2		
Gate-Body Leakage	I_{GSS}	$V_{DS} = 0\text{ V}, V_{GS} = \pm 20\text{ V}$			± 100	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS} = 24\text{ V}, V_{GS} = 0\text{ V}$			1	μA
		$V_{DS} = 24\text{ V}, V_{GS} = 0\text{ V}, T_J = 125^\circ\text{C}$			50	
		$V_{DS} = 24\text{ V}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$			150	
On-State Drain Current ^a	$I_{D(on)}$	$V_{DS} = 5\text{ V}, V_{GS} = 10\text{ V}$	50			A
Drain-Source On-State Resistance ^a	$r_{DS(on)}$	$V_{GS} = 10\text{ V}, I_D = 15\text{ A}$		0.0075	0.010	Ω
		$V_{GS} = 10\text{ V}, I_D = 15\text{ A}, T_J = 125^\circ\text{C}$			0.016	
		$V_{GS} = 10\text{ V}, I_D = 15\text{ A}, T_J = 175^\circ\text{C}$			0.019	
		$V_{GS} = 4.5\text{ V}, I_D = 15\text{ A}$		0.011	0.014	
Forward Transconductance ^a	g_{fs}	$V_{DS} = 15\text{ V}, I_D = 15\text{ A}$	20			S
Dynamic^b						
Input Capacitance	C_{iss}	$V_{GS} = 0\text{ V}, V_{DS} = 25\text{ V}, f = 1\text{ MHz}$		1500		pF
Output Capacitance	C_{oss}			530		
Reverse Transfer Capacitance	C_{rss}			240		
Total Gate Charge ^c	Q_g	$V_{DS} = 15\text{ V}, V_{GS} = 5\text{ V}, I_D = 20\text{ A}$		15.5	19	nC
Gate-Source Charge ^c	Q_{gs}			5		
Gate-Drain Charge ^c	Q_{gd}			6		
Gate Resistance	R_g		0.5		4.1	Ω
Turn-On Delay Time ^c	$t_{d(on)}$	$V_{DD} = 15\text{ V}, R_L = 0.3\text{ }\Omega$ $I_D = 20\text{ A}, V_{GEN} = 10\text{ V}, R_G = 2.5\text{ }\Omega$		10	18	ns
Rise Time ^c	t_r			8	15	
Turn-Off Delay Time ^c	$t_{d(off)}$			25	45	
Fall Time ^c	t_f			9	16	
Gate Resistance	R_g			2.3		Ω
Source-Drain Diode Ratings and Characteristics ($T_C = 25^\circ\text{C}$)^b						
Continuous Current	I_S				50	A
Pulsed Current	I_{SM}				100	
Forward Voltage ^a	V_{SD}	$I_F = 100\text{ A}, V_{GS} = 0\text{ V}$		1.2	1.5	V
Reverse Recovery Time	t_{rr}	$I_F = 20\text{ A}, di/dt = 100\text{ A}/\mu\text{s}$		30	60	ns

Notes:




- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)****Output Characteristics****Transfer Characteristics****Transconductance****On-Resistance vs. Drain Current****Capacitance****Gate Charge**

TYPICAL CHARACTERISTICS (25 °C UNLESS NOTED)



THERMAL RATINGS





Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.