

BAV199S

SURFACE MOUNT, LOW LEAKAGE SWITCHING DIODES ARRAY

VOLTAGE 100 Volts **POWER** 200mWatts


SOT-363 Unit: inch (mm)

FEATURES

- Two isolated diode pairs for significant board space savings
- Surface mount package ideally suited for automatic insertion
- Very low leakage current. 5pA typical at $V_R=75V$.
- Low capacitance. 2pF max at $V_R=0V$, $f=1MHz$
- In compliance with EU RoHS 2002/95/EC directives

MECHANICAL DATA

- Case: SOT-363 plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx weight: 0.008 gram
- Marking: PB



ABSOLUTE RATINGS (each diode)

PARAMETER	Symbol	Value	Units
Maximum Reverse Voltage	V_R	100	V
Peak Reverse Voltage	V_{RM}	100	V
Continuous Forward Current	I_F	0.2	A
Non-repetitive Peak Forward Surge Current at $t=1.0\mu s$	I_{FSM}	2.0	A

THERMAL CHARACTERISTICS

PARAMETER	Symbol	Value	Units
Power Dissipation (Note 1)	P_{TOT}	200	mW
Thermal Resistance, Junction to Ambient (Note 1)	$R_{\theta JA}$	625	$^{\circ}C/W$
Junction Temperature	T_J	-55 to 150	$^{\circ}C$
Storage Temperature	T_{STG}	-55 to 150	$^{\circ}C$

NOTE:

1. FR-5 Board = 1.0 x 0.75 x 0.062 in.

BAV199S

ELECTRICAL CHARACTERISTICS (each diode) (TA=25°C, unless otherwise noted)

PARAMETER	Symbol	Test Condition	MIN.	TYP.	MAX.	Units
Reverse Breakdown Voltage	$V_{(BR)}$	$I_R=100 \mu A$			100	V
Reverse Current	I_R	$V_R=75 V$ $V_R=75 V, T_J=150 ^\circ C$			5 80	nA
Forward Voltage	V_F	$I_F=1mA$ $I_F=10mA$ $I_F=50mA$ $I_F=150mA$			0.9 1.0 1.1 1.25	V
Total Capacitance	C_T	$V_R=0 V, f=1MHz$			2.0	pF
Reverse Recovery Time	t_{rr}	$I_F=I_R=10mA, R_L=100\Omega$			3.0	us

CHARACTERISTIC CURVES (each diode)




Figure 1. Reverse Leakage vs. Junction Temperature




Figure 2. Forward Current vs. Forward Voltage




Figure 3. Total Capacitance vs. Reverse Voltage





Fig.32

BAV199S

MOUNTING PAD LAYOUT

SOT-363

Unit: inch (mm)



ORDER INFORMATION

- Packing information

T/R - 10K per 13" plastic Reel

T/R - 3K per 7" plastic Reel

LEGAL STATEMENT

Copyright PanJit International, Inc 2007

The information presented in this document is believed to be accurate and reliable. The specifications and information herein are subject to change without notice. Pan Jit makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose. Pan Jit products are not authorized for use in life support devices or systems. Pan Jit does not convey any license under its patent rights or rights of others.