




- NOTES:
1. MATERIAL: POLYESTER, 94V-0, BLACK
 2. PRODUCT SPECIFICATION:
 3. PACKAGING SPECIFICATION: PK-70013-100
 4. OPTIONAL SPRING CLIP: 71809
RECOMMENDED ON 18-50 CKT PARTS FOR
HIGHER RETENTION FORCE
 5. INTERIM CLIP ACCEPTS:
TWO 70066 SINGLE ROW CRIMP HOUSINGS
TWO 70400 SINGLE ROW IDT ASSEMBLIES
TWO 70430 SINGLE ROW FFC ASSEMBLIES
ONE 70450 DUAL ROW CRIMP HOUSING
 6. MATES WITH:
OPTION A: HOUSINGS WITHOUT RIBS
70567 CGRID DUAL ROW VERTICAL HEADER OPTION B
74162 CGRID DUAL ROW RIGHT ANGLE HEADER OPTION B
70022 DUAL ROW PANEL MOUNT CLIP
OPTION B: HOUSINGS WITH RIBS
70567 CGRID DUAL ROW VERTICAL HEADER OPTION C
74162 CGRID DUAL ROW RIGHT ANGLE HEADER OPTION C
70568 CGRID DUAL ROW VERTICAL HEADER
70229 CGRID DUAL ROW RIGHT ANGLE HEADER
70022 DUAL ROW PANEL MOUNT CLIP





OPTION A
HOUSING WITHOUT RIBS



CIRCUIT 1



SUPPORT BEAMS PRESENT
ON ALL 14-50 CIRCUIT PARTS



INTERIM CLIP ACCEPTS CONNECTORS:
(SEE NOTE 5)
CONNECTORS SHOWN FOR REF ONLY.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
QUALITY SYMBOLS		UPDATE LOCK EC NO: 112473 DRWN: KSAMIEC CHK'D: APPR: FSMITH REV		2017/07/10 2017/07/18 FSMITH		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® SL DUAL ROW INTERIM CLIP						
F = 0 C = 0 P = 0 ▽ = 0 ▽ = 0 ⊠ = 0 ■ = 0 ▽ = 0						ANGULAR TOL ± °		MM		3:1								
						4 PLACES ±		DRWN BY		DATE								
						3 PLACES ±		KSAMIEC		2017/07/10								
2 PLACES ± 0.25						CHK'D BY		DATE		PRODUCT CUSTOMER DRAWING SERIES MATERIAL NUMBER CUSTOMER								
1 PLACE ± 0.38						CHKD BY		DATE										
0 PLACES ± 0.0						APPR BY		DATE										
FSMITH						2017/07/18												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						DRAWING SIZE		THIRD ANGLE PROJECTION		70013			DOCUMENT NUMBER			DOC TYPE	DOC PART	SHEET NUMBER
A						B		⊕ ⊞		700130000-SD			PSD	000	1 OF 3			

