

A DIVISION OF MINNEAPOLIS-MONETWELL REGULATOR COMPANY
 FREEPORT, ILLINOIS 


FED. MFR. CODE 91929

SWITCH - ENCLOSED

102ML1-E1



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.



NOTE —

- 1-LISTED BY UNDERWRITERS LABORATORY, INC. FOR USE IN CLASS 1 GROUPS C AND D VAPOR-AIR
ATMOSPHERES, AND CLASS 2 GROUPS E, F AND G DUST-AIR ATMOSPHERES
2-IT IS ESSENTIAL THAT THE CONDUIT OPENING BE PROPERLY SEALED IN ORDER TO MAINTAIN THE
EXPLOSION PROOF PROPERTIES.
3-SWITCH WILL PERFORM SATISFACTORILY IN TEMPERATURES TO MINUS 30°F.

CHARACTERISTICS (TENTATIVE) OPERATING FORCE----- 6 LB. APPROX. RELEASE FORCE----- 4 LB. APPROX. DIFFERENTIAL TRAVEL----- .020 MAX. OVERTRAVEL----- .500 MIN. SWITCH-BASIC REPLACEMENT----- 1MNI	ELECTRICAL DATA CONTACT ARRANGEMENT TWO CIRCUIT DOUBLE THROW DOUBLE BREAK		SCALE 1/2 TO 1 DO NOT SCALE PRINT
	10 A-120, 240, OR 480 VAC; 1/2 HP - 120 VAC 1 HP - 240 VAC; 0.8 A - 115 VDC ; 0.4 A - 230 VDC PILOT DUTY: 720 VA-HEAVY DUTY 600 VAC MAX		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
	(A) (B) (C)		ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.018 THREE PLACE (.000) ±.008 ANGLES ±
	 		WEIGHT