




FEATURES:

- Converts instruments with BNC inputs to triaxial, 2 lug for better shield performance
- Triaxial center and intermediate contacts are gold plated, Beryllium Copper for long insertion cycle life and low contact resistance
- Adapter outer shell has tarnish resistant plating

MATERIALS:

Outer Shell: Nickel plated Brass

Contacts (Triaxial):

Center: Gold plated Beryllium Copper

Intermediate: Gold plated Beryllium Copper

Outer Contact: tarnish resistant brass

BNC: Nickel plated brass

Marking: "POMONA ELECT. 5298"

RATINGS:

Operating Voltage: Shield/Earth: 30VAC/60VDC Max. For hands-free controlled voltage environments,

Voltage: 500 VDC

Frequency Range: DC to 500 MHz.

ORDERING INFORMATION: Model 5298

All dimensions are in inches and metric. All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90469 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com