









RECOMMENDED P.C.B HOLE LAYOUT



- NOTES:
1. MATERIAL:
HSG: LCP, GLASS-FILLED, UL94V-0,
COLOR: BLACK
PIN: 0.64MM SQ PIN, COPPER ALLOY
 2. PLATING TYPE:
(1) : 0.0254 μ m GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
(2) : 0.025 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
(3) : 0.25 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
(4) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
(5) : 0.75 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL
(6) : 2.50 μ m MIN. TIN OVER 1.25 μ m MIN. NICKEL OVERALL.
(7) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
2.50 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
(8) : 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
0.05 μ m MIN. GOLD FLASH ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
(9) : 0.05 - 0.25 μ m MIN. GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
 3. PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION
 4. THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
 5. FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
 6. RECOMMENDED PCB THICKNESS 1.60MM.
 7. PRODUCT SPECIFICATION: PS-87920-019
 8. WAFER TO BE FLAT WITHIN 0.003mm/mm
 9. IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE.
 10. PARTS ARE NOT STACKABLE ON 2.54 CENTER
 11. CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.
 12. PACKAGING SPECIFICATION:
TRAY: PK-89990-489
BULK: PK-89990-491

REVISION OF DRAWING MAY BE
CHANGED DURING FINAL RELEASED
FOR PRODUCTION.

SEE SHEET 14 EC NO: S2015-1512 DRAWN: RAMAKRISHNA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15	DESCRIPTION REV	QUALITY SYMBOLS F _A =0 F _G =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				
			4 PLACES	±---	±---	CHECKED BY PTLIM	DATE 2004/12/08					
			3 PLACES	±---	±---	APPROVED BY MLONG	DATE 2010/09/06					
			2 PLACES	±0.20	±---							
			1 PLACE	±---	±---				DOCUMENT NO. SD-87914-013			
			0 PLACE	±	±							
			ANGULAR ± 3 °			MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE			SHEET NO. 1 OF 45			
			D15			SIZE A3 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	P							
F	87914-0211	-----	-----	-----	-----	2	----	1	2.54	----	10.92	5.84	2.79	F						
	87914-0221	-----	-----	-----	-----	2	----	1	2.54	----	12.25	7.00	2.96							
	87914-0231	-----	-----	-----	-----	2	----	1	2.54	----	13.38	6.09	5.00							
	87914-0212	-----	-----	-----	-----	2	----	2	2.54	----	10.92	5.84	2.79	E						
	87914-0222	-----	-----	-----	-----	2	----	2	2.54	----	12.25	7.00	2.96							
	87914-0232	-----	-----	-----	-----	2	----	2	2.54	----	13.38	6.09	5.00							
E	87914-0213	-----	-----	-----	-----	2	----	3	2.54	----	10.92	5.84	2.79	E						
	87914-0223	-----	-----	-----	-----	2	----	3	2.54	----	12.25	7.00	2.96							
	87914-0233	-----	-----	-----	-----	2	----	3	2.54	----	13.38	6.09	5.00							
	87914-0214	-----	-----	-----	-----	2	----	4	2.54	----	10.92	5.84	2.79	D						
	87914-0224	-----	-----	-----	-----	2	----	4	2.54	----	12.25	7.00	2.96							
	87914-0234	-----	-----	-----	-----	2	----	4	2.54	----	13.38	6.09	5.00							
D	87914-0215	-----	-----	-----	-----	2	----	5	2.54	----	10.92	5.84	2.79	D						
	87914-0225	-----	-----	-----	-----	2	----	5	2.54	----	12.25	7.00	2.96							
	87914-0235	-----	-----	-----	-----	2	----	5	2.54	----	13.38	6.09	5.00							
	87914-0216	-----	-----	-----	-----	2	----	6	2.54	----	10.92	5.84	2.79	C						
	87914-0226	-----	-----	-----	-----	2	----	6	2.54	----	12.25	7.00	2.96							
	87914-0236	-----	-----	-----	-----	2	----	6	2.54	----	13.38	6.09	5.00							
C														C						
														B						
B														B						
A																			A	
	SEE SHEET 14 IEC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV		QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION									
							MM ONLY													
					DRAWN BY DATE		TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex													
					KCHO 2004/11/05															
					CHECKED BY DATE															
					PTLIM 2004/12/08		APPROVED BY DATE													
					MLONG 2010/09/06															
MATERIAL NO.					DOCUMENT NO.		SHEET NO.													
SEE TABLE		SD-87914-013		2 OF 45																
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1										

tb_frame_A3_P_AM_T
Rev. G 2012/01/11

[illegible]

	10	9	8	7	6	5	4	3	2	1				
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F
									A	B	F	M	P	
	87914-0009	-----	-----	-----	-----	6	----	1	7.62	5.08	18.84	13.25	3.30	
	87914-0642	-----	-----	-----	-----	6	----	2	7.62	5.08	18.84	13.25	3.30	
	87914-0643	-----	-----	-----	-----	6	----	3	7.62	5.08	18.84	13.25	3.30	
	87914-0644	-----	-----	-----	-----	6	----	4	7.62	5.08	18.84	13.25	3.30	
	87914-0645	-----	-----	-----	-----	6	----	5	7.62	5.08	18.84	13.25	3.30	
	87914-0646	-----	-----	-----	-----	6	----	6	7.62	5.08	18.84	13.25	3.30	
E														E
D														D
C														C
B														B
A														A

SEE SHEET 14 EC NO: S2015-1512 DRWN:HRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				
		4 PLACES	± ---	± ---	KCHO	2004/11/05					
		3 PLACES	± ---	± ---	CHECKED BY	DATE					
		2 PLACES	± 0.20	± ---	PTLIM	2004/12/08					
			1 PLACE	± ---	± ---	APPROVED BY	DATE	molex			
			0 PLACE	±	±	MLONG	2010/09/06				
		ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013		5 OF 45		
					SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

SEE SHEET 14 EC NO: S2015-1512 DRWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			
				mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE				
			4 PLACES	± ---	± ---	CHECKED BY	DATE					
			3 PLACES	± ---	± ---	PTLIM	2004/12/08	SD-87914-013				
			2 PLACES	± 0.20	± ---	APPROVED BY	DATE					
			1 PLACE	± ---	± ---	MLONG	2010/09/06			DOCUMENT NO.		
			0 PLACE	±	±	MATERIAL NO.		SEE TABLE				
			ANGULAR ± 3 °		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

	10		9		8		7		6		5		4		3		2		1
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION										
	87914-0811	-----	-----	-----	-----	8	-----	1	A	B	F	M	P	G					
									10.16	7.62	10.92	5.84	2.79	----					
87914-0821	-----	-----	-----	-----	-----	8	-----	1	10.16	7.62	12.25	7.00	2.96	----					
87914-0831	-----	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.38	6.09	5.00	----					
87914-0812	-----	-----	-----	-----	-----	8	-----	2	10.16	7.62	10.92	5.84	2.79	----					
87914-0822	-----	-----	-----	-----	-----	8	-----	2	10.16	7.62	12.25	7.00	2.96	----					
87914-0832	-----	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.38	6.09	5.00	----					
E	87914-0813	-----	-----	-----	-----	8	-----	3	10.16	7.62	10.92	5.84	2.79	----					
	87914-0823	-----	-----	-----	-----	8	-----	3	10.16	7.62	12.25	7.00	2.96	----					
	87914-0833	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----					
87914-0814	-----	-----	-----	-----	-----	8	-----	4	10.16	7.62	10.92	5.84	2.79	----					
87914-0824	-----	-----	-----	-----	-----	8	-----	4	10.16	7.62	12.25	7.00	2.96	----					
87914-0834	-----	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----					
D	87914-0815	-----	-----	-----	-----	8	-----	5	10.16	7.62	10.92	5.84	2.79	----					
	87914-0825	-----	-----	-----	-----	8	-----	5	10.16	7.62	12.25	7.00	2.96	----					
	87914-0835	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.38	6.09	5.00	----					
87914-0816	-----	-----	-----	-----	-----	8	-----	6	10.16	7.62	10.92	5.84	2.79	----					
87914-0826	-----	-----	-----	-----	-----	8	-----	6	10.16	7.62	12.25	7.00	2.96	----					
87914-0836	-----	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.38	6.09	5.00	----					
C	87914-0807	-----	-----	-----	-----	8	2,3,4,5,6,8	6	10.16	7.62	21.75	16.51	2.95	----					
															B				
																B			
A																A			
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
															A				
</																			

	10		9		8		7		6		5		4		3		2		1		
F	PART NO. FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F							
									A	B	F	M	P								
	87914-0841	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.51	8.75	2.47								
	87914-0842	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.51	8.75	2.47								
	87914-0843	-----	-----	-----	-----	8	-----	3	10.16	7.62	13.51	8.75	2.47								
	87914-0844	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.51	8.75	2.47								
E	87914-0845	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.51	8.75	2.47	E							
	87914-0005	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.51	8.75	2.47								
	87914-0108	-----	-----	-----	-----	8	-----	6	10.16	7.62	16.50	11.11	3.10								
	87914-0847	-----	-----	-----	-----	8	-----	6	10.16	7.62	26.70	20.76	3.65								
D														D							
C														C							
B														B							
A														A							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1											
SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV		QUALITY SYMBOLS $F_A=0$ $F_C=0$ $F_P=0$		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES $\pm$ --- $\pm$ --- 3 PLACES $\pm$ --- $\pm$ --- 2 PLACES $\pm$ 0.20 $\pm$ --- 1 PLACE $\pm$ --- $\pm$ --- 0 PLACE $\pm$ $\pm$ ANGULAR $\pm$ 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DOCUMENT NO. SD-87914-013		SHEET NO. 7 OF 45		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	

ib_frame_A3_P_AM_T

Rev. G 2012/01/11

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-1211	-----	-----	-----	-----	12	-----	1	15.24	12.70	10.92	5.84	2.79						
	-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79						
	87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96						
	87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00						
	87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79						
	87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96						
E	87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00	E					
	87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79						
	87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96						
	87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00						
	87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79						
	87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96						
D	87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00	D					
	87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79						
	87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96						
	87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00						
	87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79						
	87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96						
C	87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00	C					
B															B				

	10		9		8		7		6		5		4		3		2		1		
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
									A	B	F	M	P								
F	87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03								
	87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03								
	87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03								
	87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03								
	87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03								
	87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03								
E	87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26								
	87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26								
	87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26								
	87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26								
	87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26								
	87914-1246	-----	-----	-----	-----	12	-----	6	15.24	12.70	29.26	23.32	3.65								
D																					
C																					
B																					
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15		REV	DESCRIPTION	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex					SHEET NO. 10 OF 45	
						mm		INCH		DRAWN BY KCHO	DATE 2004/11/05	TITLE									
							4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08										
							3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06										
							2 PLACES	± 0.20	± ---												
							1 PLACE	± ---	± ---												
							0 PLACE	±	±												
							ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.									
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-87914-013									
							SIZE A3			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1			

10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F					
	A	B	F	M	P														
	87914-1411	-----	-----	-----	-----	14	-----	1	17.78	15.24	10.92	5.84	2.79						
	87914-1421	-----	-----	-----	-----	14	-----	1	17.78	15.24	12.25	7.00	2.96						
	87914-1431	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.38	6.09	5.00						
	87914-1412	-----	-----	-----	-----	14	-----	2	17.78	15.24	10.92	5.84	2.79						
	87914-1422	-----	-----	-----	-----	14	-----	2	17.78	15.24	12.25	7.00	2.96						
	87914-1432	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.38	6.09	5.00						
E	87914-1413	-----	-----	-----	-----	14	-----	3	17.78	15.24	10.92	5.84	2.79	E					
	87914-1423	-----	-----	-----	-----	14	-----	3	17.78	15.24	12.25	7.00	2.96						
	87914-1433	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.38	6.09	5.00						
	87914-1414	-----	-----	-----	-----	14	-----	4	17.78	15.24	10.92	5.84	2.79						
	87914-1424	-----	-----	-----	-----	14	-----	4	17.78	15.24	12.25	7.00	2.96						
	87914-1434	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.38	6.09	5.00						
D	87914-1415	-----	-----	-----	-----	14	-----	5	17.78	15.24	10.92	5.84	2.79	D					
	87914-1425	-----	-----	-----	-----	14	-----	5	17.78	15.24	12.25	7.00	2.96						
	87914-1435	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.38	6.09	5.00						
	87914-1416	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79						
	87914-1426	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96						
	87914-1436	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.38	6.09	5.00						
C	87914-0007	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.42	8.08	3.05	C					

[illegible]

	10	9	8	7	6	5	4	3	2	1					
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION						
									A	B	F	M	P		
F	87914-1611	-----	-----	-----	-----	16	-----	1	20.32	17.78	10.92	5.84	2.79	F	
	87914-1621	-----	-----	-----	-----	16	-----	1	20.32	17.78	12.25	7.00	2.96		
	87914-1631	-----	-----	-----	-----	16	-----	1	20.32	17.78	13.38	6.09	5.00		
	87914-1612	-----	-----	-----	-----	16	-----	2	20.32	17.78	10.92	5.84	2.79		
	87914-1622	-----	-----	-----	-----	16	-----	2	20.32	17.78	12.25	7.00	2.96		
	87914-1632	-----	-----	-----	-----	16	-----	2	20.32	17.78	13.38	6.09	5.00		
E	87914-1613	-----	-----	-----	-----	16	-----	3	20.32	17.78	10.92	5.84	2.79	E	
	87914-1623	-----	-----	-----	-----	16	-----	3	20.32	17.78	12.25	7.00	2.96		
	87914-1633	-----	-----	-----	-----	16	-----	3	20.32	17.78	13.38	6.09	5.00		
	87914-1614	-----	-----	-----	-----	16	-----	4	20.32	17.78	10.92	5.84	2.79		
	87914-1624	-----	-----	-----	-----	16	-----	4	20.32	17.78	12.25	7.00	2.96		
	87914-1634	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.38	6.09	5.00		
D	87914-1615	-----	-----	-----	-----	16	-----	5	20.32	17.78	10.92	5.84	2.79	D	
	87914-1625	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.25	7.00	2.96		
	87914-1635	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.38	6.09	5.00		
	87914-1616	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79		
	87914-1626	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96		
	87914-1636	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.38	6.09	5.00		
C	87914-1600	-----	-----	-----	-----	16	-----	6	20.32	17.78	9.49	4.50	2.70	C	
	87914-1637	-----	-----	-----	-----	16	-----	6	20.32	17.78	15.79	10.45	3.05		
B														B	
A	SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15														
	QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION				
	F=0 F=0 F=0		4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex DOCUMENT NO. SD-87914-013 SHEET NO. 13 OF 45		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1						

10			9		8		7		6		5		4		3		2		1							
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																		
								A	B	F	M	P	G													
F	87914-1811	-----	-----	-----	-----	18	-----	1	22.86	20.32	10.92	5.84	2.79	----												
	87914-1821	-----	-----	-----	-----	18	-----	1	22.86	20.32	12.25	7.00	2.96	----												
	87914-1831	-----	-----	-----	-----	18	-----	1	22.86	20.32	13.38	6.09	5.00	----												
	87914-1812	-----	-----	-----	-----	18	-----	2	22.86	20.32	10.92	5.84	2.79	----												
	87914-1822	-----	-----	-----	-----	18	-----	2	22.86	20.32	12.25	7.00	2.96	----												
87914-1832	-----	-----	-----	-----	18	-----	2	22.86	20.32	13.38	6.09	5.00	----													
E	87914-1813	-----	-----	-----	-----	18	-----	3	22.86	20.32	10.92	5.84	2.79	----												
	87914-1823	-----	-----	-----	-----	18	-----	3	22.86	20.32	12.25	7.00	2.96	----												
	87914-1833	-----	-----	-----	-----	18	-----	3	22.86	20.32	13.38	6.09	5.00	----												
D	87914-1814	-----	-----	-----	-----	18	-----	4	22.86	20.32	10.92	5.84	2.79	----												
	87914-1824	-----	-----	-----	-----	18	-----	4	22.86	20.32	12.25	7.00	2.96	----												
	87914-1834	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.38	6.09	5.00	----												
	87914-1815	-----	-----	-----	-----	18	-----	5	22.86	20.32	10.92	5.84	2.79	----												
	87914-1825	-----	-----	-----	-----	18	-----	5	22.86	20.32	12.25	7.00	2.96	----												
C	87914-1835	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.38	6.09	5.00	----												
	87914-1816	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79	----												
	87914-1826	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96	----												
	87914-1836	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.38	6.09	5.00	----												
	-----	-----	87914-1807	-----	-----	18	-----	6	22.86	20.32	17.02	11.05	3.68	18.02												
B																										
A																										
ADD P/N: 87914-1807 EC NO: S2015-1512 DRAWN:MRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15									QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 14 OF 45			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-87914-013													
fb_frame_A3_P_AM_T Rev. G 2012/01/11			9		8		7		6		5		4		3		2		1							

10		9		8		7		6		5		4		3		2		1																																																																																												
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																																						
								A	B	F	M	P																																																																																																		
F	87914-2011	-----	-----	-----	-----	20	----	1	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2021	-----	-----	-----	-----	20	----	1	25.40	22.86	12.25	7.00	2.96																																																																																																	
	87914-2031	-----	-----	-----	-----	20	----	1	25.40	22.86	13.38	6.09	5.00																																																																																																	
	87914-2012	-----	-----	-----	-----	20	----	2	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2022	-----	-----	-----	-----	20	----	2	25.40	22.86	12.25	7.00	2.96																																																																																																	
	87914-2032	-----	-----	-----	-----	20	----	2	25.40	22.86	13.38	6.09	5.00																																																																																																	
E	87914-2013	-----	-----	-----	-----	20	----	3	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2023	-----	-----	-----	-----	20	----	3	25.40	22.86	12.25	7.00	2.96																																																																																																	
	87914-2033	-----	-----	-----	-----	20	----	3	25.40	22.86	13.38	6.09	5.00																																																																																																	
D	87914-2014	-----	-----	-----	-----	20	----	4	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2024	-----	-----	-----	-----	20	----	4	25.40	22.86	12.25	7.00	2.96																																																																																																	
	87914-2034	-----	-----	-----	-----	20	----	4	25.40	22.86	13.38	6.09	5.00																																																																																																	
	87914-2015	-----	-----	-----	-----	20	----	5	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2025	-----	-----	-----	-----	20	----	5	25.40	22.86	12.25	7.00	2.96																																																																																																	
C	87914-2035	-----	-----	-----	-----	20	----	5	25.40	22.86	13.38	6.09	5.00																																																																																																	
	87914-2016	-----	-----	-----	-----	20	----	6	25.40	22.86	10.92	5.84	2.79																																																																																																	
	87914-2026	-----	-----	-----	-----	20	----	6	25.40	22.86	12.25	7.00	2.96																																																																																																	
B	87914-2036	-----	-----	-----	-----	20	----	6	25.40	22.86	13.38	6.09	5.00																																																																																																	
A																																																																																																														
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV</td><td rowspan="5">QUALITY SYMBOLS $\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td colspan="2"></td></tr><tr><td>4 PLACES</td><td>$\pm$---</td><td>$\pm$---</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="2">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td>3 PLACES</td><td>$\pm$---</td><td>$\pm$---</td><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td><td colspan="2"></td></tr><tr><td>2 PLACES</td><td>$\pm$0.20</td><td>$\pm$---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td><td colspan="2"></td></tr><tr><td>1 PLACE</td><td>$\pm$---</td><td>$\pm$---</td><td></td><td></td><td colspan="2"></td></tr><tr><td>0 PLACE</td><td>$\pm$</td><td>$\pm$</td><td></td><td></td><td colspan="2"></td></tr><tr><td colspan="2">ANGULAR $\pm$ 3 °</td><td colspan="2"></td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SIZE A3</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td colspan="2">15 OF 45</td></tr><tr><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="9"></td></tr></table>																			SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS $\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION										4 PLACES	$\pm$ ---	$\pm$ ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		3 PLACES	$\pm$ ---	$\pm$ ---	CHECKED BY PTL IM	DATE 2004/12/08			2 PLACES	$\pm$ 0.20	$\pm$ ---	APPROVED BY MLONG	DATE 2010/09/06			1 PLACE	$\pm$ ---	$\pm$ ---					0 PLACE	$\pm$	$\pm$					ANGULAR $\pm$ 3 °				MATERIAL NO.		DOCUMENT NO.		SHEET NO.		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE TABLE		SD-87914-013		15 OF 45		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		
SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS $\nabla_F=0$ $\nabla_F=0$ $\nabla_F=0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																																						
		4 PLACES	$\pm$ ---	$\pm$ ---	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																																							
		3 PLACES	$\pm$ ---	$\pm$ ---	CHECKED BY PTL IM	DATE 2004/12/08																																																																																																								
		2 PLACES	$\pm$ 0.20	$\pm$ ---	APPROVED BY MLONG	DATE 2010/09/06																																																																																																								
1 PLACE	$\pm$ ---	$\pm$ ---																																																																																																												
0 PLACE	$\pm$	$\pm$																																																																																																												
ANGULAR $\pm$ 3 °				MATERIAL NO.		DOCUMENT NO.		SHEET NO.																																																																																																						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE TABLE		SD-87914-013		15 OF 45																																																																																																						
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																																														
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1																																																																																												

	10		9		8		7		6		5		4		3		2		1					
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															
									A	B	F	M	P											
F	87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79								F			
	87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96											
	87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00											
	87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79											
	87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96											
	87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00											
E	87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79								E			
	87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96											
	87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00											
	87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79											
	87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96											
	87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00											
D	87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79								D			
	87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96											
	87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00											
	87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79											
	87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96											
	87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00											
C																					C			
B																					B			
A									SEE SHEET 14 IEC NO: S2015-1512 DRAWN:RAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS F=0 F=0 F=0		GENERAL TOLERANCES (UNLESS SPECIFIED) mmINCH 4 PLACES± ---± --- 3 PLACES± ---± --- 2 PLACES± 0.20± --- 1 PLACE± ---± --- 0 PLACE± ± ANGULAR ± 3 °		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTLIM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.		SCALE NTS		DESIGN UNITS METRIC		THIRD ANGLE PROJECTION			
															2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H									
															molex									
													SEE TABLE		DOCUMENT NO. SD-87914-013				SHEET NO. 16 OF 45					
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1						

10		9		8		7		6		5		4		3		2		1			
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION													
								A	B	F	M	P									
F	87914-2411	-----	-----	-----	-----	24	-----	1	30.48	27.94	10.92	5.84	2.79								
	87914-2421	-----	-----	-----	-----	24	-----	1	30.48	27.94	12.25	7.00	2.96								
	87914-2431	-----	-----	-----	-----	24	-----	1	30.48	27.94	13.38	6.09	5.00								
	87914-2412	-----	-----	-----	-----	24	-----	2	30.48	27.94	10.92	5.84	2.79								
	87914-2422	-----	-----	-----	-----	24	-----	2	30.48	27.94	12.25	7.00	2.96								
	87914-2432	-----	-----	-----	-----	24	-----	2	30.48	27.94	13.38	6.09	5.00								
E	87914-2413	-----	-----	-----	-----	24	-----	3	30.48	27.94	10.92	5.84	2.79								
	87914-2423	-----	-----	-----	-----	24	-----	3	30.48	27.94	12.25	7.00	2.96								
	87914-2433	-----	-----	-----	-----	24	-----	3	30.48	27.94	13.38	6.09	5.00								
	87914-2414	-----	-----	-----	-----	24	-----	4	30.48	27.94	10.92	5.84	2.79								
	87914-2424	-----	-----	-----	-----	24	-----	4	30.48	27.94	12.25	7.00	2.96								
	87914-2434	-----	-----	-----	-----	24	-----	4	30.48	27.94	13.38	6.09	5.00								
D	87914-2415	-----	-----	-----	-----	24	-----	5	30.48	27.94	10.92	5.84	2.79								
	87914-2425	-----	-----	-----	-----	24	-----	5	30.48	27.94	12.25	7.00	2.96								
	87914-2435	-----	-----	-----	-----	24	-----	5	30.48	27.94	13.38	6.09	5.00								
	87914-2416	-----	-----	-----	-----	24	-----	6	30.48	27.94	10.92	5.84	2.79								
	87914-2426	-----	-----	-----	-----	24	-----	6	30.48	27.94	12.25	7.00	2.96								
	87914-2436	-----	-----	-----	-----	24	-----	6	30.48	27.94	13.38	6.09	5.00								
C																					
B																					
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAWAKR / SHINA 2015/06/25 CHK'D:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO.		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SD-87914-013 SHEET NO. 17 OF 45	
											SEE TABLE										
											THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										

	10		9		8		7		6		5		4		3		2		1	
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					F						
	A	B	F	M	P															
	87914-2611	-----	-----	-----	-----	26	-----	1	33.02	30.48	10.92	5.84	2.79							
	87914-2621	-----	-----	-----	-----	26	-----	1	33.02	30.48	12.25	7.00	2.96							
	87914-2631	-----	-----	-----	-----	26	-----	1	33.02	30.48	13.38	6.09	5.00							
	87914-2612	-----	-----	-----	-----	26	-----	2	33.02	30.48	10.92	5.84	2.79							
	87914-2622	-----	-----	-----	-----	26	-----	2	33.02	30.48	12.25	7.00	2.96							
	87914-2632	-----	-----	-----	-----	26	-----	2	33.02	30.48	13.38	6.09	5.00							
E	87914-2613	-----	-----	-----	-----	26	-----	3	33.02	30.48	10.92	5.84	2.79	E						
	87914-2623	-----	-----	-----	-----	26	-----	3	33.02	30.48	12.25	7.00	2.96							
	87914-2633	-----	-----	-----	-----	26	-----	3	33.02	30.48	13.38	6.09	5.00							
	87914-2614	-----	-----	-----	-----	26	-----	4	33.02	30.48	10.92	5.84	2.79							
	87914-2624	-----	-----	-----	-----	26	-----	4	33.02	30.48	12.25	7.00	2.96							
	87914-2634	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.38	6.09	5.00							
D	87914-2615	-----	-----	-----	-----	26	-----	5	33.02	30.48	10.92	5.84	2.79	D						
	87914-2625	-----	-----	-----	-----	26	-----	5	33.02	30.48	12.25	7.00	2.96							
	87914-2635	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.38	6.09	5.00							
	87914-2616	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79							
	87914-2626	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96							
	87914-2636	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.38	6.09	5.00							
C														C						
B														B						

10		9		8		7		6		5		4		3		2		1																				
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																														
								A	B	F	M	P																										
F	87914-3011	-----	-----	-----	-----	30	----	1	38.10	35.56	10.92	5.84	2.79						F																			
	87914-3021	-----	-----	-----	-----	30	----	1	38.10	35.56	12.25	7.00	2.96																									
	87914-3031	-----	-----	-----	-----	30	----	1	38.10	35.56	13.38	6.09	5.00																									
	87914-3012	-----	-----	-----	-----	30	----	2	38.10	35.56	10.92	5.84	2.79																									
	87914-3022	-----	-----	-----	-----	30	----	2	38.10	35.56	12.25	7.00	2.96																									
	87914-3032	-----	-----	-----	-----	30	----	2	38.10	35.56	13.38	6.09	5.00																									
E	87914-3013	-----	-----	-----	-----	30	----	3	38.10	35.56	10.92	5.84	2.79						E																			
	87914-3023	-----	-----	-----	-----	30	----	3	38.10	35.56	12.25	7.00	2.96																									
	87914-3033	-----	-----	-----	-----	30	----	3	38.10	35.56	13.38	6.09	5.00																									
	87914-3014	-----	-----	-----	-----	30	----	4	38.10	35.56	10.92	5.84	2.79																									
	87914-3024	-----	-----	-----	-----	30	----	4	38.10	35.56	12.25	7.00	2.96																									
	87914-3034	-----	-----	-----	-----	30	----	4	38.10	35.56	13.38	6.09	5.00																									
D	87914-3015	-----	-----	-----	-----	30	----	5	38.10	35.56	10.92	5.84	2.79						D																			
	87914-3025	-----	-----	-----	-----	30	----	5	38.10	35.56	12.25	7.00	2.96																									
	87914-3035	-----	-----	-----	-----	30	----	5	38.10	35.56	13.38	6.09	5.00																									
	87914-3016	-----	-----	-----	-----	30	----	6	38.10	35.56	10.92	5.84	2.79																									
	87914-3026	-----	-----	-----	-----	30	----	6	38.10	35.56	12.25	7.00	2.96																									
	87914-3036	-----	-----	-----	-----	30	----	6	38.10	35.56	13.38	6.09	5.00																									
C																			C																			
B																			B																			
SEE SHEET 14 IEC NO: S2015-1512 DRW:KPRASAD CHKD:ATSEE APPR:KPRASAD REV DESCRIPTION QUALITY SYMBOLS GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE ± --- ± --- ± 0.20 ± --- ± ± --- ± --- ± --- ± --- ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS DIMENSION STYLE MM ONLY DRAWN BY DATE CHECKED BY DATE APPROVED BY DATE MATERIAL NO. SCALE NTS DESIGN UNITS METRIC THIRD ANGLE PROJECTION TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex SD-87914-013 DOCUMENT NO. SHEET NO. THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																						A
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1																				

													10			9			8			7			6			5			4			3			2			1
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																															
									A	B	F	M	P																											
F	87914-3211	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79																											
	87914-3221	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96																											
	87914-3231	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00																											
	87914-3212	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79																											
	87914-3222	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96																											
	87914-3232	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00																											
E	87914-3213	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79																											
	87914-3223	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96																											
	87914-3233	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00																											
	87914-3214	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79																											
	87914-3224	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96																											
	87914-3234	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00																											
D	87914-3215	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79																											
	87914-3225	-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96																											
	87914-3235	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00																											
	87914-3216	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79																											
	87914-3226	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96																											
	87914-3236	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00																											
C																																								
B																																								
A	SEE SHEET 14 EC NO: S2015-1512 DRW:HRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex SD-87914-013 SHEET NO. 21 OF 45																					
									▽F=0 ▽F=0 ▽F=0	4 PLACES ± --- 3 PLACES ± --- 2 PLACES ± 0.20 1 PLACE ± --- 0 PLACE ±	mm INCH	DRAWN BY DATE		TITLE	APPROVED BY DATE																									
												KCHO 2004/11/05																												
		ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.																																		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE																																				
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																		

fb_frame_A3_P_AM_T																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																																	
--------------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

	10		9		8		7		6		5		4		3		2		1	
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
									A	B	F	M	D							
F	87914-3411	-----	-----	-----	-----	34	-----	1	43.18	40.64	10.92	5.84	2.79							F
	87914-3421	-----	-----	-----	-----	34	-----	1	43.18	40.64	12.25	7.00	2.96							
	87914-3431	-----	-----	-----	-----	34	-----	1	43.18	40.64	13.38	6.09	5.00							
	87914-3412	-----	-----	-----	-----	34	-----	2	43.18	40.64	10.92	5.84	2.79							E
	87914-3422	-----	-----	-----	-----	34	-----	2	43.18	40.64	12.25	7.00	2.96							
	87914-3432	-----	-----	-----	-----	34	-----	2	43.18	40.64	13.38	6.09	5.00							
E	87914-3413	-----	-----	-----	-----	34	-----	3	43.18	40.64	10.92	5.84	2.79							D
	87914-3423	-----	-----	-----	-----	34	-----	3	43.18	40.64	12.25	7.00	2.96							
	87914-3433	-----	-----	-----	-----	34	-----	3	43.18	40.64	13.38	6.09	5.00							
	87914-3414	-----	-----	-----	-----	34	-----	4	43.18	40.64	10.92	5.84	2.79							C
	87914-3424	-----	-----	-----	-----	34	-----	4	43.18	40.64	12.25	7.00	2.96							
	87914-3434	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.38	6.09	5.00							
D	87914-3415	-----	-----	-----	-----	34	-----	5	43.18	40.64	10.92	5.84	2.79							B
	87914-3425	-----	-----	-----	-----	34	-----	5	43.18	40.64	12.25	7.00	2.96							
	87914-3435	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.38	6.09	5.00							
	87914-3416	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79							A
	87914-3426	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96							
	87914-3436	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.38	6.09	5.00							
C																				
B																				
A									QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
	SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV								F ₀ =0		4 PLACES ± --- ± ---		DRAWN BY DATE KCHO 2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
									F ₀ =0		3 PLACES ± --- ± ---		CHECKED BY DATE PTLIM 2004/12/08							
									F ₀ =0		2 PLACES ± 0.20 ± ---		APPROVED BY DATE MLONG 2010/09/06		molex					
											1 PLACE ± --- ± ---		MATERIAL NO.							DOCUMENT NO.
											0 PLACE ± ±		SEE TABLE		SD-87914-013		22 OF 45			
									ANGULAR ± 3 °											
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

10		9		8		7		6		5		4		3		2		1			
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION													
								A	B	F	M	P									
F	87914-3611	-----	-----	-----	-----	36	-----	1	45.72	43.18	10.92	5.84	2.79								
	87914-3621	-----	-----	-----	-----	36	-----	1	45.72	43.18	12.25	7.00	2.96								
	87914-3631	-----	-----	-----	-----	36	-----	1	45.72	43.18	13.38	6.09	5.00								
	87914-3612	-----	-----	-----	-----	36	-----	2	45.72	43.18	10.92	5.84	2.79								
	87914-3622	-----	-----	-----	-----	36	-----	2	45.72	43.18	12.25	7.00	2.96								
	87914-3632	-----	-----	-----	-----	36	-----	2	45.72	43.18	13.38	6.09	5.00								
E	87914-3613	-----	-----	-----	-----	36	-----	3	45.72	43.18	10.92	5.84	2.79								
	87914-3623	-----	-----	-----	-----	36	-----	3	45.72	43.18	12.25	7.00	2.96								
	87914-3633	-----	-----	-----	-----	36	-----	3	45.72	43.18	13.38	6.09	5.00								
	87914-3614	-----	-----	-----	-----	36	-----	4	45.72	43.18	10.92	5.84	2.79								
	87914-3624	-----	-----	-----	-----	36	-----	4	45.72	43.18	12.25	7.00	2.96								
	87914-3634	-----	-----	-----	-----	36	-----	4	45.72	43.18	13.38	6.09	5.00								
D	87914-3615	-----	-----	-----	-----	36	-----	5	45.72	43.18	10.92	5.84	2.79								
	87914-3625	-----	-----	-----	-----	36	-----	5	45.72	43.18	12.25	7.00	2.96								
	87914-3635	-----	-----	-----	-----	36	-----	5	45.72	43.18	13.38	6.09	5.00								
	87914-3616	-----	-----	-----	-----	36	-----	6	45.72	43.18	10.92	5.84	2.79								
	87914-3626	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.25	7.00	2.96								
	87914-3636	-----	-----	-----	-----	36	-----	6	45.72	43.18	13.38	6.09	5.00								
C	87914-3637	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.10	7.01	2.60								
B																					
A									QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		
													DRAWN BY		DATE		TITLE				
									4 PLACES		± ---		± ---		KCHO		2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		
									3 PLACES		± ---		± ---		CHECKED BY		DATE				
									2 PLACES		± 0.20		± ---		PTL IM		2004/12/08				
									1 PLACE		± ---		± ---		APPROVED BY		DATE				
									0 PLACE		±		±		MLONG		2010/09/06				
											ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.		
											DRAFT WHERE APPLICABLE		SEE TABLE				SD-87914-013		23 OF 45		
											MUST REMAIN WITHIN DIMENSIONS		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-3811	-----	-----	-----	-----	38	----	1	48.26	45.72	10.92	5.84	2.79						
	87914-3821	-----	-----	-----	-----	38	----	1	48.26	45.72	12.25	7.00	2.96						
	87914-3831	-----	-----	-----	-----	38	----	1	48.26	45.72	13.38	6.09	5.00						
	87914-3812	-----	-----	-----	-----	38	----	2	48.26	45.72	10.92	5.84	2.79						
	87914-3822	-----	-----	-----	-----	38	----	2	48.26	45.72	12.25	7.00	2.96						
	87914-3832	-----	-----	-----	-----	38	----	2	48.26	45.72	13.38	6.09	5.00						
E	87914-3813	-----	-----	-----	-----	38	----	3	48.26	45.72	10.92	5.84	2.79						
	87914-3823	-----	-----	-----	-----	38	----	3	48.26	45.72	12.25	7.00	2.96						
	87914-3833	-----	-----	-----	-----	38	----	3	48.26	45.72	13.38	6.09	5.00						
	87914-3814	-----	-----	-----	-----	38	----	4	48.26	45.72	10.92	5.84	2.79						
	87914-3824	-----	-----	-----	-----	38	----	4	48.26	45.72	12.25	7.00	2.96						
	87914-3834	-----	-----	-----	-----	38	----	4	48.26	45.72	13.38	6.09	5.00						
D	87914-3815	-----	-----	-----	-----	38	----	5	48.26	45.72	10.92	5.84	2.79						
	87914-3825	-----	-----	-----	-----	38	----	5	48.26	45.72	12.25	7.00	2.96						
	87914-3835	-----	-----	-----	-----	38	----	5	48.26	45.72	13.38	6.09	5.00						
	87914-3816	-----	-----	-----	-----	38	----	6	48.26	45.72	10.92	5.84	2.79						
	87914-3826	-----	-----	-----	-----	38	----	6	48.26	45.72	12.25	7.00	2.96						
	87914-3836	-----	-----	-----	-----	38	----	6	48.26	45.72	13.38	6.09	5.00						
C																			
B																			
A	SEE SHEET 14 EC NO: S2015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± 0.20 ± --- 1 PLACE ± --- ± --- 0 PLACE ± ± ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DIMENSION STYLE MM ONLY DRAWN BY DATE KCHO 2004/11/05 CHECKED BY DATE PTL IM 2004/12/08 APPROVED BY DATE MLONG 2010/09/06 MATERIAL NO. SEE TABLE		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		SHEET NO. 24 OF 45		
	fb_frame_A3_P_AM_T Rev. G 2012/01/11																		

	10		9		8		7		6		5		4		3		2		1		
F	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
	A	B	F	M	P																
	87914-4011	-----	-----	-----	-----	40	-----	1	50.80	48.26	10.92	5.84	2.79								F
	87914-4021	-----	-----	-----	-----	40	-----	1	50.80	48.26	12.25	7.00	2.96								
	87914-4031	-----	-----	-----	-----	40	-----	1	50.80	48.26	13.38	6.09	5.00								
	87914-4012	-----	-----	-----	-----	40	-----	2	50.80	48.26	10.92	5.84	2.79								
	87914-4022	-----	-----	-----	-----	40	-----	2	50.80	48.26	12.25	7.00	2.96								
	87914-4032	-----	-----	-----	-----	40	-----	2	50.80	48.26	13.38	6.09	5.00								
E	87914-4013	-----	-----	-----	-----	40	-----	3	50.80	48.26	10.92	5.84	2.79								E
	87914-4023	-----	-----	-----	-----	40	-----	3	50.80	48.26	12.25	7.00	2.96								
	87914-4033	-----	-----	-----	-----	40	-----	3	50.80	48.26	13.38	6.09	5.00								
	87914-4014	-----	-----	-----	-----	40	-----	4	50.80	48.26	10.92	5.84	2.79								
	87914-4024	-----	-----	-----	-----	40	-----	4	50.80	48.26	12.25	7.00	2.96								
	87914-4034	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.38	6.09	5.00								
D	87914-4015	-----	-----	-----	-----	40	-----	5	50.80	48.26	10.92	5.84	2.79								D
	87914-4025	-----	-----	-----	-----	40	-----	5	50.80	48.26	12.25	7.00	2.96								
	87914-4035	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.38	6.09	5.00								
	87914-4016	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79								
	87914-4026	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96								
	87914-4036	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.38	6.09	5.00								
C																					C
B																					B
A	SEE SHEET 14 IEC NO: S2015-1512 DRW:NRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 DESCRIPTION REV D15								QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		A		
													MM ONLY		NTS	METRIC					
									4 PLACES		± --- ± ---		DRAWN BY DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex						
									3 PLACES		± --- ± ---		CHECKED BY DATE								
									2 PLACES		± 0.20 ± ---		PTL IM 2004/12/08								
									1 PLACE		± --- ± ---		APPROVED BY DATE								
									0 PLACE		± ±		MLONG 2010/09/06		DOCUMENT NO. SD-87914-013 SHEET NO. 25 OF 45						
									ANGULAR ± 3 °		MATERIAL NO.										
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
									SIZE												
A3																					
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9	8	7	6	5	4	3	2	1											

	10		9		8		7		6		5		4		3		2		1																																								
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																		
									A	B	F	M	P																																														
F	87914-4211	-----	-----	-----	-----	42	----	1	53.34	50.80	10.92	5.84	2.79																																														
	87914-4221	-----	-----	-----	-----	42	----	1	53.34	50.80	12.25	7.00	2.96																																														
	87914-4212	-----	-----	-----	-----	42	----	2	53.34	50.80	10.92	5.84	2.79																																														
	87914-4222	-----	-----	-----	-----	42	----	2	53.34	50.80	12.25	7.00	2.96																																														
	87914-4213	-----	-----	-----	-----	42	----	3	53.34	50.80	10.92	5.84	2.79																																														
	87914-4223	-----	-----	-----	-----	42	----	3	53.34	50.80	12.25	7.00	2.96																																														
E	87914-4214	-----	-----	-----	-----	42	----	4	53.34	50.80	10.92	5.84	2.79																																														
	87914-4224	-----	-----	-----	-----	42	----	4	53.34	50.80	12.25	7.00	2.96																																														
	87914-4215	-----	-----	-----	-----	42	----	5	53.34	50.80	10.92	5.84	2.79																																														
	87914-4225	-----	-----	-----	-----	42	----	5	53.34	50.80	12.25	7.00	2.96																																														
D	87914-4216	-----	-----	-----	-----	42	----	6	53.34	50.80	10.92	5.84	2.79																																														
	87914-4226	-----	-----	-----	-----	42	----	6	53.34	50.80	12.25	7.00	2.96																																														
C																																																											
B																																																											
A																																																											
<table><tr><td rowspan="10">SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15</td><td rowspan="10">QUALITY SYMBOLS =0 =0 =0</td><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="5">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="5">mm INCH</td><td rowspan="5">± --- ± --- ± 0.20 ± --- ±</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td rowspan="5">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td colspan="2">MATERIAL NO.</td><td>DOCUMENT NO.</td><td>SHEET NO. 26 OF 45</td></tr><tr><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td></tr><tr><td colspan="3">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="5">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																						SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	± --- ± --- ± 0.20 ± --- ±	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex	CHECKED BY PTL IM	DATE 2004/12/08	APPROVED BY MLONG	DATE 2010/09/06	MATERIAL NO.		DOCUMENT NO.	SHEET NO. 26 OF 45	SEE TABLE		SD-87914-013		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																		
		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm INCH	± --- ± --- ± 0.20 ± --- ±	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																				
					CHECKED BY PTL IM	DATE 2004/12/08																																																					
					APPROVED BY MLONG	DATE 2010/09/06																																																					
					MATERIAL NO.			DOCUMENT NO.	SHEET NO. 26 OF 45																																																		
					SEE TABLE			SD-87914-013																																																			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																					
		fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1																																							

	10		9		8		7		6		5		4		3		2		1																																																																					
	PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																															
									A	B	F	M	P																																																																											
F	87914-4411	-----	-----	-----	-----	44	----	1	55.88	53.34	10.92	5.84	2.79																																																																											
	87914-4421	-----	-----	-----	-----	44	----	1	55.88	53.34	12.25	7.00	2.96																																																																											
	87914-4412	-----	-----	-----	-----	44	----	2	55.88	53.34	10.92	5.84	2.79																																																																											
	87914-4422	-----	-----	-----	-----	44	----	2	55.88	53.34	12.25	7.00	2.96																																																																											
	87914-4413	-----	-----	-----	-----	44	----	3	55.88	53.34	10.92	5.84	2.79																																																																											
E	87914-4423	-----	-----	-----	-----	44	----	3	55.88	53.34	12.25	7.00	2.96																																																																											
	87914-4414	-----	-----	-----	-----	44	----	4	55.88	53.34	10.92	5.84	2.79																																																																											
	87914-4424	-----	-----	-----	-----	44	----	4	55.88	53.34	12.25	7.00	2.96																																																																											
	87914-4415	-----	-----	-----	-----	44	----	5	55.88	53.34	10.92	5.84	2.79																																																																											
	87914-4425	-----	-----	-----	-----	44	----	5	55.88	53.34	12.25	7.00	2.96																																																																											
D	87914-4416	-----	-----	-----	-----	44	----	6	55.88	53.34	10.92	5.84	2.79																																																																											
	87914-4426	-----	-----	-----	-----	44	----	6	55.88	53.34	12.25	7.00	2.96																																																																											
C																																																																																								
B																																																																																								
A																																																																																								
<table><tr><td rowspan="10">SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15</td><td rowspan="10">DESCRIPTION REV</td><td rowspan="10">QUALITY SYMBOLS ▽F=0 ▽E=0 ▽P=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="2">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY PTLIM</td><td>DATE 2004/12/08</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY</td><td>DATE</td><td colspan="4" rowspan="2">molex</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td>MLONG</td><td>2010/09/06</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td colspan="2">27 OF 45</td></tr><tr><td colspan="3">ANGULAR ± 3 °</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="6">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																				SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	DESCRIPTION REV	QUALITY SYMBOLS ▽F=0 ▽E=0 ▽P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				4 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08	3 PLACES	± ---	± ---	APPROVED BY	DATE	molex				2 PLACES	± 0.20	± ---	MLONG	2010/09/06	1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		0 PLACE	±	±	SEE TABLE		SD-87914-013		27 OF 45		ANGULAR ± 3 °			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
SEE SHEET 14 IEC NO: S2015-1512 DRAWN:PRAMAKRISHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 D15	DESCRIPTION REV	QUALITY SYMBOLS ▽F=0 ▽E=0 ▽P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																															
				mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H																																																																																
			4 PLACES	± ---	± ---	CHECKED BY PTLIM	DATE 2004/12/08																																																																																	
			3 PLACES	± ---	± ---	APPROVED BY	DATE	molex																																																																																
			2 PLACES	± 0.20	± ---	MLONG	2010/09/06																																																																																	
			1 PLACE	± ---	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.																																																																														
			0 PLACE	±	±	SEE TABLE		SD-87914-013		27 OF 45																																																																														
			ANGULAR ± 3 °			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																															
			fb_frame_A3_P_AM_T Rev. G 2012/01/11	9		8		7		6		5		4		3		2					1																																																																	

10		9		8		7		6		5		4		3		2		1																																																																									
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																			
								A	B	F	M	P																																																																															
F	87914-4611	-----	-----	-----	-----	46	----	1	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4621	-----	-----	-----	-----	46	----	1	58.42	55.88	12.25	7.00	2.96																																																																														
	87914-4612	-----	-----	-----	-----	46	----	2	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4622	-----	-----	-----	-----	46	----	2	58.42	55.88	12.25	7.00	2.96																																																																														
	87914-4613	-----	-----	-----	-----	46	----	3	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4623	-----	-----	-----	-----	46	----	3	58.42	55.88	12.25	7.00	2.96																																																																														
E	87914-4614	-----	-----	-----	-----	46	----	4	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4624	-----	-----	-----	-----	46	----	4	58.42	55.88	12.25	7.00	2.96																																																																														
	87914-4615	-----	-----	-----	-----	46	----	5	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4625	-----	-----	-----	-----	46	----	5	58.42	55.88	12.25	7.00	2.96																																																																														
	87914-4616	-----	-----	-----	-----	46	----	6	58.42	55.88	10.92	5.84	2.79																																																																														
	87914-4626	-----	-----	-----	-----	46	----	6	58.42	55.88	12.25	7.00	2.96																																																																														
D																																																																																											
C																																																																																											
B																																																																																											
A	<table><tr><td rowspan="10">SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV</td><td rowspan="10">QUALITY SYMBOLS </td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY</td><td>DATE</td><td colspan="3" rowspan="5">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>KCHO</td><td>2004/11/05</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY</td><td>DATE</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td>PTL IM</td><td>2004/12/08</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td>APPROVED BY</td><td>DATE</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td>MLONG</td><td>2010/09/06</td><td colspan="2">MATERIAL NO.</td><td>DOCUMENT NO.</td><td>SHEET NO.</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td colspan="2">28 OF 45</td></tr><tr><td colspan="18">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																		SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			4 PLACES	± ---	± ---	KCHO	2004/11/05	3 PLACES	± ---	± ---	CHECKED BY	DATE	2 PLACES	± 0.20	± ---	PTL IM	2004/12/08	1 PLACE	± ---	± ---	APPROVED BY	DATE	0 PLACE	±	±	MLONG	2010/09/06	MATERIAL NO.		DOCUMENT NO.	SHEET NO.	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		28 OF 45		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	SEE SHEET 14 EC NO: SZ015-1512 DRAWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																																		
				mm	INCH	DRAWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																																																			
			4 PLACES	± ---	± ---	KCHO	2004/11/05																																																																																				
			3 PLACES	± ---	± ---	CHECKED BY	DATE																																																																																				
			2 PLACES	± 0.20	± ---	PTL IM	2004/12/08																																																																																				
			1 PLACE	± ---	± ---	APPROVED BY	DATE																																																																																				
			0 PLACE	±	±	MLONG	2010/09/06	MATERIAL NO.		DOCUMENT NO.	SHEET NO.																																																																																
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013		28 OF 45																																																																																		
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																								

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1						
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																
								A	B	F	M	P												
F	87914-4811	-----	-----	-----	-----	48	----	1	60.96	58.42	10.92	5.84	2.79											
	87914-4821	-----	-----	-----	-----	48	----	1	60.96	58.42	12.25	7.00	2.96											
	87914-4812	-----	-----	-----	-----	48	----	2	60.96	58.42	10.92	5.84	2.79											
	87914-4822	-----	-----	-----	-----	48	----	2	60.96	58.42	12.25	7.00	2.96											
	87914-4813	-----	-----	-----	-----	48	----	3	60.96	58.42	10.92	5.84	2.79											
	87914-4823	-----	-----	-----	-----	48	----	3	60.96	58.42	12.25	7.00	2.96											
E	87914-4814	-----	-----	-----	-----	48	----	4	60.96	58.42	10.92	5.84	2.79											
	87914-4824	-----	-----	-----	-----	48	----	4	60.96	58.42	12.25	7.00	2.96											
	87914-4815	-----	-----	-----	-----	48	----	5	60.96	58.42	10.92	5.84	2.79											
	87914-4825	-----	-----	-----	-----	48	----	5	60.96	58.42	12.25	7.00	2.96											
	87914-4816	-----	-----	-----	-----	48	----	6	60.96	58.42	10.92	5.84	2.79											
	87914-4826	-----	-----	-----	-----	48	----	6	60.96	58.42	12.25	7.00	2.96											
D																								
C																								
B																								
A	SEE SHEET 14		EC NO: S2015-1512		DRWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		REV		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
																	MM ONLY		NTS		METRIC			
																	DRAWN BY		DATE		TITLE			
																	KCHO		2004/11/05		2.54MM PITCH			
																	CHECKED BY		DATE		DUAL ROW HEADER			
																	PTL IM		2004/12/08		SINGLE WAFER, T/H			
																	APPROVED BY		DATE					
																	MLONG		2010/09/06					
																	MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
																	SEE TABLE		SD-87914-013		29 OF 45			
																SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
A3																								
D15																								

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1	
PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION											
								A	B	F	M	P							
F	87914-5011	-----	-----	-----	-----	50	----	1	63.50	60.96	10.92	5.84	2.79						
	87914-5021	-----	-----	-----	-----	50	----	1	63.50	60.96	12.25	7.00	2.96						
	87914-5012	-----	-----	-----	-----	50	----	2	63.50	60.96	10.92	5.84	2.79						
	87914-5022	-----	-----	-----	-----	50	----	2	63.50	60.96	12.25	7.00	2.96						
	87914-5013	-----	-----	-----	-----	50	----	3	63.50	60.96	10.92	5.84	2.79						
E	87914-5023	-----	-----	-----	-----	50	----	3	63.50	60.96	12.25	7.00	2.96						
	87914-5014	-----	-----	-----	-----	50	----	4	63.50	60.96	10.92	5.84	2.79						
	87914-5024	-----	-----	-----	-----	50	----	4	63.50	60.96	12.25	7.00	2.96						
	87914-5015	-----	-----	-----	-----	50	----	5	63.50	60.96	10.92	5.84	2.79						
	87914-5025	-----	-----	-----	-----	50	----	5	63.50	60.96	12.25	7.00	2.96						
D	87914-5016	-----	-----	-----	-----	50	----	6	63.50	60.96	10.92	5.84	2.79						
	87914-5026	-----	-----	-----	-----	50	----	6	63.50	60.96	12.25	7.00	2.96						
	87914-0002	-----	-----	-----	-----	50	----	8	63.50	60.96	18.54	11.58	4.47						
C																			
B																			
A																			

SEE SHEET 14 EC NO: S2015-1512 DRWN:MRAMAKRI SHINA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV	QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	TITLE			
		4 PLACES	± ---	± ---	KCHO	2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
		3 PLACES	± ---	± ---	CHECKED BY	DATE				
		2 PLACES	± 0.20	± ---	PTL IM	2004/12/08	molex			
		1 PLACE	± ---	± ---	APPROVED BY	DATE				
		0 PLACE	±	±	MLONG	2010/09/06	SD-87914-013			
		ANGULAR ± 3 °			MATERIAL NO.	DOCUMENT NO.				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		30 OF 45			
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T Rev. G 2012/01/11	9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---	---

10		9		8		7		6		5		4		3		2		1							
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																	
								A	B	F	M	P													
F	87914-5211	-----	-----	-----	-----	52	-----	1	66.04	63.50	10.92	5.84	2.79												
	87914-5221	-----	-----	-----	-----	52	-----	1	66.04	63.50	12.25	7.00	2.96												
	87914-5212	-----	-----	-----	-----	52	-----	2	66.04	63.50	10.92	5.84	2.79												
	87914-5222	-----	-----	-----	-----	52	-----	2	66.04	63.50	12.25	7.00	2.96												
	87914-5213	-----	-----	-----	-----	52	-----	3	66.04	63.50	10.92	5.84	2.79												
	87914-5223	-----	-----	-----	-----	52	-----	3	66.04	63.50	12.25	7.00	2.96												
E	87914-5214	-----	-----	-----	-----	52	-----	4	66.04	63.50	10.92	5.84	2.79												
	87914-5224	-----	-----	-----	-----	52	-----	4	66.04	63.50	12.25	7.00	2.96												
	87914-5215	-----	-----	-----	-----	52	-----	5	66.04	63.50	10.92	5.84	2.79												
	87914-5225	-----	-----	-----	-----	52	-----	5	66.04	63.50	12.25	7.00	2.96												
	87914-5216	-----	-----	-----	-----	52	-----	6	66.04	63.50	10.92	5.84	2.79												
	87914-5226	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96												
D																									
C																									
B																									
A																									
SEE SHEET 14		EC NO: S2015-1512		DRAWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
D15																		MM ONLY		NTS		METRIC		◎ THIRD ANGLE PROJECTION	
																		DRAWN BY DATE		TITLE					
																		KCHO 2004/11/05		2.54MM PITCH					
																		CHECKED BY DATE		DUAL ROW HEADER					
																		PTL IM 2004/12/08		SINGLE WAFER, T/H					
																		APPROVED BY DATE							
																		MLONG 2010/09/06							
																		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
																		SEE TABLE		SD-87914-013				31 OF 45	
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX					
																		A3		INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9	8	7	6	5	4	3	2	1
---	---	---	---	---	---	---	---	---

	10		9	8		7		6	5		4		3	2	1		
F	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION								
									A	B	F	M	P				
	87914-5411	-----	-----	-----	-----	54	----	1	68.58	66.04	10.92	5.84	2.79				
	87914-5421	-----	-----	-----	-----	54	----	1	68.58	66.04	12.25	7.00	2.96				
	87914-5412	-----	-----	-----	-----	54	----	2	68.58	66.04	10.92	5.84	2.79				
	87914-5422	-----	-----	-----	-----	54	----	2	68.58	66.04	12.25	7.00	2.96				
	87914-5413	-----	-----	-----	-----	54	----	3	68.58	66.04	10.92	5.84	2.79				
	87914-5423	-----	-----	-----	-----	54	----	3	68.58	66.04	12.25	7.00	2.96				
E	87914-5414	-----	-----	-----	-----	54	----	4	68.58	66.04	10.92	5.84	2.79				
	87914-5424	-----	-----	-----	-----	54	----	4	68.58	66.04	12.25	7.00	2.96				
	87914-5415	-----	-----	-----	-----	54	----	5	68.58	66.04	10.92	5.84	2.79				
	87914-5425	-----	-----	-----	-----	54	----	5	68.58	66.04	12.25	7.00	2.96				
	87914-5416	-----	-----	-----	-----	54	----	6	68.58	66.04	10.92	5.84	2.79				
	87914-5426	-----	-----	-----	-----	54	----	6	68.58	66.04	12.25	7.00	2.96				
D																	
C																	
B																	

10		9		8		7		6		5		4		3		2		1																																																																			
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					A	B	F	M	P																																																																				
F	87914-5611	-----	-----	-----	-----	56	----	1	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5621	-----	-----	-----	-----	56	----	1	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5612	-----	-----	-----	-----	56	----	2	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5622	-----	-----	-----	-----	56	----	2	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5613	-----	-----	-----	-----	56	----	3	71.12	68.58	10.92	5.84	2.79																																																																								
E	87914-5623	-----	-----	-----	-----	56	----	3	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5614	-----	-----	-----	-----	56	----	4	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5624	-----	-----	-----	-----	56	----	4	71.12	68.58	12.25	7.00	2.96																																																																								
	87914-5615	-----	-----	-----	-----	56	----	5	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5625	-----	-----	-----	-----	56	----	5	71.12	68.58	12.25	7.00	2.96																																																																								
D	87914-5616	-----	-----	-----	-----	56	----	6	71.12	68.58	10.92	5.84	2.79																																																																								
	87914-5626	-----	-----	-----	-----	56	----	6	71.12	68.58	12.25	7.00	2.96																																																																								
C																																																																																					
B																																																																																					
A																																																																																					
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKR / SHINA 2015/06/25 CHK'D:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15</td><td rowspan="5">QUALITY SYMBOLS =0 =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td rowspan="5"> THIRD ANGLE PROJECTION</td><td colspan="3" rowspan="5">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td><td colspan="2" rowspan="5">SD-87914-013</td><td colspan="2" rowspan="5">SHEET NO. 33 OF 45</td></tr><tr><td colspan="2">mm INCH</td><td>DRAWN BY DATE</td><td>TITLE</td></tr><tr><td colspan="2">4 PLACES ± --- ± ---</td><td>KCHO 2004/11/05</td><td></td></tr><tr><td colspan="2">3 PLACES ± --- ± ---</td><td>CHECKED BY DATE</td><td></td></tr><tr><td colspan="2">2 PLACES ± 0.20 ± ---</td><td>PTL IM 2004/12/08</td><td></td></tr><tr><td colspan="2">1 PLACE ± --- ± ---</td><td>APPROVED BY DATE</td><td></td></tr><tr><td colspan="2">0 PLACE ± ±</td><td>MLONG 2010/09/06</td><td></td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td>MATERIAL NO.</td><td>DOCUMENT NO.</td><td colspan="8"></td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr></table>																					SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKR / SHINA 2015/06/25 CHK'D:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			SD-87914-013		SHEET NO. 33 OF 45		mm INCH		DRAWN BY DATE	TITLE	4 PLACES ± --- ± ---		KCHO 2004/11/05		3 PLACES ± --- ± ---		CHECKED BY DATE		2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08		1 PLACE ± --- ± ---		APPROVED BY DATE		0 PLACE ± ±		MLONG 2010/09/06		ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAWAKR / SHINA 2015/06/25 CHK'D:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV D15	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex			SD-87914-013		SHEET NO. 33 OF 45																																																																							
		mm INCH		DRAWN BY DATE	TITLE																																																																																
		4 PLACES ± --- ± ---		KCHO 2004/11/05																																																																																	
		3 PLACES ± --- ± ---		CHECKED BY DATE																																																																																	
		2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08																																																																																	
1 PLACE ± --- ± ---		APPROVED BY DATE																																																																																			
0 PLACE ± ±		MLONG 2010/09/06																																																																																			
ANGULAR ± 3 °		MATERIAL NO.	DOCUMENT NO.																																																																																		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																		

[illegible]

10		9		8		7		6		5		4		3		2		1					
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION															
								A	B	F	M	P											
F	87914-6211	-----	-----	-----	-----	62	-----	1	78.74	76.20	10.92	5.84	2.79										
	87914-6221	-----	-----	-----	-----	62	-----	1	78.74	76.20	12.25	7.00	2.96										
	87914-6212	-----	-----	-----	-----	62	-----	2	78.74	76.20	10.92	5.84	2.79										
	87914-6222	-----	-----	-----	-----	62	-----	2	78.74	76.20	12.25	7.00	2.96										
	87914-6213	-----	-----	-----	-----	62	-----	3	78.74	76.20	10.92	5.84	2.79										
	87914-6223	-----	-----	-----	-----	62	-----	3	78.74	76.20	12.25	7.00	2.96										
E	87914-6214	-----	-----	-----	-----	62	-----	4	78.74	76.20	10.92	5.84	2.79										
	87914-6224	-----	-----	-----	-----	62	-----	4	78.74	76.20	12.25	7.00	2.96										
	87914-6215	-----	-----	-----	-----	62	-----	5	78.74	76.20	10.92	5.84	2.79										
	87914-6225	-----	-----	-----	-----	62	-----	5	78.74	76.20	12.25	7.00	2.96										
	87914-6216	-----	-----	-----	-----	62	-----	6	78.74	76.20	10.92	5.84	2.79										
	87914-6226	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96										
D																							
C																							
B																							
A	SEE SHEET 14		EC NO: S2015-1512		DRWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		
	D15										F=0		mm INCH		MM ONLY		NTS		METRIC		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
												F=0		4 PLACES ± --- ± ---		DRAWN BY DATE							
												F=0		3 PLACES ± --- ± ---		KCHO 2004/11/05							
												F=0		2 PLACES ± 0.20 ± ---		CHECKED BY DATE							
														1 PLACE ± --- ± ---		PTL IM 2004/12/08							
														0 PLACE ± ±		APPROVED BY DATE							
														ANGULAR ± 3 °		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
														DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-87914-013				36 OF 45	
														SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1					

10		9		8		7		6		5		4		3		2		1																																																																							
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																																	
								A	B	F	M	P																																																																													
F	87914-6411	-----	-----	-----	-----	64	----	1	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6421	-----	-----	-----	-----	64	----	1	81.28	78.74	12.25	7.00	2.96																																																																												
	87914-6412	-----	-----	-----	-----	64	----	2	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6422	-----	-----	-----	-----	64	----	2	81.28	78.74	12.25	7.00	2.96																																																																												
	87914-6413	-----	-----	-----	-----	64	----	3	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6423	-----	-----	-----	-----	64	----	3	81.28	78.74	12.25	7.00	2.96																																																																												
E	87914-6414	-----	-----	-----	-----	64	----	4	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6424	-----	-----	-----	-----	64	----	4	81.28	78.74	12.25	7.00	2.96																																																																												
	87914-6415	-----	-----	-----	-----	64	----	5	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6425	-----	-----	-----	-----	64	----	5	81.28	78.74	12.25	7.00	2.96																																																																												
	87914-6416	-----	-----	-----	-----	64	----	6	81.28	78.74	10.92	5.84	2.79																																																																												
	87914-6426	-----	-----	-----	-----	64	----	6	81.28	78.74	12.25	7.00	2.96																																																																												
D																																																																																									
C																																																																																									
B																																																																																									
A	<table><tr><td rowspan="3">SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHK'D: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15</td><td rowspan="3">REV</td><td rowspan="3">DESCRIPTION</td><td rowspan="3">QUALITY SYMBOLS ▽=0 ▽=0 ▽=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td colspan="2">4 PLACES ± --- ± ---</td><td colspan="2">DRAWN BY DATE</td><td colspan="4" rowspan="3">TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td><td colspan="2" rowspan="3">DOCUMENT NO. SD-87914-013</td><td colspan="2" rowspan="3">SHEET NO. 37 OF 45</td></tr><tr><td colspan="2">3 PLACES ± --- ± ---</td><td colspan="2">CHECKED BY DATE</td></tr><tr><td colspan="2">2 PLACES ± 0.20 ± ---</td><td colspan="2">PTL IM 2004/12/08</td></tr><tr><td colspan="2">1 PLACE ± --- ± ---</td><td colspan="2">APPROVED BY DATE</td><td colspan="7" rowspan="3">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td></tr><tr><td colspan="2">0 PLACE ± ±</td><td colspan="2">MLONG 2010/09/06</td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td colspan="2">MATERIAL NO.</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">SIZE A3</td></tr></table>																		SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHK'D: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																4 PLACES ± --- ± ---		DRAWN BY DATE		TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				DOCUMENT NO. SD-87914-013		SHEET NO. 37 OF 45		3 PLACES ± --- ± ---		CHECKED BY DATE		2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08		1 PLACE ± --- ± ---		APPROVED BY DATE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							0 PLACE ± ±		MLONG 2010/09/06		ANGULAR ± 3 °		MATERIAL NO.		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3	
	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHK'D: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15	REV	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																														
4 PLACES ± --- ± ---		DRAWN BY DATE		TITLE 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				DOCUMENT NO. SD-87914-013		SHEET NO. 37 OF 45																																																																															
3 PLACES ± --- ± ---		CHECKED BY DATE																																																																																							
2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08																																																																																							
1 PLACE ± --- ± ---		APPROVED BY DATE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																																					
0 PLACE ± ±		MLONG 2010/09/06																																																																																							
ANGULAR ± 3 °		MATERIAL NO.																																																																																							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SIZE A3																																																																																					

fb_frame_A3_P_AM_T
Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1				
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION														
								A	B	F	M	P										
F	87914-6611	-----	-----	-----	-----	66	----	1	83.82	81.28	10.92	5.84	2.79									
	87914-6621	-----	-----	-----	-----	66	----	1	83.82	81.28	12.25	7.00	2.96									
	87914-6612	-----	-----	-----	-----	66	----	2	83.82	81.28	10.92	5.84	2.79									
	87914-6622	-----	-----	-----	-----	66	----	2	83.82	81.28	12.25	7.00	2.96									
	87914-6613	-----	-----	-----	-----	66	----	3	83.82	81.28	10.92	5.84	2.79									
	87914-6623	-----	-----	-----	-----	66	----	3	83.82	81.28	12.25	7.00	2.96									
E	87914-6614	-----	-----	-----	-----	66	----	4	83.82	81.28	10.92	5.84	2.79									
	87914-6624	-----	-----	-----	-----	66	----	4	83.82	81.28	12.25	7.00	2.96									
	87914-6615	-----	-----	-----	-----	66	----	5	83.82	81.28	10.92	5.84	2.79									
	87914-6625	-----	-----	-----	-----	66	----	5	83.82	81.28	12.25	7.00	2.96									
	87914-6616	-----	-----	-----	-----	66	----	6	83.82	81.28	10.92	5.84	2.79									
	87914-6626	-----	-----	-----	-----	66	----	6	83.82	81.28	12.25	7.00	2.96									
D																						
C																						
B																						
A	SEE SHEET 14		EC NO: SZ015-1512		DRAWN:MRAMAKRI SHINA 2015/06/25		CHKD:ATSEE 2015/06/25		APPR:KPRASAD 2015/07/15		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
															MM ONLY		NTS		METRIC			
															DRAWN BY		DATE		TITLE			
															KCHO		2004/11/05		2.54MM PITCH			
															CHECKED BY		DATE		DUAL ROW HEADER			
															PTL IM		2004/12/08		SINGLE WAFER, T/H			
															APPROVED BY		DATE					
															MLONG		2010/09/06					
															MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
															SEE TABLE		SD-87914-013				38 OF 45	
														SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
A3																						
D15																						
								</														

10		9		8		7		6		5		4		3		2		1																																		
PART NO. FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																												
								A	B	F	M	P																																								
F	87914-6811	-----	-----	-----	-----	68	----	1	86.36	83.82	10.92	5.84	2.79																																							
	87914-6821	-----	-----	-----	-----	68	----	1	86.36	83.82	12.25	7.00	2.96																																							
	87914-6812	-----	-----	-----	-----	68	----	2	86.36	83.82	10.92	5.84	2.79																																							
	87914-6822	-----	-----	-----	-----	68	----	2	86.36	83.82	12.25	7.00	2.96																																							
	87914-6813	-----	-----	-----	-----	68	----	3	86.36	83.82	10.92	5.84	2.79																																							
	87914-6823	-----	-----	-----	-----	68	----	3	86.36	83.82	12.25	7.00	2.96																																							
E	87914-6814	-----	-----	-----	-----	68	----	4	86.36	83.82	10.92	5.84	2.79																																							
	87914-6824	-----	-----	-----	-----	68	----	4	86.36	83.82	12.25	7.00	2.96																																							
	87914-6815	-----	-----	-----	-----	68	----	5	86.36	83.82	10.92	5.84	2.79																																							
	87914-6825	-----	-----	-----	-----	68	----	5	86.36	83.82	12.25	7.00	2.96																																							
	87914-6816	-----	-----	-----	-----	68	----	6	86.36	83.82	10.92	5.84	2.79																																							
	87914-6826	-----	-----	-----	-----	68	----	6	86.36	83.82	12.25	7.00	2.96																																							
D																																																				
C																																																				
B																																																				
A	<table><tr><td rowspan="2">SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV</td><td rowspan="2">QUALITY SYMBOLS =0 =0 =0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td>4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td>mm ± --- ± --- ± 0.20 ± --- ±</td><td>INCH ± --- ± --- ± --- ± --- ±</td><td>DRAWN BY KCHO CHECKED BY PTL IM APPROVED BY MLONG</td><td>DATE 2004/11/05 DATE 2004/12/08 DATE 2010/09/06</td><td colspan="2">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td>SIZE A3</td><td colspan="10">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="2">DOCUMENT NO. SD-87914-013</td><td colspan="2">SHEET NO. 39 OF 45</td></tr></table>																		SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	mm ± --- ± --- ± 0.20 ± --- ±	INCH ± --- ± --- ± --- ± --- ±	DRAWN BY KCHO CHECKED BY PTL IM APPROVED BY MLONG	DATE 2004/11/05 DATE 2004/12/08 DATE 2010/09/06	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										DOCUMENT NO. SD-87914-013		SHEET NO. 39 OF 45	
	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																											
4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE			mm ± --- ± --- ± 0.20 ± --- ±	INCH ± --- ± --- ± --- ± --- ±	DRAWN BY KCHO CHECKED BY PTL IM APPROVED BY MLONG	DATE 2004/11/05 DATE 2004/12/08 DATE 2010/09/06	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																													
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										DOCUMENT NO. SD-87914-013		SHEET NO. 39 OF 45																																					

10		9		8		7		6		5		4		3		2		1		
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION												
								A	B	F	M	P								
F	87914-7011	-----	-----	-----	-----	70	-----	1	88.90	86.36	10.92	5.84	2.79							
	87914-7021	-----	-----	-----	-----	70	-----	1	88.90	86.36	12.25	7.00	2.96							
	87914-7012	-----	-----	-----	-----	70	-----	2	88.90	86.36	10.92	5.84	2.79							
	87914-7022	-----	-----	-----	-----	70	-----	2	88.90	86.36	12.25	7.00	2.96							
	87914-7013	-----	-----	-----	-----	70	-----	3	88.90	86.36	10.92	5.84	2.79							
	87914-7023	-----	-----	-----	-----	70	-----	3	88.90	86.36	12.25	7.00	2.96							
E	87914-7014	-----	-----	-----	-----	70	-----	4	88.90	86.36	10.92	5.84	2.79							
	87914-7024	-----	-----	-----	-----	70	-----	4	88.90	86.36	12.25	7.00	2.96							
	87914-7015	-----	-----	-----	-----	70	-----	5	88.90	86.36	10.92	5.84	2.79							
	87914-7025	-----	-----	-----	-----	70	-----	5	88.90	86.36	12.25	7.00	2.96							
	87914-7016	-----	-----	-----	-----	70	-----	6	88.90	86.36	10.92	5.84	2.79							
	87914-7026	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96							
D																				
C																				
B																				
A	SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI / SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV DESCRIPTION							QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
									mm		INCH		DRAWN BY DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex					
									4 PLACES ± --- ± ---		KCHO 2004/11/05									
									3 PLACES ± --- ± ---		CHECKED BY DATE									
									2 PLACES ± 0.20 ± ---		PTL IM 2004/12/08									
									1 PLACE ± --- ± ---		APPROVED BY DATE									
									0 PLACE ± ±		MLONG 2010/09/06		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
									DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE		SD-87914-013					
									SIZE A3				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
									D15											
fb_frame_A3_P_AM_T Rev. G 2012/01/11		9		8		7		6		5		4		3		2		1		

[illegible]

10		9		8		7		6		5		4		3		2		1																																																								
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																																																																		
								A	B	F	M	P																																																														
F	87914-7411	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79																																																													
	87914-7421	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96																																																													
	87914-7412	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79																																																													
	87914-7422	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96																																																													
	87914-7413	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79																																																													
E	87914-7423	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96																																																													
	87914-7414	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79																																																													
	87914-7424	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96																																																													
	87914-7415	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79																																																													
	87914-7425	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96																																																													
D	87914-7416	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79																																																													
	87914-7426	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96																																																													
C																																																																										
B																																																																										
A																																																																										
<table><tr><td rowspan="5">SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV</td><td rowspan="5">QUALITY SYMBOLS =0 =0 =0 </td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td></td><td>mm</td><td>INCH</td><td>DRAWN BY KCHO</td><td>DATE 2004/11/05</td><td colspan="4" rowspan="3">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex</td></tr><tr><td>4 PLACES</td><td>± ---</td><td>± ---</td><td>CHECKED BY PTL IM</td><td>DATE 2004/12/08</td></tr><tr><td>3 PLACES</td><td>± ---</td><td>± ---</td><td>APPROVED BY MLONG</td><td>DATE 2010/09/06</td></tr><tr><td>2 PLACES</td><td>± 0.20</td><td>± ---</td><td colspan="2">MATERIAL NO.</td><td colspan="2">DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td>1 PLACE</td><td>± ---</td><td>± ---</td><td colspan="2">SEE TABLE</td><td colspan="2">SD-87914-013</td><td colspan="2">42 OF 45</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="2"></td></tr></table>																			SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex				4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08	3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06	2 PLACES	± 0.20	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.		1 PLACE	± ---	± ---	SEE TABLE		SD-87914-013		42 OF 45		0 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			
SEE SHEET 14 EC NO: SZ015-1512 DRAWN: MRAKRI SHINA 2015/06/25 CHKD: ATSEE 2015/06/25 APPR: KPRASAD 2015/07/15 REV	QUALITY SYMBOLS =0 =0 =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION																																																																		
			mm	INCH	DRAWN BY KCHO	DATE 2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H molex																																																																			
		4 PLACES	± ---	± ---	CHECKED BY PTL IM	DATE 2004/12/08																																																																				
		3 PLACES	± ---	± ---	APPROVED BY MLONG	DATE 2010/09/06																																																																				
		2 PLACES	± 0.20	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.																																																																	
1 PLACE	± ---	± ---	SEE TABLE		SD-87914-013		42 OF 45																																																																			
0 PLACE	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																																																					

[illegible]

10		9		8		7		6		5		4		3		2		1							
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION																	
								A	B	F	M	P													
F	87914-7811	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79												
	87914-7821	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96												
	87914-7812	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79												
	87914-7822	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96												
	87914-7813	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79												
	87914-7823	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96												
E	87914-7814	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79												
	87914-7824	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96												
	87914-7815	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79												
	87914-7825	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96												
	87914-7816	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79												
	87914-7826	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96												
D																									
C																									
B																									
A																									
SEE SHEET 14		EC NO: S2015-1512		DRAWN: MRAKRI / SHINA 2015/06/25		CHKD: ATSEE 2015/06/25		APPR: KPRASAD 2015/07/15		REV		DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
D15														F=0		mm		MM ONLY		NTS		METRIC		⊙	
														F=0		INCH		DRAWN BY		DATE		TITLE		2.54MM PITCH	
														F=0				KCHO		2004/11/05				DUAL ROW HEADER	
																		CHECKED BY		DATE				SINGLE WAFER, T/H	
																		PTL IM		2004/12/08					
																		APPROVED BY		DATE					
																		MLONG		2010/09/06					
																		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
																		SEE TABLE		SD-87914-013				44 OF 45	
																		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
A3																									

fb_frame_A3_P_AM_T

Rev. G 2012/01/11

9

8

7

6

5

4

3

2

1

10		9		8		7		6		5		4		3		2		1																																																																	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSIONS																																																																											
								A	B	F	M	P																																																																							
F	87914-8011	-----	-----	-----	-----	80	-----	1	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8021	-----	-----	-----	-----	80	-----	1	101.60	99.06	12.25	7.00	2.96																																																																						
	87914-8012	-----	-----	-----	-----	80	-----	2	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8022	-----	-----	-----	-----	80	-----	2	101.60	99.06	12.25	7.00	2.96																																																																						
	87914-8013	-----	-----	-----	-----	80	-----	3	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8023	-----	-----	-----	-----	80	-----	3	101.60	99.06	12.25	7.00	2.96																																																																						
E	87914-8014	-----	-----	-----	-----	80	-----	4	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8024	-----	-----	-----	-----	80	-----	4	101.60	99.06	12.25	7.00	2.96																																																																						
	87914-8015	-----	-----	-----	-----	80	-----	5	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8025	-----	-----	-----	-----	80	-----	5	101.60	99.06	12.25	7.00	2.96																																																																						
	87914-8016	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79																																																																						
	87914-8026	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96																																																																						
D																																																																																			
C																																																																																			
B																																																																																			
A	SEE SHEET 14 EC NO: SZ015-1512 DRWN:MRAMAKRI SHNA 2015/06/25 CHKD:ATSEE 2015/06/25 APPR:KPRASAD 2015/07/15 REV DESCRIPTION QUALITY SYMBOLS =0 =0 =0 GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>3 PLACES</td><td>±---</td><td>±---</td></tr><tr><td>2 PLACES</td><td>±0.20</td><td>±---</td></tr><tr><td>1 PLACE</td><td>±---</td><td>±---</td></tr><tr><td>0 PLACE</td><td>±</td><td>±</td></tr></table> ANGULAR ± 3 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS <table><tr><td>DIMENSION STYLE</td><td>SCALE</td><td>DESIGN UNITS</td><td>THIRD ANGLE PROJECTION</td></tr><tr><td>MM ONLY</td><td>NTS</td><td>METRIC</td><td></td></tr><tr><td>DRAWN BY</td><td>DATE</td><td colspan="2">TITLE</td></tr><tr><td>KCHO</td><td>2004/11/05</td><td colspan="2">2.54MM PITCH</td></tr><tr><td>CHECKED BY</td><td>DATE</td><td colspan="2">DUAL ROW HEADER</td></tr><tr><td>PTL IM</td><td>2004/12/08</td><td colspan="2">SINGLE WAFER, T/H</td></tr><tr><td>APPROVED BY</td><td>DATE</td><td colspan="2">molex</td></tr><tr><td>MLONG</td><td>2010/09/06</td><td colspan="2"></td></tr><tr><td>MATERIAL NO.</td><td>DOCUMENT NO.</td><td colspan="2">SHEET NO.</td></tr><tr><td>SEE TABLE</td><td>SD-87914-013</td><td colspan="2">45 OF 45</td></tr></table>								mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±---	2 PLACES	±0.20	±---	1 PLACE	±---	±---	0 PLACE	±	±	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	MM ONLY	NTS	METRIC		DRAWN BY	DATE	TITLE		KCHO	2004/11/05	2.54MM PITCH		CHECKED BY	DATE	DUAL ROW HEADER		PTL IM	2004/12/08	SINGLE WAFER, T/H		APPROVED BY	DATE	molex		MLONG	2010/09/06			MATERIAL NO.	DOCUMENT NO.	SHEET NO.		SEE TABLE	SD-87914-013	45 OF 45		SIZE		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
									mm	INCH																																																																									
								4 PLACES	±---	±---																																																																									
								3 PLACES	±---	±---																																																																									
								2 PLACES	±0.20	±---																																																																									
								1 PLACE	±---	±---																																																																									
								0 PLACE	±	±																																																																									
								DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION																																																																								
								MM ONLY	NTS	METRIC																																																																									
								DRAWN BY	DATE	TITLE																																																																									
KCHO	2004/11/05	2.54MM PITCH																																																																																	
CHECKED BY	DATE	DUAL ROW HEADER																																																																																	
PTL IM	2004/12/08	SINGLE WAFER, T/H																																																																																	
APPROVED BY	DATE	molex																																																																																	
MLONG	2010/09/06																																																																																		
MATERIAL NO.	DOCUMENT NO.	SHEET NO.																																																																																	
SEE TABLE	SD-87914-013	45 OF 45																																																																																	
A3																																																																																			

fb_frame_A3_P_AM_T		9		8		7		6		5		4		3		2		1	
Rev. G 2012/01/11																			