

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0		M1	REVISED PER ECO-11-004820	11MAR11	RK
						HMR

D

C

B


A

D


C

B



A



RECOMMENDED PANEL CUTOUT



RECOMMENDED HOLE PATTERN
1.57[0.062] THICK PC BOARD
COMPONENT SIDE



- 1 2.54um[0.000100] MIN TIN-LEAD FOR A MIN LENGTH OF .195 ON END OPPOSITE MATING FACE, OVER 1.27um[0.000050] MIN NICKEL ON ENTIRE CONTACT.
- 2 2.54um[0.000100] MIN TIN FOR A MIN LENGTH OF .195 ON END OPPOSITE MATING FACE, OVER 1.27 MIN NICKEL ON ENTIRE CONTACT.
- 3 HOUSING: NYLON, COLOR: SEE TABLE. CONTACTS: BRASS

WHITE	3-213598-4
BLACK	3-213598-2
GRAY	3-213598-1
WHITE	213598-4
BLACK	213598-2
GRAY	213598-1
COLOR	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 23JUNE2005	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 23JUNE2005				
		APVD D. BOSSI 23JUNE2005	NAME			
		PRODUCT SPEC	RECEPTACLE ASSEMBLY, CONVENIENCE OUTLET			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC				
0 PLC ± -		—				
1 PLC ± -		—				
2 PLC ± 0.13[0.005]		—				
3 PLC ± -		—				
4 PLC ± -		—				
ANGLES ± -		—				
FINISH		WEIGHT				
CONTACTS 1		—				
MATERIAL 3		CUSTOMER DRAWING				
		SCALE 2:1				
		SHEET 1 of 1				
		REV M1				