


Standard Recovery Diodes, 250 A to 320 A (MAGN-A-PAK Power Modules)



MAGN-A-PAK

FEATURES

- High voltage
- Electrically isolated base plate
- 3000 V_{RMS} isolating voltage
- Industrial standard package
- Simplified mechanical designs, rapid assembly
- High surge capability
- Large creepage distances
- UL approved file E78996 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS
COMPLIANT

PRODUCT SUMMARY

I _{F(AV)}	250 A to 320 A
Type	Modules - Diode, High Voltage
Package	MAGN-A-PAK
Circuit	Two diodes doubler circuit

DESCRIPTION

This new VS-VSK series of MAGN-A-PAKs uses high voltage power diodes in two basic configurations. The semiconductors are electrically isolated from the metal base, allowing common heatsinks and compact assemblies to be built. They can be interconnected to form single phase or three phase bridges and the single diode module can be used in conjunction with the thyristor modules as a freewheel diode. These modules are intended for general purpose applications such as battery chargers, welders and plating equipment and where high voltage and high current are required (motor drives, etc.).

MAJOR RATINGS AND CHARACTERISTICS

SYMBOL	CHARACTERISTICS	VSK.250..	VSK.270..	VSK.320..	UNITS
I _{F(AV)}		250	270	320	A
	T _C	100	100	100	°C
I _{F(RMS)}		393	424	502	A
I _{FSM}	50 Hz	7015	8920	10 110	
	60 Hz	7345	9430	10 580	
I ² t	50 Hz	246	398	511	kA ² s
	60 Hz	225	363	466	
I ² √t		2460	3980	5110	kA ² √s
V _{RRM}		400 to 3000			V
T _J		-40 to +150			°C



ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V_{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V_{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I_{RRM} MAXIMUM AT 150 °C mA
VS-VSK.250 VS-VSK.270 VS-VSK.320	04	400	500	50
	08	800	900	
	12	1200	1300	
	16	1600	1700	
	20	2000	2100	
VS-VSK.270	30	3000	3100	

FORWARD CONDUCTION								
PARAMETER	SYMBOL	TEST CONDITIONS			VSK.250	VSK.270	VSK.320	UNITS
Maximum average forward current at case temperature	I _{F(AV)}	180° conduction, half sine wave			250	270	320	A
					100	100	100	°C
Maximum RMS forward current	I _{F(RMS)}	As AC switch			393	424	502	A
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplied	Sinusoidal half wave, initial T _J = T _J maximum	7015	8920	10 110	
		t = 8.3 ms			7345	9340	10 580	
		t = 10 ms	100 % V _{RRM} reapplied		5900	7500	8500	
		t = 8.3 ms			6180	7850	8900	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplied		246	398	511	kA ² s
		t = 8.3 ms		225	363	466		
		t = 10 ms	100 % V _{RRM} reapplied	174	281	361		
		t = 8.3 ms		159	257	330		
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplied			2460	3980	5110	kA ² √s
Low level value of threshold voltage	V _{F(TO)1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J = T _J maximum			0.79	0.74	0.69	V
High level value of threshold voltage	V _{F(TO)2}	(I > π × I _{F(AV)}), T _J = T _J maximum			0.92	0.87	0.86	
Low level forward slope resistance	r _{f1}	(16.7 % × π × I _{F(AV)} < I < π × I _{F(AV)}), T _J = T _J maximum			0.63	0.94	0.59	mΩ
High level forward slope resistance	r _{f2}	(I > π × I _{F(AV)}), T _J = T _J maximum			0.49	0.81	0.44	
Maximum forward voltage drop	V _{FM}	I _{FM} = π × I _{F(AV)} , T _J = T _J maximum, 180° conduction Average power = V _{F(TO)} × I _{F(AV)} + r _f × (I _{F(RMS)}) ²			1.29	1.48	1.28	V

BLOCKING				
PARAMETER	SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum peak reverse leakage current	I_{RRM}	$T_J = 150\text{ °C}$	50	mA
RMS insulation voltage	V_{INS}	50 Hz, circuit to base, all terminals shorted, t = 1 s	3000	V



THERMAL AND MECHANICAL SPECIFICATIONS							
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES			UNITS
				VSK.250	VSK.270	VSK.320	
Maximum junction operating and storage temperature range		T _J , T _{Stg}		-40 to +150			°C
Maximum thermal resistance, junction to case per junction		R _{thJC}	DC operation	0.16	0.125		K/W
Maximum resistance, case to heatsink per module		R _{thCS}	Mounting surface flat, smooth and greased	0.035			
Mounting torque ± 10 %	MAP to heatsink		A mounting compound is recommended and the torque should be rechecked after a period of about 3 hours to allow for the spread of the compound.	4 to 6			Nm
	busbar to MAP			8 to 10			
Approximate weight				800			g
				30			oz.
Case style				MAGN-A-PAK			

ΔR CONDUCTION PER JUNCTION											
DEVICE	SINUSOIDAL CONDUCTION AT T _J MAXIMUM					RECTANGULAR CONDUCTION AT T _J MAXIMUM					UNITS
	180°	120°	90°	60°	30°	180°	120°	90°	60°	30°	
VSK.250	0.009	0.010	0.014	0.020	0.032	0.007	0.011	0.015	0.021	0.033	K/W
VSK.270	0.008	0.012	0.014	0.020	0.032	0.007	0.011	0.015	0.020	0.033	
VSK.320	0.008	0.010	0.013	0.020	0.032	0.007	0.011	0.015	0.020	0.033	

Note

- The table above shows the increment of thermal resistance R_{thJC} when devices operate at different conduction angles than DC




Fig. 1 - Current Ratings Characteristics




Fig. 3 - Forward Power Loss Characteristics




Fig. 2 - Current Ratings Characteristics




Fig. 4 - Forward Power Loss Characteristics




Fig. 5 - Forward Power Loss Characteristics




Fig. 6 - Forward Power Loss Characteristics




Fig. 7 - Forward Power Loss Characteristics




Fig. 8 - Maximum Non-Repetitive Surge Current




Fig. 9 - Maximum Non-Repetitive Surge Current




Fig. 10 - Forward Voltage Drop Characteristics




Fig. 13 - Current Ratings Characteristics




Fig. 11 - Thermal Impedance Z_{thJC} Characteristics




Fig. 14 - Forward Power Loss Characteristics




Fig. 12 - Current Ratings Characteristics




Fig. 15 - Forward Power Loss Characteristics




Fig. 16 - Forward Power Loss Characteristics




Fig. 17 - Forward Power Loss Characteristics




Fig. 18 - Forward Power Loss Characteristics




Fig. 19 - Maximum Non-Repetitive Surge Current




Fig. 22 - Thermal Impedance Z_{thJC} Characteristics




Fig. 20 - Maximum Non-Repetitive Surge Current




Fig. 23 - Current Ratings Characteristics




Fig. 21 - Forward Voltage Drop Characteristics




Fig. 24 - Current Ratings Characteristics




Fig. 25 - Forward Power Loss Characteristics




Fig. 26 - Forward Power Loss Characteristics




Fig. 27 - Forward Power Loss Characteristics




Fig. 28 - Forward Power Loss Characteristics




Fig. 29 - Forward Power Loss Characteristics




Fig. 30 - Maximum Non-Repetitive Surge Current




Fig. 32 - Forward Voltage Drop Characteristics




Fig. 31 - Maximum Non-Repetitive Surge Current




Fig. 33 - Thermal Impedance $Z_{\theta JC}$ Characteristics



ORDERING INFORMATION TABLE


Device code	VS-VS	KD	320	-	24	PbF
	1	2	3		4	5
1	Vishay Semiconductors product					
2	Circuit configuration (see Circuit Configuration table)					
3	Current rating: $I_{F(AV)}$ rounded					
4	Voltage code x 100 = V_{RRM} (see Voltage Ratings table)					
5	Lead (Pb)-free					

CIRCUIT CONFIGURATION		
CIRCUIT DESCRIPTION	CIRCUIT CONFIGURATION CODE	CIRCUIT DRAWING
Two diodes doubler circuit	KD	VSKD...
Two diodes common cathodes	KC	VSKC...
Two diodes common anodes	KJ	VSKJ...
Single diode	KE	VSKE...

LINKS TO RELATED DOCUMENTS	
Dimensions	www.vishay.com/doc?95086

MAGN-A-PAK

DIMENSIONS in millimeters (inches)



Notes

- Dimensions are nominal
- Full engineering drawings are available on request
- UL identification number for gate and cathode wire: UL 1385
- UL identification number for package: UL 94 V-0



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Vishay:

[VSKE270-08](#) [VSKJ320-12](#) [VSKJ250-08](#) [VSKH250-08](#) [VSKL250-08](#) [VSKD250-20](#) [VSKC320-20](#) [VSKH250-04](#)
[VSKD270-08](#) [VSKD320-20](#) [VSKL250-16D25](#) [VSKE320-20](#) [VSKE320-04](#) [VSKJ320-08](#) [VSKC320-08](#) [VSKJ320-04](#)
[VSKJ270-12](#) [VSKC320-04](#) [VSKL250-14D20](#) [VSKD320-08](#) [VSKE320-08](#) [VSKE250-20](#) [VSKJ320-16](#) [VSKD320-04](#)
[VSKH250-16D25](#) [VSKH250-14D20](#) [VSKT250-14](#) [VSKD320-12](#) [VSKE320-16](#) [VSKD270-30](#) [VSKC320-12](#) [VSKD320-16](#) [VSKE320-12](#) [VSKD270-16](#) [VSKE270-12](#) [VSKL250-12](#) [VSKL250-16](#) [VSKD270-12](#) [VSKE270-16](#) [VSKE270-20](#)
[VSKD250-08](#) [VSKE250-04](#) [VSKC250-16](#) [VSKT250-12](#) [VSKT250-16](#) [VSKT250-04](#) [VSKJ320-20](#) [VSKT250-08](#)
[VSKL250-14](#) [VSKD250-16](#) [VSKE250-12](#) [VSKD250-04](#) [VSKJ250-16](#) [VSKH250-16](#) [VSKC270-12](#) [VSKH250-14](#)
[VSKH250-12](#) [VSKE250-16](#) [VSKC250-08](#) [VSKD250-12](#) [VSKC250-12](#) [VSKE250-08](#) [VS-VSKC320-20PBF](#) [VS-VSKD270-04PBF](#) [VS-VSKC250-08PBF](#) [VS-VSKC320-12PBF](#) [VS-VSKC320-16PBF](#) [VS-VSKD270-16PBF](#) [VS-VSKD250-08PBF](#) [VS-VSKD250-20PBF](#) [VS-VSKE320-08PBF](#) [VS-VSKE250-08PBF](#) [VS-VSKE270-12PBF](#) [VS-VSKE320-16PBF](#) [VS-VSKJ320-08PBF](#) [VS-VSKJ320-04PBF](#) [VS-VSKJ320-16PBF](#) [VS-VSKJ320-12PBF](#) [IRKC250-08](#)
[IRKC250-12](#) [IRKC250-16](#) [IRKC270-12](#) [IRKC320-04](#) [IRKC320-08](#) [IRKC320-12](#) [IRKC320-20](#) [IRKD250-04](#)
[IRKD250-08](#) [IRKD250-12](#) [IRKD250-16](#) [IRKD250-20](#) [IRKD270-08](#) [IRKD270-12](#) [IRKD270-16](#) [IRKD270-30](#) [IRKD320-04](#) [IRKD320-08](#) [IRKD320-12](#) [IRKD320-16](#) [IRKD320-20](#)