

Customer Information Sheet

DRAWING No.: M80-305 TO M80-307

SHEET 2 OF 2

IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:**MATERIALS:**

BODY, SLEEVE, INNER CONTACT AND
LATCHING COLLAR = COPPER ALLOY
INSULATOR = PTFE

FINISH:

BODY, SLEEVE, INNER CONTACT = GOLD
LATCHING COLLAR = NICKEL

ELECTRICAL:

FREQUENCY RANGE = 6GHz

IMPEDANCE = 50Ω V.S.W.R. = $1.05 + (0.04 \times \text{FREQUENCY}) \text{ GHz MAX}$ CONTACT RESISTANCE = $6m\Omega \text{ MAX}$ INSULATION RESISTANCE = $10^6 m\Omega @ 250V \text{ AC}$

OPERATING VOLTAGE = 180V AC @ 500mA

MAXIMUM VOLTAGE = 1,000V AC

MECHANICAL:

DURABILITY = 500 OPERATIONS

INSERTION FORCE = 8N MAX

WITHDRAWAL FORCE = 0.5N MIN


CONTACT REPLACEMENT IN INSULATOR = 5 TIMES

ENVIRONMENTAL:TEMPERATURE RANGE = -55°C TO $+125^\circ\text{C}$ **NOTES:**

- CONNECTOR COMES SUPPLIED AS A KIT OF PARTS: BODY, INSULATOR, AND LATCHING COLLAR ARE PRE-ASSEMBLED, SLEEVE AND INNER CONTACT ARE SEPARATE.
- RECOMMENDED HAND CRIMP TOOL FOR INNER CONTACT = Z80-292 WITH POSITIONER Z80-291.
RECOMMENDED HAND CRIMP TOOL AND DIE SET FOR SLEEVE = Z80-293.
- CONTACT EXTRACTION TOOL = Z80-290
- FOR ALL OTHER ELECTRICAL/MECHANICAL REQUIREMENTS, SEE COMPONENT SPECIFICATION C005XX (LATEST ISSUE).

PART No.	CABLE DIAMETER (TYPE)	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'E'
M80-305	$\varnothing 2.0\text{mm}$ (RG178)	$\varnothing 0.50 \pm 0.05$	$\varnothing 1.25$	$\varnothing 1.70$	$\varnothing 2.20$	$\varnothing 2.85$
M80-306	$\varnothing 2.4\text{mm}$ (PTFE CELLULAR)	$\varnothing 0.35 +0.05/-0$	$\varnothing 1.25$	$\varnothing 1.70$	$\varnothing 2.70$	$\varnothing 3.20$
M80-307	$\varnothing 2.7\text{mm}$ (RG174, 179, 316)	$\varnothing 0.70 \pm 0.05$	$\varnothing 1.75$	$\varnothing 2.35$	$\varnothing 2.85$	$\varnothing 3.50$

3.00⁰_{-0.10}
SQUARE



MGP	6	03.01.13	11898
NAME	ISS.	DATE	C/NOTE
APPROVED: MGP			
CHECKED: SB			
DRAWN: W. J. BOURNE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm 1\text{mm}$
X.X = $\pm 0.25\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$

ANGLES = $\pm 5^\circ$

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA: mm²

TITLE: DATAMATE MIX-TEK
COAX CONTACT
FEMALE STRAIGHT CRIMP

DRAWING NUMBER:

M80-305 TO M80-307

SHT
2 OF 2