

D

C

B

A

D

C



B

A


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- . - .
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K7	REVISED PER ECR-17-013854	22SEP2017	BDA	KR

-  2-5µm Sn über Ni in der crimpzone.
-  0.8µM Gold über Nickel in der kontaktzone
- 3 Für isolations Ø3.3-5.1 mm geeignet
-  OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



	OBSOLETE	926902-7	926899-7	BRASS		
	OBSOLETE	926902-6	926899-6	PHOS BRONZE		
	OBSOLETE	926902-5	926899-5	COPPER ALLOY	vorverzinnt	
	OBSOLETE	926902-4	926899-4	COPPER ALLOY	blank	
		926902-3	926899-3	PHOS BRONZE	vorverzinnt	
		926902-1	926899-1	BRASS	vorverzinnt	
		LOOSE PIECE	Bestell-Nr	werkstoff	Oberfläche	
					Farbe	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	11.11.03	 TE Connectivity		
		CHK	12.11.03			
		APVD	13.11.03			
		PRODUCT SPEC	-			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
	0 PLC	±	-	UNIVERSAL M-N-L STIFT DGB 1.5-2.5 mm2 -		
	1 PLC	±	-			
	2 PLC	±	0.2			
	3 PLC	±	-			
MATERIAL	4 PLC	±	-	SIZE		
	ANGLES	±	-	CAGE CODE		
		FINISH	-	DRAWING NO		
				RESTRICTED TO		
				A2 00779 C=926899		
				CUSTOMER DRAWING		
				SCALE	SHEET	REV
				5:1	1 of 1	K7